

COAXIAL CABLE

RG59/U Coaxial & 18 AWG
Siamese Construction
Non-Shielded Pair
UL CL2, CATV, CM, c(UL) CM



CONSTRUCTION	
Conductors	- Copper-clad steel per ASTM B-869 - Copper per ASTM B-3 - Twisted pair color code: black and red
Insulation/Core	- Foam Polyethylene (PE) design
Shield	- Bare copper braid
Jacket	- Premium PVC Compound

Applications:

- Suitable for RF signal transmission
- MATV
- CATV
- CCTV
- Local Area Network
- Monitor VDT display

Part #	AWG Size Nom. DCR	Nominal O.D. over Insulation	Shield Coverage Nom Shld DCR	Nom. O.D.	Nom. Cap./Ft.	Vel. of Prop.
E55918-NS	20 AWG Solid Bare Copper Coax - 18 AWG (7/26) Unshielded Pair	Foam PE 0.144" - Premium PVC 0.010"	95% Bare Copper Braid - Unshielded Pair	Black PVC - 0.238" X 0.440"	16.20	78%

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.