

Project:

Type:

Prepared By:

Date:



UPC: 19813749457



Features and Benefits

- PAR REPLACEMENT - Replaces conventional PAR lamps
- ENERGY SAVINGS - Save up to 85% on energy
- DAMP RATED - Suitable for damp locations
- ENCLOSED FIXTURE RATED - May be used in enclosed and open fixtures
- DIMMABLE - Compatible with most common dimmer models
- SHATTERPROOF - Plastic lamps for rugged applications
- 90 CRI - Produces rich and vibrant colors

Technical Specifications

Product Type	PAR
Bulb Shape	PAR20
Wattage	7W
Wattage Equivalency	50W Halogen
Typical Lumen Output	550
Efficacy	79 lm/W
Color Temperature	2700K Soft White
CRI	90
Base Type	E26
L70 Lifespan	40,000 hours
Operating Temperature	-20°C - 45°C
Dimmable	Yes, down to 10%
Beam Angle	40°
Warranty	4-Year, No-Compromise Warranty
For Use in Emergency Fixtures	No
For Use Outdoors in Open Fixtures	No


Electrical Characteristics

Input Voltage	120V
Power Factor	0.9
Flicker	<30%

Listings

UL Listed	Yes
ENERGY STAR V2.0	This product is ENERGY STAR® Version 2.0 Certified
Energy Star ID	2329946
CEC Status	Lawful for sale in California

Light Distribution



Case and Pallet Dimensions

	QTY	LENGTH	WIDTH	HEIGHT
CASE	12	10.8	8.1	4.1
PALLET	2880	43.2	37.9	48.7

Dimension

