

Project:

Type:

Prepared By:

Date:



UPC: 19813749495



### Features and Benefits

PAR REPLACEMENT - Replaces conventional PAR lamps

ENERGY SAVINGS - Save up to 85% on energy

DAMP RATED - Suitable for damp locations

ENCLOSED FIXTURE RATED - May be used in enclosed and open fixtures

DIMMABLE - Compatible with most common dimmer models

SHATTERPROOF - Plastic lamps for rugged applications

90 CRI - Produces rich and vibrant colors

### Technical Specifications

|                                   |                                |
|-----------------------------------|--------------------------------|
| Product Type                      | PAR                            |
| Bulb Shape                        | PAR30S                         |
| Wattage                           | 11W                            |
| Wattage Equivalency               | 75W Halogen                    |
| Typical Lumen Output              | 900                            |
| Efficacy                          | 82 lm/W                        |
| Color Temperature                 | 2700K Soft White               |
| CRI                               | 90                             |
| Base Type                         | E26                            |
| L70 Lifespan                      | 40,000 hours                   |
| Operating Temperature             | -20°C - 40°C                   |
| Dimmable                          | Yes, down to 10%               |
| Beam Angle                        | 25°                            |
| Warranty                          | 5-Year, No-Compromise Warranty |
| For Use in Emergency Fixtures     | No                             |
| For Use Outdoors in Open Fixtures | No                             |


### Electrical Characteristics

|               |      |
|---------------|------|
| Input Voltage | 120V |
| Power Factor  | 0.9  |
| Flicker       | <30% |

### Listings

|                  |  |
|------------------|--|
| UL Listed        | Yes  |
| ENERGY STAR V2.0 | This product is ENERGY STAR® Version 2.0 Certified |
| Energy Star ID   | 2328358  |
| CEC Status       | Lawful for sale in California                      |

Light Distribution



Case and Pallet Dimensions

|        | QTY | LENGTH | WIDTH | HEIGHT |
|--------|-----|--------|-------|--------|
| CASE   | 6   | 12.8   | 8.5   | 4.7    |
| PALLET | 864 | 46.7   | 38.4  | 37.8   |

Dimension

