



BURNDY Catalog Number
UPC Number
Description
Status

YA3CTC38
 7818100196277
 CU HYDENT- 3STR-3/8 IN.
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	2.42
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Long
Thickness	0.08
B Length (in)	1.25
Pad Width (in)	0.58
Strip Length	1-5/16

General

Number of Holes	1
Product Description	Uninsul Cu Comp Terminal Code Cond, Bvl Entry, 1 Hole/W/O/InspWindow, #2 Sol,#3 AWG Code, 50 Navy, 600 V-35 kV, 3/8" Stud, Lng bbl, White, 9 Index

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	2 AWG
DLO Size (Range)	N/A
Copper Stranded (Range)	3 AWG

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	3/8
Color Code	White
Plated (Yes or No)	Y
Index Number	9
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175