



### 31661EN3-962: Five Light Chandelier



#### Dimensions:

<b>Diameter:</b>	25"	<b>Overall Height:</b>	143 1/2"
<b>Height:</b>	21 1/4"	<b>Wire:</b>	144" (color/Clear Silver)
<b>Weight:</b>	11.16 lbs.	<b>Chain:</b>	120"
		<b>Mounting Proc.:</b>	Center Lock-Up
		<b>Connection:</b>	Mounted To Box

#### Bulbs:

5 - LED Medium A19 9.3w Max. 120v - included

#### Features:

- ENERGY STAR® Qualified
- A decorative canopy is included
- LED Bulbs are an efficient, versatile and durable light source that deliver exceptional performance.
- Meets Title 24 energy efficiency standards
- Title 24 compliant when used with included Joint Appendix (JA8) approved lamp.
- Supplied with wire pre-laced through chain

**Collection:** Winnetka

Five Light LED Chandelier in Brushed Nickel Finish with Satin Etched Glass Shades

**UPC #:**785652047947

**Finish:** Brushed Nickel (962)

#### Material List:

- 1 Body - Steel - Undefined
- 1 Chain - Steel - Undefined

#### Safety Listing:

Safety Listed for Dry Locations  
Safety Listed for Dry Locations

#### Instruction Sheets:

English (HC-1424)

#### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Satin Etched	5				5 3/4	4	1 5/8			

#### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	1 9/16			6		

#### Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97502S	Frosted		A19	Medium	9.3	9.3	120v	15000	800 230°	3000	90

#### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	31661EN3-962	1	785652047947	25	11.5	17	2.828	16.1	175	Yes
NJ Pallet		24		48	40	73	81.111	386.4		No
NV Pallet		24		48	40	73	81.111	386.4		No