



S21402

PLT/16W/H/LED/840/4P/DR
16W LED PL 4-Pin; 4000K; 1850 Lumens; G24q base; 50000
Average rated hours; Horizontal; Type A; Ballast dependent



Features

- 42 Watt direct replacement
- Direct Replacement - for use with Electronic, Instant Start, Rapid Start, and Programmed Start ballasts with no rewiring required
- Instant on to full brightness / no flickering
- Horizontal operation
- Up to 60% energy saving
- Long life - 50,000 hours
- 5 year warranty

S21402

View:

[Ballast Compatibility Chart](#)

Item Number	UPC	Voltage	Watts	Fluorescent Equivalent	Lamp Shape	Base	Lamp Code	
S21402	045923224027	120-277	16	42W	PL	G24q	PLT/16W/H/LED/840/4P/DR	
Dimmable/Non-Dimmable		Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color
Non-Dimmable		Frost	6-7/16"	1-11/16"	1850	50000	4000	Cool White
CRI	Burning Position	Operating Temperature		Pack	Package Type	CEC Status	DLC ID:	RoHS Compliant
82	Horizontal Operation	-20C (-4F) to a maximum of +45C (+113F)		20	Box	Lawful for sale in California	PL3HRCPOQ1U7 DLC Search	Yes
UL Classification							Warranty	
cULus Classified - Damp Location Rated							5 Year Limited	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051