



75952-710: Two Light Ceiling Flush Mount



Collection: Stirling

Two Light Ceiling Flush Mount in Burnt Sienna Finish with Beige Linen Shade and Satin Etched Glass Bottom Diffuser.

UPC #:785652182464

Finish: Burnt Sienna (710)

Dimensions:

Diameter: 14" **Wire:** 6 1/2"
Height: 7 1/4" **Mounting Proc.:** Universal Mounting Bar
Weight: 5.8 lbs. **Connection:** Mounted To Box

Bulbs:

2 - Medium A19 60w Max. 120v - Not included
2 - LED Medium A19 8w Max. 120v - Not included
2 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Steel - Burnt Sienna

Safety Listing:

Safety Listed for Damp Locations
Safety Listed for Damp Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (HC-1726FS)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Fabric	Beige Linen	1	650236-1005			5 7/8	14	4 15/16			
Diffuser	Glass	Satin Etched	1				1/8	13 5/16	1/2			

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	1 3/8			5 1/2		

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	75952-710	1	785652182464	16.25	16.25	9.25	1.414	7.2	150	Yes
NJ Pallet		48		48	40	70	77.778	345.2		No
NV Pallet		48		48	40	70	77.778	345		No