



75435-962: Two Light Ceiling Flush Mount



Collections: Nash (Primary)
Driscoll

Two Light Flush Mount Fixture in Brushed Nickel Finish with Satin Etched Glass Shade

UPC #:785652754333

Finish: Brushed Nickel (962)

Dimensions:

Diameter: 14" **Wire:** 6 1/2" (color/Black/White)
Height: 4 1/2" **Mounting Proc.:** Cap Nuts
Weight: 3.7 lbs. **Connection:** Mounted To Box

Bulbs:

2 - Medium A19 60w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.
- Sleek architectural look with exclusive 'twist-lock' design makes installation and relamping easy with no exposed screws

Material List:

1 Body - Steel - Brushed Nickel

Safety Listing:

Safety Listed for Damp Locations

Instruction Sheets:

French (F-003)
Trilingual (English, Spanish, and French) (990C7543_-NSH)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Diffuser	Glass	Satin Etched	1				3 7/8	10 7/8				

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	75435-962	1	785652754333	15.25	15.25	7.75	1.043	5.2	150	Yes
NJ Pallet		66		48	40	77	85.556	343.2		No
NV Pallet		66		48	40	76.75	85.278	343		No