



75436-962: Three Light Ceiling Flush Mount



Collections: Nash (Primary)
Driscoll

Three Light Flush Mount Fixture in Brushed Nickel Finish with Satin Etched Glass Shade

UPC #:785652754395

Finish: Brushed Nickel (962)

Dimensions:

Diameter: 16 3/4" **Wire:** 6 1/2"
Height: 5 1/2" **Mounting Proc.:** Cap Nuts
Weight: 8.8 lbs. **Connection:** Mounted To Box

Bulbs:

3 - Medium A19 60w Max. 120v - Not included
3 - LED Medium A19 8w Max. 120v - Not included
3 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.
- Sleek architectural look with exclusive 'twist-lock' design makes installation and relamping easy with no exposed screws

Material List:

1 Body - Steel - Brushed Nickel

Safety Listing:

Safety Listed for Damp Locations

Instruction Sheets:

English (HC-1491)
French (F-003)
Trilingual (English, Spanish, and French) (990C7543_-NSH)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Diffuser	Glass	Satin Etched	1				4 13/32	12 3/4				

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	75436-962	1	785652754395	18	18	9	1.688	8.1	150	Yes
NJ Pallet		34		48	40	69.5	77.222	275.4		No
NV Pallet		40		48	40	72	80	348.6		No