



Actual

Catalog Number: 1260
Product ID: 7TAA040290R0002
UPC Number: 78635856560
Status: Active

Single-Gang Nail-On Outlet Box, Volume 22.5 Cubic Inches, Length 3-7/8 Inches, Width 2-3/8 Inches, Depth 3-21/32 Inches, Color Brown, Material Phenolic, Mounting Means Recessed Angled Nails

North American Specifications (UNSPSC)

UNSPSC	39121308 Outlet box
IGCC	4433 Outlet box
Brand Name	Carlon
Type	Outlet Boxes
Application	Can be installed in the same stud cavity of a shared two-hour wall.
Standard	UL E11461
Material	Non-Metallic
Color	Brown
Cubic Capacity	22.5 Cubic Inches

European Specifications (ETIM)

ETIM	EC002601 Box/housing for built-in mounting in the wall/ceiling
Mounting method	Other
Shape	Rectangular
Construction type	Device connection box (round/square)
Equipped with	None
Length	98.425mm
Width	59.055mm
Depth	92.8624-92.8624mm
Mounting switching equipment	Screwing
With screws	N
Pipe locking	N
Pipe locking optional	N
Inlet from the rear	N
Material	Plastic
Colour	Other
Cover	None
Cover attachment	Not applicable
Sealable	N

Packaging

Outer Quantity	100
Outer Dimensions (inches)	19.7x12x10.4
Weight Uom	37.63 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com