



Siemens Low Voltage Residential Circuit Breakers Miniature Thermal Mag Circuit Breakers - Type QP/MP, 3-Pole, 240VAC are Circuit Protection Load Center Mains, Feeders, and Miniature Circuit Breakers. Type: MP-T Application: For Use In 100 AMP, 3-Phase Output WML Meter Stacks Only Standard: HACR Rated Voltage Rating: 240 Amperage Rating: 90 Interrupt Rating: 10 Number Of Poles: 3 Operating Temperature: 40

Number of poles	3
Suitability for operation	For Use In 100 AMP, 3-Phase Output WML Meter Stacks Only
Electricity	
Continuous current rated value	90 A
Supply voltage frequency rated value 50/60 Hz	Yes
Environmental conditions	
Ambient temperature during operation maximum	40 °C
Model	
Product brand name	SIEMENS
Mechanical Design	
Design of the product	MP-T
General product approval	
Standard	HACR Rated
last modified:	11/09/2017