

Ceiling Space Collection
Flush Mt 2Lt
8102NI (Brushed Nickel)



Dimensions

Height	4.75"
Width	9.25"

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Hybrid	CFL	13-15W		

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____

Ordering Information

Product ID	8102NI
Finish	Brushed Nickel
Available Finishes	NI, NI, WH, WH
Collection	Ceiling Space Collection

Dimensions

Base Backplate	8.75 DIA
----------------	----------

Specifications

Material	Steel
Diffuser Description	White Clip On Glass

Electrical

Voltage	120V
---------	------

Qualifications

Safety Rated	Dry
Warranty	www.kichler.com/warranty

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
# of Bulbs/LED Modules	2
Max or Nominal Watt	60W
Socket Wire	150
Socket Type	Medium
Lamp Type	A19