
Canfield 30" Collection 30 Inch Canfield Fan

300103WH (White)



Dimensions



Downrod	Α	В	С	D
1.00 OD X 6.00	15.00	12.80	9.25	6.02

Available Finishes

Finish	Fixture	Glass	Blade 1	Blade 2

Project Name:	
Location:	
Туре:	
Qty:	
Comments:	

Product Information

Product ID	300103WH
Finish	White
Blade Finish	White/White
Collection	Canfield 30" Collection

Airflow, Power and Efficiency

	Speed	RPM	CFM	CFM/ Watt	Amps	Watts
	High	230	2266	48	.39	47
	Med	167	1564	63	.28	25
	Low	87	847	94	.16	9

Specifications

Number of Blades	5
Blades Included	Yes
Blade Pitch	24 Degrees
Blade Sweep	30"
Blades Reversible	No
Blade Material	UV COATED WOOD
Optional Blades Available	No
Downrod 1	1.00 OD X 6.00
Primary Control System	Pull Chain - In project applications using multiple ceiling fans, alternative remote controls may be required. Please contact Kichler Advanced Product Solutions at 844-542-4537 to confirm your project requirements.
Remote Included	No
Wall Control Included	No
Low Ceiling Adaptable	Yes, Dual Mount Included
Lead Wire Length	78.00"
Motor Size	153MM X 17MM
Motor Type	AC

Downlight


Downlight Bulb Included	Not Included
Watts	47/25/9
Glass Description	NONE
Optional Light Kit Available	No



7711 East Pleasant Valley Road Cleveland, Ohio 44131-8010 Toll free: 866.558.5706 or kichler.com

Notes

1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.





Canfield 30" Collection 30 Inch Canfield Fan

300103WH (White)

Finish	Fixture	Glass	Blade 1	Blade 2
Brushed Nickel	300103NI	N/A	CHERRY	WALNUT
Oil Brushed Bronze	300103OBB	N/A	CHERRY	WALNUT
White	300103WH	N/A	WHITE	WHITE
Oil Brushed Bronze	300103OBB220		CHERRY	WALNUT
Satin Natural White	300103SNW220		SATIN NAT WHITE	SATIN NAT WHITE
Brushed Stainless Steel	300103BSS220		LIGHT OAK	MEDIUM OAK
Brushed Nickel	300103NI220		CHERRY	WALNUT
White	300103WH220		WHITE	WHITE

_			
()or	ntrol	Options	٠
COL	iti Oi	Options)

Product ID	Descr
337012ALM	4 Speed Fan Slide Control
337012IV	4 Speed Fan Slide Control
337012WH	4 Speed Fan Slide Control
337214	Limited Function Cooltouch
370039MUL	Wall Control System L-Function
370040	4 Speed Rotary Switch 10 AMP

Project Name: _	
Location:	
Туре:	
Qty:	
Comments:	

Safaty Listings & Cartifications

Floor

Safety Listings & Certifications		
Safety Rated	Dry	
Warranty	www.kichler.com/warranty	
Installation		
Installation requirements	The electrical junction box and support structure must be securely mounted and capable of reliably supporting a minimum of 50 pounds. Use only ETL/UL listed electrical junction boxes marked ""For Fan Support""	
Electrical Requirements	120V 60Hz AC	
Hanging Weight	14.8 LBS	
Minimum Distance Between Bottom Of Fan Blade To	7.5 feet	