

Project Name

Location

Prepared By



Notes

**General**

Status	Active
Fixture Type	BLINK Slim
Finish	White
Wattage	16
Lumen Output	1300
CCT (Kelvin)	3000

**Specifications**

Technology	LED
Color Temperature	Warm White
CRI	90
Voltage	120V/277V
Beam Angle	108
Rated Hours	50000
Operating Temperature	-17C (+1.4F) to a maximum of +45C (+113F)
Dimmable	Yes Dimmable - 120V only

**Dimensions**

Height (in.)	0.63
Width (in.)	9

**Compliance**

Safety Listing	cETLus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2287652
CEC Status	Lawful for sale in California
CA Prop 65	Lead
RoHS Compliant	Yes

**Additional Information**

Warranty	5 Year Limited
----------	----------------