



ALLIED  
MOULDED  
PRODUCTS, Inc.

419-636-4217  
222 N. Union St.  
Bryan, OH 43506



## Product Info

**Brand:** fiberglassBOX

**UPC:** 85339102700

**UNSPSC:** 39121316

**Carton Weight:** 21 lbs

**Country of Origin:** United States of America

**Color:** Off white

**Material:** Fiberglass reinforced polyester

**Additional Materials:** Carbon steel fasteners, Polyvinyl chloride clamps

**Box Diameter:** 3.5

## 9336-N

3.5" dia. round fixture support box for use with nonmetallic sheathed cable

**Carton Quantity:** 50

**Closure Type:**

**Mounting Description:** Nail-on with fether ring nails

**Box Type:** Ceiling - Fixture

**Box Features:** Nails

**Installation Type:** New Work

**Width:** 3.5 in

**Depth:** 2-3/8 in

**Volume:** 16 cu in

**Fixture Rating:** 50lbs

## Features:

Machine tapped fixture holes, rigid hard box construction, no distortion with high temperatures, shatter resistant with low temperatures, Speed "K" Clamps bulk packed

## Application:

New work residential construction 2 HR fire resistive walls and ceilings (50 lbs. fixture support)

**Box Diameter:** 3.5

## Standards:

ANSI / UL 514C: [File No. E30594](#)



**LISTED**

## Fire Classification:

### Fire Test of Building Construction Materials

ANSI / UL 263: [File No. CEYY.R9379](#) (Category / File No.)

Note: Products must also be certified to: ANSI / UL 514C

### Fire Resistance Classification in Wall Assemblies 2-Hours or less

Shall be separated by a horizontal distance of not less than 3 inches

### Fire Resistance Classification in Floor-Ceiling Assemblies 2-Hours or Less

Distance between boxes in adjacent cavities may be reduced to 5 ½ inches

*Note: For more details please refer to the UL fire resistive*

*directory and Allied Moulded's CEYY.9379 (Outlet boxes  
and fittings classified for fire resistance)*

---