

Inspire V5 Standard Super Bright



LED Tape Light













Туре	Tape Light Part #	Connector Part #	Driver Part #	Channel Part #

Specifications

Color Temperatures	• 1800K • 2100K • 2700K
	• 3000K • 3500K • 4000K
Lumen Output	up to 490 LM/FT
Input Power	24V DC
Max Run Length	23FT
0	Air (404 Orana)
Cut Increments	every 4in (101.6mm)
Power Consumption	4.2 Watts/FT
Power Consumption	4.2 \\dits/1
Product Color	White
1 100000 00101	777.11.0
LEDs per Foot	24
·	
Light Distribution	120°

Mounting	3M VHB Adhesive
Modifing	JIVI VI ID Adriesive
Dimensions (WxH)	1/2" x 1/8" (12mm x 3.2mm)
Operating Temperature	-22°F to 140°F (-30°C to 60°C)
Lamp Life	50,000 Hours
Certifications	UL Listed (E467147)
Dimming & Control	MLVIncandescentCFL/LEDELV0-10V
Warranty	5 Year Limited
Environment	• IP20 Indoor, Dry (tape light only)

1/2" (12.7mm)



Cut Increment: 4" (101.6mm)

1/4" (6.4mm)

1/2"

• IP54 Indoor, Damp (with channel)

Performance Summary

					TM-	30-15
Color Temperature	Lumens/FT	Efficacy (LM/W)	CRI	R9	Rf	Rg
4000K	490	116	94+	95	91	100
3500K	465	110	94+	99	94	101
3000K	460	109	94+	92	93	102
2700K	400	95	94+	86	92	104
2100K	398	94	94+	87	95	100
1800K	349	83	94+	84	90	91

Ordering LED Tape Light

	4
1	LEDI
	LEDI

Version	Series	Brightness	Color Temp.	Roll Length			,
V 5	STND	SB (Super Bright)	18 (1800K)	Order a Bulk Roll:	N Evample Port #/a.		
			21 (2100K)	16 (16FT)	Example Part #'s:	QTY	QTY in
			27 (2700K)	100 (100FT)	Part #	Ordered	FT
			30 (3000K)	Order a Custom Roll:		1	16FT
			35 (3500K)	Custom	 V5-STND-SB-30-100 V5-STND-SB-40-CUSTOM 	3 25	300FT 25FT
			40 (4000K)		- 40-00310M	EU	201 1

Ordering LED Tape Light Connectors

Zeus HD™ Connectors (Single Color; 2-Wire)

Connector Type	Part #	Wire Length	Wire Size	Wire Rating
10FT In-Wall Rated Lead Wire	V5-CON-HW-10	10FT	18AWG	CL2
25FT In-Wall Rated Lead Wire	V5-CON-HW-25	25FT	18AWG	CL2
10FT Plenum (In-Wall) Rated Lead Wire	V5-CON-HW-PL-10	10FT	18AWG	CL3P
25FT Plenum (In-Wall) Rated Lead Wire	V5-CON-HW-PL-25	25FT	18AWG	CL3P
2-Inch Extension (Jumper)	V5-EXT-2IN	2in	22AWG	UL2464
4-Inch Extension (Jumper)	V5-EXT-4IN	4in	22AWG	UL2464
1FT Extension (Jumper)	V5-EXT-1FT	1FT	22AWG	UL2464
3FT Extension (Jumper)	V5-EXT-3FT	3FT	22AWG	UL2464
6FT Extension (Jumper)	V5-EXT-6FT	6FT	22AWG	UL2464
Splice Connector	V5-CON-SPLICE	n/a	n/a	n/a

Ordering an LED Driver

Hybrid MLV & Incandescent Dimmable 120V Drivers (UL Listed)

For use with MLV, Incandescent, & CFL/LED dimmers. See our Dimmer Compatibility List for a list of approved dimmers.

20-Watt: **DR-20W-24VDC-120V-2-MLV-m** 40-Watt: DR-40W-24VDC-120V-2-MLV-m 60-Watt: **DR-60W-24VDC-120V-2-MLV-m** 96-Watt: **DR-96W-24VDC-120V-2-MLV-m**

All LED drivers listed above are Class 2 compliant.

Magnetic Low Voltage Dimmable 120V Drivers (ETL Listed)

For use with MLV dimmers only. See our Dimmer Compatibility List for a list of approved dimmers.

150-Watt: **DR-150W-24VDC-DIM** 192-Watt*: **DR-192W-24VDC-DIM** 200-Watt: **DR-200W-24VDC-DIM** 288-Watt*: **DR-288W-24VDC-DIM** 300-Watt: **DR-300W-24VDC-DIM**

Electronic 0-10V Dimmable 120V Drivers (UL Listed & UL Recognized)

25-Watt (UL Recognized)*:	DR-25W-24VDC-DIM10
60-Watt (UL Recognized)*:	DR-60W-24VDC-DIM10
60-Watt (UL Listed)*:	DR-60W-24VDC-U-2-10-c
100-Watt (UL Listed)*:	DR-100W-24VDC-U-2-10-c
100-Watt (UL Recognized)*:	DR-100W-24VDC-DIM10
150-Watt (UL Recognized):	DR-150W-24VDC-U-1-10-w
200-Watt (UL Recognized):	DR-200W-24VDC-U-2-10-g
240-Watt (UL Recognized):	DR-240W-24VDC-U-1-10-w
320-Watt (UL Recognized):	DR-320W-24VDC-U-1-10-w
600-Watt (UL Recognized):	DR-600W-24VDC-U-1-10-w

^{*}Class 2 compliant LED driver.

Electronic Plug-In Non-Dimmable 120-240V Drivers (UL Listed)

36-Watt*: **DR-36W-24VDC-120V-2-ND-e** 96-Watt*: DR-96W-24VDC-120V-2-ND-e 144-Watt: **DR-144W-24VDC-120V-2-ND-e**

^{*}Class 2 compliant LED driver.

^{*}Class 2 compliant LED driver.

Ordering a Channel Kit

LEDI

► Example Part #: CH1-KIT-ANG-FR-6

- Pre-packaged channels with all applicable parts and pieces (tape light specified separately).
- All channel kits channels ship unassembled.

			V Example Part #: GHI-KII-ANG-FK-0
		3FT Kit Part #'s	6FT Kit Part #'s
		with Frosted Lens: CH1-KIT-SLM-FR-3	with Frosted Lens: CH1-KIT-SLM-FR-6
Slim Channel with Standard Len		with Clear Lens: CH1-KIT-SLM-CL-3 with Frosted Lens: CH1-KIT-SLM-FR-3 with Clear Lens: CH1-KIT-SLM-CL-3	with Clear Lens: CH1-KIT-SLM-CL-6
{ }	Slim Channel with Tall Lens	with Frosted Lens: CH1-KIT-SLM-TFR-3	with Frosted Lens: CH1-KIT-SLM-TFR-6
}	Square Channel with Standard Lens	with Frosted Lens: CH1-KIT-SQ-FR-3 with Clear Lens: CH1-KIT-SQ-CL-3	with Frosted Lens: CH1-KIT-SQ-FR-6 with Clear Lens: CH1-KIT-SQ-CL-6
\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	Square Channel with Tall Lens	with Frosted Lens: CH1-KIT-SQ-TFR-3	with Frosted Lens: CH1-KIT-SQ-TFR-6
	Angled Channel with Angled Lens	with Frosted Lens: CH1-KIT-ANG-FR-3 with Clear Lens: CH1-KIT-ANG-CL-3	with Frosted Lens: CH1-KIT-ANG-FR-6 with Clear Lens: CH1-KIT-ANG-CL-6
lb di	Recessed Channel with Standard Lens	with Frosted Lens: CH1-KIT-REC-FR-3	with Frosted Lens: CH1-KIT-REC-FR-6
		with Clear Lens: CH1-KIT-REC-CL-3	with Clear Lens: CH1-KIT-REC-CL-6

Ordering a Custom Channel

- · LEDI can custom cut channel to a length you specify.
- · Channels that are longer than 6ft must ship unassembled.
- Channels shorter than 6ft may ship assembled or unassembled based on the Build Type you select below.
- Tape light must be specified spearately.
- Optimized lengths (see Build Types below) vary depending upon the LED tape light model, channel model, and the lengths associated with them.
- · End caps and mounting hardware will be added to each fixture and reflected in any pricing quotes.
- · Lead time may vary based on quantities required.

			► Example Part #: REC-STFR-B3-9FT4IN
Channel	Lens	Build Type	Channel Length
SLM (Slim)	STFR Standard, Frosted STCL Standard, Clear TFR Tall, Frosted	FOR ALL LENGTHS • Cut to the exact length specified * • Ships unassembled	XX ft XX in Example: 9ft 4in
SQ (Square)	STFR Standard, Frosted STCL Standard, Clear TFR Tall, Frosted	 Lead time up to 5 business days B2 • Cut to an optimized length ** • Ships unassembled • Lead time up to 5 business days. 	* Gaps in light may be visible at each end of the channel because the channel is NOT optimized to the model and length of LED tape light you're using.
ANG (Angled)	ANGFR Angled, Frosted ANGCL Angled, Clear	FOR LENGTHS SHORTER THAN 6FT ONLY 83 • Cut to the exact length specified * • Ships fully assembled IF LESS THAN 6FT †	light. The optimized length may differ from the requested length depending
REC (Recessed)	STFR Standard, Frosted STCL Standard, Clear	Lead time up to 10 business days Out to an optimized length ** Ships fully assembled IF LESS THAN 6FT † Lead time up to 10 business days	on the model of LED tape light you're using. † If channel is longer than 6ft, the channel must be shipped unassembled.

Ordering a Build-Your-Own Channel

• All Build-Your-Own channels ship unassembled.

You select the exact parts and pieces you need for your project (tape light specified separately).

6FT Standard, Clear Lens: CH1-LENS-STCL-6

- Example Part #'s:
 - CH1-SQ-6
 - CH1-LENS-TFR-6
 - CH1-MNT-SM
 - CH1-END-TSQ



Channel Length Lens Type & Length Mounting Hardware End Caps Slim 3FT: CH1-SLM-3 3FT Standard, Frosted Lens: CH1-LENS-STFR-3 Surface Mount: CH1-MNT-SM for Standard Lenses: CH1-END-STSLM Channel 6FT: CH1-SLM-6 6FT Standard, Frosted Lens: CH1-LENS-STFR-6 for Tall Lenses: CH1-END-TSLM 3FT Standard, Clear Lens: CH1-LENS-STCL-3 6FT Standard, Clear Lens: CH1-LENS-STCL-6 3FT Tall, Frosted Lens: CH1-LENS-TFR-3 6FT Tall, Frosted Lens: CH1-LENS-TFR-6 **Square** 3FT: CH1-SQ-3 3FT Standard, Frosted Lens: CH1-LENS-STFR-3 Surface Mount: CH1-MNT-SM for Standard Lenses: CH1-END-STSQ Channel for Tall Lenses: CH1-END-TSQ 6FT: CH1-SQ-6 6FT Standard, Frosted Lens: CH1-LENS-STFR-6 3FT Standard, Clear Lens: CH1-LENS-STCL-3 6FT Standard, Clear Lens: CH1-LENS-STCL-6 3FT Tall, Frosted Lens: CH1-LENS-TFR-3 6FT Tall. Frosted Lens: CH1-LENS-TFR-6 **Analed** 3FT: CH1-ANG-3 3FT Angled, Frosted Lens: CH1-LENS-ANGFR-3 Surface Mount: CH1-MNT-ANG for Angled Lenses: CH1-END-ANG Channel 6FT: CH1-ANG-6 6FT Angled, Frosted Lens: CH1-LENS-ANGFR-6 3FT Angled, Clear Lens: CH1-LENS-ANGCL-3 6FT Angled, Clear Lens: CH1-LENS-ANGCL-6 Recessed 3FT: CH1-REC-3 3FT Standard, Frosted Lens: CH1-LENS-STFR-3 Recess Mount: CH1-MNT-REC for Standard Lenses: CH1-END-REC Channel 6FT: CH1-REC-6 6FT Standard, Frosted Lens: CH1-LENS-STFR-6 3FT Standard, Clear Lens: CH1-LENS-STCL-3