

Project:

Type:

Prepared By:

Date:



UPC: 019813833866



Features and Benefits

UNIVERSAL BULBS - Replace 60W, 125W, 200W and 300W incandescent lamps operated on 120V or 277V

UNIVERSAL VOLTAGE - Bulbs have high lumen packages for industrial and commercial applications

ENERGY SAVINGS - Save up to 85% on energy

ENCLOSED FIXTURE RATED - May be used in both enclosed and open fixtures

DAMP RATED - Suitable for damp locations

SHATTERPROOF - Plastic constructed bulbs are ideal for rugged applications

Technical Specifications

Technical Specifications

Product Type:

A-Line

Bulb Shape:

A19 E26

Wattage:

8.5W

Wattage Equivalency:

60WW Incandescent

Typical Lumen Output:

840

Efficacy:

98 lm/W

Color Temperature:

5000K Daylight

CRI:

80

Base Type:

E26

L70 Lifespan:

25,000 hours

Operating Temperature:

-20°C - 45°C

Dimmable:

No

Beam Angle:

230°

Warranty:

3-Year, No-Compromise Warranty

For Use in Emergency Fixtures:

No

For Use Outdoors in Open Fixtures:

No

Electrical Characteristics

Input Voltage:

120-277V

Technical Specifications (continued)

Electrical Characteristics

Power Factor:

0.8

Operating Frequency:

60 Hz

Input Current @ 120V:

108mA

Input Current @ 277V:

42mA

Listings

UL Listed:

Yes

ENERGY STAR V2.0:

This product is ENERGY STAR® Version 2.0 Certified

Energy Star Model Number:

A10016

Energy Star ID:

2340613

CEC Status:

Not lawful for sale in California

Other

:

Case and Pallet Dimensions

	QTY	LENGTH	WIDTH	HEIGHT
CASE	12	5.2	4.9	15.4
PALLET	2268	48.1	47.3	39.8