

Straight Blade Devices  
20A, 125V, 2 Pole, 3 Wire Grounding  
Straight and Right Angle Pigtailed Terminal



Features

- Transparent housing to inspect contacts
- Audible SNAP, indicates solid connection
- Reduces installation time
- Fully insulated design

Ordering Information

Description	Wire Type	UPC	Catalog Number
Right angle, clear terminal with 6-inch leads, assembled in USA	Solid	783585251967	SNAP1RNA

Listings

UL Listed to UL498 File No. E2186  
Certified to CSA, C22.2, No. 42 File 285  
Fed. Spec. W-C-596

Specifications

Contact	Brass
Terminal Body	PBT
Wire	#12 AWG, T90 Nylon FT-1, PVC 90°C (min)

Performance

<b>Electrical</b>	
Current Interrupting	Receptacle certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
<b>Mechanical</b>	
Terminal Identification	Terminal Wire Leads- Identified in accordance with UL 498
<b>Environmental</b>	
Flammability	UL 94V-2
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)



Accessories

Mating Receptacle	Hubbell SNAPConnect® Receptacle
-------------------	---------------------------------

Resources

eCatalog
----------

