



Product Number: 55091

Order Abbr eviation: 36PAR36/HAL/WFL30 12V

General Description: Tungsten Halogen CAPSYLITE PAR36 Screw Terminal & Spade Connector Base 36W 12Volt Wide Flood Beam

Product Information

Abbrev. With Packaging Info.	36PAR36HALWFL30 12V 12/CS 1/SKU
Approx. Lumens	500
Average Rated Life (hr)	4000
Base	Screw Terminal
Beam Angle (deg)	30
Beam Type	WFL
Bulb	PAR36
Centerbeam Candlepower (cp)	1000
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	3000
Diameter (in)	4.500
Diameter (mm)	114.30
Ecologic	YES
Family Brand Name	CAPSYLITE® PAR36
Filament	C-8
Horizontal Beam Angle (deg)	32
Lamp Finish	Reflector
Maximum Overall Length - MOL (in)	2.750
Maximum Overall Length - MOL (mm)	69.85
Nominal Voltage (V)	12.00
Nominal Wattage (W)	36.00
Vertical Beam Angle (deg)	32



Footnotes

- For indoor or outdoor use where not directly exposed to weather. Exposure to weather may damage the bulb.