

Eileen Collection
Semi Flush 3Lt NI
3797NI (Brushed Nickel)



Dimensions

Height	14.50"
Overall Height	53.00"
Width	17.25"

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Hybrid	CFL	23-30W		

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____

Ordering Information

Product ID	3797NI
Finish	Brushed Nickel
Available Finishes	CH, CH, NI, NI, OZ, OZ
Collection	Eileen Collection

Dimensions

Base Backplate	5.00 DIA
Chain/Stem Length	36.00"
Weight	7.00 LBS

Specifications

Material	Steel
Diffuser Description	Satin Etched White

Electrical

Voltage	120 V
Lead Wire Length	10.00"

Qualifications

Safety Rated	Dry
Warranty	www.kichler.com/warranty

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
# of Bulbs/LED Modules	3
Max or Nominal Watt	100W
Socket Wire	150
Socket Type	Medium
Lamp Type	A19