

Project Name

Location

Prepared By



SATCO S39473

9WLED/DIR/5-6/30K/120V

Notes

General

Status	Active
Recessed Can Size	5-6 in.
Wattage	9
Voltage	120V
Finish	White
CCT (Kelvin)	3000
Color Temperature	Warm White
Lumen Output	800

Specifications

Technology	LED
CRI	90
Beam Angle	90
Rated Hours	50000
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
Dimmable	Yes Dimmable

Dimensions

Width (in.)	7.41
Height (in.)	3.91

Compliance

Safety Listing	cULus Classified
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2338430
CEC Status	California T24 Qualified
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited
----------	----------------