



TYPE: _____
 CATALOG #: _____
 NOTES: _____

Prestige™ Series Edge-Lit Die-Cast Aluminum Edge-Lit Exit Sign

Design upgrade: introducing new features

1. Easier installation: component-free back-box housing and canopy can be installed in advance, like a regular junction box.
2. 20 – 30% less power consumption: max. 1.4W (AC-only models) and max. 2.3W (Self-Powered)
3. Bi-color LED pilot light allows visual diagnostic without the need to open the unit (self-test and diagnostic option)
4. Listed by the Underwriting Laboratories UL Listed
5. Also available with white LEDs for custom-design legends: pictograms, special wording, etc. (Ask your sales representatives)

Features

- Designed to achieve superior visual clarity and performance with a red and green LED light source
 - Clear acrylic panel provides optimum light transmission. Illumination is 100% in both AC and emergency mode
 - Computer engraving is used to crisply define each letter and chevron. LED sensitive inks are formulated to provide a rich color in red or green. Choice of legend background includes clear (for single face), white or mirror (for single or double face signs)
 - Clean trim plate design eliminates visible fasteners. Choice of trim plates: circular or angular. Standard finish is brushed aluminum for the housing, trim plate, trim ring and canopy
 - Self-Powered models contain a sealed maintenance-free Nickel-Cadmium battery that provides 90 minutes of emergency illumination.
 - Two-wire universal 120 through 277VAC, 50/60Hz for AC-only and Self-Powered models. AC-only signs consume maximum 1.4W. Self-Powered signs use 2.3W max while recharging batteries. Solid state transfer automatically and instantly supplies the LED lamps from the back-up battery upon failure of AC supply. Close tolerance electronic circuit activates emergency unit when utility power dips below nominal voltage for brownout protection. Current-limited and short-circuit-proof charger. Full battery recharge is made in compliance with UL924 specifications. Test switch incorporates a green LED AC pilot light
 - Self-test and silent diagnostic is optional on all Self-Powered models. It is programmed to ensure product readiness and reliability by continuously monitoring every critical function of the unit. The unit is self-tested for one minute every 30 days, 30 minutes every 60 days and 90 minutes annually. When a fault is detected the pilot light will change color from green to red and blink following a particular code, identifying the cause: battery, charger circuitry, or LED lamps
 - Modular design allows for several mounting configurations. A trim ring and two 27-inch bar hangers are used for recessed mounting on walls or ceilings. A canopy allows for surface mounting on ceilings or walls as back- or end-mount. Face panels snap securely into trim plate on all mounting configurations
 - UL924 Listed
 - 5-year limited warranty
- Detailed warranty terms located at: www.emergi-lite.com/usa/files/EL_Warranty.pdf

Accessories (order as a separate item)

DESCRIPTION	SUFFIX
White Pendant	P*-WT
Black Pendant	P*-BK
Gray Pendant	P*-GY

* Custom pendant lengths and colors available, specify (12", 24", 36", etc)

Backbox (order as a separate item)




DESCRIPTION	SUFFIX
Backbox Kit white	BBKTS-WT-E
Backbox Kit black	BBKTS-BK-E
Backbox kit brushed aluminum	BBKTS-BA-E
Backbox kit chrome	BBKTS-CH-E
Backbox kit dark bronze	BBKTS-DB-E
Backbox kit polished brass	BBKTS-PB-E

Electrical

Power requirements: 120 to 277VAC, 50/60Hz. AC-only signs use 1.4 watts max, Self-Powered signs use 2.3 watts max while recharging batteries

Available Models

Circular trim plate models shown. optional Angular trim plate available.



Power Consumption

Model	AC Specs		DC Specs	
AC-only	120 to 277VAC, 50/60Hz	Less than 1.4W		
AC/DC-remote	120 to 277VAC, 50/60Hz	Less than 1.4W	6 to 24VDC	Less than 1.4W
Self-Powered	120 to 277VAC, 50/60Hz	Less than 2.3W	Ni-Cd battery	Min. 90 minutes
Self-Powered diagnostic	120/277VAC, 50/60Hz	Less than 2.3W	Ni-Cd battery	Min. 90 minutes


TYPE: _____
 CATALOG #: _____
 NOTES: _____



The Prestige™ Series Edge-Lite combines a clean, modular design with state-of-the-art technology, ease of installation for surface or recessed mount applications and options to meet the most prestigious interiors




Standard
Circular Trim Plate



Optional
Angular Trim Plate


Dimensions

Dimensions are approximate and subject to change.




Mounting Configurations

All mounting configurations use the same basic components. Inserting a trim ring allows for recessed mounting on walls or ceilings. Applying a canopy allows for surface mounting on ceilings or walls as back or end mount.



Arrow (Chevron) Designation



*Wording and chevrons not to scale. For illustration purposes only.

How to Order

HOUSING COLOR	SERIES	FACES	DESIGNATION	LEGEND COLOR	BACKGROUND COLOR	ARROWS	TRIM	MOUNTING	OPTIONS	LEGEND SIZE
Blank= Brushed aluminum W= White B= Black PB= Polished brass CH= Polished chrome BR= Bronze	LX= AC-only LXN= Self-Powered	1= Single face 2= Double face	N= New design	R= Red G= Green	C= Clear (single face only) W= White M= Mirror	Blank= No arrow L= Arrow left R= Arrow right RL= Right and left (double face) D= Double arrow UA= Universal field installed arrows	-A= Angular -C= Circular	Blank= Universal mount S= Surface mount (canopy)*	Blank= No option -NEX= Nexus® Wired (consult your sales representative) -NEXRF= Nexus® Wireless (consult your sales representative) -FA= Fire alarm -D= Self-Test and diagnostic -DC= AC/DC remote 6-24 VDC -2CKT= Two circuit, AC only -FZ= Flasher & buzzer (Self-Powered only) -X= Back box shipped separately	Blank= 6" EXIT legend -8= 8" EXIT legend (red only) -LP= Panel shipped separately

Example: WLXN2NRLWR-A-D