



A3686

40BA9 1/2/F
40 watt BA9 1/2 Incandescent; Frost; 2500 average rated hours; 384 lumens; Candelabra base; 130 volts

Features

- Decorative incandescent
- Long Life
- Brass Base
- 130 volt



A3686

Item Number	UPC		Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
A3686	045923036866		40	BA9 1/2	Candelabra	E12	40BA9 1/2/F	130
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours		Pack	Package Type
Frost	3-1/2"	1.19"	CC-2V	384	2500		500/25	Box
Dimmable/Non-Dimmable					RoHS Compliant			
Dimmable					Yes			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

