



Actual

Catalog Number: 63160
Product ID: 7TAH007420R0006
UPC Number: 78621063160
Status: Active

Aluminum Compression H-Tap: Wire Range Main: 500-4/0, Branch 4/0-2, Side Tap 2-6, Length 2-3/4 Inches, Die Code N, Die Color Code Red

- Fillerlok Tab provides positive interlock and extends wire range.
- Wire Bore coated with T&B oxide inhibitor.
- Recommended for aluminum to aluminum, aluminum to copper, and copper to copper connectors.
- Application Tools: TBM15I

North American Specifications (UNSPSC)

UNSPSC	39121428 Electrical taps
IGCC	4600 Electrical taps
Brand Name	Color-Keyed
Type	H-Tap
Special Features	Fillerlok Tab provides positive interlock and extends wire range.
Standard	UL E9809
Conductor Size	500-4/0
Tap Size	4/0-2
Voltage Rating	600V
Material	Aluminum

Packaging

Inner Quantity	1
Inner Dimensions (inches)	3x2.25x3.1
Outer Quantity	10
Outer Dimensions (inches)	7.13x6.13x4.81
Weight Uom	37.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com