



Representative

Catalog Number: CPC125
Product ID: 7TBA005370R0004
UPC Number: 61601310704
EAN Number: 05415022256468
Status: Active

Clamp, One-Piece Cable and Pipe, EMT and Rigid Conduit Trade Size 1-1/4 Inches, Cable Outer Diameter Range 1.400-1.725 Inches, Steel

- Heavy-duty 5/16 Inch hex bolt with multi-driver head, Robertson square, Phillips cross-recess and slot, provides a full range of installation options.
- Reconfigure wiring without complete disassembly. Remove cables easily without disturbing neighboring clamps.
- Parallel hook design keeps conduits and cable square with strut.
- Works with all depths of strut - 13/16 Inch to 3 1/4 Inch

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	31162906 Hose or pipe clamps
IGCC	3064 Hose or pipe clamps
Brand Name	Superstrut
Type	Pipe Straps, Pipe Clamps & Hangers (Series 700)
Special Features	One-piece, heavy-duty construction ready to install right out of the box, no need to break apart and re-assemble, no screws or bolts to drop.
Application	Attaches a full range of EMT, Rigid conduit and cable to strut channels.
Standard	UL E160899
Material	Steel
Finish	SilverGalv/Electro-Galvanized
Maximum Clamp Diameter	1.725 Inches
Minimum Clamp Diameter	1.400 Inches

European Specifications (ETIM)

ETIM	EC002470 Mounting clamp for cable protection tubes
Material	Steel
Rotatable	N

Packaging

Outer Quantity	50
Outer Dimensions (inches)	10.5x5.75x7.5
Weight Uom	12.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com