

Path & Spread 1-Lt 12V

15005AZT (Textured Architectural Bronze)

Project Name: _____

Location: _____

Type: _____

Qty: _____

Comments: _____



Dimensions

| | |
|--------|-------|
| Height | 9.50" |
| Width | 6.00" |

Ordering Information

| | |
|--------------------|-------------------------------|
| Product ID | 15005AZT |
| Finish | Textured Architectural Bronze |
| Available Finishes | AZT, BKT |

Specifications

| | |
|-------------------|---------------------|
| Material | Aluminum |
| Glass Description | Clear Polycarbonate |

Electrical

| | |
|------------------|--------|
| Voltage | 12V |
| Lead Wire Length | 52.00" |

Qualifications

| | |
|--------------|--|
| Safety Rated | 12V |
| Warranty | www.kichler.com/warranty |

Primary Lamping

| | |
|-----------------------|----------|
| Lamp Included | Included |
| Number of Lights/LEDs | 1 |
| Max or Nominal Watt | 24.4W |
| Socket Type | Wedge S8 |

Notes:

1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.

2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.