

Metal, selector switch Maintained, short lever position, B Cam 3 position Operator only white insert Non-Illuminated UL file E22655 in Vol. 6 (7) Sec. 13 (2)

Design of the product	Actuator round
Enclosure	
Number of command points	1
Delivery state	
• as a kit	No
Actuator	
Design of the operating mechanism	selector switch
Material of the actuating element	plastic
Type of unlocking device	rotate-to-unlatch mechanism
Number of switching positions	3
Front ring	
Product component front ring	Yes
Design of the front ring	standard
Material of the front ring	metal
Color of the front ring	chrome
Holder	
Material of the holder	Metal
General technical data	
Product component	
• Light source	No
Degree of pollution	1
Protection class IP	IP66
Operating frequency maximum	600 1/h
Ambient conditions	
Ambient temperature	
• during operation	-35 ... +70 °C
• during storage	-40 ... +85 °C
Installation/ mounting/ dimensions	
Shape of the installation opening	round
Certificates/approvals	
Further information	

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=US2:52SA2BAB>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=US2:52SA2BAB>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/US2:52SA2BAB>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:52SA2BAB&lang=en

last modified:

12/21/2016