


NOTE:
 1. ALL DIMENSIONS ARE IN INCHES.
 2. ALL DIMENSIONS HAVE ±0.125 TOLERANCE.

	MOD.	KO VIEW	A	B	C	D	E	F	G	H	I	J	X	Y
TH3221/ TH4321/ THN321	10	1	10.28	6.28	7.12	6.09	10.07	3.31	8.57	4.50	6.12	0.31	-	-
TH3222/ TH4322/ THN3362/ THN2262DC	10	2	17.59	9.38	10.05	9.12	17.32	5.00	15.81	7.50	9.00	0.44	-	17.19
THN3361/ THN2261DC	10	3	10.31	8.31	9.25	8.09	10.07	4.00	8.57	6.50	7.72	0.31	9.94	-
TH3361/ TH2261DC	10	3	12.56	8.31	9.50	8.09	12.32	4.00	10.82	6.50	7.62	0.31	12.19	-
TH3362/ TH2262DC	10	2	21.34	9.12	9.38	9.00	21.12	5.00	19.56	7.50	8.62	0.44	-	20.99

KNOCKOUT TABLE				
SYM.	SIZE	QTY.		
		VIEW 1	VIEW 2	VIEW 3
A	9/32 KO	3	3	3
B	1/2 X 3/4 KO	11	-	1
C	1/2 X 3/4 X 1 KO	-	-	3
D	1/2 X 3/4 X 1 X 1 1/4 KO	-	3	7
E	3/4 X 1 X 1 1/4 X 1 1/2 KO	-	6	2
F	1 X 1 1/4 X 1 1/2 X 2 KO	-	5	-
G	3/8 X 1/2 X 3/4 X 1 KO	3	-	-

 imagination at work

OUTLINE DRAWING-HEAVY DUTY SAFETY SWITCH
 30 & 60A, NEMA -TYPE 1 ENCLOSURE

DWG NO.	DATE	REV
10103091SH102	09-26-14	02