

N		т	F	2	-
	$\sim$	•	_	$\sim$	-

- 1. DIMENSIONS ARE INCHES ± .02 [mm] ± .5
- 2. RATING: 600V 400 AMP.
- 3. UL/c-UL ENCLOSURE TYPES 3R, 4X, 12, SEE INSTRUCTION SHEET.
- 4. CABLE SIZE #4 AWG 4/0, COPPER ONLY.
- 5. LEAD WIRE & COPPER SHEET NOT SHOWN.

HUBBELL CAT. NO.	COLOR	
HBLMRBK	BLACK	
HBLMRW	WHITE	
HBLMRGN	GREEN	
HBLMRR	RED	
HBLMRBL	BLUE	
HBLMRO	ORANGE	
HBLMRBN	BROWN	
HBLMRY	YELLOW	

1.15	ST OF DARTS					
LIST OF PARTS  DESCRIPTION MATERIAL FINISH						
HOUSING	TPE	+	SEE TABLE	DIMENSION SHEET FOR CAT. NO SEE TABLE		
CONTACT	BRASS			ШО		
CAGE	NYLON		BLACK	III .		
SET SCREW	NYLON		NICKEL	<b>√</b> 1		
LEAD WIRE COPPER SHEET	COPPER	+		EET FOR CAT.  TABLE		
0011211011221	OSIT ER			CAT CAT		
				]		
		+		-		
				-		
				-		
				-		
CATALOG NO. HBLMRBK (NOT SHOWN TO SCALE)						
(INOT SHOVV	14 10 30	<u>~~L</u>	<b>-1</b>	R E		
		I	I	REPAIRABLE		
				₽		
				BLE		
				l '''		
				╽└┘		
				7		
				NON-REP		
				교		
				_		
				Ŕ		
				NRABLE		
5 REVISED NOTE 600VAC/250VD		RGP	11/01/17	Ш		
PER DCN 2341						
4 REDRAWN WITH						
EMBEDDED CAD MODEL WITH NO CHANGES TO DJP 2/5/16						
PART GEOMETRY		$\square$				
SYM REVISION		APP	DATE			
THE TREE PAIR						
THE DESIGN AND DIMENSIONS OF THE						
PRODUCT SHOWN ON THIS DRAWING ARE						
SUBJECT TO CHANGE WITHOUT NOTICE						
TITLE SINGLE POLE MALE						
RECEPTACLE WITH						
DOUBLE SET SCREW						
				M-8923		
TOLERANCES UNLESS WIRING DEVICE-KELLEMS						
OTHERWISE SPECIFIED HUBBELL INCORPORATED SHELTON, CT						
.×× = ± .01	DR. BY MJI	Τ.	PP. BY TWB	•		
.XXX = ± .005	TR. BY	· -	CALE 1:1	5		
ANGLES = ± 2° CHK. BY TWB DATE 6/11/03						
<u> </u>	- IVV		2, 11,00	ĺ		