





THIS DRAWING AND THE INFORMATION
HEREON ARE OUR PROPERTY AND MAY
BE USED BY OTHERS ONLY AS
AUTHORIZED BY STAHLIN ENCLOSURES,
DIVISION OF ROBROY INDUSTRIES
ALL RIGHTS RESERVED
UNDER THE COPYRIGHT LAWS

SPECIAL REQUIREMENTS

NEMA 250: TYPE 1, 3, 3R, 4, 4X, 12, 13 IEC 60529: IP66 COLOR: GLACIER GRAY (WPR3013) COLOR STANDARD: PANTONE 428 C				STANDARD P/N: J2424HPL		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03	.XXX ± 0.010
MATERIAL: FIBERGLASS REINFORCED POLYESTER (FRP)				CUSTOMER DWG:		STAHLIN A DIVISION OF ROBROY INDUSTRIES Stahlin Non-Metallic Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-794-0700 Fax: 616-749-3378					
REVISION HISTORY											
REV	DESCRIPTION	DATE	ENG	DRAWN BY		DATE	CUSTOMER		DWG		
-	-	-	-	DRH		12/05/2013	SCALE DO NOT SCALE		DESCRIPTION STANDARD ENCLOSURE		PART NUMBER J2424HPL



PARTS LIST			
ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	WP2424H&LBOX	J2424 MOLDED H&L BOX
2	1	WP2424H&LCVR	J2424 MOLDED H&L CVR
3	1	RMGAS_WP2424H&LCVR	WP2424HLU GASKET
4	1	RMHING19-1/2	19.5" HINGE
5	4	RMKEEPSSL	HPL KEEPER
6	4	RMLATSSL	HPL LATCH
7	28	RMRIV44	RIVET
8	4	RMINSDOD700154500	1/4-20 x 5/16 DODGE EXPANSION INSERT
9	1	N/A	J2424HPL LABEL

THIS DRAWING AND THE INFORMATION
HEREON ARE OUR PROPERTY AND MAY
BE USED BY OTHERS ONLY AS
AUTHORIZED BY STAHLIN ENCLOSURES,
DIVISION OF ROBROY INDUSTRIES
ALL RIGHTS RESERVED
UNDER THE COPYRIGHT LAWS

SPECIAL REQUIREMENTS

NEMA 250: TYPE 1, 3, 3R, 4, 4X, 12, 13 IEC 60529: IP66 COLOR: GLACIER GRAY (WPR3013) COLOR STANDARD: PANTONE 428 C		STANDARD P/N: J2424HPL CUSTOMER DWG:		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03		.XXX ± 0.010	
MATERIAL: FIBERGLASS REINFORCED POLYESTER (FRP)				STAHLIN A DIVISION OF ROBROY INDUSTRIES Stahlin Non-Metallic Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-794-0700 Fax: 616-749-3378		DWG J2424HPL					
DRAWN BY: DRH		DATE: 12/05/2013									
SCALE DO NOT SCALE				DESCRIPTION STANDARD ENCLOSURE		PART NUMBER J2424HPL					