

Parts List ITEM QTY DESCRIPTION TOP COVER - REMOVABLE DIAGRAMATIC NAMEPLATE 2 FRONT & REAR PANEL - REMOVABLE 3 HV TERMINAL 4 LV TERMINAL



## HT45A3B2-D16

S.O. NO:

DWG FOR: RECORD APPROVAL QUOTE CUST/JOB NAME: **CUST ORDER NO:** SERIAL NO: ID TAG: KVA: 45 HIGH VOLTAGE: 480D LOW VOLTAGE: 208Y/120 HV TAPS: 2A4B 2-1/2% HV-KV BIL: 10 LV-KV BIL: 10 PHASE: SINGLE THREE FREQ-HZ: **□** 60 **□** 50 80 COOLING CLASS: AA WINDING COND: ALUMINUM COPPER PAINT/COATING: ANSI 61 LIGHT GRAY APPRX WT - LBS: 425 ☐ STANDARD

- - 2) TRANSFORMERS ARE MANUFACTURED AND TESTED PER APPLICABLE ANSI, NEMA, AND IEEE STANDARDS.
  - 3) UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES WITH ± 1/4" TOLERANCE.
  - 4) TRANSFORMER IS UL & CSA LISTED AND LABLED.
  - 5) UNIT IS DESIGNED FOR INDOOR (NEMA1) AND OUTDOOR (NEMA3R) APPLICATION.

		SCALE : N/A	PAGE 1 OF 1	3PH, 600V GENERAL PURPOSE DRY TYPE		
		CADD:		TRANSFORMER OUTLINE, CASE B (CASE 2)		
		CHKD:		MGM TRANSFORMER CO.	CAD NO.	REV:
REVISIONS		APPD:		CITY OF COMMERCE, CALIFORNIA TEL: (323) 726–0888, FAX: (323) 726–8192		