

Parts List

ITEM QTY DESCRIPTION

1 1 TOP COVER - REMOVABLE

2 1 DIAGRAMATIC NAMEPLATE

3 2 FRONT & REAR PANEL - REMOVABLE

4 3 HV TERMINAL

5 4 LV TERMINAL



HT45A3K2-D16

S.O. NO: DWG FOR: RECORD APPROVAL QUOTE CUST/JOB NAME: **CUST ORDER NO:** SERIAL NO: ID TAG: KVA: 45 HIGH VOLTAGE: 480D LOW VOLTAGE: 240D/120CT HV TAPS: 2A4B 2-1/2% HV-KV BIL: 10 LV-KV BIL: 10 PHASE: SINGLE THREE FREQ-HZ: **☑** 60 **☐** 50 □ 80 COOLING CLASS: AA WINDING COND: ALUMINUM COPPER PAINT/COATING: ANSI 61 LIGHT GRAY APPRX WT - LBS: 413 STANDARD

SCALE : N/A PAGE 1 OF 1

CADD:

CHKD:

APPD:

REVISIONS

3PH, 600V GENERAL PURPOSE DRY TYPE TRANSFORMER OUTLINE, CASE B (CASE 2)



CAD NO.

REV: