



Transformer Specifications

PRIMARY VOLTAGE(S)	208/277
SECONDARY VOLTAGE(S)	120
RATED V/A	50
RATED FREQUENCY	50/60
INSULATION CLASS	105
AGENCY APPROVALS	UL, CUL
ESTIMATED WEIGHT	2.8 LBS

TEST REQUIREMENTS


WINDING	H3-H2-H1	X2-X1
DC VOLTS	207.9-277	135.4
LOAD VOLTS	208-277	120
F.L. AMPS	0.350	0.417
HI-POT	3000V	1800V
EXCITING AMPS	0.25AMPS @ 277 VOLTS, 50HZ	
EXCITING WATTS	7.7 MAX	



NOTE:
1. ALL MEASUREMENTS IN INCHES(MM).

MAIN PRODUCT IDENTIFICATION LABEL

Culter-Hammer INDUSTRIAL CONTROL TRANSFORMER
50V/A 50/60HZ
TEMP CL. 105°C
CAT. NO. C0050E3AFB
SERIES 2
B050-2224-8
Listed 70xX



1
REVISION DT

UNLESS OTHERWISE SPECIFIED

DIMENSIONS IN INCHES	APPRO	DATE
ONE PLACE DEC	S.CASTRO	07/01/09
TWO PLACE DEC		
THREE PLACE DEC		
ANGLES	E:ROBLES	DATE
VOLTAJE		07/01/09
RESISTANCE		
FORCE/TORQUE/SPEED		
TIME		
TEMPERATURE		
DIMENSIONS BEING METRIC		
ASME Y14.5M-1994		
DIMENSIONS IN ACCORDANCE WITH		
(S) PER DRAWING 6542750		

DEPARTER/DESIGNER	DATE
S.CASTRO	07/01/09
APPD	DATE
E:ROBLES	07/01/09
APPD	DATE
O.SANDOVAL	07/01/09
ENGR REF	
ENGR REF	
NEXT ASSY	

EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY
NOTICE TO REUSE: REUSE OF THIS DOCUMENT AND/OR TECHNICAL INFORMATION IS CONFIDENTIAL AND IS THE EXCLUSIVE PROPERTY OF EATON CORPORATION. IF YOU ARE A REUSEE, YOU MUST OBTAIN WRITTEN PERMISSION FROM EATON CORPORATION TO REUSE THIS DOCUMENT. BY HAVING POSSESSION OF THIS DOCUMENT, THE REUSEE ACKNOWLEDGES AND AGREES THAT THIS DOCUMENT CANNOT BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM, WITHOUT THE WRITTEN PERMISSION OF EATON CORPORATION. THIS NOTICE SHALL GOVERN THE STATUS OF THIS DOCUMENT.

INDUSTRIAL CONTROL TRANSFORMER
DWG NO. C0050E3AFB
PARTS LIST
SCALE

PRODUCT CODE C0050E3AFB
SHEET NO 1 OF 1