

ONYX Series

LED Retrofit Downlight

Nora Lighting's new Onyx Series offers an economical quality solution to LED Retrofit Downlighting. Deep-set optics produce visual comfort in 4" and 5"/6" apertures. The Onyx produces 90+ CRI for true vibrant color rendition. Baffle and reflector styles blend with popular trims and create an uniform ceiling appearance. The 4" 650 lumen/10 watt unit is compatible with Nora's dedicated housing to meet energy rebate requirements, as well as Nora's 4" medium base housings and 4" housings by others. The 5"/6" 750 lumen/ 12 watt unit is compatible with Nora's dedicated 5" and 6" housings to meet energy rebate requirements, as well as Nora's 5" and 6" medium base housings and 5" and 6" housings by others. cULus, Energy Star and Title 24 listed, the Onyx by Nora can be used in new construction, remodel and retrofit applications. Onyx is the smart choice for energy-efficient, dimmable lighting.



Each unit includes a medium base socket

NOX-43127WW
4" Reflector, 2700K

NOX-43230WW
4" Baffle, 3000K

NOX-563130WW
5"/6" Reflector, 3000K

NOX-563227WW
5"/6" Baffle, 2700K

FEATURES

- 5 year limited warranty
- Deep set optics
- Available in 4" and 5"/6" apertures
- 90+ CRI
- 4" – 650 Lumen / 10 watt
- 5"/6" – 750 Lumen / 12 watt
- 2700K and 3000K CCT
- Baffle and Reflector styles
- White Finish
- Dimmable
- Includes Medium Base socket for easy retrofitting
- Small disconnect compatible with most dedicated housing by others.
- 36,000 Hour Life
- Energy Star rated
- cULus listed for Wet location
- Title 24 Compliant









ONYX SERIES 4" AND 5"/6" LED RETROFIT DOWNLIGHTS

ONYX SERIES 4", 5"/6" LED RECESSED RETROFIT

SERIES	APERTURE	TRIM STYLE	COLOR TEMP	FINISH
NOX- Onyx Retrofit	4 4" Aperture	31 Reflector	27 2700K	WW White with White Flange
	56 5"/6" Aperture	32 Baffle	30 3000K	

Example: **NOX-43127WW** - 4" Onyx Series LED Retrofit unit, Reflector, 2700K, White Reflector, White Flange

COMPATIBLE NORA HOUSINGS

NEW CONSTRUCTION		REMODEL	
NSIC-401QAT	4" ICAT Line Voltage	NSR-404QAT	4" AT Line Voltage
NS-401QAT	4" AT Line Voltage	NHRIC-4G24AT	4" ICAT GU24
N HIC-4G24AT	4" ICAT GU24	NHRIC-4LMRAT*	4" ICAT Dedicated LED
NHIC-4LMRAT*	4" ICAT Dedicated LED		
NHIC-4LMRAT/277*	4" ICAT Dedicated LED, 277V	NHRIC-504QAT	5" ICAT Line Voltage
 NFBIC-4INCAT	4" ICAT Fire Box	NHR-504Q	5" Line Voltage
 NFBIC-4LMRAT*	4" ICAT Dedicated LED Fire Box	NHRIC-527QAT	5" ICAT Shallow Line Voltage
		NHRIC-5G24ATFL	5" ICAT GU24
NHIC-501QAT	5" ICAT Line Voltage	NHRIC-5LMRAT*	5" ICAT Dedicated LED
NH-501Q	5" Line Voltage	NHRIC-527LMRAT*	5" ICAT Shallow Dedicated LED
NHIC-5G24ATFL	5" ICAT GU24		
NHIC-527QAT	5" ICAT Shallow Line Voltage	NHRIC-17QAT	6" ICAT Line Voltage
NHIC-5LMRAT*	5" ICAT Dedicated LED	NHRIC-17QNBAT	6" ICAT Line Volt (No Bracket)
NHIC-5LMRAT/277*	5" ICAT Dedicated LED, 277V	NHRIC-27QAT	6" ICAT Shallow Line Voltage
NHIC-527LMRAT*	5" ICAT Shallow Dedicated LED	NHR-26Q	6" Line Voltage
 NFBIC-5INCAT	5" ICAT Fire Box	NHRIC-6G24ATFL	6" ICAT GU24
 NFBIC-5LMRAT*	5" ICAT Dedicated LED Fire Box	NHRIC-6LMRAT*	6" ICAT Dedicated LED
		NHRIC-27LMRAT*	6" ICAT Shallow Dedicated LED
NHIC-17QAT	6" ICAT Line Voltage		
NHIC-17QNBAT	6" ICAT Line Volt (No Bracket)		
NHIC-27QAT	6" ICAT Shallow Line Voltage		
NH-26Q	6" Line Voltage		
NH-26QNB	6" Line Voltage (No Bracket)		
NHIC-6G24ATFL	6" ICAT GU24		
NHIC-6LMRAT*	6" ICAT Dedicated LED		
NHIC-6LMRAT/277*	6" ICAT Dedicated LED, 277V		
NHIC-27LMRAT*	6" ICAT Shallow Dedicated LED		
 NFBIC-6INCAT	6" ICAT Fire Box		
 NFBIC-6LMRAT*	6" ICAT Dedicated LED Fire Box		

* Nora LED Dedicated housings are cULus listed for use only with Nora Diamond/Cobalt/Onyx Series LED Retrofits.

**Consult factory for EM options