


INSULATED METALLIC GROUNDING BUSHINGS WITH ALUMINUM LAY-IN LUG

- 105° C. THERMOPLASTIC LINERS
 - FOR COPPER OR ALUMINUM BARE GROUND CONNECTOR
- ZINC DIE CAST**



CAT#	A	B
331	1.25	.50
332	1.50	.50
333	1.75	.56
334	2.12	.62
334A	2.12	.62
335	2.37	.75
335A	2.37	.75
336	2.81	.75
336A	2.81	.75
337	3.62	.93
337A	3.62	.93
338	4.18	.93
338A	4.18	.93
339	4.68	.93
339A	4.68	.93
340	5.25	.93
340A	5.25	.93

331M	1.25	.50
332M	1.48	.54
333M	1.80	.65
334M	2.40	.73
334AM	2.40	.73
335M	2.50	.80
335AM	2.50	.80
336M	3.03	.80
336AM	3.03	.80
337M	3.60	.95
337AM	3.60	.95
338M	4.16	1.03
338AM	4.16	1.03
339M	4.75	1.15
339AM	4.75	1.15
340M	5.30	1.17
340AM	6.15	1.30
340ALM	6.15	1.30
340BLM	7.19	1.30

331MSS	1.25	.50
332MSS	1.48	.54
333MSS	1.80	.65
334MSS	2.40	.73
335MSS	2.50	.80
336MSS	3.03	.80
337MSS	3.60	.95
338MSS	4.16	1.03
339MSS	4.75	1.15
340MSS	5.30	1.17
340AMSS	6.15	1.30
340BMSS	7.19	1.30

GROUNDING LUG

TOPAZ CAT #	UPC#	SIZE	WIRE SIZE MIN MAX	UNIT CTN	SHIP CASE	WT/ CASE
331	13130	1/2"	14 4	50	500	30
332	13140	3/4"	14 4	50	500	35
333	13150	1"	14 4	25	250	23
334	13160	1 1/4"	14 4	20	200	26
334A	13170	1 1/4"	14 1/0	20	200	26
335	13180	1 1/2"	14 4	10	100	16
335A	13190	1 1/2"	14 1/0	10	100	16
336	13200	2"	14 4	10	100	21
336A	13210	2"	14 1/0	10	100	21
337	13220	2 1/2"	14 1/0	—	50	20
337A	13230	2 1/2"	6 250 MCM	—	50	20
338	13240	3"	14 1/0	—	50	29
338A	13250	3"	6 250 MCM	—	50	29
339	13260	3 1/2"	14 1/0	—	10	15
339A	13270	3 1/2"	6 250 MCM	—	10	15
340	13280	4"	14 1/0	—	10	20
340A	13290	4"	6 250 MCM	—	10	20

MALLEABLE IRON

331M	13300	1/2"	14 4	50	500	45
332M	13310	3/4"	14 4	50	500	50
333M	13320	1"	14 4	25	250	40
334M	13330	1 1/4"	14 4	20	200	35
334AM	13340	1 1/4"	14 1/0	20	200	35
335M	13350	1 1/2"	14 4	10	100	25
335AM	13360	1 1/2"	14 1/0	10	100	25
336M	13370	2"	14 4	10	100	30
336AM	13380	2"	14 1/0	10	100	30
337M	13390	2 1/2"	14 1/0	—	50	25
337AM	13400	2 1/2"	6 250 MCM	—	50	25
338M	13410	3"	14 1/0	—	25	18
338AM	13420	3"	6 250 MCM	—	25	18
339M	13430	3 1/2"	14 1/0	—	10	20
339AM	13440	3 1/2"	6 250 MCM	—	10	20
340M	13450	4"	14 1/0	—	10	25
340AM	13460	4"	6 250 MCM	—	10	25
340ALM	13462	5"	6 250 MCM	—	10	25
340BLM	13463	6"	6 250 MCM	—	10	35

SET SCREW NO THREAD

331MSS	13321	1/2"	14 4	50	500	25
332MSS	13331	3/4"	14 4	50	500	30
333MSS	13341	1"	14 4	25	250	23
334MSS	13351	1 1/4"	14 4	20	200	30
335MSS	13361	1 1/2"	14 4	10	100	25
336MSS	13371	2"	14 4	10	100	30
337MSS	13391	2 1/2"	14 1/0	5	50	38
338MSS	13411	3"	14 1/0	—	25	35
339MSS	13431	3 1/2"	14 1/0	—	10	15
340MSS	13451	4"	14 1/0	—	10	20
340AMSS	13461	5"	6 250MCM	—	10	25
340BMSS	13471	6"	6 250MCM	—	10	35



E195122



E195122



E195122