



Locking-Type Mounting, Thermal Type — K4500 Series

Easy to install; just plug in and twist. This series is equipped with standard 3-prong NEMA locking-type plug connections. Incorporates K4000 style thermal switch for reliable long life performance. Complies with ANSI C136.10.

Size – 3-3/4" (9.5 cm) High, 3" (7.6 cm) Diameter.

Model #	Watts Tungsten	VA Ballast	Amps Tungsten	Amps Ballast	Volts
K4521	1800	1000	15	8.3	120
K4524**	3100	1700	15	8.3	208
K4522	3600	2000	15	8.3	240
K4533**	4100	2300	15	8.3	277
K4535**	7200	4000	15	8.3	480

* Ballast rating meets UL testing at 50% power factor.

** Not CSA certified.



UL773
E59121



C22.2-177
LR38068



3/4 lbs
.34 kg



5 Year
Warranty

Accessories for Locking-Type Controls

Pole Bracket Adapter – Model K122 - 105 to 480 Volts; for use with K1200, K4500 or LC4500 Series locking-type controls. K121 – receptacle only, K121-30 receptacle with 30 inch leads.

Shorting Cap – Model K4500 - 105 to 480 Volts; replaces locking-type photo control to complete circuit.



Low Cost Locking-Type, Thermal Type — LC4500 Series

The LC4500 Series provides low cost reliable control for street lighting and other applications requiring a NEMA twist and lock type plug connection. An integral housing and lens, with UV protection, keeps moisture out and ensures long life. Complies with ANSI C136.10.

Activation – .5 FC minimum "ON"; 15 FC maximum "OFF".

Size – 2-3/4" (7.0 cm) High, 3" (7.6 cm.) Diameter.

Color – Translucent with color coded band for voltage identification.

Model #	Watts Tungsten	VA Ballast	Volts
LC4521C	1000	1000	120
LC4523	1700-2300	1700-2300	208-277
LC4527	5205	2880	347
LC4535**	7200	4000	480
LC4536C	1000-2300	1000-2300	120 or 208-277
LC4521LA	1000	1000	120
LC4523LA	1700-2300	1700-2300	208-277
LC4535LA**	7200	4000	480
LC4536LAC	1000-2300	1000-2300	120 or 208-277

LA Models equipped with 2400 volt open type spark gap arrester.

* Ballast rating meets UL testing at 50% power factor.

** Not CSA certified.



UL773
E59121



C22.2-55
LR38068



2 lbs
.09 kg



3 Year
Warranty



K4521



K122



K4500



K121
K121-30



LC4521C