

28-Piece Electrician Tool Set



80028

Cat. No.	Set Contains	Weight (lbs.)
80028		17.2
Cat. No.	Description	
D203-8	heavy-duty long-nose pliers – side-cutting	
D213-9NETP	high-leverage side-cutting pliers – fish tape pulling	
D248-8	high-leverage diagonal-cutting pliers – angled head	
D502-10	10" pump pliers with 1-3/4" (44 mm) jaw capacity	
506-10	10" adjustable wrench – standard capacity	
600-4	1/4" keystone-tip cushion-grip screwdriver – 4" (102 mm) heavy-duty square-shank	
601-6	3/16" cabinet-tip cushion-grip screwdriver – 6" (152 mm) round-shank	
602-6	5/16" keystone-tip cushion-grip screwdriver – 6" (152 mm) heavy-duty round-shank	
603-4B	wire bending No. 2 Phillips cushion-grip screwdriver – 4" (102 mm) round-shank	
605-6	1/4" cabinet-tip screwdriver – 6" (152 mm) heavy-duty round-shank	
631	7-piece cushion-grip nut driver set (3/16", 1/4", 5/16", 11/32", 3/8", 7/16", 1/2")	
662	No. 2 square-recess tip cushion-grip screwdriver – 4" (102 mm) round-shank	
670-6	3/16" cabinet-tip cushion-grip screwdriver – Rapi-Driv®	

Cat. No.	Description
93025	25' x 1" tape measure
930-9	magnetic torpedo level
1005	crimping/cutting tool – non-insulated and insulated connectors
5102-16	16" canvas tool bag
5139	canvas zipper bag
11045	wire stripper/cutter – 10-18 AWG solid wire
44100	utility knife – retractable blade
60056	frameless protective eyewear
85191	conduit-fitting and reaming screwdriver

All dimensions are in inches and (millimeters) unless otherwise specified.

▲WARNING: The tool belt provided in this kit is NOT an occupational protective belt.

▲WARNING: NOT insulated. Do NOT use these tools on or near live electrical circuits.

▲WARNING: Do NOT use screwdrivers to pry or chisel.

▲WARNING: Always wear approved eye protection.

▲WARNING: Do NOT open the tape measure case. Spring motor is under tension, and opening may cause injury.

