



Friendly Service... Powerful Solutions


Topaz Specification Sheet

Description: Set Screw Conduit Bodies for EMT - EMT LB Type

Standard Material: Aluminum Die Cast Copper Free
Steel Screw

Features: Suitable for use in concrete.

Application: To provide access to conductors for pulling, slicing
and maintenance



TOPAZ CAT #	A	B	C	Max No. Conductors
ELB1	4.295	2.150	1.330	1 #6AWG
ELB2	5.090	2.430	1.540	2 #6AWG
ELB3	5.915	2.765	1.740	3 #6AWG
ELB4	7.894	3.665	2.490	3 #2AWG
ELB5	7.894	3.665	2.490	3 #2AWG
ELB6	10.134	4.275	3.100	3 #2/OAWG
ELB7	12.500	5.437	4.450	3 #2/OAWG
ELB8	12.500	5.657	4.450	3 #4/OAWG
ELB9	15.500	6.922	5.500	3 #500MCM
ELB10	15.500	6.922	5.500	3 #500MCM

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
ELB1	20470	1/2"	10	100	28
ELB2	20480	3/4"	10	50	19
ELB3	20490	1"	5	25	20
ELB4	20500	1 1/4"	2	10	13
ELB5	20510	1 1/2"	2	10	14
ELB6	20520	2"	1	5	13
ELB7	20530	2 1/2"	-	1	6
ELB8	20540	3"	-	1	6
ELB9	20550	3 1/2"	-	1	8
ELB10	20560	4"	-	1	8

Approved by Quality Control: John Cavalieri



NEW YORK
925 Waverly Avenue
Holtsville, NY 11742
800-666-2852
Fax: 800-333-3488

CALIFORNIA
225 Parkside Drive
San Fernando, CA 91340
888-551-2852
Fax: 888-690-2852

FLORIDA
2020 West 26th Street
Jacksonville, FL 32209
800-666-2852
Fax: 800-333-3488




Topaz Specification Sheet

Description: Set Screw Conduit Bodies for EMT - EMT LL Type

Standard Material: Aluminum Die Cast Copper Free Steel Screw

Features: Suitable for use in concrete.

Application: To provide access to conductors for pulling, slicing and maintenance



TOPAZ CAT #	A	B	C	Max No. Conductors
ELL1	4.295	1.370	2.030	1 #6AWG
ELL2	5.090	1.625	2.330	2 #6AWG
ELL3	5.915	1.900	2.650	3 #6AWG
ELL4	7.894	2.770	3.385	3 #2AWG
ELL5	7.894	2.770	3.385	3 #2AWG
ELL6	10.134	3.335	3.810	3 #2/0AWG
ELL7	12.500	5.437	4.450	3 #4/0AWG
ELL8	12.500	5.657	4.450	3 #250MCM
ELL9	15.500	6.922	5.500	3 #350MCM
ELL10	15.500	6.922	5.500	4 #350MCM

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
ELL1	20570	1/2"	10	100	30
ELL2	20580	3/4"	10	50	23
ELL3	20590	1"	5	25	18
ELL4	20600	1 1/4"	2	10	14
ELL5	20610	1 1/2"	2	10	16
ELL6	20620	2"	1	5	14
ELL7	20621	2 1/2"	-	1	6
ELL8	20622	3"	-	1	6
ELL9	20623	3 1/2"	-	1	8
ELL10	20624	4"	-	1	8

Approved by Quality Control: John Cavalieri



NEW YORK
925 Waverly Avenue
Holtsville, NY 11742
800-666-2852
Fax: 800-333-3488

CALIFORNIA
225 Parkside Drive
San Fernando, CA 91340
888-551-2852
Fax: 888-690-2852

FLORIDA
2020 West 26th Street
Jacksonville, FL 32209
800-666-2852
Fax: 800-333-3488



Friendly Service ... Powerful Solutions


Topaz Specification Sheet

Description: Set Screw Conduit Bodies for EMT - EMT LR Type

Standard Material: Aluminum Die Cast Copper Free Steel Screw

Features: Suitable for use in concrete.

Application: To provide access to conductors for pulling, slicing and maintenance



TOPAZ CAT #	A	B	C	Max No. Conductors
ELR1	4.295	1.370	2.030	1 #6AWG
ELR2	5.090	1.625	2.330	2 #6AWG
ELR3	5.915	1.900	2.650	3 #6AWG
ELR4	7.894	2.770	3.385	3 #2AWG
ELR5	7.894	2.770	3.385	3 #2AWG
ELR6	10.134	3.335	3.810	3 #2/OAWG
ELR7	12.500	5.437	4.450	3 #4/OAWG
ELR8	12.500	5.657	4.450	3 #250MCM
ELR9	15.500	6.922	5.500	3 #350MCM
ELR10	15.500	6.922	5.500	4 #350MCM

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
ELR1	20630	1/2"	10	100	30
ELR2	20640	3/4"	10	50	24
ELR3	20650	1"	5	25	16
ELR4	20660	1 1/4"	2	10	14
ELR5	20670	1 1/2"	2	10	17
ELR6	20680	2"	1	5	14
ELR7	20681	2 1/2"	-	1	6
ELR8	20682	3"	-	1	6
ELR9	20683	3 1/2"	-	1	8
ELR10	20684	4"	-	1	8

Approved by Quality Control: John Cavalieri



NEW YORK
925 Waverly Avenue
Holtsville, NY 11742
800-666-2852
Fax: 800-333-3488

CALIFORNIA
225 Parkside Drive
San Fernando, CA 91340
888-551-2852
Fax: 888-690-2852

FLORIDA
2020 West 26th Street
Jacksonville, FL 32209
800-666-2852
Fax: 800-333-3488



Friendly Service... Powerful Solutions


Topaz Specification Sheet

Description: Set Screw Conduit Bodies for EMT - EMT C Type

Standard Material: Aluminum Die Cast Copper Free Steel Screw

Features: Suitable for use in concrete.

Application: To provide access to conductors for pulling, slicing and maintenance



TOPAZ CAT #	A	B	C	Max No. Conductors
EC1	4.720	1.370	1.330	1 #6AWG
EC2	5.570	1.625	1.540	2 #6AWG
EC3	6.460	1.900	1.740	3 #6AWG
EC4	8.528	2.770	2.490	3 #2AWG
EC5	8.528	2.770	2.490	3 #2AWG
EC6	10.831	3.335	3.100	3 #2/OAWG
EC7	13.00	4.063	5.709	3 #4/OAWG
EC8	12.50	4.682	5.506	3 #250MCM
EC9	15.50	5.452	6.171	3 #350MCM
EC10	15.50	5.452	6.171	4 #350MCM

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
EC1	20410	1/2"	10	100	24
EC2	20420	3/4"	10	50	21
EC3	20430	1"	5	25	25
EC4	20440	1 1/4"	2	10	15
EC5	20450	1 1/2"	2	10	17
EC6	20460	2"	1	5	13
EC7	20461	2 1/2"	-	1	6
EC8	20462	3"	-	1	7
EC9	20463	3 1/2"	-	1	8
EC10	20464	4"	-	1	8

Approved by Quality Control: John Cavalieri



NEW YORK
925 Waverly Avenue
Holtsville, NY 11742
800-666-2852
Fax: 800-333-3488

CALIFORNIA
225 Parkside Drive
San Fernando, CA 91340
888-551-2852
Fax: 888-690-2852

FLORIDA
2020 West 26th Street
Jacksonville, FL 32209
800-666-2852
Fax: 800-333-3488



Friendly Service... Powerful Solutions


Topaz Specification Sheet

Description: Set Screw Conduit Bodies for EMT - EMT T Type

Standard Material: Aluminum Die Cast Copper Free Steel Screw

Features: Suitable for use in concrete.

Application: To provide access to conductors for pulling, slicing and maintenance



TOPAZ CAT #	A	B	C	Max No. Conductors
ET1	4.720	1.370	2.030	1 #6AWG
ET2	5.570	1.625	2.335	2 #6AWG
ET3	6.460	1.900	2.705	3 #6AWG
ET4	8.528	2.770	3.630	3 #2AWG
ET5	8.528	2.770	3.630	3 #2AWG
ET6	10.831	3.335	3.980	3 #2/OAWG
ET7	13.500	4.060	5.825	3 #4/OAWG
ET8	13.500	4.685	5.825	3 #250MCM
ET9	15.937	5.450	7.060	3 #350MCM
ET10	15.937	5.450	7.060	4 #350MCM

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
ET1	20690	1/2"	10	100	32
ET2	20700	3/4"	10	50	30
ET3	20710	1"	5	25	15
ET4	20720	1 1/4"	2	10	17
ET5	20730	1 1/2"	2	10	19
ET6	20740	2"	-	2	5
ET7	20781	2 1/2"	-	1	7
ET8	20782	3"	-	1	7
ET9	20783	3 1/2"	-	1	9
ET10	20784	4"	-	1	9

Approved by Quality Control: John Cavalieri



NEW YORK
925 Waverly Avenue
Holtsville, NY 11742
800-666-2852
Fax: 800-333-3488

CALIFORNIA
225 Parkside Drive
San Fernando, CA 91340
888-551-2852
Fax: 888-690-2852

FLORIDA
2020 West 26th Street
Jacksonville, FL 32209
800-666-2852
Fax: 800-333-3488