



Sealtite Type EFST: Extra Flexible Conduit

Trade Size	Item ID	Std. Pkg. M (FT)	Inside Diameter Min	Outside Diameter Min / Max		Bend Diameter	Weight Kg/m (lbs/cft)
1/4"	35983	30 (100)	6.22 (0.245)	11.30 (0.445)	11.68 (0.460)	89 (3.5)	0.21 (14)
	35981	152 (500)					
5/16" (10)	35993	30 (100)	9.91 (0.390)	14.22 (0.560)	14.61 (0.575)	102 (4.0)	0.22 (15)
	35991	152 (500)					
3/8" (12)	36202	30 (100)	12.32 (0.485)	17.53 (0.690)	18.03 (0.710)	101 (4.0)	0.31 (21)
1/2" (16)	36212	30 (100)	15.75 (0.620)	20.83 (0.820)	21.34 (0.840)	127 (5.0)	0.37 (25)
3/4" (21)	36222	30 (100)	20.70 (0.815)	26.16 (1.030)	26.67 (1.050)	152 (6.0)	0.58 (39)
1" (27)	36231	30 (100)	26.16 (1.030)	32.77 (1.290)	33.40 (1.315)	203 (8.0)	0.76 (51)
1-1/4" (35)	36241	15 (50)	34.80 (1.370)	41.53 (1.635)	42.16 (1.660)	229 (9.0)	0.98 (66)
1-1/2" (41)	36251	15 (50)	40.01 (1.575)	47.37 (1.865)	48.26 (1.900)	279 (11.0)	1.55 (104)
2" (53)	36261	15 (50)	51.31 (2.020)	59.44 (2.340)	60.33 (2.375)	355 (14.0)	2.02 (136)
2-1/2"	34272	7.6 (25)	62.99 (2.480)	72.14 (2.840)	73.03 (2.875)	482 (19.0)	2.71 (182)
3"	34281	7.6 (25)	77.98 (3.070)	87.88 (3.460)	88.90 (3.500)	762 (30.0)	3.79 (255)
3-1/2"	34301	7.6 (25)	88.90 (3.500)	100.58 (3.960)	101.60 (4.000)	813 (32.0)	4.67 (314)
4"	36291	7.6 (25)	101.60 (4.000)	113.28 (4.460)	114.30 (4.500)	864 (34.0)	5.40 (363)
5"	36351	7.6 (25)	126.37 (4.975)	139.83 (5.505)	141.35 (5.565)	1118 (44.0)	7.94 (534)
6"	36361	7.6 (25)	152.78 (6.015)	166.75 (6.565)	168.28 (6.625)	1524 (60.0)	9.91 (666)

All dimensions in mm (inches)



Square Lock Profile with cord packing 1/4" thru 1-1/4"



Interlocked Profile 1-1/2" thru 6"

Sealtite Type EFST:

RoHS

- Flexible metal core liquid-tight conduit
- Designed for applications where no approvals are required.
- Also available in Black by special order.
- Uses standard liquid-tight connectors for easy installation.
- Available in custom cut lengths

For connectors for this conduit, see page 19-20
 For cutting instructions, see page 37
 For Chemical Resistance, see page 38

SPECIFICATIONS:

- Galvanized steel core with Liquid-tight PVC jacket
- Colour: Grey (1/4" and 5/16" standard colour Black)
- Temp. range: -20°C to +60°C (-4°F to +140°F)
- UV (sunlight) Resistant
- Corrosion Resistant

APPLICATIONS:

- Applications where very small ID liquid-tight is required (ie: 1/4")
- Applications where no approvals are required.