


HR2LEDT309P

2" Tesla™ Pro LED 0°-30° Adjustable Trim

WAC LIGHTING

Responsible Lighting®



Fixture Type:

Catalog Number:

Project:

Location:

PRODUCT DESCRIPTION

Minimum profile, round 0° to 30° adjustable trim with interior open reflector.

FEATURES

- 2" aperture
- Energy Star® rated
- CEC Title 24 Compliant (see below for list of models)
- Damp location listed
- 30° visual cutoff angle for glare control
- Adjustable fixtures are ideal for sloped ceiling applications
- 5 year WAC Lighting product warranty

SPECIFICATIONS

Construction: Durable die-cast aluminum construction with borosilicate glass lens. Extruded aluminum heat sink.

Light Source: Utilizes one 14.5W LED, CRI: 85 & 90+


Dimming: 0-10V Dimming: 100%-10%
ELV Dimming: 100%-15% (120V only)

Mounting: Two heavy gauge retention clips hold trim firmly to housing

Finish: White (WT) powder coat paint and electroplated Brushed Nickel (BN) and Copper Bronze (CB).

Standards: ETL & cETL Listed. See table below for Energy Star® and 2013 California Title 24 qualifying products.

TRIMS

Model#	Beam	Color Temp	CRI	Lumens	CBCP	Energy Star®	2013 Title 24	Finish
HR2LEDT309P 0°-30° Adjustable	N 27°	827 2700K	85	780	2020	Yes	No	BN Brushed Nickel CB Copper Bronze WT White 
		927 2700K	90	635	1619	Yes	No	
		830 3000K	85	810	2044	Yes	No	
		930 3000K	90	730	1924	Yes	Yes	
		835 3500K	85	875	2227	Yes	No	
	840 4000K	85	895	2332	Yes	No		
	F 40°	827 2700K	85	750	1315	Yes	No	
		927 2700K	90	610	1038	Yes	No	
		830 3000K	85	785	1371	Yes	No	
		930 3000K	90	695	1181	Yes	Yes	
		835 3500K	85	840	1458	Yes	No	
	840 4000K	85	865	1507	Yes	No		

HR2LEDT309P

Example: HR2LEDT309PF835BN

COMPATIBLE HOUSINGS See individual housing spec sheets for complete information.

REPLACEMENT MODULES

New Construction

HR-2LED-H09D-ICA IC-Rated, Airtight 120V-277V	HR-2LED-H09D-ICAC IC-Rated, Airtight Chicago Plenum 120V-277V
--	---

Reflectors

Narrow Flood Flood	SL-REF-BL10-1-N SL-REF-BL10-1-F
-----------------------	--

Remodel

HR-2LED-R14D Non-IC 120V-277V
--

LED

2700K	85 CRI	BXRC-27E1000-B-03
2700K	90 CRI	BXRC-27G1000-B-03
3000K	85 CRI	BXRC-30E1000-B-03
3000K	90 CRI	BXRC-30G1000-B-03
3500K	85 CRI	BXRC-35E1000-B-03
4000K	85 CRI	BXRC-40E1000-B-03

wacighting.com

Phone (800) 526.2588

Fax (800) 526.2585

Headquarters/Eastern Distribution Center

44 Harbor Park Drive

Port Washington, NY 11050

Central Distribution Center

1600 Distribution Ct

Lithia Springs, GA 30122

Western Distribution Center

1750 Archibald Avenue

Ontario, CA 91760