

# Malleable Iron Straight Liquidtight Connectors

## For Liquidtight Flexible Metallic Conduit

### Application:

To secure, ground and seal Liquidtight Flexible Metal conduit, to boxes and enclosures

### Features:


- Tapered threaded male hub NPT
- Compact, slim diameter with small turning radius
- Furnished with an insulated throat with steel locknut and sealing ring
- Liquidtight/Raintight/Oiltight
- Suitable for wet locations
- Long ferrule prevents pullout and tight bend conduit "pop-out"
- UL Listed liquidtight flexible metal conduit fittings are suitable for use in the following Hazardous Locations under NEC 501-4(b), 502-4(a)(2); Class I, Div.2; Class II, Div. 1 and 2; and Class III, Div. 1 and 2 and are suitable for grounding in sizes 3/8" through 1-1/2" under NEC 351-1

### Standard Materials:

Malleable Iron/Steel Ferrule


### Standard Finish:

Zinc Plated

 **UL Listed:**  
US E198258



TYPE SLT27T



## All Furnished with Insulated Throats

CATALOG NUMBER	TRADE SIZE	KO SIZE	DIM A	DIM B	DIM C	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100	NAED MFG #78-5994 UPC/DCI #
SLT47T	3/8"	1/2"	1.140	0.500	1.150	25	250	16	14419
SLT27T	1/2"	1/2"	1.250	0.500	1.280	25	250	18	14630
SLT28T	3/4"	3/4"	1.280	0.520	1.550	10	100	29	14640
SLT29T	1"	1"	1.430	0.650	1.800	5	50	40	14650
SLT30T	1-1/4"	1-1/4"	1.500	0.660	2.250	5	50	56	14309
SLT31T	1-1/2"	1-1/2"	1.610	0.730	2.440	10	50	71	14319
SLT32T	2"	2"	1.760	0.750	2.970	5	25	100	14329
SLT33T	2-1/2"	2-1/2"	2.180	1.010	4.010	1	10	367	14339
SLT34T	3"	3"	2.500	1.150	4.180	1	10	461	14349
SLT60T	3-1/2"	3-1/2"	2.610	1.180	5.250	1	10	675	14609
SLT61T	4"	4"	2.740	1.250	5.780	1	5	797	14619
SLT62T	5"	5"	3.125	1.500	6.063	-	1	1047	78062
SLT63T	6"	6"	3.375	1.563	7.500	-	1	1381	60001

