


OUTDOOR



HINKLEY®



"When selecting outdoor lighting, I think you really need to stay true to the style of the house and choose lighting that is in the same vein. I don't think outdoor lighting is the place to be eclectic."

RYAN KORBAN, RYAN KORBAN
NEW YORK CITY

MIDNIGHT IN THE GARDEN

Before selecting outdoor lighting, consider the key architectural and landscaping elements of your home. By adding different sources of light at varying heights, your exterior will come alive at night.

Fixture shown on page 403: Shelter 1321 KZ, page 457
Fixtures shown here: Trellis 1435 RB, page 567 and Hardy Island path lights 16007 MZ (Hinkley Landscape Lighting Catalog).

WHY STOP AT THE FRONT DOOR? Make a lighting statement while increasing the usability of porches, patios and decks by adding chic outdoor lanterns that reflect your home as well as your personal style. From Colonial to Contemporary to Cape Cod, have fun discovering how different designs can energize your exterior.

FIXTURE FUSION

“Think of the exterior fixtures on your home like jewelry on a person. It should enhance and complete the ensemble. It can either reinforce the architectural style of the home, or provide a hint towards what you will discover inside. Proper illumination adds visual balance and when executed properly and with quality products, reflects a homeowner’s attention to detail. I’m starting to see more of a fusion of styles now, with experimentation between traditional architecture and modern fixtures. It is a delicate balance to strike, but magnificent when it works!”

LISA McDENNON, LISA McDENNON DESIGN
LAGUNA BEACH, CA



Fixtures shown: Pembroke 2084 SB, page 462 and Mondrian 4571 KZ, page 107

“The exterior of your home is the first thing guests see so it’s important to address it and make sure it gives a good impression. Is it welcoming? Is the lighting well-placed so people approaching can safely enter and leave your home? Is it attractive? All of these are important questions to ask about your outdoor lighting.”

MONA ROSS BERMAN, MONA ROSS BERMAN INTERIORS
PHILADELPHIA, PA

LIGHT HOUSE

“Consistency in the style of fixtures unifies your landscape plan and defines your property, making it easier for visitors to find and approach your home. The post light serves as a welcoming beacon, the primary fixture announcing your home’s presence, so it’s appropriate that it set a style tone for the rest of the property.”

AMY ELBERT, SENIOR ARCHITECTURE EDITOR
TRADITIONAL HOME



Fixtures shown: Atlantis 1641 BZ, page 423
Atlantis path lights 1518 BZ-LED (Hinkley Landscape Lighting Catalog).



66"
Standard
suggested height
from center of light
bulb to threshold

"Exterior lighting provides a warm welcome and guides visitors safely up walkways and into your home. It leads people from the natural environment into the comforts of your home and should do so in an inviting and seamless way."

AMY ELBERT, SENIOR ARCHITECTURE EDITOR
TRADITIONAL HOME

Fixtures shown: Bingham 2045 SN, page 518



1 - 
LANTERN
 should measure
 1/3 the height of
 the door

 - 2 - 
LANTERNS
 should measure
 1/4 the height of
 the door

PERFECT FIT

Fixtures shown: Revere 1184 SN, page 517

"When choosing decorative fixtures, consider the architectural style of your home and the interior design elements you wish to complement. Fixtures should be appropriate to the time period the house was built and its overall styling, whether Arts & Crafts or Colonial or Modern. Consider scale as well, making sure that the fixture is in proper proportion to the space it is illuminating and nearby architectural elements such as corbels and doors."

AMY ELBERT, SENIOR ARCHITECTURE EDITOR
 TRADITIONAL HOME

Sizing Guidelines

OUTDOOR LANTERNS

Selecting the right-sized outdoor lantern can sometimes pose a challenge. Follow these sizing guidelines for a fit that's just right.

The height of an outdoor lantern should be based on the height of the door:

DON'T UNDERSIZE YOUR LANTERNS: As a rule of thumb, your lanterns should appear to be proportionate to the size of your door from 50' away.

FOR 1 LANTERN: If you place a lantern on only one side of the door, it should measure one-third the height of the door. The center of the bulb should rest 66" above the threshold of the door.

FOR 2 LANTERNS: When two lanterns are used, they should each measure approximately one-fourth the height of the door. The center of the bulb should rest 66" above the threshold of the door.

TIP: In either case, if you choose a fixture with a long tail or top scroll, pay attention to the overall bulk of the fixture.

TIP: When in doubt, always go larger.



AMERICAN BEAUTY

STYLE GUIDE OUTDOOR

All-American beauty never goes out of style with timeless designs and patriotic details.

1



2



3



4



Create a salute to style in your outdoor space with classic elements, traditional touches and crisp colors topped off with a touch of whimsy.

- BOLD MIXES OF TEXTURE
- MODERN LINES
- CRISP COLORS
- COMFORTABLE UPHOLSTERED FURNITURE
- TUFTING AND CONTRAST PIPING
- TOUCHES OF LUCITE
- STRIPES & CHEVRONS

OUR LIGHTING SUGGESTIONS:

1. YORK Outdoor Collection
1845 BK; Pages 520-521

2. FREEPORT Outdoor Collection
1802 OP; Page 464-467
Additional finishes available.

3. LIBERTY Outdoor Collection
2174 SN; Pages 502-503
Additional finishes available.

4. SULLIVAN Outdoor Collection
1745 HE; Pages 458-459
Additional finishes available.





“Create spaces that are pulled together yet informal in feel with a strong, specific color palette and fun patterns.”

MONA ROSS BERMAN
MONA ROSS BERMAN INTERIORS
PHILADELPHIA, PA

"Outdoor living has become very important to our clients and now we are adding in very comfortable seating, upholstery, rugs and artwork just to name a few. These pieces accent our outdoor spaces and make them useful year round. I love to line up a few lanterns over a dining area or sitting area in covered loggias. I think it is a gift to be outside enjoying additional living spaces in this way day and night."

CHRISTINA FLUEGGE
GREIGE DESIGN
SAN JOSE, CA

MAXIN' & RELAXIN'

"WE RECENTLY WORKED ON A BACK PATIO AREA FOR A CLIENT WHO WANTED FUN LIGHTING AND POPS OF COLOR. I THINK YOUR OUTDOOR SPACE SHOULD BE A FUN DESTINATION AND DOES NOT HAVE TO BE TOO SERIOUS. IT'S A GREAT PLACE TO STEP OUTSIDE OF THE BOX AND I THINK CLIENTS ARE REALLY STARTING TO GET THAT."

MONA ROSS BERMAN, MONA ROSS BERMAN INTERIORS
PHILADELPHIA, PA

Fixtures shown: Aria 2305 KZ and 2302 KZ, page 450-451 and Luna 1664 BZ, page 441.

FRESH AIR FUND With our busy lives and persistent use of technology, now more than ever it's important to take the time to unplug. Re-connect with life's simple pleasures by extending your home's living spaces into the outdoors, meshing creature comforts with natural beauty.

"Using our outdoor spaces as an extension of our home and creating rooms outside, the lighting needs are going to be slightly different than inside the home. Can you see the way to the seating area in the dark if you're entertaining? Do we have proper task lighting? Comfort as well as safety is upped with layers of outdoor lighting!"

SARAH SWANSON
SARAH SWANSON DESIGN
CALGARY, ALBERTA CANADA



1.



2.



3.

"Think even beyond lighting patios and spaces immediately outside your house—light trees (trunks and branches) or vine-wrapped trellises in far corners of your yard. These accents coax guests outdoors and create magical settings for entertaining and relaxing."

AMY ELBERT
SENIOR ARCHITECTURE EDITOR
TRADITIONAL HOME



4.

"Living in Los Angeles with amazing weather year round, outdoor spaces become a continuation of the indoors. I look at outdoor spaces the same way I do indoor rooms and lighting is crucial to the overall mood of the space."

TAMARA KAYE-HONEY
HOUSE OF HONEY
LOS ANGELES



5.

"Having a residence in Arizona where the sunsets are spectacular, to living in Manhattan and having views of the city at night makes outdoor living spaces absolutely as important as the indoor ones. I incorporate seating areas that really are like living rooms except outdoors."

JAMIE HERZLINGER
JAMIE HERZLINGER INTERIORS
NEW YORK CITY & SCOTTSDALE, AZ

Fixtures shown: 1. Fredrick Ramond's Zen FR46204BAM, page 305 2. Shelter 1325 BK, page 454 3. Shelter Path Lights 1547 KZ (Hinkley Landscape Lighting Catalog) 4. Barrington 1752 VZ, page 571 5. Ledgewood 1129 MR, page 480

IDEA
 CENTER
 VISIT US AT HINKLEYLIGHTING.COM FOR
 MORE LIGHTING TIPS, DESIGNER IDEAS
 AND STYLE GUIDES.

Hinkley is proud to offer a wide variety of lighting options that meet vital environmental guidelines while simultaneously giving homeowners energy-efficient, fashion-forward styles. Check out our "Eco-Options" throughout the Outdoor section.



E C O C H I C

"ENERGY EFFICIENCY AND ENVIRONMENTAL CONCERNS ARE IMPORTANT TO TODAY'S HOMEOWNERS, AND WILL CONTINUE TO BE SO AS NEW TECHNOLOGIES EVOLVE. OUTDOOR LIGHTING OFTEN REMAINS ON OVERNIGHT AND FOR LONG STRETCHES OF TIME, SO CHOOSING THE MOST ENERGY-EFFICIENT SYSTEMS ARE A PRIORITY."

AMY ELBERT, SENIOR ARCHITECTURE EDITOR
 TRADITIONAL HOME

1. Luna 1664 TT, page 441 2. Atlantis 1684 TT, page 425 3. Aria 2304 KZ, page 451 4. Cedar Hill 1985 BK, page 541
 5. Pembroke 2084 SB, page 426 6. Surf 2355 SS, page 414 7. District 2114 TT, page 421 8. Freeport 1805 OZ, page 464
 9. Shelter 1325 KZ, page 456 10. Cascade 1830 BZ, page 433 11. Randolph 1495 AM, page 536 12. Harbor 2579 TT, page 468.

INTELLIGENT LIGHTING Hinkley is dedicated to staying at the forefront of technology, utilizing the latest expertise and components so we can continue to serve as protective stewards of our environment. Look for the following icons throughout the Hinkley Outdoor section to identify our Eco-Options:

DARK SKY

SELECT HINKLEY OUTDOOR LANTERNS COME STANDARD DARK SKY COMPLIANT. ADDITIONAL ITEMS INDICATED AS SUCH CAN BE FITTED WITH THE LED DSL-40 TO CONVERT TO DARK SKY.
(Specs below)

GU24

WHEN ORDERING HINKLEY OUTDOOR LANTERNS WITH -GU24, THE LANTERN WILL COME STANDARD WITH A GU24 SOCKET THAT WILL ACCEPT COMPACT FLUORESCENT BULBS (NOT INCLUDED). THESE ITEMS CAN ALSO BE FITTED WITH THE LED DSLG-40 TO CONVERT TO LED. ONLY ITEMS INDICATED AS SUCH WILL BECOME DARK SKY COMPLIANT WHEN FITTED WITH THIS BULB.
(Specs below)

LED

WHEN ORDERING HINKLEY OUTDOOR LANTERNS WITH -LED, THE LANTERN WILL COME STANDARD WITH AN INTEGRATED LED ENGINE.
(Specs below)



00GU2413



00GU2418



00GU2426



EB-04A



DSLG-40



DSLM-40



COL-35



UNI-60™
UNI-75™
UNI-100™

U.S. Patent Pending

LAMPS Available to Purchase

| ITEM | DESCRIPTION | LUMENS | COLOR TEMP. | CRI | WATTS CONSUMED | INCANDESCENT EQUIVALENCY | DIMMABLE | LIFESPAN |
|----------|-------------------------------------|--------|-------------|-----|----------------|--------------------------|----------|-------------|
| 00GU2413 | 13w Compact Fluorescent Spiral Bulb | 850 | 2700k | 80 | 13w | 60w | | 10,000 Hrs. |
| 00GU2418 | 18w Compact Fluorescent Spiral Bulb | 1380 | 2700k | 82 | 18w | 75w | | 10,000 Hrs. |
| 00GU2426 | 26w Compact Fluorescent Spiral Bulb | 1850 | 2700k | 84 | 26w | 100w | | 10,000 Hrs. |
| DSLG-40 | Full Cut-Off LED GU-24 Lamp | 400 | 3000k | 80 | 5w | 40w | | 35,000 Hrs. |
| DSLM-40 | Full Cut-Off LED E26 Lamp | 400 | 3000k | 80 | 5w | 40w | | 35,000 Hrs. |
| EB-04A | E26 to GU24 Adapter | | | | | | | |

INTEGRATED LED SPECIFICATIONS Not Available to Purchase

| ITEM | DESCRIPTION | LUMENS | COLOR TEMP. | CRI | WATTS CONSUMED | INCANDESCENT EQUIVALENCY | DIMMABLE | LIFESPAN |
|----------|-----------------------------|--------|-------------|-----|----------------|--------------------------|----------|-------------|
| COL-35 | Medium Flood Integrated LED | 320 | 3000k | 83 | 4.5w | 35w | • | 60,000 Hrs. |
| UNI-60™ | Integrated LED Engine | 800 | 3000k | 80 | 9w | 60w | | 40,000 Hrs. |
| UNI-75™ | Integrated LED Engine | 1000 | 3000k | 80 | 12w | 75w | | 40,000 Hrs. |
| UNI-100™ | Integrated LED Engine | 1200 | 3000k | 80 | 14w | 100w | | 40,000 Hrs. |

SURF™

Surf's chic design reflects the natural curl of a breaking wave. Constructed of solid stainless steel as well as solid aluminum, this LED lantern emits light both up and down.

FINISH Bronze, Stainless Steel

LED 




2355 BZ



2355 SS
stainless steel





2350 BZ



2350 SS
stainless steel



2354 BZ



2354 SS
stainless steel



SURF Bronze (BZ), Stainless Steel (SS)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | LIGHT ENGINE | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|--------------------------|-----------------|-----------------------|
| 2350 BZ | 6" W | 15" | 4¾" | 8¾" | 4½" W, 7½" H Back Plate | 2 UNI-60 | BZ, SS |
| 2350 SS | 6" W | 15" | 4¾" | 8¾" | 4½" W, 7½" H Back Plate | 2 UNI-60 | BZ, SS |
| 2354 BZ | 7½" W | 19" | 5¾" | 11" | 4½" W, 7½" H Back Plate | 2 UNI-75 | BZ, SS |
| 2354 SS | 7½" W | 19" | 5¾" | 11" | 4½" W, 7½" H Back Plate | 2 UNI-75 | BZ, SS |
| 2355 BZ | 9½" W | 24" | 7" | 13¾" | 4½" W, 11½" H Back Plate | 2 UNI-100 | BZ, SS |
| 2355 SS | 9½" W | 24" | 7" | 13¾" | 4½" W, 11½" H Back Plate | 2 UNI-100 | BZ, SS |

For LED light engine specification and performance details see pages 412-413.

SATURN™

Saturn is a stunning, modern design in stainless steel, offering robust construction and intersecting lines that create a striking contrast against the etched opal glass.

FINISH Stainless Steel

GLASS Etched Opal



Saturn path lights are available in the Hinkley Landscape Lighting catalog.



1909 SS
(pocket wall mount)
1909 SS-GU24





1902 SS
1902 SS-GU24



1904 SS
1904 SS-GU24



1908 SS
(pocket wall mount)
1908 SS-GU24



1900 SS
1900 SS-GU24



1905 SS
1905 SS-GU24



1901 SS
1901 SS-GU24



SATURN Stainless Steel (SS)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-----------------------|----------|
| | | | | | | | | AVAILABLE FINISHES | ADA |
| 1900 SS | 6" W | 12" | 7½" | 7½" | 4¾" W, 9" H Back Plate | | 1-60w Med. | 1900 SS-GU24 | MT, SS |
| 1901 SS | 10" Dia. | 21¼" | | | 3" Dia. Post Fitter | | 1-100w Med. | 1901 SS-GU24 | MT, SS |
| 1902 SS | 10" Dia. | 21¼" | | | 5" Dia. Canopy | 6', 5' | 1-100w Med. | 1902 SS-GU24 | MT, SS |
| 1904 SS | 8" W | 16" | 9½" | 9" | 4¾" W, 12" H Back Plate | | 1-75w Med. | 1904 SS-GU24 | MT, SS |
| 1905 SS | 10" W | 20¼" | 11½" | 12¼" | 4¾" W, 14" H Back Plate | | 1-100w Med. | 1905 SS-GU24 | MT, SS |
| 1908 SS | 7¼" W | 12½" | 4" | 6¼" | 5¾" W, 12" H Back Plate | | 2-40w Cand. | 1908 SS-GU24 | MT, SS • |
| 1909 SS | 8" W | 20½" | 4¼" | 10¼" | 5" W, 20" H Back Plate | | 2-75w Med. | 1909 SS-GU24 | MT, SS |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

SATURN™

Saturn is a stunning, modern design in solid brass, offering robust construction and intersecting lines that create a striking contrast against the etched opal glass.

FINISH Metro Bronze

GLASS Etched Opal



Saturn path lights are available in the Hinkley Landscape Lighting catalog.



1909 MT
(pocket wall mount)
1909 MT-GU24





1902 MT
1902 MT-GU24



1904 MT
1904 MT-GU24



1908 MT
(pocket wall mount)
1908 MT-GU24



1900 MT
1900 MT-GU24



1905 MT
1905 MT-GU24



1901 MT
1901 MT-GU24



SATURN Metro Bronze (MT)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-----------------------|----------|
| | | | | | | | | AVAILABLE FINISHES | ADA |
| 1900 MT | 6" W | 12" | 7½" | 7½" | 4¾" W, 9" H Back Plate | | 1-60w Med. | 1900 MT-GU24 | MT, SS |
| 1901 MT | 10" Dia. | 21¾" | | | 3" Dia. Post Fitter | | 1-100w Med. | 1901 MT-GU24 | MT, SS |
| 1902 MT | 10" Dia. | 21¼" | | | 5" Dia. Canopy | 6', 5' | 1-100w Med. | 1902 MT-GU24 | MT, SS |
| 1904 MT | 8" W | 16" | 9½" | 9" | 4¾" W, 12" H Back Plate | | 1-75w Med. | 1904 MT-GU24 | MT, SS |
| 1905 MT | 10" W | 20¼" | 11½" | 12¼" | 4¾" W, 14" H Back Plate | | 1-100w Med. | 1905 MT-GU24 | MT, SS |
| 1908 MT | 7¼" W | 12½" | 4" | 6¼" | 5¾" W, 12" H Back Plate | | 2-40w Cand. | 1908 MT-GU24 | MT, SS • |
| 1909 MT | 8" W | 20½" | 4¼" | 10¼" | 5" W, 20" H Back Plate | | 2-75w Med. | 1909 MT-GU24 | MT, SS |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

DISTRICT™

District is a contemporary design of solid aluminum construction with a sleek panel of ¼" bent rain glass on the front of the lantern. Available in two finishes, the angled side panels in this collection feature vents of etched glass, adding a soft yet modern design element.

FINISH Bronze, Titanium

GLASS Etched Rain Glass



2115 BZ
2115 BZ-GU24



2115 TT
2115 TT-GU24





Angled side and bottom view of glass panels on 2110 TT



2110 BZ
2110 BZ-GU24



2110 TT
2110 TT-GU24



2114 BZ
2114 BZ-GU24



2114 TT
2114 TT-GU24



DISTRICT Bronze (BZ), Titanium (TT)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | |
|---------|----------------|--------|------|------------------|-------------------------|-------------|-------------------------------------------------------------------------------------------|-----------------------|
| | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | AVAILABLE FINISHES |
| 2110 BZ | 7¼" W | 12" | 4½" | 6" | 4½" W, 6¾" H Back Plate | 1-100w Med. | 2110 BZ-GU24 | BZ, TT |
| 2110 TT | 7¼" W | 12" | 4½" | 6" | 4½" W, 6¾" H Back Plate | 1-100w Med. | 2110 TT-GU24 | BZ, TT |
| 2114 BZ | 7¼" W | 18" | 4½" | 9" | 4½" W, 6¾" H Back Plate | 1-100w Med. | 2114 BZ-GU24 | BZ, TT |
| 2114 TT | 7¼" W | 18" | 4½" | 9" | 4½" W, 6¾" H Back Plate | 1-100w Med. | 2114 TT-GU24 | BZ, TT |
| 2115 BZ | 7¼" W | 24" | 4½" | 12" | 4½" W, 6¾" H Back Plate | 2-100w Med. | 2115 BZ-GU24 | BZ, TT |
| 2115 TT | 7¼" W | 24" | 4½" | 12" | 4½" W, 6¾" H Back Plate | 2-100w Med. | 2115 TT-GU24 | BZ, TT |

For Fluorescent/GU24 lamps, see pages 412-413.

ATLANTIS™

Atlantis features a minimalist design for the ultimate in urban sophistication. Constructed of solid aluminum and Dark Sky compliant, Atlantis provides a chic solution to eco-conscious homeowners.


FINISH Bronze

GLASS Cased Opal or Etched Glass Lenses

LIGHTING FOR TOMORROW
AWARD WINNER




Atlantis path lights are available in the Hinkley Landscape Lighting catalog.




Scan to view a video of the Atlantis collection.

DARK SKY



1649 BZ
1649 BZ-LED





1646 (left) will cast light down
1645 (right) will cast light up and down



1646 BZ
(pocket down light)
1646 BZ-GU24
LED icon
1646 BZ-LED
LED icon



1645 BZ
(pocket up/down light)
1645 BZ-GU24
LED icon
1645 BZ-LED
LED icon



1648 BZ
1648 BZ-LED
LED icon



1640 BZ
1640 BZ-LED
LED icon




1650 BZ
1650 BZ-GU24
LED icon



1655 BZ
1655 BZ-GU24
LED icon



1644 BZ
1644 BZ-LED
LED icon



1641 BZ
1641 BZ-LED
LED icon

ATLANTIS Bronze (BZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. DEPTH | TOP TO OUTLET | BACK PLATE | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES | ADA |
|----------|----------------|--------|------------|------------------|------------------------|------------------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|-----|
| | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | | |
| 1640 BZ | 2¾" W | 16" | 6¾" | 8" | 4½" W, 4½" H | 2-12 volt, 20w MR-16** | | 1640 BZ-LED | 2 COL-35 | BZ, SK, SW, TT | |
| 1641 BZ | 6¾" W | 23½" | 2¾" | | 3" Dia. Post Fitter | 2-12 volt, 20w MR-16** | | 1641 BZ-LED | 2 COL-35 | BZ, SK, SW, TT | |
| 1644 BZ | 3" W | 24" | 7" | 12" | 4½" W, 4½" H | 2-12 volt, 20w MR-16** | | 1644 BZ-LED | 2 COL-35 | BZ, SK, SW, TT | |
| 1645 BZ* | 9" W | 5½" | 4" | 2¾" | 4½" W, 4½" H | 1-75w Med. | 1645 BZ-GU24 | 1645 BZ-LED | 2 COL-35 | BZ, SK, SW, TT | • |
| 1646 BZ | 9" W | 5½" | 4" | 2¾" | 4½" W, 4½" H | 1-75w Med. | 1646 BZ-GU24 | 1646 BZ-LED | COL-35 | BZ, SK, SW, TT | • |
| 1648 BZ | 6" W | 16" | 3½" | 13¾" | 4½" W, 4½" H | 2-12 volt, 20w MR-16** | | 1648 BZ-LED | 2 COL-35 | BZ, SK, SW, TT | • |
| 1649 BZ | 9" W | 24" | 4" | 20¾" | 4½" W, 6½" H | 2-12 volt, 20w MR-16** | | 1649 BZ-LED | 2 COL-35 | BZ, SK, SW, TT | • |
| 1650 BZ* | 6¼" W | 10½" | 4" | 5½" | 5½" W, 5½" H | 1-60w Med. | 1650 BZ-GU24 | | | BZ, TT | • |
| 1655 BZ* | 9" W | 15¼" | 5¾" | 7¾" | 5½" W, 8" H | 1-100w Med. | 1655 BZ-GU24 | | | BZ, TT | • |

Atlantis comes standard Dark Sky compliant. *Does not meet Dark Sky requirements. **MR-16 bulbs included. For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

ATLANTIS™

Atlantis features a minimalist design for the ultimate in urban sophistication.

Constructed of solid aluminum and Dark Sky compliant, Atlantis

provides a chic solution to eco-conscious homeowners.


FINISH Titanium

GLASS Cased Opal or Etched Glass Lenses

LIGHTING FOR TOMORROW
AWARD WINNER



Atlantis path lights are available in the Hinkley Landscape Lighting catalog.




Scan to view a video of the Atlantis collection.



DARK SKY

1649 TT
1649 TT-LED





1646 (left) will cast light down
1645 (right) will cast light up and down



1646 TT
(pocket down light)
1646 TT-GU24

1646 TT-LED



1645 TT
(pocket up/down light)
1645 TT-GU24


1645 TT-LED


1648 TT
1648 TT-LED


1640 TT
1640 TT-LED














1650 TT
1650 TT-GU24


1655 TT
1655 TT-GU24


1644 TT
1644 TT-LED


1641 TT
1641 TT-LED


ATLANTIS Titanium (TT)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. DEPTH | TOP TO OUTLET | BACK PLATE | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |  ADA | |
|----------|----------------|--------|------------|------------------|------------------------|------------------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|----------------------------------------------------------------------------------------------|---|
| | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | | | |
| 1640 TT | 2¾" W | 16" | 6¾" | 8" | 4½" W, 4½" H | 2-12 volt, 20w MR-16** |  | 1640 TT-LED | 2 COL-35 | BZ, SK, SW, TT | | |
| 1641 TT | 6¾" W | 23½" | 2¾" | | 3" Dia. Post Fitter | 2-12 volt, 20w MR-16** |  | 1641 TT-LED | 2 COL-35 | BZ, SK, SW, TT | | |
| 1644 TT | 3" W | 24" | 7" | 12" | 4½" W, 4½" H | 2-12 volt, 20w MR-16** |  | 1644 TT-LED | 2 COL-35 | BZ, SK, SW, TT | | |
| 1645 TT* | 9" W | 5½" | 4" | 2¾" | 4½" W, 4½" H | 1-75w Med. |  | 1645 TT-GU24 | 1645 TT-LED | 2 COL-35 | BZ, SK, SW, TT | • |
| 1646 TT | 9" W | 5½" | 4" | 2¾" | 4½" W, 4½" H | 1-75w Med. |  | 1646 TT-GU24 | 1646 TT-LED | COL-35 | BZ, SK, SW, TT | • |
| 1648 TT | 6" W | 16" | 3½" | 13¾" | 4½" W, 4½" H | 2-12 volt, 20w MR-16** |  | 1648 TT-LED | 2 COL-35 | BZ, SK, SW, TT | • | |
| 1649 TT | 9" W | 24" | 4" | 20¾" | 4½" W, 6½" H | 2-12 volt, 20w MR-16** |  | 1649 TT-LED | 2 COL-35 | BZ, SK, SW, TT | • | |
| 1650 TT* | 6¼" W | 10½" | 4" | 5½" | 5½" W, 5½" H | 1-60w Med. |  | 1650 TT-GU24 | | BZ, TT | • | |
| 1655 TT* | 9" W | 15¼" | 5¾" | 7¾" | 5½" W, 8" H | 1-100w Med. |  | 1655 TT-GU24 | | BZ, TT | • | |

Atlantis comes standard Dark Sky compliant. *Does not meet Dark Sky requirements. **MR-16 bulbs included. For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

ATLANTIS™


Atlantis features a minimalist design for the ultimate in urban sophistication. Constructed of solid aluminum and Dark Sky compliant, Atlantis provides a chic solution to eco-conscious homeowners.

FINISH Satin White

GLASS Etched Opal or Etched Glass Lenses

LIGHTING FOR TOMORROW
AWARD WINNER

Atlantis path lights are available in the Hinkley Landscape Lighting catalog.



Scan to view a video of the Atlantis collection.

DARK SKY 




1649 SW
1649 SW-LED





1646 will cast light down



1645 will cast light up and down



1646 SW
(pocket down light)
1646 SW-GU24

1646 SW-LED





1645 SW
(pocket up/down light)
1645 SW-GU24

1645 SW-LED




1648 SW
1648 SW-LED





1640 SW
1640 SW-LED














1644 SW
1644 SW-LED




1641 SW
1641 SW-LED


ATLANTIS Satin White (SW)

| ITEM | WIDTH/DIA. | HEIGHT | EXT. | DEPTH | TOP TO OUTLET | BACK PLATE | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |  ADA | |
|----------|------------|--------|------|-------|---------------------|------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------|------------------|--------------------|-------------------------------------------------------------------------------------------|---|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | | | |
| 1640 SW | 2¾" W | 16" | 6¾" | 8" | 4½" W, 4½" H | 2-12 volt, 20w MR-16** | |  | 1640 SW-LED | 2 COL-35 | BZ, SK, SW, TT | | |
| 1641 SW | 6¾" W | 23½" | | 2¾" | 3" Dia. Post Fitter | 2-12 volt, 20w MR-16** | |  | 1641 SW-LED | 2 COL-35 | BZ, SK, SW, TT | | |
| 1644 SW | 3" W | 24" | 7" | 12" | 4½" W, 4½" H | 2-12 volt, 20w MR-16** | |  | 1644 SW-LED | 2 COL-35 | BZ, SK, SW, TT | | |
| 1645 SW* | 9" W | 5¼" | 4" | 2¾" | 4½" W, 4½" H | 1-75w Med. |  |  | 1645 SW-GU24 | 1645 SW-LED | 2 COL-35 | BZ, SK, SW, TT | • |
| 1646 SW | 9" W | 5¼" | 4" | 2¾" | 4½" W, 4½" H | 1-75w Med. |  |  | 1646 SW-GU24 | 1646 SW-LED | COL-35 | BZ, SK, SW, TT | • |
| 1648 SW | 6" W | 16" | 3½" | 13¾" | 4½" W, 4½" H | 2-12 volt, 20w MR-16** | |  | 1648 SW-LED | 2 COL-35 | BZ, SK, SW, TT | • | |
| 1649 SW | 9" W | 24" | 4" | 20¾" | 4½" W, 6½" H | 2-12 volt, 20w MR-16** | |  | 1649 SW-LED | 2 COL-35 | BZ, SK, SW, TT | • | |

Atlantis comes standard Dark Sky compliant. *Does not meet Dark Sky requirements. **MR-16 bulbs included. For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

ATLANTIS™

Atlantis features a minimalist design for the ultimate in urban sophistication. Constructed of solid aluminum and Dark Sky compliant, Atlantis provides a chic solution to eco-conscious homeowners.


FINISH Satin Black

GLASS Etched Opal or Etched Glass Lenses

LIGHTING FOR TOMORROW
AWARD WINNER



Atlantis path lights are available in the Hinkley Landscape Lighting catalog.



Scan to view a video of the Atlantis collection.

DARK SKY



1649 SK
1649 SK-LED





1646 will cast light down



1645 will cast light up and down



1646 SK
(pocket down light)
1646 SK-GU24


1646 SK-LED





1645 SK
(pocket up/down light)
1645 SK-GU24

1645 SK-LED





1648 SK
1648 SK-LED




1640 SK
1640 SK-LED











1644 SK
1644 SK-LED




1641 SK
1641 SK-LED


ATLANTIS Satin Black (SK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | DEPTH | TOP TO OUTLET | BACK PLATE | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |  ADA |
|----------|----------------|--------|------|-------|------------------|------------------------|------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|------------------------|-----------------------|-------------------------------------------------------------------------------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | | |
| 1640 SK | 2¾" W | 16" | 6¾" | | 8" | 4½" W, 4½" H | 2-12 volt, 20w MR-16** |  |  | | BZ, SK, SW, TT | |
| 1641 SK | 6¾" W | 23½" | | 2¾" | | 3" Dia. Post Fitter | 2-12 volt, 20w MR-16** | | | | BZ, SK, SW, TT | |
| 1644 SK | 3" W | 24" | 7" | | 12" | 4½" W, 4½" H | 2-12 volt, 20w MR-16** | | | | BZ, SK, SW, TT | |
| 1645 SK* | 9" W | 5¼" | 4" | | 2¾" | 4½" W, 4½" H | 1-75w Med. |  |  | | BZ, SK, SW, TT | • |
| 1646 SK | 9" W | 5¼" | 4" | | 2¾" | 4½" W, 4½" H | 1-75w Med. |  |  | | BZ, SK, SW, TT | • |
| 1648 SK | 6" W | 16" | 3½" | | 13¾" | 4½" W, 4½" H | 2-12 volt, 20w MR-16** | | | | BZ, SK, SW, TT | • |
| 1649 SK | 9" W | 24" | 4" | | 20¾" | 4½" W, 6½" H | 2-12 volt, 20w MR-16** | | | | BZ, SK, SW, TT | • |

Atlantis comes standard Dark Sky compliant. *Does not meet Dark Sky requirements. **MR-16 bulbs included. For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

LET THERE BE NIGHT Residential outdoor lighting is an amenity that requires careful consideration and research. Hinkley offers a variety of tools to help you along the way. Explore our full-line Landscape Lighting catalog, learn from our easy-to-follow educational videos or visit us online at hinkleylandscapelighting.com for detailed guidelines, tips and recommendations. If you decide to enlist the help of an expert, use our convenient showroom locator to find professional lighting consultants in your area.

PATH LIGHTING | CAST BRASS PATH, SPOT, DECK & STEP LIGHTING | 12V LED PATH, SPOT, DECK & STEP LIGHTING | ACCENT LIGHTING
120v LED LINE VOLTAGE | 120v LINE VOLTAGE | DECK & STEP LIGHTING | TRANSFORMERS | 120v LED SIGN LIGHT KITS

CREATE ENCHANTMENT


The purpose of landscape lighting is to unify the relationship between your house and the landscaping that surrounds it. One of the great features of landscape lighting is that it allows you to start slowly and gradually add in more lights as your time, budget or exterior space allows. You may choose to begin with path lights to add safety to your walkways and then slowly fill in various accent lights to emphasize features of your landscaping.

Landscape lighting enhances your outdoor living environment, extends the hours of enjoyment you and your family spend outdoors and provides safety and security. Well-designed landscape lighting will reinforce aesthetic appeal and increasingly add more value to your home.

“Exterior lighting provides a warm welcome and guides visitors safely up walkways and into your home. It leads people from the natural environment into the comforts of your home and should do so in an inviting and seamless way.

Landscape lighting also extends living outdoors and plays an integral part in fostering indoor-outdoor connections. Today’s homes often feature family rooms, kitchens, and bedrooms that open via glass doors to patios, balconies, swimming pools, decks, and other outdoor areas. Developing an exterior lighting plan that is consistent in style and mood with the interior of your home helps to blur the boundaries, and encourages people to enjoy all a home’s living spaces—inside and out.”

AMY ELBERT, SENIOR ARCHITECTURE EDITOR
TRADITIONAL HOME



COORDINATE & COMPLEMENT

Look for the following collections in Hinkley’s Outdoor Section that offer coordinating landscape lighting options:

| COLLECTION | PAGES |
|------------|---------|
| ATLANTIS | 422-429 |
| BOLLA | 486-489 |
| HARBOR | 468-473 |
| LEDGEWOOD | 478-481 |
| MONTICELLO | 592-593 |
| PLANTATION | 608-611 |
| RALEY | 526-527 |
| REEF | 460-461 |
| SATURN | 416-419 |
| SHELTER | 452-457 |



“Introducing light from multiple sources creates an interesting play of light and shadows that enhances a home’s architecture, lawn, and gardens. Illuminating the exterior is much like lighting a home’s interior – you need to layer light, using different types and sources of light to serve a variety of purposes – from safety to ambience to drama. One source of light, such as a porch lamp, certainly won’t show off your gardens; nor will a single uplight on a tree illuminate your front stairs. Light layered from a variety of angles and levels gives property a nice sense of balance and provides a lovely wash of light that is practical and pretty.”

AMY ELBERT, SENIOR ARCHITECTURE EDITOR
TRADITIONAL HOME

CASCADE™

The clean, modern lines of Cascade complement the rich alabaster or rain glass while creating a glowing, indirect lighting effect. The sleek aluminum construction adds to the design's versatility, making this contemporary style perfect for either interior or exterior use. Cascade is standard Dark Sky compliant.

FINISH Bronze, Satin Black, Titanium

GLASS Clear Etched Organic Rain, Amber Etched Organic Rain, Alabaster

DARK SKY 



1834 BZ
1834 BZ-GU24



1834 BZ-LED





1830 BZ
1830 BZ-GU24



1830 BZ-LED



1830 TT
1830 TT-GU24



1830 TT-LED




1830 SK
1830 SK-GU24



1830 SK-LED



amber glass detail



clear glass detail



1834 TT
1834 TT-GU24



1834 TT-LED
















1834 SK
1834 SK-GU24



1834 SK-LED



CASCADE Bronze (BZ), Satin Black (SK), Titanium (TT)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOPTO OUTLET | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |  ADA |
|---------|----------------|--------|------|-----------------|-------------------------|-------------|----------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|------------------------|-----------------------|-------------------------------------------------------------------------------------------|
| | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | | |
| 1830 BZ | 8" W | 14½" | 4" | 4¾" | 8" W, 14½" H Back Plate | 1-100w Med. |  1830 BZ-GU24 |  1830 BZ-LED | UNI-100 | BZ, SK, TT | • |
| 1830 SK | 8" W | 14½" | 4" | 4¾" | 8" W, 14½" H Back Plate | 1-100w Med. |  1830 SK-GU24 |  1830 SK-LED | UNI-100 | BZ, SK, TT | • |
| 1830 TT | 8" W | 14½" | 4" | 4¾" | 8" W, 14½" H Back Plate | 1-100w Med. |  1830 TT-GU24 |  1830 TT-LED | UNI-100 | BZ, SK, TT | • |
| 1834 BZ | 8" W | 18" | 4" | 4¾" | 8" W, 18" H Back Plate | 1-100w Med. |  1834 BZ-GU24 |  1834 BZ-LED | UNI-100 | BZ, SK, TT | • |
| 1834 SK | 8" W | 18" | 4" | 4¾" | 8" W, 18" H Back Plate | 1-100w Med. |  1834 SK-GU24 |  1834 SK-LED | UNI-100 | BZ, SK, TT | • |
| 1834 TT | 8" W | 18" | 4" | 4¾" | 8" W, 18" H Back Plate | 1-100w Med. |  1834 TT-GU24 |  1834 TT-LED | UNI-100 | BZ, SK, TT | • |

Cascade comes standard Dark Sky compliant. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.



1832 BZ
1832 BZ-GU24



1832 BZ-LED



1832 TT
1832 TT-GU24



1832 TT-LED



alabaster glass detail



1836 BZ
1836 BZ-GU24



1836 BZ-LED



1836 TT
1836 TT-GU24



1836 TT-LED



CASCADE Bronze (BZ), Titanium (TT)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES | ADA |
|---------|----------------|--------|------|------------------|-------------------------|-------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|-----|
| | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | | |
| 1832 BZ | 8" W | 14½" | 4" | 4¾" | 8" W, 14½" H Back Plate | 1-100w Med. | 1832 BZ-GU24 | 1832 BZ-LED | UNI-100 | BZ, TT | • |
| 1832 TT | 8" W | 14½" | 4" | 4¾" | 8" W, 14½" H Back Plate | 1-100w Med. | 1832 TT-GU24 | 1832 TT-LED | UNI-100 | BZ, TT | • |
| 1836 BZ | 8" W | 18" | 4" | 4¾" | 8" W, 18" H Back Plate | 1-100w Med. | 1836 BZ-GU24 | 1836 BZ-LED | UNI-100 | BZ, TT | • |
| 1836 TT | 8" W | 18" | 4" | 4¾" | 8" W, 18" H Back Plate | 1-100w Med. | 1836 TT-GU24 | 1836 TT-LED | UNI-100 | BZ, TT | • |

Cascade comes standard Dark Sky compliant. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.



side view of 1831 BZ



side view of 1831 TT



side view of 1831 SK



1831 BZ
1831 BZ-GU24

1831 BZ-LED




1831 TT
1831 TT-GU24

1831 TT-LED




1831 SK
1831 SK-GU24

1831 SK-LED


CASCADE Bronze (BZ), Satin Black (SK), Titanium (TT)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|---------------------|-------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1831 BZ | 9½" W | 22½" | | | 3" Dia. Post Fitter | 1-100w Med. | 1831 BZ-GU24 | 1831 BZ-LED | UNI-100 | BZ, SK, TT |
| 1831 SK | 9½" W | 22½" | | | 3" Dia. Post Fitter | 1-100w Med. | 1831 SK-GU24 | 1831 TT-LED | UNI-100 | BZ, SK, TT |
| 1831 TT | 9½" W | 22½" | | | 3" Dia. Post Fitter | 1-100w Med. | 1831 TT-GU24 | 1831 BZ-LED | UNI-100 | BZ, SK, TT |

Cascade comes standard Dark Sky compliant. For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

KUBE™

A collection of sleek designs, Kube's contemporary style featuring solid aluminum construction provides a chic, minimalist statement to complement a variety of exteriors. Kube is standard Dark Sky compliant.

FINISH Bronze, Satin Black, Satin White, Titanium

GLASS Clear Etched Organic Rain, Amber Etched Organic Rain, Etched Lenses

DARK SKY 



1764 TT
1764 TT-LED





1760 TT
1760 TT-LED



1760 SK
1760 SK-LED



1760 BZ
1760 BZ-LED



amber glass detail



clear glass detail




1764 SK
1764 SK-LED



1764 BZ
1764 BZ-LED



KUBE Bronze (BZ), Satin Black (SK), Titanium (TT)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | | |
|---------|----------------|--------|------|------------------|-------------------------|-------------|-------------------------------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | LED  | LED LIGHT ENGINE | AVAILABLE FINISHES |
| 1760 BZ | 4½" W | 12" | 5" | 5½" | 4½" W, 6¾" H Back Plate | 1-50w GU10* | 1760 BZ-LED | UNI-60 | BZ, SK, TT |
| 1760 SK | 4½" W | 12" | 5" | 5½" | 4½" W, 6¾" H Back Plate | 1-50w GU10* | 1760 SK-LED | UNI-60 | BZ, SK, TT |
| 1760 TT | 4½" W | 12" | 5" | 5½" | 4½" W, 6¾" H Back Plate | 1-50w GU10* | 1760 TT-LED | UNI-60 | BZ, SK, TT |
| 1764 BZ | 6" W | 16" | 6½" | 8" | 4½" W, 6¾" H Back Plate | 1-50w GU10* | 1764 BZ-LED | UNI-60 | BZ, SK, TT |
| 1764 SK | 6" W | 16" | 6½" | 8" | 4½" W, 6¾" H Back Plate | 1-50w GU10* | 1764 SK-LED | UNI-60 | BZ, SK, TT |
| 1764 TT | 6" W | 16" | 6½" | 8" | 4½" W, 6¾" H Back Plate | 1-50w GU10* | 1764 TT-LED | UNI-60 | BZ, SK, TT |

Kube comes standard Dark Sky compliant. *GU10 bulb included. For LED specifications, see pages 412-413.



1763 BZ
(ceiling mount)
1763 BZ-GU24



1763 TT
(ceiling mount)
1763 TT-GU24



1763 SW
(ceiling mount)
1763 SW-GU24



1763 SK
(ceiling mount)
1763 SK-GU24



1761 BZ
1761 BZ-LED



1761 TT
1761 TT-LED



1761 SK
1761 SK-LED



KUBE Bronze (BZ), Satin Black (SK), Satin White (SW), Titanium (TT)

| ITEM | WIDTH/ DIA. | HEIGHT | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|----------|----------------|--------|---------------------|--------------|------------------------------------------------------------------------------|--------------------------------------------------------------|------------------|--------------------|
| | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1761 BZ | 6" W | 18½" | 3" Dia. Post Fitter | 2-50w GU10** | | | UNI-100 | BZ, SK, TT |
| 1761 SK | 6" W | 18½" | 3" Dia. Post Fitter | 2-50w GU10** | | | UNI-100 | BZ, SK, TT |
| 1761 TT | 6" W | 18½" | 3" Dia. Post Fitter | 2-50w GU10** | | | UNI-100 | BZ, SK, TT |
| 1763 BZ* | 6" W | 6¼" | 6" W, 6" L Canopy | 1-75w Med. | 1763 BZ-GU24 | 1763 BZ-LED | UNI-100 | BZ, SK, SW, TT |
| 1763 SK* | 6" W | 6¼" | 6" W, 6" L Canopy | 1-75w Med. | 1763 SK-GU24 | 1763 SK-LED | UNI-100 | BZ, SK, SW, TT |
| 1763 SW* | 6" W | 6¼" | 6" W, 6" L Canopy | 1-75w Med. | 1763 SW-GU24 | 1763 SW-LED | UNI-100 | BZ, SK, SW, TT |
| 1763 TT* | 6" W | 6¼" | 6" W, 6" L Canopy | 1-75w Med. | 1763 TT-GU24 | 1763 TT-LED | UNI-100 | BZ, SK, SW, TT |

Kube comes standard Dark Sky compliant. *Does not meet Dark Sky requirements. **GU10 bulb included.
For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.



1766 will cast light down



1767 will cast light up and down



1766 BZ
(pocket down light)
1766 BZ-GU24



1766 TT
(pocket down light)
1766 TT-GU24



1766 SW
(pocket down light)
1766 SW-GU24



1766 SK
(pocket down light)
1766 SK-GU24



1767 BZ
(pocket up/down light)
1767 BZ-GU24



1767 TT
(pocket up/down light)
1767 TT-GU24



1767 SW
(pocket up/down light)
1767 SW-GU24



1767 SK
(pocket up/down light)
1767 SK-GU24



KUBE Bronze (BZ), Satin Black (SK), Satin White (SW), Titanium (TT)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|----------|----------------|--------|------|------------------|-------------------------|------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1766 BZ | 6" W | 6" | 6¾" | 3" | 4½" W, 4½" H Back Plate | 1-75w Med. | 1766 BZ-GU24 | 1766 BZ-LED | COL-35 | BZ, SK, SW, TT |
| 1766 SK | 6" W | 6" | 6¾" | 3" | 4½" W, 4½" H Back Plate | 1-75w Med. | 1766 SK-GU24 | 1766 SK-LED | COL-35 | BZ, SK, SW, TT |
| 1766 SW | 6" W | 6" | 6¾" | 3" | 4½" W, 4½" H Back Plate | 1-75w Med. | 1766 SW-GU24 | 1766 TT-LED | COL-35 | BZ, SK, SW, TT |
| 1766 TT | 6" W | 6" | 6¾" | 3" | 4½" W, 4½" H Back Plate | 1-75w Med. | 1766 TT-GU24 | 1766 BZ-LED | COL-35 | BZ, SK, SW, TT |
| 1767 BZ* | 6" W | 6" | 6¾" | 3" | 4½" W, 4½" H Back Plate | 1-75w Med. | 1767 BZ-GU24 | 1767 BZ-LED | 2 COL-35 | BZ, SK, SW, TT |
| 1767 SK* | 6" W | 6" | 6¾" | 3" | 4½" W, 4½" H Back Plate | 1-75w Med. | 1767 SK-GU24 | 1767 SK-LED | 2 COL-35 | BZ, SK, SW, TT |
| 1767 SW* | 6" W | 6" | 6¾" | 3" | 4½" W, 4½" H Back Plate | 1-75w Med. | 1767 SW-GU24 | 1767 SW-LED | 2 COL-35 | BZ, SK, SW, TT |
| 1767 TT* | 6" W | 6" | 6¾" | 3" | 4½" W, 4½" H Back Plate | 1-75w Med. | 1767 TT-GU24 | 1767 TT-LED | 2 COL-35 | BZ, SK, SW, TT |

Kube comes standard Dark Sky compliant. *Does not meet Dark Sky requirements. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

LUNA™

Luna is a modern collection of solid aluminum fixtures offered in a unique combination of contemporary styles, including sleek wall lanterns with a dual light source and decorative reflector. Luna also offers chic pocket wall sconces and compact ceiling mounts that are ideal for indoor or out. Luna is standard ADA compliant.

FINISH Bronze, Satin Black, Titanium

GLASS Etched Glass Lenses

DARK SKY 



1664 SK
1664 SK-LED





1664 TT
1664 TT-LED



1664 BZ
1664 BZ-LED



1660 SK
1660 SK-LED



1660 TT
1660 TT-LED



1660 BZ
1660 BZ-LED



LUNA Bronze (BZ), Satin Black (SK), Titanium (TT)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | | AVAILABLE FINISHES | ADA |
|---------|----------------|--------|------|------------------|------------------------|--------------------------|-------------|------------------------|-----------------------|-----|
| | | | | | | | LED | LED LIGHT ENGINE | | |
| 1660 BZ | 6" W | 16" | 3½" | 10" to 13½" | 6" W, 16" H Back Plate | 2-12 volt, 2-20w MR-16** | 1660 BZ-LED | 2 COL-35 | BZ, SK, TT | • |
| 1660 SK | 6" W | 16" | 3½" | 10" to 13½" | 6" W, 16" H Back Plate | 2-12 volt, 2-20w MR-16** | 1660 SK-LED | 2 COL-35 | BZ, SK, TT | • |
| 1660 TT | 6" W | 16" | 3½" | 10" to 13½" | 6" W, 16" H Back Plate | 2-12 volt, 2-20w MR-16** | 1660 TT-LED | 2 COL-35 | BZ, SK, TT | • |
| 1664 BZ | 9" W | 24" | 4" | 11½" to 20½" | 9" W, 24" H Back Plate | 2-12 volt, 2-20w MR-16** | 1664 BZ-LED | 2 COL-35 | BZ, SK, TT | • |
| 1664 SK | 9" W | 24" | 4" | 11½" to 20½" | 9" W, 24" H Back Plate | 2-12 volt, 2-20w MR-16** | 1664 SK-LED | 2 COL-35 | BZ, SK, TT | • |
| 1664 TT | 9" W | 24" | 4" | 11½" to 20½" | 9" W, 24" H Back Plate | 2-12 volt, 2-20w MR-16** | 1664 TT-LED | 2 COL-35 | BZ, SK, TT | • |

Luna comes standard Dark Sky compliant. *Adjustable mounting hardware. **CFL/MR-16 bulbs included. For LED specifications, see pages 412-413.



1663 BZ
(ceiling mount)
1663 BZ-GU24



1663 BZ-LED



1663 TT
(ceiling mount)
1663 TT-GU24



1663 TT-LED



1663 SK
(ceiling mount)
1663 SK-GU24



1663 SK-LED



1647 BZ



1647 SW



1647 SK



1647 TT

LUNA Bronze (BZ), Satin Black (SK), Satin White (SW), Titanium (TT)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES | ADA |
|----------|----------------|--------|------|------------------|-------------------------|-------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|-----|
| | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | | |
| 1647 BZ | 9" W | 9" | 4" | 4½" | 4½" W, 6¾" H Back Plate | 2-13w CFL** | | | | BZ, SK, SW, TT | • |
| 1647 SK | 9" W | 9" | 4" | 4½" | 4½" W, 6¾" H Back Plate | 2-13w CFL** | | | | BZ, SK, SW, TT | • |
| 1647 SW | 9" W | 9" | 4" | 4½" | 4½" W, 6¾" H Back Plate | 2-13w CFL** | | | | BZ, SK, SW, TT | • |
| 1647 TT | 9" W | 9" | 4" | 4½" | 4½" W, 6¾" H Back Plate | 2-13w CFL** | | | | BZ, SK, SW, TT | • |
| 1663 BZ* | 8" W | 7¼" | | | | 1-75w Med. | 1663 BZ-GU24 | 1663 BZ-LED | UNI-100 | BZ, SK, TT | |
| 1663 SK* | 8" W | 7¼" | | | | 1-75w Med. | 1663 SK-GU24 | 1663 SK-LED | UNI-100 | BZ, SK, TT | |
| 1663 TT* | 8" W | 7¼" | | | | 1-75w Med. | 1663 TT-GU24 | 1663 TT-LED | UNI-100 | BZ, SK, TT | |

Luna comes standard Dark Sky compliant. *Does not meet Dark Sky requirements. **CFL bulbs included. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.



1666 will cast light down



1667 will cast light up and down



1666 BZ
(pocket down light)
1666 BZ-GU24

1666 BZ-LED




1666 TT
(pocket down light)
1666 TT-GU24



1666 TT-LED




1666 SK
(pocket down light)
1666 SK-GU24

1666 SK-LED




1667 BZ
(pocket up/down light)
1667 BZ-GU24

1667 BZ-LED




1667 TT
(pocket up/down light)
1667 TT-GU24

















1667 TT-LED




1667 SK
(pocket up/down light)
1667 SK-GU24

1667 SK-LED


LUNA Bronze (BZ), Satin Black (SK), Titanium (TT)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |  ADA |
|----------|----------------|--------|------|------------------|------------------------|------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|-----------------------|----------------------------------------------------------------------------------------------|
| | | | | | | |  GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. |  LED Includes integrated high efficiency LED light source. |  LED LIGHT ENGINE | | |
| 1666 BZ | 9" W | 7" | 4" | 3½" | 9" W, 5¼" H Back Plate | 1-75w Med. |  1666 BZ-GU24 |  1666 BZ-LED | COL-35 | BZ, SK, TT | • |
| 1666 SK | 9" W | 7" | 4" | 3½" | 9" W, 5¼" H Back Plate | 1-75w Med. |  1666 SK-GU24 |  1666 SK-LED | COL-35 | BZ, SK, TT | • |
| 1666 TT | 9" W | 7" | 4" | 3½" | 9" W, 5¼" H Back Plate | 1-75w Med. |  1666 TT-GU24 |  1666 TT-LED | COL-35 | BZ, SK, TT | • |
| 1667 BZ* | 9" W | 7" | 4" | 3½" | 9" W, 5¼" H Back Plate | 1-75w Med. |  1667 BZ-GU24 |  1667 BZ-LED | 2 COL-35 | BZ, SK, TT | • |
| 1667 SK* | 9" W | 7" | 4" | 3½" | 9" W, 5¼" H Back Plate | 1-75w Med. |  1667 SK-GU24 |  1667 SK-LED | 2 COL-35 | BZ, SK, TT | • |
| 1667 TT* | 9" W | 7" | 4" | 3½" | 9" W, 5¼" H Back Plate | 1-75w Med. |  1667 TT-GU24 |  1667 TT-LED | 2 COL-35 | BZ, SK, TT | • |

Luna comes standard Dark Sky compliant. *Does not meet Dark Sky requirements. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

TITAN™

Titan's sleek design in solid aluminum features organic etched glass that creates an indirect wall wash for a sophisticated appearance.

FINISH Buckeye Bronze, Hematite, Titanium

GLASS Organic Ribbed Etched



2054 HE
2054 HE-GU24





2054 KZ
2054 KZ-GU24



2054 TT
2054 TT-GU24



2050 HE
2050 HE-GU24




2050 KZ
2050 KZ-GU24



2050 TT
2050 TT-GU24

TITAN Buckeye Bronze (KZ), Hematite (HE), Titanium (TT)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | |
|---------|----------------|--------|------|------------------|--------------------------|-------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|
| | | | | | | |  GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | AVAILABLE FINISHES |
| 2050 HE | 6¾" W | 14" | 4½" | 7" | 6¾" W, 14" H Back Plate | 1-100w Med. | 2050 HE-GU24 | HE, KZ, TT |
| 2050 KZ | 6¾" W | 14" | 4½" | 7" | 6¾" W, 14" H Back Plate | 1-100w Med. | 2050 KZ-GU24 | HE, KZ, TT |
| 2050 TT | 6¾" W | 14" | 4½" | 7" | 6¾" W, 14" H Back Plate | 1-100w Med. | 2050 TT-GU24 | HE, KZ, TT |
| 2054 HE | 8½" W | 17½" | 4¾" | 8¾" | 8½" W, 17½" H Back Plate | 1-100w Med. | 2054 HE-GU24 | HE, KZ, TT |
| 2054 KZ | 8½" W | 17½" | 4¾" | 8¾" | 8½" W, 17½" H Back Plate | 1-100w Med. | 2054 KZ-GU24 | HE, KZ, TT |
| 2054 TT | 8½" W | 17½" | 4¾" | 8¾" | 8½" W, 17½" H Back Plate | 1-100w Med. | 2054 TT-GU24 | HE, KZ, TT |

For Fluorescent/GU24 lamps, see pages 412-413.

DORIAN™

Dorian's robust design in durable aluminum construction is offered in either Titanium or Bronze finishes. This contemporary fixture allows light to emit from white etched glass windows on five sides.

FINISH Titanium

GLASS Clear Painted White Inside



2190 TT
2190 TT-GU24



2191 TT
2191 TT-GU24



2194 TT
2194 TT-GU24



2195 TT
2195 TT-GU24



2192 TT
2192 TT-GU24



DORIAN Titanium (TT)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | |
|---------|----------------|--------|------|------------------|-----------------------|----------------|-------------|---------------------------------------------------------------------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | AVAILABLE FINISHES |
| 2190 TT | 6" W | 12¼" | 6¾" | 6¼" | 4½" Square Back Plate | | 1-100w Med. | 2190 TT-GU24 | BZ, TT |
| 2191 TT | 6" W | 20¾" | | | 3" Dia. Post Fitter | | 1-100w Med. | 2191 TT-GU24 | BZ, TT |
| 2192 TT | 6" W | 18¼" | | | 5" Dia. Canopy | 6' Wire | 1-100w Med. | 2192 TT-GU24 | BZ, TT |
| 2194 TT | 6" W | 18¼" | 6¾" | 9¼" | 4½" Square Back Plate | | 1-100w Med. | 2194 TT-GU24 | BZ, TT |
| 2195 TT | 6" W | 25¼" | 6¾" | 12½" | 4½" Square Back Plate | | 2-100w Med. | 2195 TT-GU24 | BZ, TT |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

Dorian's robust design in durable aluminum construction is offered in either Titanium or Bronze finishes. This contemporary fixture allows light to emit from white etched glass windows on five sides.

DORIAN™

Bronze FINISH
Clear Painted White Inside GLASS



2192 BZ
2192 BZ-GU24



2195 BZ
2195 BZ-GU24



2190 BZ
2190 BZ-GU24



2194 BZ
2194 BZ-GU24



2191 BZ
2191 BZ-GU24

DORIAN Bronze (BZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-----------------------|----------------|-------------|-------------------------------------------------------------------------------------------|-----------------------|
| 2190 BZ | 6" W | 12¼" | 6¾" | 6¼" | 4½" Square Back Plate | | 1-100w Med. | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | BZ, TT |
| 2191 BZ | 6" W | 20¾" | | | 3" Dia. Post Fitter | | 1-100w Med. | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | BZ, TT |
| 2192 BZ | 6" W | 18¼" | | | 5" Dia. Canopy | 6' Wire | 1-100w Med. | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | BZ, TT |
| 2194 BZ | 6" W | 18¼" | 6¾" | 9¼" | 4½" Square Back Plate | | 1-100w Med. | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | BZ, TT |
| 2195 BZ | 6" W | 25¼" | 6¾" | 12½" | 4½" Square Back Plate | | 2-100w Med. | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | BZ, TT |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

SOLARA™

Solara offers a chic, modern style with solid aluminum construction in a wall pocket mounting. The bottom lens provides optimal down lighting.

FINISH Titanium

GLASS Inside White Etched



2026 TT
2026 TT-GU24



2027 TT



2020 TT
2020 TT-GU24



side view of 2021 TT



2024 TT
2024 TT-GU24



2025 TT
2025 TT-GU24



2021 TT
2021 TT-GU24



SOLARA Titanium (TT)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | | AVAILABLE FINISHES | ADA |
|---------|----------------|---------|--------|------------------|----------------------------|-------------|---------------------------------------------------------------------------------------|--|-----------------------|-----|
| | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | | | |
| 2020 TT | 9" W | 9" | 4" | 3/4" | 9" Square Back Plate | 1-100w Med. | 2020 TT-GU24 | | BZ, TT | • |
| 2021 TT | 8" Dia. | 20 1/2" | | | 3" Dia. Post Fitter | 1-100w Med. | 2021 TT-GU24 | | BZ, TT | |
| 2024 TT | 9" W | 15 1/2" | 4" | 4" | 9" W, 15 1/2" H Back Plate | 1-100w Med. | 2024 TT-GU24 | | BZ, TT | • |
| 2025 TT | 9" W | 22" | 4" | 4" | 9" W, 22" H Back Plate | 2-100w Med. | 2025 TT-GU24 | | BZ, TT | • |
| 2026 TT | 6" W | 14" | 3 1/2" | 6" | 6" W, 14" H Back Plate | 1-100w Med. | 2026 TT-GU24 | | BZ, TT | • |
| 2027 TT | 6" W | 14" | 3 1/2" | 6" | 6" W, 14" H Back Plate | 1-24w CFL* | | | BZ, TT | • |

*CFL bulb included. For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

Solara offers a chic, modern style with solid aluminum construction in a wall pocket mounting. The bottom lens provides optimal down lighting.

Bronze FINISH
Inside White Etched GLASS

SOLARA™



side view of 2021 BZ



2020 BZ
2020 BZ-GU24



2026 BZ
2026 BZ-GU24



2027 BZ



2021 BZ
2021 BZ-GU24



2025 BZ
2025 BZ-GU24



2024 BZ
2024 BZ-GU24



SOLARA Bronze (BZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOPTO OUTLET | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | | AVAILABLE FINISHES | ADA |
|---------|----------------|---------|--------|-----------------|----------------------------|-------------|---------------------------------------------------------------------------------------|--|-----------------------|-----|
| | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | | | |
| 2020 BZ | 9" W | 9" | 4" | 3/4" | 9" Square Back Plate | 1-100w Med. | 2020 BZ-GU24 | | BZ, TT | • |
| 2021 BZ | 8" Dia. | 20 1/2" | | | 3" Dia. Post Fitter | 1-100w Med. | 2021 BZ-GU24 | | BZ, TT | |
| 2024 BZ | 9" W | 15 1/2" | 4" | 4" | 9" W, 15 1/2" H Back Plate | 1-100w Med. | 2024 BZ-GU24 | | BZ, TT | • |
| 2025 BZ | 9" W | 22" | 4" | 4" | 9" W, 22" H Back Plate | 2-100w Med. | 2025 BZ-GU24 | | BZ, TT | • |
| 2026 BZ | 6" W | 14" | 3 1/2" | 6" | 6" W, 14" H Back Plate | 1-100w Med. | 2026 BZ-GU24 | | BZ, TT | • |
| 2027 BZ | 6" W | 14" | 3 1/2" | 6" | 6" W, 14" H Back Plate | 1-24w CFL* | | | BZ, TT | • |

*CFL bulb included. For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

ARIA™

Aria is a contemporary style that effortlessly complements the façade of any exterior. Its modern shape in durable aluminum is enhanced by a stainless steel mesh shade. Aria comes standard Dark Sky compliant.

FINISH Buckeye Bronze

GLASS Stainless Steel Mesh

DARK SKY 



2305 KZ
2305 KZ-GU24



2305 KZ-LED





2302 KZ
2302 KZ-GU24

2302 KZ-LED




2300 KZ
2300 KZ-GU24

2300 KZ-LED




2306 KZ
2306 KZ-GU24




2306 KZ-LED




2304 KZ
2304 KZ-GU24

2304 KZ-LED


ARIA Buckeye Bronze (KZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE | STEMS INCLUDED | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------------------|------|------------------|-------------------------|-------------|-------------------|-------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------|-----------------------|
| | | | | | | | | |  GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. |  LED Includes high efficiency LED light source. |  LED LIGHT ENGINE | |
| 2300 KZ | 5" W | 15½" | 6¾" | 5" | 4½" W, 8¼" H Back Plate | | | 1-75w Med. | 2300 KZ-GU24 | 2300 KZ-LED | DSLML-40 | KZ |
| 2302 KZ | 5" Dia. | 19¼" 51½" Max.* | | | 6" Dia. Canopy | 10' Wire | 1-6", 2-12" | 1-100w Med. | 2302 KZ-GU24 | 2302 KZ-LED | DSLML-40 | KZ |
| 2304 KZ | 5" W | 18½" | 6¾" | 5" | 4½" W, 8¼" H Back Plate | | | 1-100w Med. | 2304 KZ-GU24 | 2304 KZ-LED | DSLML-40 | KZ |
| 2305 KZ | 7" W | 21¾" | 8¾" | 5" | 4½" W, 8¼" H Back Plate | | | 1-100w Med. | 2305 KZ-GU24 | 2305 KZ-LED | DSLML-40 | KZ |
| 2306 KZ | 4½" W | 14½" | 4¾" | 5" | 4½" W, 8¼" H Back Plate | | | 1-100w Med. | 2306 KZ-GU24 | 2306 KZ-LED | DSLML-40 | KZ |
| 4312 KZ | ½" Dia. | 12" (stem) | | | | | | | | | | KZ |

*Maximum achievable height with stems included. Additional stems available, see above. Aria comes standard Dark Sky compliant. Reflector type or Par type lamp recommended. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

SHELTER™

Shelter's minimalist style in solid aluminum creates a chic, dramatic statement as the light from above grazes through its clear seedy glass. Shelter comes standard Dark Sky compliant.

FINISH Hematite

GLASS Clear Seedy

DARK SKY 





1325 HE
1325 HE-GU24



1325 HE-LED







1322 HE
1322 HE-GU24

1322 HE-LED





1326 HE
1326 HE-GU24

1326 HE-LED





1324 HE
1324 HE-GU24

1324 HE-LED




1320 HE
1320 HE-LED




1321 HE
1321 HE-GU24

1321 HE-LED


SHELTER Hematite (HE)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE | STEMS INCLUDED | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------------------|------|------------------|-------------------------|-------------|-------------------|-------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1320 HE | 6¼" W | 15½" | 6½" | 5¾" | 4½" W, 12" H Back Plate | | | 1-75w Med. | | 1320 HE-LED | UNI-60 | BK, HE, KZ |
| 1321 HE | 8¼" Dia. | 27¾" | | | 3" Dia. Post Fitter | | | 1-100w Med. | 1321 HE-GU24 | 1321 HE-LED | UNI-100 | BK, HE, KZ |
| 1322 HE | 6¼" Dia. | 21¾", 54" Max.* | | | 6" Dia. Canopy | 10" Wire | 1-6", 2-12" | 1-100w Med. | 1322 HE-GU24 | 1322 HE-LED | UNI-100 | BK, HE, KZ |
| 1324 HE | 6¼" W | 20½" | 6½" | 5¾" | 4½" W, 12" H Back Plate | | | 1-100w Med. | 1324 HE-GU24 | 1324 HE-LED | UNI-100 | BK, HE, KZ |
| 1325 HE | 8¼" W | 23¼" | 8½" | 5¾" | 4½" W, 12" H Back Plate | | | 1-100w Med. | 1325 HE-GU24 | 1325 HE-LED | UNI-100 | BK, HE, KZ |
| 1326 HE | 4½" W | 15½" | 4¾" | 5¾" | 4½" W, 12" H Back Plate | | | 1-60w Med. | 1326 HE-GU24 | 1326 HE-LED | DSLML-40 | BK, HE, KZ |
| 4312 HE | ½" Dia. | 12" (stem) | | | | | | | | | | BK, HE, KZ |

*Maximum achievable height with stems included. Additional stems available, see above. Shelter comes standard Dark Sky compliant. Reflector type or Par type lamp recommended. For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

SHELTER™

Shelter's minimalist style in solid aluminum creates a chic, dramatic statement as the light from above grazes through its clear seedy glass. Shelter comes standard Dark Sky compliant.

FINISH Black

GLASS Clear Seedy

DARK SKY 



1325 BK
1325 BK-GU24



1325 BK-LED





SHELTER Black (BK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE | STEMS INCLUDED | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------------------|------|------------------|-------------------------|-------------|-------------------|-------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1320 BK | 6¼" W | 15½" | 6½" | 5¾" | 4½" W, 12" H Back Plate | | | 1-75w Med. | | 1320 BK-LED | UNI-60 | BK, HE, KZ |
| 1321 BK | 8¼" Dia. | 27¾" | | | 3" Dia. Post Fitter | | | 1-100w Med. | 1321 BK-GU24 | 1321 BK-LED | UNI-100 | BK, HE, KZ |
| 1322 BK | 6¼" Dia. | 21¾", 54" Max.* | | | 6" Dia. Canopy | 10' Wire | 1-6", 2-12" | 1-100w Med. | 1322 BK-GU24 | 1322 BK-LED | UNI-100 | BK, HE, KZ |
| 1324 BK | 6¼" W | 20½" | 6½" | 5¾" | 4½" W, 12" H Back Plate | | | 1-100w Med. | 1324 BK-GU24 | 1324 BK-LED | UNI-100 | BK, HE, KZ |
| 1325 BK | 8¼" W | 23¾" | 8½" | 5¾" | 4½" W, 12" H Back Plate | | | 1-100w Med. | 1325 BK-GU24 | 1325 BK-LED | UNI-100 | BK, HE, KZ |
| 1326 BK | 4½" W | 15½" | 4¾" | 5¾" | 4½" W, 12" H Back Plate | | | 1-60w Med. | 1326 BK-GU24 | 1326 BK-LED | DSL-40 | BK, HE, KZ |
| 1328 BK | 8¼" Dia. | 24½", 57" Max.* | | | 6" Dia. Canopy | 10' Wire | 1-6", 2-12" | 1-100w Med. | 1328 BK-GU24 | 1328 BK-LED | UNI-100 | BK |
| 4312 BK | ½" Dia. | 12" (stem) | | | | | | | | | | BK, HE, KZ |

*Maximum achievable height with stems included. Additional stems available, see above. Shelter comes standard Dark Sky compliant. Reflector type or Par type lamp recommended. For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

SHELTER™

Shelter's minimalist style in solid aluminum creates a chic, dramatic statement as the light from above grazes through its clear seedy glass. Shelter comes standard Dark Sky compliant.

FINISH Buckeye Bronze

GLASS Clear Seedy

DARK SKY 





1325 KZ
1325 KZ-GU24





1325 KZ-LED






1322 KZ
1322 KZ-GU24

1322 KZ-LED






1326 KZ
1326 KZ-GU24

1326 KZ-LED




1320 KZ
1320 KZ-LED




1324 KZ
1324 KZ-GU24

1324 KZ-LED




1321 KZ
1321 KZ-GU24

1321 KZ-LED


SHELTER Buckeye Bronze (KZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACKPLATE/CANOPY | WIRE | STEMS INCLUDED | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------------------|------|------------------|-------------------------|-------------|-------------------|-------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1320 KZ | 6¼" W | 15½" | 6½" | 5¾" | 4½" W, 12" H Back Plate | | | 1-75w Med. | | 1320 KZ-LED | UNI-60 | BK, HE, KZ |
| 1321 KZ | 8¼" Dia. | 27¾" | | | 3" Dia. Post Fitter | | | 1-100w Med. | 1321 KZ-GU24 | 1321 KZ-LED | UNI-100 | BK, HE, KZ |
| 1322 KZ | 6¼" Dia. | 21¾", 54" Max.* | | | 6" Dia. Canopy | 10' Wire | 1-6", 2-12" | 1-100w Med. | 1322 KZ-GU24 | 1322 KZ-LED | UNI-100 | BK, HE, KZ |
| 1324 KZ | 6¼" W | 20½" | 6½" | 5¾" | 4½" W, 12" H Back Plate | | | 1-100w Med. | 1324 KZ-GU24 | 1324 KZ-LED | UNI-100 | BK, HE, KZ |
| 1325 KZ | 8¼" W | 23¼" | 8½" | 5¾" | 4½" W, 12" H Back Plate | | | 1-100w Med. | 1325 KZ-GU24 | 1325 KZ-LED | UNI-100 | BK, HE, KZ |
| 1326 KZ | 4½" W | 15½" | 4¾" | 5¾" | 4½" W, 12" H Back Plate | | | 1-60w Med. | 1326 KZ-GU24 | 1326 KZ-LED | DLSLM-40 | BK, HE, KZ |
| 4312 KZ | ½" Dia. | 12" (stem) | | | | | | | | | | BK, HE, KZ |

*Maximum achievable height with stems included. Additional stems available, see above. Shelter comes standard Dark Sky compliant. Reflector type or Par type lamp recommended. For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

SULLIVAN™

Sullivan's clean transitional style features a minimalist cast aluminum body that frames the contemporary, candle-like etched opal glass. A large cast ring finial is mounted on top for a traditional finishing touch to this sleek lantern design.

FINISH Hematite

GLASS Etched Opal



1741 HE
1741 HE-GU24



1744 HE
1744 HE-GU24



1745 HE
1745 HE-GU24



SULLIVAN Hematite (HE)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | |
|---------|----------------|--------|------|------------------|-------------------------|-------------|---------------------------------------------------------------------------------------|-----------------------|
| | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | AVAILABLE FINISHES |
| 1741 HE | 11¾" W | 26" | | | 3" Dia. Post Fitter | 1-100w Med. | 1741 HE-GU24 | BK, HE |
| 1744 HE | 9" W | 18¾" | 10" | 11¾" | 5" W, 11¾" H Back Plate | 1-100w Med. | 1744 HE-GU24 | BK, HE |
| 1745 HE | 11¾" W | 23" | 12¾" | 15¾" | 5" W, 15¾" H Back Plate | 1-100w Med. | 1745 HE-GU24 | BK, HE |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

Sullivan's clean transitional style features a minimalist cast aluminum body that frames the contemporary, candle-like etched opal glass. A large cast ring finial is mounted on top for a traditional finishing touch to this sleek lantern design.

Black **FINISH**
Etched Opal **GLASS**

SULLIVAN™



1745 BK
1745 BK-GU24



1744 BK
1744 BK-GU24



1741 BK
1741 BK-GU24



SULLIVAN Black (BK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|-------------|--------------------------------------------------------------------------------------------------|-----------------------|
| 1741 BK | 11¾" W | 26" | | | 3" Dia. Post Fitter | 1-100w Med. | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | BK, HE |
| 1744 BK | 9" W | 18¼" | 10" | 11¾" | 5" W, 11¾" H Back Plate | 1-100w Med. | | BK, HE |
| 1745 BK | 11¾" W | 23" | 12¾" | 15¼" | 5" W, 15¼" H Back Plate | 1-100w Med. | | BK, HE |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

REEF™

Reef's contemporary nautical shape features a sleek capsule of inside etched glass captured by bold rings of cast aluminum.

FINISH Hematite

GLASS Inside Etched



1956 HE
1956 HE-GU24



1950 HE
1950 HE-GU24



1951 HE
1951 HE-GU24



1954 HE
1954 HE-GU24



1952 HE
1952 HE-GU24



REEF Hematite (HE)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|--------------------|--------|
| | | | | | | | | AVAILABLE FINISHES | |
| 1950 HE | 7¾" W | 10¾" | 8¾" | 4" | 4½" W, 7" H Back Plate | | 1-75w Med. | 1950 HE-GU24 | HE, VZ |
| 1951 HE | 9" Dia. | 16¾" | | | 3" Dia. Post Fitter | | 1-100w Med. | 1951 HE-GU24 | HE, VZ |
| 1952 HE | 9" Dia. | 15" | | | 5½" Dia. Canopy | 6', 5' | 1-100w Med. | 1952 HE-GU24 | HE, VZ |
| 1954 HE | 9" W | 12¾" | 10" | 4¼" | 4½" W, 7" H Back Plate | | 1-100w Med. | 1954 HE-GU24 | HE, VZ |
| 1956 HE | 5½" W | 8" | 6½" | 2¾" | 4½" W, 5¼" H Back Plate | | 1-60w Med. | 1956 HE-GU24 | HE, VZ |

ECO-OPTIONS

GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps.

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

Reef's contemporary nautical shape features a sleek capsule of inside etched glass captured by bold rings of cast aluminum.

Victorian Bronze **FINISH**
Inside Etched **GLASS**

REEF™



1952 VZ
1952 VZ-GU24



1950 VZ
1950 VZ-GU24



1956 VZ
1956 VZ-GU24



1954 VZ
1954 VZ-GU24



1951 VZ
1951 VZ-GU24



REEF Victorian Bronze (VZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-------------------------------------------------------------------------------------------|-----------------------|
| 1950 VZ | 7¾" W | 10¾" | 8¾" | 4" | 4½" W, 7" H Back Plate | | 1-75w Med. | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | HE, VZ |
| 1951 VZ | 9" Dia. | 16¼" | | | 3" Dia. Post Fitter | | 1-100w Med. | | HE, VZ |
| 1952 VZ | 9" Dia. | 15" | | | 5½" Dia. Canopy | 6', 5' | 1-100w Med. | | HE, VZ |
| 1954 VZ | 9" W | 12¾" | 10" | 4¼" | 4½" W, 7" H Back Plate | | 1-100w Med. | | HE, VZ |
| 1956 VZ | 5½" W | 8" | 6½" | 2¾" | 4½" W, 5¼" H Back Plate | | 1-60w Med. | | HE, VZ |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

PEMBROOK™

Pembrook is a classic, all-American style traditional hanging wall lantern featuring solid aluminum construction with cast ball knob detailing and acorn shaped glass.

FINISH Spanish Bronze

GLASS Etched Opal



2084 SB
2084 SB-LED





2082 SB
2082 SB-LED



2080 SB
2080 SB-LED



2081 SB
2081 SB-LED



PEMBROOK Spanish Bronze (SB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | |
|---------|----------------|--------|------|------------------|---------------------|----------------|-------------|-------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | AVAILABLE FINISHES |
| 2080 SB | 10" W | 13¾" | 10½" | 4¼" | 6" Dia. Back Plate | | 1-100w Med. | 2080 SB-LED | UNI-100 | SB |
| 2081 SB | 13¾" W | 18" | | | 3" Dia. Post Fitter | | 1-100w Med. | 2081 SB-LED | UNI-100 | SB |
| 2082 SB | 10" Dia. | 14¾" | | | 6" Dia. Canopy | 6', 5' | 1-100w Med. | 2082 SB-LED | UNI-100 | SB |
| 2084 SB | 12" W | 15¾" | 13" | 4¼" | 6" Dia. Back Plate | | 1-100w Med. | 2084 SB-LED | UNI-100 | SB |

For posts and pier mounts, see pages 613-614. For LED specifications, see pages 412-413.

FREEPORT™

Freeport features a classic New England design in cast aluminum construction for timeless, traditional style.

FINISH Oil Rubbed Bronze

GLASS Clear Seedy



1805 OZ
1805 OZ-GU24



1805 OZ-LED





1802 OZ
1802 OZ-GU24

1802 OZ-LED




1804 OZ
1804 OZ-GU24

1804 OZ-LED







1800 OZ
1800 OZ-GU24

1800 OZ-LED




1801 OZ
1801 OZ-GU24


FREEMONT Oil Rubbed Bronze (OZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES | | | |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-----------------------|-------------|---------|------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | | | | |
| 1800 OZ | 6" W | 9¼" | 7" | 2½" | 4½" W, 6" H Back Plate | | 1-75w Med. |  | | | 1800 OZ-GU24 | 1800 OZ-LED | UNI-60 | BK, OP, OZ |
| 1801 OZ | 10" Dia. | 20¼" | | | 3" Dia. Post Fitter | | 1-100w Med. | |  | | 1801 OZ-GU24 | | | BK, OP, OZ |
| 1802 OZ | 10" Dia. | 14" | | | 4¼" Dia. Canopy | 6', 5' | 1-100w Med. | | |  | 1802 OZ-GU24 | 1802 OZ-LED | UNI-100 | BK, OP, OZ |
| 1804 OZ | 8" W | 12¼" | 9" | 3" | 5" W, 8" H Back Plate | | 1-100w Med. | | | | 1804 OZ-GU24 | 1804 OZ-LED | UNI-100 | BK, OP, OZ |
| 1805 OZ | 10" W | 15¼" | 11¼" | 3¼" | 5¾" W, 9½" H Back Plate | | 1-100w Med. | | | | 1805 OZ-GU24 | 1805 OZ-LED | UNI-100 | BK, OP, OZ |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

FREEPORT™

Freeport features a classic New England design in cast aluminum construction for timeless, traditional style.

FINISH Black
GLASS Clear Seedy



1804 BK
1804 BK-GU24


1804 BK-LED




1800 BK
1800 BK-GU24

1800 BK-LED




1801 BK
1801 BK-GU24




1805 BK
1805 BK-GU24










1805 BK-LED




1802 BK
1802 BK-GU24

1802 BK-LED


FREEPORT Black (BK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|----------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1800 BK | 6" W | 9¼" | 7" | 2½" | 4½" W, 6" H Back Plate | | 1-75w Med. |  1800 BK-GU24 |  1800 BK-LED | UNI-60 | BK, OP, OZ |
| 1801 BK | 10" Dia. | 20¼" | | | 3" Dia. Post Fitter | | 1-100w Med. |  1801 BK-GU24 | | | BK, OP, OZ |
| 1802 BK | 10" Dia. | 14" | | | 4¼" Dia. Canopy | 6', 5' | 1-100w Med. |  1802 BK-GU24 |  1802 BK-LED | UNI-100 | BK, OP, OZ |
| 1804 BK | 8" W | 12¼" | 9" | 3" | 5" W, 8" H Back Plate | | 1-100w Med. |  1804 BK-GU24 |  1804 BK-LED | UNI-100 | BK, OP, OZ |
| 1805 BK | 10" W | 15¼" | 11¼" | 3¼" | 5¾" W, 9½" H Back Plate | | 1-100w Med. |  1805 BK-GU24 |  1805 BK-LED | UNI-100 | BK, OP, OZ |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

Freeport features a classic New England design in cast aluminum construction for timeless, traditional style.

FREEPORT™

Olde Penny FINISH
Etched Seedy GLASS



FREEPORT Olde Penny (OP)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1800 OP | 6" W | 9¼" | 7" | 2½" | 4½" W, 6" H Back Plate | | 1-75w Med. | 1800 OP-GU24 | 1800 OP-LED | UNI-60 | BK, OP, OZ |
| 1801 OP | 10" Dia. | 20¼" | | | 3" Dia. Post Fitter | | 1-100w Med. | 1801 OP-GU24 | | | BK, OP, OZ |
| 1802 OP | 10" Dia. | 14" | | | 4¼" Dia. Canopy | 6', 5' | 1-100w Med. | 1802 OP-GU24 | 1802 OP-LED | UNI-100 | BK, OP, OZ |
| 1804 OP | 8" W | 12¼" | 9" | 3" | 5" W, 8" H Back Plate | | 1-100w Med. | 1804 OP-GU24 | 1804 OP-LED | UNI-100 | BK, OP, OZ |
| 1805 OP | 10" W | 15¼" | 11¼" | 3¼" | 5¾" W, 9½" H Back Plate | | 1-100w Med. | 1805 OP-GU24 | 1805 OP-LED | UNI-100 | BK, OP, OZ |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

HARBOR™

Harbor has an updated nautical feel, with a style inspired by the clean, strong lines of a welcoming lighthouse. The cast aluminum and brass construction is accented by bold stripes against the seedy glass.


FINISH Titanium

GLASS Etched Seedy Bound



Harbor path lights are available in the Hinkley Landscape Lighting catalog.

Scan to view a video of the Harbor collection.



2579 TT
2579 TT-GU24



2579 TT-LED





2572 TT
2572 TT-GU24
2572 TT-LED



2575 TT
2575 TT-GU24
2575 TT-LED



2573 TT
2573 TT-GU24



2570 TT
2570 TT-GU24



2574 TT
2574 TT-GU24
2574 TT-LED



2576 TT
(pier mount)
2576 TT-GU24
2576 TT-LED



2571 TT
2571 TT-GU24
2571 TT-LED

HARBOR Titanium (TT)

ECO-OPTIONS

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | AVAILABLE FINISHES | |
|---------|----------------|--------|------|------------------|--------------------------|----------------|-------------|-------------------------------------------------------------------------------------------|------------------------------------------------------------------------|-----------------------|------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | | |
| 2570 TT | 7" W | 10½" | 7¾" | 4¾" | 4½" W, 7" H Back Plate | | 1-60w Med. | 2570 TT-GU24 | 2570 TT-LED | UNI-100 | AR, SK, TT |
| 2571 TT | 11" W | 19½" | | | 3" Dia. Post Fitter | | 1-100w Med. | 2571 TT-GU24 | 2571 TT-LED | UNI-100 | AR, SK, TT |
| 2572 TT | 11" W | 19" | | | 5" Dia. Canopy | 6', 5' | 1-100w Med. | 2572 TT-GU24 | 2572 TT-LED | UNI-100 | AR, SK, TT |
| 2573 TT | 12¼" W | 7" | | | | | 2-60w Med. | 2573 TT-GU24 | | | AR, SK, TT |
| 2574 TT | 9" W | 13½" | 10" | 6" | 4½" W, 9" H Back Plate | | 1-75w Med. | 2574 TT-GU24 | 2574 TT-LED | UNI-60 | AR, SK, TT |
| 2575 TT | 11" W | 16¼" | 11¾" | 8" | 4½" W, 12" H Back Plate | | 1-100w Med. | 2575 TT-GU24 | 2575 TT-LED | UNI-100 | AR, SK, TT |
| 2576 TT | 11" W | 17" | | | 8" Square Base | | 1-100w Med. | 2576 TT-GU24 | 2576 TT-LED | UNI-100 | AR, SK, TT |
| 2579 TT | 13" W | 20½" | 13¼" | 13¾" | 4½" W, 14¼" H Back Plate | | 1-100w Med. | 2579 TT-GU24 | 2579 TT-LED | UNI-100 | AR, SK, TT |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

HARBOR™

Harbor has an updated nautical feel, with a style inspired by the clean, strong lines of a welcoming lighthouse. The cast aluminum and brass construction is accented by bold stripes against the seedy glass.


FINISH Anchor Bronze

GLASS Etched Seedy Bound



Harbor path lights are available in the Hinkley Landscape Lighting catalog.

Scan to view a video of the Harbor collection.



2579 AR
2579 AR-GU24



2579 AR-LED





2572 AR
2572 AR-GU24
2572 AR-LED



2575 AR
2575 AR-GU24
2575 AR-LED



2573 AR
2573 AR-GU24



2570 AR
2570 AR-GU24



2574 AR
2574 AR-GU24
2574 AR-LED



2576 AR
(pier mount)
2576 AR-GU24
2576 AR-LED



2571 AR
2571 AR-GU24
2571 AR-LED

HARBOR Anchor Bronze (AR)

ECO-OPTIONS

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|--------------------------|----------------|-------------|-------------------------------------------------------------------------------------------|------------------------------------------------------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | |
| 2570 AR | 7" W | 10½" | 7¾" | 4¾" | 4½" W, 7" H Back Plate | | 1-60w Med. | 2570 AR-GU24 | | AR, SK, TT |
| 2571 AR | 11" W | 19½" | | | 3" Dia. Post Fitter | | 1-100w Med. | 2571 AR-GU24 | 2571 AR-LED | UNI-100 AR, SK, TT |
| 2572 AR | 11" W | 19" | | | 5" Dia. Canopy | 6', 5' | 1-100w Med. | 2572 AR-GU24 | 2572 AR-LED | UNI-100 AR, SK, TT |
| 2573 AR | 12¼" W | 7" | | | | | 2-60w Med. | 2573 AR-GU24 | | AR, SK, TT |
| 2574 AR | 9" W | 13½" | 10" | 6" | 4½" W, 9" H Back Plate | | 1-75w Med. | 2574 AR-GU24 | 2574 AR-LED | UNI-60 AR, SK, TT |
| 2575 AR | 11" W | 16¼" | 11¾" | 8" | 4½" W, 12" H Back Plate | | 1-100w Med. | 2575 AR-GU24 | 2575 AR-LED | UNI-100 AR, SK, TT |
| 2576 AR | 11" W | 17" | | | 8" Square Base | | 1-100w Med. | 2576 AR-GU24 | 2576 AR-LED | UNI-100 AR, SK, TT |
| 2579 AR | 13" W | 20½" | 13¼" | 13¾" | 4½" W, 14¼" H Back Plate | | 1-100w Med. | 2579 AR-GU24 | 2579 AR-LED | UNI-100 AR, SK, TT |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

HARBOR™

Harbor has an updated nautical feel, with a style inspired by the clean, strong lines of a welcoming lighthouse. The cast aluminum and brass construction is accented by bold stripes against the seedy glass.


FINISH Satin Black

GLASS Etched Seedy Bound



Harbor path lights are available in the Hinkley Landscape Lighting catalog.

Scan to view a video of the Harbor collection.



2579 SK
2579 SK-GU24



2579 SK-LED





2572 SK
2572 SK-GU24


2572 SK-LED




2575 SK
2575 SK-GU24

2575 SK-LED






2573 SK
2573 SK-GU24






2570 SK
2570 SK-GU24




2574 SK
2574 SK-GU24

2574 SK-LED




2576 SK
(pier mount)
2576 SK-GU24

2576 SK-LED




















2571 SK
2571 SK-GU24

2571 SK-LED


HARBOR Satin Black (SK)

ECO-OPTIONS

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|--------------------------|----------------|-------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|
| | | | | | | | |  GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. |  LED Includes integrated high efficiency LED light source. | |
| 2570 SK | 7" W | 10½" | 7¾" | 4¾" | 4½" W, 7" H Back Plate | | 1-60w Med. |  | | AR, SK, TT |
| 2571 SK | 11" W | 19½" | | | 3" Dia. Post Fitter | | 1-100w Med. |  |  | AR, SK, TT |
| 2572 SK | 11" W | 19" | | | 5" Dia. Canopy | 6', 5' | 1-100w Med. |  |  | AR, SK, TT |
| 2573 SK | 12¼" W | 7" | | | | | 2-60w Med. |  | | AR, SK, TT |
| 2574 SK | 9" W | 13½" | 10" | 6" | 4½" W, 9" H Back Plate | | 1-75w Med. |  |  | AR, SK, TT |
| 2575 SK | 11" W | 16¼" | 11¾" | 8" | 4½" W, 12" H Back Plate | | 1-100w Med. |  |  | AR, SK, TT |
| 2576 SK | 11" W | 17" | | | 8" Square Base | | 1-100w Med. |  |  | AR, SK, TT |
| 2579 SK | 13" W | 20½" | 13¼" | 13¾" | 4½" W, 14¼" H Back Plate | | 1-100w Med. |  |  | AR, SK, TT |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

SIERRA™

Sierra's transitional style has an organic elegance with a natural stone centerpiece and panels of clear seedy glass. The solid aluminum construction in a Spanish Bronze finish completes its chic style.

FINISH Spanish Bronze

GLASS Stone and Clear Seedy



1454 SB
1454 SB-GU24



1450 SB
1450 SB-GU24



1455 SB
1455 SB-GU24



1452 SB
1452 SB-GU24



SIERRA Spanish Bronze (SB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOPTO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | |
|---------|----------------|--------|------|-----------------|-----------------------|----------------|------------|--------------------|-------------------------------------------------------------------------------------------|
| | | | | | | | | AVAILABLE FINISHES | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. |
| 1450 SB | 6" W | 8" | 7" | 4" | 5" W, 5" H Back Plate | | 1-75w Med. | 1450 SB-GU24 | SB |
| 1452 SB | 6" W | 13" | | | 4½" Dia. Canopy | 6', 5' | 1-75w Med. | 1452 SB-GU24 | SB |
| 1454 SB | 6" W | 13" | 7" | 6½" | 5" W, 7" H Back Plate | | 1-75w Med. | 1454 SB-GU24 | SB |
| 1455 SB | 7" W | 15" | 8" | 7½" | 5" W, 7" H Back Plate | | 1-75w Med. | 1455 SB-GU24 | SB |

For Fluorescent/GU24 lamps, see pages 412-413.

Mondrian's unique patterned glass adds a geometric panache to the durable brass and aluminum construction. These chic pocket style wall mounted lanterns are ADA compliant.

Buckeye Bronze **FINISH**
Art Glass Panels **GLASS**

MONDRIAN™

Mondrian Chandeliers,
pages 106-107




2150 KZ



2154 KZ

MONDRIAN Buckeye Bronze (KZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | BULBS | AVAILABLE FINISHES |  ADA |
|---------|----------------|--------|------|------------------|-------------------------|-------------|-----------------------|----------------------------------------------------------------------------------------------|
| 2150 KZ | 7" W | 11" | 4" | 5½" | 7" W, 10¼" H Back Plate | 1-60w Cand. | KZ | • |
| 2154 KZ | 9" W | 14¼" | 4" | 7¼" | 9" W, 13¼" H Back Plate | 2-60w Cand. | KZ | • |

MANHATTAN™

Manhattan is a classic update to the traditional train station lantern. The hand-painted Olde Bronze finish complements the clean lines of its durable die cast construction.

FINISH Olde Bronze

GLASS Etched Seedy



2235 OZ
2235 OZ-GU24



2235 OZ-LED





2232 OZ
2232 OZ-GU24

2232 OZ-LED


2234 OZ
2234 OZ-GU24

2234 OZ-LED












2230 OZ
2230 OZ-GU24

2230 OZ-LED


2231 OZ
2231 OZ-GU24

2231 OZ-LED


MANHATTAN Olde Bronze (OZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|----------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 2230 OZ | 7¼" W | 11¾" | 8" | 2½" | 4½" W, 5¾" H Back Plate | | 1-100w Med. |  2230 OZ-GU24 |  2230 OZ-LED | UNI-60 | OZ |
| 2231 OZ | 11¼" W | 21½" | | | 3" Dia. Post Fitter | | 1-100w Med. |  2231 OZ-GU24 |  2231 OZ-LED | UNI-100 | OZ |
| 2232 OZ | 11¼" W | 19¼" | | | | 6', 5' | 1-100w Med. |  2232 OZ-GU24 |  2232 OZ-LED | UNI-100 | OZ |
| 2234 OZ | 9¼" W | 15" | 10¼" | 3¼" | 5¼" W, 8" H Back Plate | | 1-100w Med. |  2234 OZ-GU24 |  2234 OZ-LED | UNI-100 | OZ |
| 2235 OZ | 11¼" W | 18½" | 12½" | 3¾" | 7¼" W, 12" H Back Plate | | 1-100w Med. |  2235 OZ-GU24 |  2235 OZ-LED | UNI-100 | OZ |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413. When fitted with DSL-40, this item is Dark Sky compliant, see pages 412-413.

For Eco Details, see pages 412-413. For an explanation of icons, see page 8.

LEDGEWOOD™

Ledgewood's bold cast aluminum construction features a unique oval shaped, overscaled design with elegant, clean line details.

FINISH Vintage Black

GLASS Cased Opal



Ledgewood path lights are available in the Hinkley Landscape Lighting catalog.



1129 VK
1129 VK-GU24





1122 VK
1122 VK-GU24



1124 VK
1124 VK-GU24



1125 VK
1125 VK-GU24



1126 VK
1126 VK-GU24



1120 VK
1120 VK-GU24



1121 VK
1121 VK-GU24

LEDGEWOOD Vintage Black (VK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOPTO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | AVAILABLE FINISHES |
|---------|----------------|--------|------|-----------------|-------------------------|----------------|-------------|-------------------------------------------------------------------------------------|-----------------------|
| 1120 VK | 7½" W | 10½" | 6½" | 6" | 4½" W, 7" H Back Plate | | 1-60w Med. | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | MR, VK |
| 1121 VK | 13" W | 20¾" | | | 3" Dia. Post Fitter | | 1-100w Med. | | MR, VK |
| 1122 VK | 13" W | 19¾" | | | 5" Dia. Canopy | 6', 5' | 1-100w Med. | | MR, VK |
| 1124 VK | 8" W | 12" | 7¼" | 6¾" | 4½" W, 10" H Back Plate | | 1-75w Med. | | MR, VK |
| 1125 VK | 10" W | 15½" | 9¼" | 8¾" | 4½" W, 10" H Back Plate | | 1-100w Med. | | MR, VK |
| 1126 VK | 6½" W | 7¼" | 6" | 3¾" | 4½" W, 5½" H Back Plate | | 1-60w Med. | | MR, VK |
| 1129 VK | 13" W | 19½" | 11¼" | 11" | 5" W, 13" H Back Plate | | 1-100w Med. | | MR, VK |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

LEDGEWOOD™

Ledgewood's bold cast aluminum construction features a unique oval shaped, overscaled design with elegant, clean line details.

FINISH Museum Bronze

GLASS Champagne Inside-Etched



Ledgewood path lights are available in the Hinkley Landscape Lighting catalog.



1129 MR
1129 MR-GU24





1122 MR
1122 MR-GU24



1124 MR
1124 MR-GU24



1125 MR
1125 MR-GU24



1126 MR
1126 MR-GU24



1120 MR
1120 MR-GU24



1121 MR
1121 MR-GU24

LEDGEWOOD Museum Bronze (MR)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOPTO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | AVAILABLE FINISHES | |
|---------|----------------|--------|------|-----------------|-------------------------|----------------|-------------|-------------------------------------------------------------------------------------|-----------------------|--------|
| 1120 MR | 7½" W | 10½" | 6½" | 6" | 4½" W, 7" H Back Plate | | 1-60w Med. | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | MR, VK | |
| 1121 MR | 13" W | 20¾" | | | 3" Dia. Post Fitter | | 1-100w Med. | | 1121 MR-GU24 | MR, VK |
| 1122 MR | 13" W | 19¾" | | | 5" Dia. Canopy | 6', 5' | 1-100w Med. | | 1122 MR-GU24 | MR, VK |
| 1124 MR | 8" W | 12" | 7¼" | 6¾" | 4½" W, 10" H Back Plate | | 1-75w Med. | | 1124 MR-GU24 | MR, VK |
| 1125 MR | 10" W | 15½" | 9¼" | 8¾" | 4½" W, 10" H Back Plate | | 1-100w Med. | | 1125 MR-GU24 | MR, VK |
| 1126 MR | 6½" W | 7¼" | 6" | 3¾" | 4½" W, 5½" H Back Plate | | 1-60w Med. | | 1126 MR-GU24 | MR, VK |
| 1129 MR | 13" W | 19½" | 11¼" | 11" | 5" W, 13" H Back Plate | | 1-100w Med. | | 1129 MR-GU24 | MR, VK |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

CASTELLE™

Castelle's transitional style in cast aluminum features clean lines and a ribbed etched glass cylinder accented by etched corner panels, adding to its sophisticated look.

FINISH Black

GLASS Ribbed Etched Cylinder and Etched Corner Panels



1395 BK
1395 BK-GU24





1392 BK
1392 BK-GU24



1390 BK
1390 BK-GU24



1397 BK
(pier mount)
1397 BK-GU24



1396 BK
1396 BK-GU24



1394 BK
1394 BK-GU24



1391 BK
1391 BK-GU24



CASTELLE Black (BK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | |
|---------|----------------|--------|------|------------------|--------------------------|----------------|-------------|---------------------------------------------------------------------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | AVAILABLE FINISHES |
| 1390 BK | 6" W | 15" | 7" | 6¼" | 4¼" W, 12¼" H Back Plate | | 1-100w Med. | 1390 BK-GU24 | BK, BZ |
| 1391 BK | 7" W | 16½" | | | 3" Dia. Post Fitter | | 1-100w Med. | 1391 BK-GU24 | BK, BZ |
| 1392 BK | 7" W | 15¾" | | | 5" Dia. Canopy | 6', 5' | 1-100w Med. | 1392 BK-GU24 | BK, BZ |
| 1394 BK | 7" W | 13¼" | 8¼" | 5¾" | 4¾" W, 10¼" H Back Plate | | 1-100w Med. | 1394 BK-GU24 | BK, BZ |
| 1395 BK | 7" W | 18" | 8¼" | 7" | 4¾" W, 15" H Back Plate | | 1-100w Med. | 1395 BK-GU24 | BK, BZ |
| 1396 BK | 6" W | 11½" | 7" | 4¾" | 4¾" W, 8¾" H Back Plate | | 1-75w Med. | 1396 BK-GU24 | BK, BZ |
| 1397 BK | 8½" W | 12¾" | | | 8½" Square Base | | 1-100w Med. | 1397 BK-GU24 | BK, BZ |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

CASTELLE™

Castelle's transitional style in cast aluminum features clean lines and a ribbed etched amber glass cylinder accented by etched amber corner panels, adding to its sophisticated look.

FINISH Bronze

GLASS Ribbed Etched Amber Cylinder and Etched Amber Corner Panels



1395 BZ
1395 BZ-GU24





1392 BZ
1392 BZ-GU24



1390 BZ
1390 BZ-GU24



1397 BZ
(pier mount)
1397 BZ-GU24



1396 BZ
1396 BZ-GU24



1394 BZ
1394 BZ-GU24



1391 BZ
1391 BZ-GU24

CASTELLE Bronze (BZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | |
|---------|----------------|--------|------|------------------|--------------------------|----------------|-------------|---------------------------------------------------------------------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | AVAILABLE FINISHES |
| 1390 BZ | 6" W | 15" | 7" | 6¼" | 4¼" W, 12¼" H Back Plate | | 1-100w Med. | 1390 BZ-GU24 | BK, BZ |
| 1391 BZ | 7" W | 16½" | | | 3" Dia. Post Fitter | | 1-100w Med. | 1391 BZ-GU24 | BK, BZ |
| 1392 BZ | 7" W | 15¾" | | | 5" Dia. Canopy | 6', 5' | 1-100w Med. | 1392 BZ-GU24 | BK, BZ |
| 1394 BZ | 7" W | 13¼" | 8¼" | 5¾" | 4¾" W, 10¼" H Back Plate | | 1-100w Med. | 1394 BZ-GU24 | BK, BZ |
| 1395 BZ | 7" W | 18" | 8¼" | 7" | 4¾" W, 15" H Back Plate | | 1-100w Med. | 1395 BZ-GU24 | BK, BZ |
| 1396 BZ | 6" W | 11½" | 7" | 4¾" | 4¾" W, 8¾" H Back Plate | | 1-75w Med. | 1396 BZ-GU24 | BK, BZ |
| 1397 BZ | 8½" W | 12¾" | | | 8½" Square Base | | 1-100w Med. | 1397 BZ-GU24 | BK, BZ |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

BOLLA™

The graceful lines of Bolla create a soft elegance, while the solid brass construction and heavy cast ball transitions add to its innovative style.

FINISH Olde Bronze

GLASS Light Amber Seedy



Bolla Chandeliers,
pages 108-119




Bolla Bath,
pages 388-390



Bolla path lights
are available in the
Hinkley Landscape
Lighting catalog.

Scan to view a video of
the Bolla collection.



2639 OB
2639 OB-GU24





BOLLA Olde Bronze (OB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | |
|---------|----------------|--------|------|------------------|--------------------------|----------------|-------------|---------------------------------------------------------------------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | AVAILABLE FINISHES |
| 2630 OB | 7¼" W | 12¼" | 9" | 7" | 4½" W, 7¼" H Back Plate | | 1-60w Med. | 2630 OB-GU24 | BK, OB |
| 2631 OB | 11" W | 20½" | | | 3" Dia. Post Fitter | | 3-40w Cand. | 2631 OB-GU24 | BK, OB |
| 2632 OB | 11" W | 20½" | | | 5" Dia. Canopy | 6', 5' | 3-40w Cand. | 2632 OB-GU24 | BK, OB |
| 2633 OB | 16¾" W | 8" | | | | | 2-75 w Med. | 2633 OB-GU24 | BK, OB |
| 2634 OB | 9" W | 15¾" | 10½" | 8" | 4½" W, 7¼" H Back Plate | | 2-40w Med. | 2634 OB-GU24 | BK, OB |
| 2635 OB | 11" W | 18¾" | 12½" | 9¾" | 4½" W, 9" H Back Plate | | 3-40w Cand. | 2635 OB-GU24 | BK, OB |
| 2636 OB | 6" W | 11" | 6¾" | 3" | 5" W, 6" H Back Plate | | 1-60w Med. | | BK, OB |
| 2639 OB | 14" W | 26" | 16" | 12¾" | 4½" W, 11½" H Back Plate | | 4-40w Cand. | 2639 OB-GU24 | BK, OB |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

BOLLA™

The graceful lines of Bolla create a soft elegance, while the sturdy aluminum construction and heavy cast ball transitions add to its innovative style.

FINISH Black

GLASS Clear Inside Etched Seedy



Bolla Chandeliers,
pages 108-119




Bolla Bath,
pages 388-390



Bolla path lights
are available in the
Hinkley Landscape
Lighting catalog.

Scan to view a video of
the Bolla collection.



2639 BK
2639 BK-GU24





2632 BK
2632 BK-GU24



2633 BK
2633 BK-GU24



2634 BK
2634 BK-GU24



2635 BK
2635 BK-GU24



2636 BK



2630 BK
2630 BK-GU24



2631 BK
2631 BK-GU24



BOLLA Black (BK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | |
|---------|----------------|--------|------|------------------|--------------------------|----------------|-------------|---------------------------------------------------------------------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | AVAILABLE FINISHES |
| 2630 BK | 7¼" W | 12¼" | 9" | 7" | 4½" W, 7¼" H Back Plate | | 1-60w Med. | 2630 BK-GU24 | BK, OB |
| 2631 BK | 11" W | 20½" | | | 3" Dia. Post Fitter | | 3-40w Cand. | 2631 BK-GU24 | BK, OB |
| 2632 BK | 11" W | 20½" | | | 5" Dia. Canopy | 6', 5' | 3-40w Cand. | 2632 BK-GU24 | BK, OB |
| 2633 BK | 16¾" W | 8" | | | | | 2-75 w Med. | 2633 BK-GU24 | BK, OB |
| 2634 BK | 9" W | 15¾" | 10½" | 8" | 4½" W, 7¼" H Back Plate | | 2-40w Med. | 2634 BK-GU24 | BK, OB |
| 2635 BK | 11" W | 18¾" | 12½" | 9¾" | 4½" W, 9" H Back Plate | | 3-40w Cand. | 2635 BK-GU24 | BK, OB |
| 2636 BK | 6" W | 11" | 6¾" | 3" | 5" W, 6" H Back Plate | | 1-60w Med. | | BK, OB |
| 2639 BK | 14" W | 26" | 16" | 12¾" | 4½" W, 11½" H Back Plate | | 4-40w Cand. | 2639 BK-GU24 | BK, OB |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

AURORA™

Aurora's clean, transitional style effortlessly complements a variety of exteriors. The solid brass construction in a Metro Bronze finish and amber etched seedy glass complete its refined appearance.

FINISH Metro Bronze

GLASS Etched Amber Seedy



2289 MT
2289 MT-GU24





AURORA Metro Bronze (MT)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|----------------------------------------------------------------------------------------------|-----------------------|
| 2280 MT | 7" W | 11½" | 8½" | 6½" | 4½" W, 7" H Back Plate | | 1-60w Med. | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | MT |
| 2281 MT | 11" Dia. | 19" | | | 3" Dia. Post Fitter | | 1-100w Med. | | MT |
| 2282 MT | 11" Dia. | 18¾" | | | 5¼" Dia. Canopy | 6', 5' | 1-100w Med. | | MT |
| 2284 MT | 9" W | 15" | 10¾" | 8¼" | 4½" W, 9" H Back Plate | | 1-75w Med. | | MT |
| 2285 MT | 11" W | 18" | 13" | 10" | 4½" W, 14" H Back Plate | | 1-100w Med. | | MT |
| 2289 MT | 13" W | 21½" | 15" | 12" | 4½" W, 14" H Back Plate | | 1-100w Med. | | MT |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

GRAYSON™

The Grayson collection has an elegant, European silhouette. The fully enclosed, thick rectangular glass shade sits atop an overscaled yet graceful, ribbon-inspired scroll base constructed from die cast aluminum.

FINISH Autumn

GLASS Linen Etched Opal





2034 AM
2034 AM-GU24



2030 AM
2030 AM-GU24



GRAYSON Autumn (AM)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | |
|---------|----------------|--------|------|------------------|------------------------|-------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------|
| | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | AVAILABLE FINISHES |
| 2030 AM | 6" W | 15" | 6¼" | 8" | 4½" W, 7" H Back Plate | 1-100w Med. |  GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | 2030 AM-GU24 AM, CL |
| 2034 AM | 8" W | 18¾" | 7" | 8½" | 4½" W, 9" H Back Plate | 1-100w Med. |  GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | 2034 AM-GU24 AM, CL |

For Fluorescent/GU24 lamps, see pages 412-413.

The Grayson collection has an elegant, European silhouette. The fully enclosed, thick rectangular glass shade sits atop an overscaled yet graceful, ribbon-inspired scroll base constructed from die cast aluminum.

GRAYSON™

Charcoal **FINISH**
Etched Opal **GLASS**





2030 CL
2030 CL-GU24



2034 CL
2034 CL-GU24



GRAYSON Charcoal (CL)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | |
|---------|----------------|--------|------|------------------|------------------------|-------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------|
| | | | | | | | AVAILABLE FINISHES | |
| 2030 CL | 6" W | 15" | 6¼" | 8" | 4½" W, 7" H Back Plate | 1-100w Med. |  GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | AM, CL |
| 2034 CL | 8" W | 18¾" | 7" | 8½" | 4½" W, 9" H Back Plate | 1-100w Med. |  GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | AM, CL |

For Fluorescent/GU24 lamps, see pages 412-413.

CAPE COD™

Cape Cod's classic onion lantern design conveys classic New England style. The solid brass construction and clear seedy glass add vintage appeal.

FINISH Sienna Bronze

GLASS Clear Seedy



2205 SZ
2205 SZ-LED





CAPE COD Sienna Bronze (SZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | |
|---------|----------------|---------|------|------------------|-------------------------|----------------|-------------|-------------|------------------------|-----------------------|
| | | | | | | | | LED | LED LIGHT ENGINE | AVAILABLE FINISHES |
| 2200 SZ | 8¾" W | 18" | 10¼" | 11½" | 4¼" W, 5½" H Back Plate | | 1-75w Med. | 2200 SZ-LED | UNI-60 | SZ |
| 2201 SZ | 14" Dia. | 23¾" | | | 3" Dia. Post Fitter | | 4-40w Cand. | | | SZ |
| 2202 SZ | 11" Dia. | 18" | | | 5" Dia. Canopy | 6', 5' | 1-100w Med. | 2202 SZ-LED | UNI-100 | SZ |
| 2203 SZ | 7" Dia. | 9", 9¾" | | | 5" Dia. Canopy | 6', 5' | 1-60w Med. | 2203 SZ-LED | UNI-60 | SZ |
| 2204 SZ | 11" W | 23¾" | 13" | 16" | 4½" W, 9½" H Back Plate | | 1-100w Med. | 2204 SZ-LED | UNI-100 | SZ |
| 2205 SZ | 14" W | 26¾" | 15" | 17" | 4½" W, 10" H Back Plate | | 1-100w Med. | 2205 SZ-LED | UNI-100 | SZ |
| 2206 SZ | 7¼" W | 14" | 8" | 9¼" | 4¼" W, 5½" H Back Plate | | 1-60w Med. | 2206 SZ-LED | UNI-60 | SZ |
| 2207 SZ | 11¼" Dia. | 21¼" | | | 3" Dia. Post Fitter | | 3-40w Cand. | | | SZ |

*Height when hung with chain. For posts and pier mounts, see pages 613-614. For LED specifications, see pages 412-413.

NEW CASTLE™

The New Castle collection gives this traditional lantern design a modern twist with a recessed light source inside a seedy glass cylinder. The solid aluminum construction in a durable powder coat Black finish is Dark Sky compliant.

FINISH Black

GLASS Clear Seedy

DARK SKY 



2258 BK



2252 BK



2254 BK



2250 BK



2255 BK



2251 BK

NEW CASTLE Black (BK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-----------------------|
| 2250 BK | 7" W | 9¾" | 8" | 5¾" | 4½" W, 6¾" H Back Plate | | 1-35W GU10* | BK |
| 2251 BK | 11" W | 22¼" | | | 3" Dia. Post Fitter | | 1-50W GU10* | BK |
| 2252 BK | 11" W | 15" | | | 5½" Dia. Canopy | 6', 5' | 1-50W GU10* | BK |
| 2254 BK | 9" W | 16¾" | 10" | 11¼" | 4½" W, 6¾" H Back Plate | | 1-50W GU10* | BK |
| 2255 BK | 11" W | 19½" | 12¼" | 12¼" | 4½" W, 6¾" H Back Plate | | 1-50W GU10* | BK |
| 2258 BK | 11" W | 24" | 12¼" | 12¼" | 4½" W, 6¾" H Back Plate | | 1-50W GU10* | BK |

*MR-16 bulbs included. For posts and pier mounts, see pages 613-614.

WESTWINDS™

Westwinds features intricate stamped filigree detailing in a classic Sienna finish. The durable solid brass construction and clear water glass panels impart an authentic, timeless feel.

FINISH Sienna

GLASS Clear Water Glass Panels



2996 SN



2992 SN



2993 SN
(flush wall mount)



2994 SN
(flush wall mount)



2999 SN



2989 SN



2990 SN



2995 SN



2991 SN

WESTWINDS Sienna (SN)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|--------------------------|----------------|-------------|-----------------------|
| 2989 SN | 6" W | 11¾" | 6½" | 7½" | 4¾" W, 5½" H Back Plate | | 1-60w Med. | SN |
| 2990 SN | 8½" W | 19" | 9½" | 13½" | 4½" W, 9½" H Back Plate | | 2-40w Cand. | SN |
| 2991 SN | 13" Dia. | 20½" | | | 3" Dia. Post Fitter | | 3-40w Cand. | SN |
| 2992 SN | 10½" Dia. | 16¼" | | | 5½" Dia. Canopy | 6', 5' | 3-40w Cand. | SN |
| 2993 SN | 8" W | 10" | 6¼" | 6" | 4½" W, 8" H Back Plate | | 1-75w Med. | SN |
| 2994 SN | 10½" W | 12½" | 6" | 8" | 7¾" W, 9½" H Back Plate | | 1-40w Cand. | SN |
| 2995 SN | 10½" W | 22½" | 12½" | 17½" | 4½" W, 9½" H Back Plate | | 3-40w Cand. | SN |
| 2996 SN | 12¾" W | 27½" | 14¼" | 21½" | 4¾" W, 12¼" H Back Plate | | 3-40w Cand. | SN |
| 2999 SN | 13½" Dia. | 7½" | | | | | 3-40w Cand. | SN |


For posts and pier mounts, see pages 613-614.

IDEA

CENTER

VISIT US AT HINKLEYLIGHTING.COM FOR
MORE LIGHTING 101 TIPS, DESIGNER
IDEAS AND STYLE STORIES.

Heritage COLLECTION



HINKLEY LIGHTING, INC.
SINCE 1922

Heritage Revival! Our archives provided a wealth of inspiration to develop our "Heritage" outdoor lantern collection. This collection represents a unique grouping of premium outdoor fixtures that pay tribute to the nostalgia of America's past while reinforcing the Hinkley philosophy of timeless, classic lighting design.

1. Bingham 2045 SN, page 518 2. Liberty 2174 SN page 502 3. Putney Bridge 2655 BK, page 512 4. Sedgwick 1774 SN, page 515
5. Valley Forge 2070 SN, page 511 6. Revere 1184 SN, page 517 7. Valley Forge 2075 SN, page 510 8. Nantucket 2374 AS, page
506 9. York 1845 BK, page 520 10. Montauk 1204 SN, page 505 11. Liberty 2174 VZ, page 503 12. Brighton 2298 SN, page 508.



1940s

HINKLEY LIGHTING FACTORY

HINKLEY

LIBERTY™

Liberty's minimal, pure design gives it vintage New England style. The solid brass construction features spun bell-shaped reflectors for that timeless appeal.

FINISH Sienna

Heritage
COLLECTION

DARK SKY 



2171 SN



2172 SN



2170 SN



2174 SN

LIBERTY Sienna (SN)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOPTO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|-----------------|---------------------|----------------|-------------|-----------------------|
| 2170 SN | 7" W | 8¾" | 8½" | 4¼" | 6¼" Dia. Back Plate | | 1-100w Med. | SN, VZ |
| 2171 SN | 11½" W | 19½" | | | 3" Dia. Post Fitter | | 1-100w Med. | SN, VZ |
| 2172 SN | 9" Dia. | 10¾" | | | 6¼" Dia. Canopy | 6', 5' | 1-100w Med. | SN, VZ |
| 2174 SN | 9" W | 10½" | 10¼" | 5½" | 6¼" Dia. Back Plate | | 1-100w Med. | SN, VZ |

For posts and pier mounts, see pages 613-614.

Liberty's minimal, pure design gives it vintage New England style. The solid brass construction features spun bell-shaped reflectors for that timeless appeal.

Victorian Bronze FINISH

LIBERTY™

DARK SKY

Heritage
COLLECTION



2170 VZ



2172 VZ



2174 VZ



2171 VZ

LIBERTY Victorian Bronze (VZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOPTO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|-----------------|---------------------|----------------|-------------|-----------------------|
| 2170 VZ | 7" W | 8¾" | 8½" | 4¼" | 6¼" Dia. Back Plate | | 1-100w Med. | SN, VZ |
| 2171 VZ | 11½" W | 19½" | | | 3" Dia. Post Fitter | | 1-100w Med. | SN, VZ |
| 2172 VZ | 9" Dia. | 10¾" | | | 6¼" Dia. Canopy | 6', 5' | 1-100w Med. | SN, VZ |
| 2174 VZ | 9" W | 10½" | 10¼" | 5½" | 6¼" Dia. Back Plate | | 1-100w Med. | SN, VZ |


For posts and pier mounts, see pages 613-614.

MONTAUK™

The classic sophistication of the Montauk collection brings together the finest elements of traditional East Coast style. The entire collection is made from solid brass, complemented by clear seedy glass and candelabra sockets for authentic appeal.

FINISH Sienna
GLASS Clear Seedy

Heritage
COLLECTION



Scan to view a video of the Montauk collection.



1205 SN
1205 SN-LED





1200 SN
1200 SN-LED



1202 SN
1202 SN-LED



1204 SN
1204 SN-LED



1201 SN

MONTAUK Sienna (SN)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | |
|---------|----------------|--------|------|------------------|------------------------|----------------|-------------|-------------|------------------------|-----------------------|
| | | | | | | | | LED | LED LIGHT ENGINE | AVAILABLE FINISHES |
| 1200 SN | 7" W | 17¼" | 9¼" | 10¼" | 4½" W, 8" H Back Plate | | 2-60w Cand. | 1200 SN-LED | UNI-100 | SN |
| 1201 SN | 9" W | 23¾" | | | 3" Dia. Post Fitter | | 4-60w Cand. | | | SN |
| 1202 SN | 7" W | 17¼" | | | 5" Dia. Canopy | 6', 5' | 2-60w Cand. | 1202 SN-LED | UNI-100 | SN |
| 1204 SN | 7" W | 20¾" | 9¼" | 11½" | 4½" W, 8" H Back Plate | | 3-60w Cand. | 1204 SN-LED | UNI-100 | SN |
| 1205 SN | 9" W | 19½" | 11¼" | 10½" | 4½" W, 8" H Back Plate | | 4-60w Cand. | 1205 SN-LED | UNI-100 | SN |

For posts and pier mounts, see pages 613-614. For LED specifications, see pages 412-413.

NANTUCKET™

A Hinkley classic, Nantucket features a timeless New England design for the ultimate in vintage nautical chic. An Aged Brass finish, clear seedy glass panels and durable solid brass construction add to its retro appeal.

FINISH Aged Brass

GLASS Clear Seedy Panels

Heritage
COLLECTION



2374 AS



2372 AS



2370 AS



2376 AS



2371 AS

NANTUCKET Aged Brass (AS)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-----------------------|
| 2370 AS | 5½" W | 13½" | 5½" | 8¾" | 5½" W, 7" H Back Plate | | 1-75w Med. | AS |
| 2371 AS | 7½" W | 20¾" | | | 3" Dia. Post Fitter | | 3-60w Cand. | AS |
| 2372 AS | 5½" W | 14½" | | | 5" Dia. Canopy | 6', 5' | 2-40w Cand. | AS |
| 2374 AS | 7½" W | 17" | 6¾" | 11¼" | 7½" W, 8¼" H Back Plate | | 2-60w Cand. | AS |
| 2376 AS | 4½" W | 9¾" | 4½" | 7" | 4½" W, 5" H Back Plate | | 1-60w Med. | AS |


For posts and pier mounts, see pages 613-614.

BRIGHTON™

Brighton's regal design features hand-soldered solid brass construction. The triangular-shaped stamped window pattern with circular medallion accent gives this style a distinguished sophistication.

FINISH Sienna
GLASS Clear Seedy

Heritage
COLLECTION



Scan to view a video of the Brighton collection.



2298 SN



2292 SN
2292 SN-LED



2290 SN
2290 SN-LED



2295 SN



2294 SN
2294 SN-LED



2291 SN



2297 SN

BRIGHTON Sienna (SN)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | AVAILABLE FINISHES |
| 2290 SN | 7" W | 14" | 7" | 8" | 4½" W, 11" H Back Plate | | 1-100w Med. | 2290 SN-LED | UNI-100 | SN |
| 2291 SN | 9" W | 19¾" | | | 3" Dia. Post Fitter | | 3-60w Cand. | | | SN |
| 2292 SN | 9" Dia. | 16¾" | | | 5" Dia. Canopy | 6', 5' | 3-60w Cand. | 2292 SN-LED | UNI-60 | SN |
| 2294 SN | 9" W | 15½" | 8¾" | 10" | 4½" W, 11" H Back Plate | | 3-60w Cand. | 2294 SN-LED | UNI-100 | SN |
| 2295 SN | 9" W | 24" | 9¼" | 11" | 4½" W, 11" H Back Plate | | 3-60w Cand. | | | SN |
| 2297 SN | 11" W | 27¾" | | | 3" Dia. Post Fitter | | 4-60w Cand. | | | SN |
| 2298 SN | 11" W | 29¼" | 12" | 12¼" | 4½" W, 11" H Back Plate | | 4-60w Cand. | | | SN |

For posts and pier mounts, see pages 613-614. For LED specifications, see pages 412-413.

VALLEY FORGE™

Valley Forge reaches back in time to create a striking traditional lantern design in solid brass construction. The authentic mirror glass reflector and soft arching candle cluster add to its historical appeal.

FINISH Sienna

GLASS Clear Seedy

Heritage
COLLECTION



2075 SN



2072 SN



2074 SN



2070 SN



2071 SN

VALLEY FORGE Sienna (SN)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|--------------------------|----------------|-------------|-----------------------|
| 2070 SN | 6" W | 11" | 4¾" | 5" | 5¾" W, 10¼" H Back Plate | | 2-60w Cand. | SN |
| 2071 SN | 10" W | 23¾" | | | 3" Dia. Post Fitter | | 3-60w Cand. | SN |
| 2072 SN | 9" W | 19½" | | | 5" Square Canopy | 6', 5' | 3-60w Cand. | SN |
| 2074 SN | 8" W | 15" | 4¾" | 8¼" | 5¾" W, 10¼" H Back Plate | | 3-60w Cand. | SN |
| 2075 SN | 9" W | 20" | 4¾" | 12½" | 5¾" W, 10¼" H Back Plate | | 3-60w Cand. | SN |

For posts and pier mounts, see pages 613-614.

PUTNEY BRIDGE™

Putney Bridge is a classic Shaker-inspired style constructed of durable solid aluminum. The generous panels of dense seedy glass, forged metal roof and classic rivet construction combine with a bold Black finish to complete this authentic design.

FINISH Black

GLASS Etched Seedy

Heritage
COLLECTION



2655 BK



2652 BK



2654 BK



2650 BK



2651 BK

PUTNEY BRIDGE Black (BK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|--------------------------|----------------|-------------|-----------------------|
| 2650 BK | 6" W | 11¼" | 7½" | 6¾" | 4½" W, 9¼" H Back Plate | | 1-75w Med. | BK |
| 2651 BK | 10" W | 19¼" | | | 3" Dia. Post Fitter | | 1-100w Med. | BK |
| 2652 BK | 10" W | 17½" | | | 6" Dia. Canopy | 6', 5' | 1-100w Med. | BK |
| 2654 BK | 8" W | 13¼" | 9½" | 7¾" | 4½" W, 10¾" H Back Plate | | 1-100w Med. | BK |
| 2655 BK | 10" W | 15¾" | 9¾" | 9½" | 6½" W, 12½" H Back Plate | | 1-100w Med. | BK |

For posts and pier mounts, see pages 613-614.

SEDGWICK™

Sedgwick's brass construction symbolizes the best of vintage Hinkley quality and style. This traditional tapered rectangular lantern features a charming hinged door with sliding latch for authentic appeal. The classic Sienna finish combines beautifully with generous panels of clear seedy glass and embodies the essence of historic New England architecture and sophistication.

FINISH Sienna GLASS Clear Seedy

Heritage
COLLECTION



1775 SN



1772 SN



1774 SN



1770 SN



1771 SN

SEDGWICK Sienna (SN)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOPTO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|-----------------|--------------------------|----------------|-------------|-----------------------|
| 1770 SN | 4½" W | 14½" | 6½" | 9" | 4½" W, 11½" H Back Plate | | 1-60w Cand. | SN |
| 1771 SN | 7" W | 21¾" | | | 3" Dia. Post Fitter | | 3-60w Cand. | SN |
| 1772 SN | 7" W | 18¾" | | | 5" Dia. Canopy | 6', 5' | 3-60w Cand. | SN |
| 1774 SN | 7" W | 19¾" | 6½" | 14" | 4½" W, 11½" H Back Plate | | 2-60w Cand. | SN |
| 1775 SN | 7" W | 19¾" | 9½" | 14" | 4½" W, 11¾" H Back Plate | | 3-60w Cand. | SN |

For posts and pier mounts, see pages 613-614.

REVERE™

Revere is a classic, traditional coach lantern in solid brass with clear seedy glass panels. The glass faux candle sleeves complete the authentic appearance.

FINISH Sienna

GLASS Clear Seedy

Heritage
COLLECTION



1185 SN



1182 SN



1184 SN



1187 SN



1180 SN



1181 SN

REVERE Sienna (SN)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-----------------------|
| 1180 SN | 4½" W | 17½" | 5½" | 10¼" | 4½" W, 11" H Back Plate | | 1-60w Cand. | SN |
| 1181 SN | 7" W | 22¼" | | | 3" Dia. Post Fitter | | 3-60w Cand. | SN |
| 1182 SN | 7" W | 20½" | | | 5" Dia. Canopy | 6', 5' | 3-60w Cand. | SN |
| 1184 SN | 7" W | 21¾" | 7¼" | 12¼" | 4½" W, 11" H Back Plate | | 2-60w Cand. | SN |
| 1185 SN | 7" W | 21¾" | 10" | 12¼" | 4½" W, 11" H Back Plate | | 3-60w Cand. | SN |
| 1187 SN | 6¾" W | 20¼" | | | 9¾" Square Base | | 3-60w Cand. | SN |

For posts and pier mounts, see pages 613-614.

BINGHAM™

Bingham's traditional style recalls a turn-of-the-century gas light reproduction. The vintage look is nautical in nature and recognizes Hinkley's origins on the shores of Lake Erie. The brass construction features clear seedy glass and a Sienna finish, while candelabra lamping completes the authentic style.

FINISH Sienna

GLASS Clear Seedy

Heritage
COLLECTION



2045 SN



2042 SN



2044 SN



2040 SN



2041 SN

BINGHAM Sienna (SN)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOPTO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|-----------------|-------------------------|----------------|-------------|-----------------------|
| 2040 SN | 4¾" W | 12½" | 6½" | 8" | 4½" W, 7¼" H Back Plate | | 1-60w Cand. | SN |
| 2041 SN | 8" W | 23½" | | | 3" Dia. Post Fitter | | 3-60w Cand. | SN |
| 2042 SN | 8" W | 23½" | | | 5" Dia. Canopy | 6', 5' | 3-60w Cand. | SN |
| 2044 SN | 6" W | 16" | 8" | 10" | 6" W, 9¼" H Back Plate | | 2-60w Cand. | SN |
| 2045 SN | 8" W | 21" | 10¼" | 13¼" | 7¼" W, 12" H Back Plate | | 3-60w Cand. | SN |

For posts and pier mounts, see pages 613-614. For Dark Sky options, see page 431.

YORK™

York uses authentic exposed rivet construction hand-made in solid aluminum and celebrates the bold traditional lantern design Hinkley is renowned for. This classic hip roof and wire cage turn of the century style comes with a functional interior metallic reflector and rolled top loop. The gallant proportions of its striking silhouette are reinforced with a vintage Black finish, cast face plate and clear seedy glass.

FINISH Black **GLASS** Clear Seedy

Heritage
COLLECTION



1845 BK



1842 BK



1844 BK



1840 BK



1841 BK

YORK Black (BK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|---------------------|----------------|-------------|-----------------------|
| 1840 BK | 5½" W | 15¼" | 5½" | 11½" | 5" Dia. Back Plate | | 1-100w Med. | BK |
| 1841 BK | 9½" W | 28" | | | 3" Dia. Post Fitter | | 3-60w Cand. | BK |
| 1842 BK | 9½" W | 24¾" | | | 5" Dia. Canopy | 6', 5' | 3-60w Cand. | BK |
| 1844 BK | 7½" W | 21¼" | 7½" | 16" | 5" Dia. Back Plate | | 2-60w Cand. | BK |
| 1845 BK | 9½" W | 25" | 9¼" | 18¾" | 5" Dia. Back Plate | | 3-60w Cand. | BK |

For posts and pier mounts, see pages 613-614.



Senator's stately cast aluminum and brass design features a striking Black finish with crisp panels of beveled, bound glass.

Black FINISH
Bound and Beveled GLASS

SENATOR™



SENATOR Black (BK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-----------------------|
| 2500 BK | 8½" W | 14" | 9" | 6½" | 5" W, 6¾" H Back Plate | | 1-60w Med. | BK |
| 2501 BK | 13" Dia. | 26½" | | | 3" Dia. Post Fitter | | 3-40w Cand. | BK |
| 2502 BK | 13" Dia. | 25½" | | | 5" Dia. Canopy | 6', 5' | 3-40w Cand. | BK |
| 2504 BK | 11" W | 21¾" | 11½" | 7¾" | 5" W, 6¾" H Back Plate | | 3-40w Cand. | BK |
| 2505 BK | 13" W | 26" | 15" | 10" | 6½" W, 8¾" H Back Plate | | 3-40w Cand. | BK |
| 2506 BK | 6" W | 9" | 6½" | 4¾" | 5" W, 7" H Back Plate | | 1-60w Med. | BK |

For posts and pier mounts, see pages 613-614.

RICHMOND™

The traditional style of the Richmond collection features curved seedy glass side panels with candelabra lamping. Made from cast aluminum, this design pays tribute to the classic age of artisan craftsmanship.

FINISH Museum Black

GLASS Clear Seedy



1485 MB



1482 MB



1484 MB



1480 MB



1481 MB



1487 MB

RICHMOND Museum Black (MB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-----------------------|
| 1480 MB | 7" W | 10" | 5" | 5" | 4½" W, 5½" H Back Plate | | 1-60w Cand. | MB |
| 1481 MB | 9" W, 6" D | 16½" | | | 3" Dia. Post Fitter | | 2-60w Cand. | MB |
| 1482 MB | 9" W | 12" | | | 5¼" Dia. Canopy | 6', 5' | 2-60w Cand. | MB |
| 1484 MB | 9" W | 13" | 6¼" | 8¼" | 5" W, 7¾" H Back Plate | | 2-60w Cand. | MB |
| 1485 MB | 11" W | 15¾" | 7¼" | 8" | 6" W, 8½" H Back Plate | | 3-60w Cand. | MB |
| 1487 MB | 11" W, 7¼" D | 19¼" | | | 3" Dia. Post Fitter | | 3-60w Cand. | MB |

For posts and pier mounts, see pages 613-614.

RALEY™

Raley's regal appearance features cast aluminum construction, a bold Museum Black finish, flourishing details and clear water glass panels for a dignified style statement.

FINISH Museum Black

GLASS Clear Water Glass Panels



Raley path lights are available in the Hinkley Landscape Lighting catalog.



1609 MB



1602 MB

1600 MB
1600 MB-LED

1606 MB
1606 MB-LED

1604 MB

1605 MB

1601 MB

RALEY Museum Black (MB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | AVAILABLE FINISHES |
| 1600 MB | 7¼" W | 16½" | 9½" | 10½" | 4½" W, 7½" H Back Plate | | 1-60w Med. | 1600 MB-LED | UNI-60 | MB |
| 1601 MB | 11¾" Dia. | 26¼" | | | 3" Dia. Post Fitter | | 4-40w Cand. | | | MB |
| 1602 MB | 11¾" Dia. | 27½" | | | 5½" Dia. Canopy | 6', 5' | 4-40w Cand. | | | MB |
| 1604 MB | 9½" W | 25½" | 12¼" | 14" | 4½" W, 9½" H Back Plate | | 3-40w Cand. | | | MB |
| 1605 MB | 11¾" W | 31¼" | 14¾" | 16¼" | 4½" W, 9½" H Back Plate | | 4-40w Cand. | | | MB |
| 1606 MB | 5½" W | 8¾" | 6¼" | 3½" | 4½" W, 5½" H Back Plate | | 1-60w Med. | 1606 MB-LED | UNI-60 | MB |
| 1609 MB | 13" W | 41¾" | 17½" | 20¾" | 5½" W, 18" H Back Plate | | 4-40w Cand. | | | MB |

For posts and pier mounts, see pages 613-614. For LED specifications, see pages 412-413.

MANOR HOUSE™

Manor House is a classic lantern design featuring durable cast aluminum, clear beveled glass panels and a bold Black finish. Select-A-Lite options come standard with both candelabra and medium based sockets.

FINISH Black

GLASS Clear Beveled Panels



1449 BK



1419 BK



1410 BK



1440 BK



1470 BK



1810 BK

MANOR HOUSE Black (BK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------------------|-----------------------|
| 1410 BK | 9" W | 25" | 11" | 13" | 4½" W, 6¾" H Back Plate | 1-60w Med. or 3-25w Cand. | BK |
| 1419 BK | 9" W | 18" | 11" | 13" | 4½" W, 6¾" H Back Plate | 1-60w Med. | BK |
| 1440 BK | 11" W | 31" | 12" | 14" | 5" W, 8¼" H Back Plate | 1-75w Med. or 3-25w Cand. | BK |
| 1449 BK | 11" W | 21" | 12" | 14" | 5" W, 8¼" H Back Plate | 1-75w Med. or 3-25w Cand. | BK |
| 1470 BK | 14" W | 41" | 16" | 18" | 5" W, 8¼" H Back Plate | 1-100w Med. or 3-40w Cand. | BK |
| 1810 BK | 7" W | 18" | 7" | 8" | 4½" W, 5¾" H Back Plate | 1-60w Med. | BK |

For posts and pier mounts, see pages 613-614.

Manor House is a classic lantern design featuring durable cast aluminum, clear beveled glass panels and a bold Black finish. Select-A-Lite options come standard with both candelabra and medium based sockets.

Black FINISH
Clear Beveled Panels GLASS

MANOR HOUSE™



MANOR HOUSE Black (BK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|----------------------------|-----------------------|
| 1412 BK | 9" Dia. | 15" | | | 5½" Dia. Canopy | 6', 5' | 1-60w Med. | BK |
| 1441 BK | 11" Dia. | 22" | | | 3" Dia. Post Fitter | | 1-75w Med. or 3-25w Cand. | BK |
| 1445 BK | 36" W Max.* | 21" | 12" | 14" | 5" W, 8¼" H Back Plate | | 1-75w Med. or 3-25w Cand. | BK |
| 1471 BK | 14" Dia. | 27" | | | 3" Dia. Post Fitter | | 1-100w Med. or 3-40w Cand. | BK |
| 1472 BK | 14" Dia. | 24" | | | 5" Dia. Canopy | 6', 5' | 3-40w Cand. | BK |
| 1819 BK | 7" W | 12" | 12" | 8" | 4½" W, 5¾" H Back Plate | | 1-60w Med. | BK |

For posts and pier mounts, see pages 613-614.

EDGEWATER™

Edgewater's classic design features durable cast aluminum and brass construction in a rich Black finish with clear seedy glass.

FINISH Black

GLASS Clear Seedy Panels



1675 BK
1675 BK-LED





1672 BK



1683 BK



1676 BK
1676 BK-LED



1674 BK
1674 BK-LED



1670 BK



1671 BK



1677 BK

EDGEWATER Black (BK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | |
|---------|----------------|--------|------|------------------|------------------------|----------------|-------------|-------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | AVAILABLE FINISHES |
| 1670 BK | 10" W | 21" | 9½" | 14½" | 5" W, 14" H Back Plate | | 3-40w Cand. | | | BK |
| 1671 BK | 10" Dia. | 20½" | | | 3" Dia. Post Fitter | | 3-40w Cand. | | | BK |
| 1672 BK | 10" Dia. | 18½" | | | 5" Dia. Canopy | 6', 5' | 3-40w Cand. | | | BK |
| 1674 BK | 6½" W | 11" | 6½" | 5½" | 5" W, 7" H Back Plate | | 1-60w Med. | 1674 BK-LED | UNI-60 | BK |
| 1675 BK | 16" W | 25½" | 14½" | 11" | 5" W, 14" H Back Plate | | 4-40w Cand. | 1675 BK-LED | UNI-100 | BK |
| 1676 BK | 10" W | 17½" | 9½" | 6½" | 4½" W, 9" H Back Plate | | 3-40w Cand. | 1676 BK-LED | UNI-100 | BK |
| 1677 BK | 16" Dia. | 27" | | | 3" Dia. Post Fitter | | 4-40w Cand. | | | BK |
| 1683 BK | 13" Dia. | 9" | | | | | 2-60w Med. | | | BK |

For posts and pier mounts, see pages 613-614. For LED specifications, see pages 412-413.

CAMELOT™

Camelot's stunning clear beveled glass panels add a regal elegance to this traditional cast aluminum design in a rich Black finish.

FINISH Black

GLASS Clear Beveled Panels



1705 BK



1712 BK



1704 BK



1700 BK
1700 BK-LED



1702 BK
1702 BK-LED



1701 BK



1707 BK

CAMELOT Black (BK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | |
|---------|----------------|------------|------|------------------|-------------------------|----------------|-------------|-------------|------------------------|-----------------------|
| | | | | | | | | LED | LED LIGHT ENGINE | AVAILABLE FINISHES |
| 1700 BK | 6½" W | 15¾", 13¼" | 7½" | 10½" | 4½" W, 7½" H Back Plate | | 1-75w Med. | 1700 BK-LED | UNI-60 | BK |
| 1701 BK | 8½" Dia. | 19¾" | | | 3" Dia. Post Fitter | | 3-40w Cand. | | | BK |
| 1702 BK | 12" Dia. | 25" | | | 5" Dia. Canopy | 6', 5' | 3-40w Cand. | 1702 BK-LED | UNI-100 | BK |
| 1704 BK | 8½" W | 26¾", 21½" | 10" | 17¼" | 4½" W, 9" H Back Plate | | 3-40w Cand. | | | BK |
| 1705 BK | 12" W | 35", 29¼" | 14¼" | 22½" | 5¼" W, 14" H Back Plate | | 3-40w Cand. | | | BK |
| 1707 BK | 12" Dia. | 25½" | | | 3" Dia. Post Fitter | | 3-40w Cand. | | | BK |
| 1712 BK | 11¼" Dia. | 9¼" | | | | | 4-40w G16½ | | | BK |

*Measurement without removable scroll. For posts and pier mounts, see pages 613-614. For LED specifications, see pages 412-413.

REGAL™

Regal has a grand Old World style that features cast aluminum construction and elegant decorative stamped detailing in a Black Granite finish. Clear seedy water glass adds timeless sophistication.

FINISH Black Granite

GLASS Clear Seedy Water Glass



1726 BG



1713 BG



1725 BG



1720 BG



1722 BG



1721 BG



1727 BG

REGAL Black Granite (BG)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-----------------------|
| 1713 BG | 11¾" Dia. | 9" | | | | | 4-40w G16½ | BG |
| 1720 BG | 6½" W | 13" | 8¼" | 4¾" | 4½" W, 9" H Back Plate | | 2-40w Cand. | BG |
| 1721 BG | 8½" Dia. | 22½" | | | 3" Dia. Post Fitter | | 3-40w Cand. | BG |
| 1722 BG | 8¼" Dia. | 18" | | | 5" Dia. Canopy | 6', 5' | 3-40w Cand. | BG |
| 1725 BG | 8½" W | 23½" | 11¼" | 7¼" | 5" W, 14" H Back Plate | | 3-40w Cand. | BG |
| 1726 BG | 12" W | 32¼" | 14¼" | 10" | 5" W, 18½" H Back Plate | | 4-40w Cand. | BG |
| 1727 BG | 12" Dia. | 30¼" | | | 3" Dia. Post Fitter | | 4-40w Cand. | BG |

For posts and pier mounts, see pages 613-614.

RANDOLPH™

Randolph's traditional design features a bold oval pattern in die cast aluminum construction that complements a variety of exteriors.

FINISH Autumn

GLASS Clear Seedy Glass Panels, Etched Seedy Glass Panels





1495 AM
(shown with
etched seedy glass)
1495 AM-GU24





1495 AM-LED






1492 AM
(shown with
clear seeded glass)
1492 AM-GU24

1492 AM-LED





1494 AM
(shown with
clear seeded glass)
1494 AM-GU24

1494 AM-LED




1490 AM
(shown with
etched seeded glass)
1490 AM-GU24




1491 AM
(shown with
etched seeded glass)
1491 AM-GU24

1491 AM-LED




1499 AM
(shown with
clear seeded glass)
1499 AM-GU24

1499 AM-LED


RANDOLPH Autumn (AM)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|------------------------|----------------|-------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1490 AM | 6" W | 11" | 7" | 2" | 4½" W, 6" H Back Plate | | 1-75 w Med. | 1490 AM-GU24 | | | AM, BK |
| 1491 AM | 8" W | 16¼" | | | 3" Dia. Post Fitter | | 1-100w Med. | 1491 AM-GU24 | 1491 AM-LED | UNI-100 | AM, BK |
| 1492 AM | 8" W | 14¼" | | | 5" Square Canopy | 6', 5' | 1-100w Med. | 1492 AM-GU24 | 1492 AM-LED | UNI-100 | AM, BK |
| 1494 AM | 8" W | 13¾" | 9" | 2¼" | 5¼" W, 8" H Back Plate | | 1-100w Med. | 1494 AM-GU24 | 1494 AM-LED | UNI-100 | AM, BK |
| 1495 AM | 11" W | 19½" | 12" | 3¼" | 7" W, 11" H Back Plate | | 1-100w Med. | 1495 AM-GU24 | 1495 AM-LED | UNI-100 | AM, BK |
| 1499 AM | 11" W | 20¾" | | | 3" Dia. Post Fitter | | 1-100w Med. | 1499 AM-GU24 | 1499 AM-LED | UNI-100 | AM, BK |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

RANDOLPH™

Randolph's traditional design features a bold oval pattern in die cast aluminum construction that complements a variety of exteriors.

FINISH Black

GLASS Clear Seedy Glass Panels, Etched Seedy Glass Panels



1495 BK
(shown with
etched seedy glass)
1495 BK-GU24



1495 BK-LED





1492 BK
(shown with
clear seeded glass)
1492 BK-GU24

1492 BK-LED






1494 BK
(shown with
clear seeded glass)
1494 BK-GU24

1494 BK-LED




1490 BK
(shown with
etched seeded glass)
1490 BK-GU24




1491 BK
(shown with
etched seeded glass)
1491 BK-GU24

1491 BK-LED




1499 BK
(shown with
clear seeded glass)
1499 BK-GU24

1499 BK-LED


RANDOLPH Black (BK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|------------------------|----------------|-------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1490 BK | 6" W | 11" | 7" | 2" | 4½" W, 6" H Back Plate | | 1-75 w Med. | 1490 BK-GU24 | | | AM, BK |
| 1491 BK | 8" W | 16¼" | | | 3" Dia. Post Fitter | | 1-100w Med. | 1491 BK-GU24 | 1491 BK-LED | UNI-100 | AM, BK |
| 1492 BK | 8" W | 14¼" | | | 5" Square Canopy | 6', 5' | 1-100w Med. | 1492 BK-GU24 | 1492 BK-LED | UNI-100 | AM, BK |
| 1494 BK | 8" W | 13¾" | 9" | 2¼" | 5¼" W, 8" H Back Plate | | 1-100w Med. | 1494 BK-GU24 | 1494 BK-LED | UNI-100 | AM, BK |
| 1495 BK | 11" W | 19½" | 12" | 3¼" | 7" W, 11" H Back Plate | | 1-100w Med. | 1495 BK-GU24 | 1495 BK-LED | UNI-100 | AM, BK |
| 1499 BK | 11" W | 20¾" | | | 3" Dia. Post Fitter | | 1-100w Med. | 1499 BK-GU24 | 1499 BK-LED | UNI-100 | AM, BK |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

CEDAR HILL™

Cedar Hill is a traditional outdoor lantern in durable die cast aluminum construction with medium base lamping. This four-sided soft tapered design features linen glass behind arched window pane panels and is available in two popular finishes.

FINISH Oil Rubbed Bronze

GLASS Amber Linen



1984 OZ
1984 OZ-GU24



1984 OZ-LED



1985 OZ
1985 OZ-GU24



1985 OZ-LED



1982 OZ
1982 OZ-GU24



1982 OZ-LED



1989 OZ
1989 OZ-GU24



1989 OZ-LED



1981 OZ
1981 OZ-GU24



1981 OZ-LED



1980 OZ
1980 OZ-GU24



1980 OZ-LED



CEDAR HILL Oil Rubbed Bronze (OZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|------------------------|----------------|-------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1980 OZ | 5¾" W | 9¼" | 6¾" | 4½" | 4½" W, 6" H Back Plate | | 1-75w Med. | 1980 OZ-GU24 | 1980 OZ-LED | UNI-60 | BK, OZ |
| 1981 OZ | 7¾" W | 16" | | | 3" Dia. Post Fitter | | 1-100w Med. | 1981 OZ-GU24 | 1981 OZ-LED | UNI-100 | BK, OZ |
| 1982 OZ | 7¾" W | 13¾" | | | 5¾" W, 5¾" L Canopy | 6', 5' | 1-100w Med. | 1982 OZ-GU24 | 1982 OZ-LED | UNI-100 | BK, OZ |
| 1984 OZ | 7¾" W | 12½" | 9¼" | 5¾" | 5¼" W, 8" H Back Plate | | 1-100w Med. | 1984 OZ-GU24 | 1984 OZ-LED | UNI-100 | BK, OZ |
| 1985 OZ | 11" W | 16¾" | 12¼" | 7½" | 6" W, 9¾" H Back Plate | | 1-100w Med. | 1985 OZ-GU24 | 1985 OZ-LED | UNI-100 | BK, OZ |
| 1989 OZ | 11" W | 20¼" | | | 3" Dia. Post Fitter | | 1-100w Med. | 1989 OZ-GU24 | 1989 OZ-LED | UNI-100 | BK, OZ |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

Cedar Hill is a traditional outdoor lantern in durable die cast aluminum construction with medium base lamping. This four-sided soft tapered design features linen glass behind arched window pane panels and is available in two popular finishes.

Black FINISH
White Linen GLASS

CEDAR HILL™



1982 BK
1982 BK-GU24
1982 BK-LED



1985 BK
1985 BK-GU24
1985 BK-LED



1984 BK
1984 BK-GU24
1984 BK-LED



1980 BK
1980 BK-GU24
1980 BK-LED



1981 BK
1981 BK-GU24
1981 BK-LED



1989 BK
1989 BK-GU24
1989 BK-LED

CEDAR HILL Black (BK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|------------------------|----------------|-------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1980 BK | 5¾" W | 9¼" | 6¾" | 4½" | 4½" W, 6" H Back Plate | | 1-75w Med. | 1980 BK-GU24 | 1980 BK-LED | UNI-60 | BK, OZ |
| 1981 BK | 7¾" W | 16" | | | 3" Dia. Post Fitter | | 1-100w Med. | 1981 BK-GU24 | 1981 BK-LED | UNI-100 | BK, OZ |
| 1982 BK | 7¾" W | 13¾" | | | 5¾" W, 5¾" L Canopy | 6', 5' | 1-100w Med. | 1982 BK-GU24 | 1982 BK-LED | UNI-100 | BK, OZ |
| 1984 BK | 7¾" W | 12½" | 9¼" | 5¾" | 5¼" W, 8" H Back Plate | | 1-100w Med. | 1984 BK-GU24 | 1984 BK-LED | UNI-100 | BK, OZ |
| 1985 BK | 11" W | 16¾" | 12¼" | 7½" | 6" W, 9¾" H Back Plate | | 1-100w Med. | 1985 BK-GU24 | 1985 BK-LED | UNI-100 | BK, OZ |
| 1989 BK | 11" W | 20¼" | | | 3" Dia. Post Fitter | | 1-100w Med. | 1989 BK-GU24 | 1989 BK-LED | UNI-100 | BK, OZ |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

STRATFORD™

Stratford offers a classic tapered square design in sturdy cast aluminum with generous panels of seedy linen glass. The classic finish options complement a variety of exteriors.

FINISH Oil Rubbed Bronze

GLASS White Linen Seedy Panels



1356 OZ
1356 OZ-GU24



1356 OZ-LED



1354 OZ
1354 OZ-GU24



1354 OZ-LED



1352 OZ
1352 OZ-GU24



1352 OZ-LED



1351 OZ
1351 OZ-GU24



1351 OZ-LED



1350 OZ
1350 OZ-GU24



1350 OZ-LED



STRATFORD Oil Rubbed Bronze (OZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|------------------------|----------------|-------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1350 OZ | 7½" W | 12½" | 8¾" | 3½" | 5¼" W, 8" H Back Plate | | 1-60w Med. | 1350 OZ-GU24 | 1350 OZ-LED | UNI-100 | MB, OZ |
| 1351 OZ | 9½" W | 21" | | | 3" Dia. Post Fitter | | 1-100w Med. | 1351 OZ-GU24 | 1351 OZ-LED | UNI-100 | MB, OZ |
| 1352 OZ | 9½" W | 15½" | | | 4¾" Dia. Canopy | 6', 5' | 1-100w Med. | 1352 OZ-GU24 | 1352 OZ-LED | UNI-100 | MB, OZ |
| 1354 OZ | 9½" W | 16" | 11" | 3¾" | 6" W, 9¾" H Back Plate | | 1-75w Med. | 1354 OZ-GU24 | 1354 OZ-LED | UNI-100 | MB, OZ |
| 1356 OZ | 6" W | 10¾" | 7" | 3" | 4½" W, 6" H Back Plate | | 1-60w Med. | 1356 OZ-GU24 | 1356 OZ-LED | UNI-60 | MB, OZ |



For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

Stratford offers a classic tapered square design in sturdy cast aluminum with generous panels of seedy linen glass. The classic finish options complement a variety of exteriors.



STRATFORD™

Museum Black FINISH
White Linen Seedy Panels GLASS





1352 MB
1352 MB-GU24

1352 MB-LED






1354 MB
1354 MB-GU24

1354 MB-LED






1356 MB
1356 MB-GU24

1356 MB-LED














1350 MB
1350 MB-GU24

1350 MB-LED




1351 MB
1351 MB-GU24

1351 MB-LED


STRATFORD Museum Black (MB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|------------------------|----------------|-------------|----------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1350 MB | 7½" W | 12½" | 8¾" | 3½" | 5¼" W, 8" H Back Plate | | 1-60w Med. |  1350 MB-GU24 |  1350 MB-LED | UNI-100 | MB, OZ |
| 1351 MB | 9½" W | 21" | | | 3" Dia. Post Fitter | | 1-100w Med. |  1351 MB-GU24 |  1351 MB-LED | UNI-100 | MB, OZ |
| 1352 MB | 9½" W | 15½" | | | 4¾" Dia. Canopy | 6', 5' | 1-100w Med. |  1352 MB-GU24 |  1352 MB-LED | UNI-100 | MB, OZ |
| 1354 MB | 9½" W | 16" | 11" | 3¾" | 6" W, 9¾" H Back Plate | | 1-75w Med. |  1354 MB-GU24 |  1354 MB-LED | UNI-100 | MB, OZ |
| 1356 MB | 6" W | 10¾" | 7" | 3" | 4½" W, 6" H Back Plate | | 1-60w Med. |  1356 MB-GU24 |  1356 MB-LED | UNI-60 | MB, OZ |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

CHERRY CREEK™

Cherry Creek's modern take on the popular Arts & Crafts style has a timeless appeal. The cast aluminum construction is enhanced by the Black finish and the vintage-looking white linen glass.

FINISH Vintage Black

GLASS White Linen



1275 VK
1275 VK-GU24
















1275 VK-LED





CHERRY CREEK Vintage Black (VK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|-----------------------|
| | | | | | | | |  GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. |  LED Includes integrated high efficiency LED light source. |  LED LIGHT ENGINE | |
| 1270 VK | 6½" W | 11" | 7¼" | 4¼" | 4½" W, 7" H Back Plate | | 1-60w Med. |  1270 VK-GU24 |  1270 VK-LED | UNI-60 | OZ, VK |
| 1271 VK | 12" W | 22¼" | | | 3" Dia. Post Fitter | | 1-100w Med. |  1271 VK-GU24 |  1271 VK-LED | UNI-100 | OZ, VK |
| 1272 VK | 12" W | 20¾" | | | 5½" Dia. Canopy | 6', 5' | 1-100w Med. |  1272 VK-GU24 |  1272 VK-LED | UNI-100 | OZ, VK |
| 1273 VK | 12" W | 7¼" | | | | | 2-60w Med. | | | | OZ, VK |
| 1274 VK | 8½" W | 15¼" | 9¼" | 5" | 4½" W, 10" H Back Plate | | 1-75w Med. |  1274 VK-GU24 |  1274 VK-LED | UNI-60 | OZ, VK |
| 1275 VK | 12" W | 20½" | 12¾" | 6½" | 5" W, 13" H Back Plate | | 1-100w Med. |  1275 VK-GU24 |  1275 VK-LED | UNI-100 | OZ, VK |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

CHERRY CREEK™

Cherry Creek's modern take on the popular Arts & Crafts style has a timeless appeal. The cast aluminum construction is enhanced by the warmth of the finish and the vintage-looking amber linen glass.

FINISH Oil Rubbed Bronze

GLASS Amber Linen



1275 OZ
1275 OZ-GU24



1275 OZ-LED





CHERRY CREEK Oil Rubbed Bronze (OZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1270 OZ | 6½" W | 11" | 7¼" | 4¼" | 4½" W, 7" H Back Plate | | 1-60w Med. | 1270 OZ-GU24 | 1270 OZ-LED | UNI-60 | OZ, VK |
| 1271 OZ | 12" W | 22¼" | | | 3" Dia. Post Fitter | | 1-100w Med. | 1271 OZ-GU24 | 1271 OZ-LED | UNI-100 | OZ, VK |
| 1272 OZ | 12" W | 20¾" | | | 5½" Dia. Canopy | 6', 5' | 1-100w Med. | 1272 OZ-GU24 | 1272 OZ-LED | UNI-100 | OZ, VK |
| 1273 OZ | 12" W | 7¼" | | | | | 2-60w Med. | | | | OZ, VK |
| 1274 OZ | 8½" W | 15¼" | 9¼" | 5" | 4½" W, 10" H Back Plate | | 1-75w Med. | 1274 OZ-GU24 | 1274 OZ-LED | UNI-60 | OZ, VK |
| 1275 OZ | 12" W | 20½" | 12¾" | 6½" | 5" W, 13" H Back Plate | | 1-100w Med. | 1275 OZ-GU24 | 1275 OZ-LED | UNI-100 | OZ, VK |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

TAHOE™

Tahoe makes a classic Arts & Crafts design statement in cast aluminum construction with panels of clear seedy water glass and copper foil art glass accents.

FINISH Regency Bronze

GLASS Clear Seedy Water Glass with Copper Foil Art Glass Accents



2244 RB



2242 RB



2240 RB



2243 RB



2246 RB



2241 RB

TAHOE Regency Bronze (RB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-----------------------|
| 2240 RB | 8½" W | 17" | 11" | 9¾" | 4½" W, 14" H Back Plate | | 3-40w Cand. | RB |
| 2241 RB | 12" W | 22¼" | | | 3" Dia. Post Fitter | | 4-40w Cand. | RB |
| 2242 RB | 12" W | 22½" | | | 5½" Dia. Canopy | 6', 5' | 4-40w Cand. | RB |
| 2243 RB | 9½" W | 6" | | | | | 2-60w Med. | RB |
| 2244 RB | 12" W | 22½" | 14¾" | 13¾" | 4½" W, 18" H Back Plate | | 4-40w Cand. | RB |
| 2246 RB | 6½" W | 12" | 9" | 7½" | 4½" W, 9¼" H Back Plate | | 1-60w Med. | RB |

For posts and pier mounts, see pages 613-614.

HOLBROOK™

Holbrook features a tall, slim silhouette with aluminum construction and a simple Black finish with modest design elements. The dense, seedy glass complements its updated Arts & Crafts style, creating a new classic in outdoor lanterns.

FINISH Black

GLASS Clear Seedy



1794 BK
1794 BK-GU24





1792 BK
1792 BK-GU24



1790 BK
(pocket wall mount)
1790 BK-GU24




1797 BK
(pocket wall mount)
1797 BK-GU24



1791 BK
1791 BK-GU24

HOLBROOK Black (BK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | DEPTH | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | AVAILABLE FINISHES |
|---------|----------------|--------|------|-------|------------------|-------------------------|----------------|-------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|
| 1790 BK | 9" W | 15¾" | 9" | | 9¼" | 4½" W, 12" H Back Plate | | 1-100w Med. |  GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | BK |
| 1791 BK | 11" W | 19¼" | | 9½" | | 3" Dia. Post Fitter | | 3-60w Cand. | | BK |
| 1792 BK | 11" W | 19¼" | | 9½" | | 5" Square Canopy | 6', 5' | 3-60w Cand. | | BK |
| 1794 BK | 11" W | 18" | 11" | | 11¼" | 4½" W, 12" H Back Plate | | 2-60w Cand. | | BK |
| 1797 BK | 7" W | 12" | 5½" | | 7½" | 5" W, 9¼" H Back Plate | | 1-60w Med. | | BK |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

ELM™

Elm's nature-inspired design offers an organic feel with hand-made sculptural detailing set against a backdrop of elegant distressed etched amber glass.

FINISH Regency Bronze

GLASS Distressed Etched Amber



1155 RB
(pocket wall mount)
1155 RB-GU24





1152 RB
1152 RB-GU24



1154 RB
(pocket wall mount)
1154 RB-GU24



1150 RB
(pocket wall mount)
1150 RB-GU24



1151 RB
1151 RB-GU24



E L M Regency Bronze (RB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|---------------------------------------------------------------------------------------|-----------------------|
| 1150 RB | 8" W | 10" | 5½" | 5" | 8" W, 10" H Back Plate | | 1-100w Med. | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | RB |
| 1151 RB | 9" Dia. | 19" | | | 3" Dia. Post Fitter | | 1-100w Med. | | RB |
| 1152 RB | 8¼" Dia. | 17½" | | | 6½" Dia. Canopy | 6', 5' | 1-100w Med. | | RB |
| 1154 RB | 9" W | 14" | 5½" | 7" | 9" W, 14" H Back Plate | | 1-100w Med. | | RB |
| 1155 RB | 11" W | 18" | 7" | 9" | 11" W, 18" H Back Plate | | 1-100w Med. | | RB |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

CASA™

Casa features solid aluminum construction with twisted wrought iron details and hand-forged scrollwork in an Olde Black finish to complete its rustic-chic appeal with a Southwestern flair.

FINISH Olde Black

GLASS Light Etched Amber



Casa Chandeliers,
pages 140-143



Casa Bath,
page 394



1145 OL
1145 OL-GU24





1142 OL
1142 OL-GU24



1140 OL
1140 OL-GU24



1144 OL
1144 OL-GU24



1141 OL
1141 OL-GU24



CASA Olde Black (OL)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | AVAILABLE FINISHES |
|---------|---------------------------------------|----------------------------------|----------------------------------|----------------------------------|----------------------------------------------------|----------------|-------------|--------------------------------------------------------------------------------------------------|-----------------------|
| 1140 OL | 7" W | 13" | 8" | 6 ³ / ₄ " | 4 ¹ / ₂ " W, 7" H Back Plate | | 1-60w Med. | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | OL |
| 1141 OL | 11 ³ / ₄ " Dia. | 24" | | | 3" Dia. Post Fitter | | 3-60w Cand. | | OL |
| 1142 OL | 11 ³ / ₄ " Dia. | 18 ¹ / ₂ " | | | 5 ¹ / ₄ " Dia. Canopy | 6', 5' | 1-100w Med. | | OL |
| 1144 OL | 9 ³ / ₄ " W | 17 ¹ / ₄ " | 9 ¹ / ₄ " | 9 ¹ / ₂ " | 4 ¹ / ₂ " W, 9" H Back Plate | | 1-75w Med. | | OL |
| 1145 OL | 11 ³ / ₄ " W | 20 ³ / ₄ " | 11 ¹ / ₄ " | 10 ³ / ₄ " | 4 ¹ / ₂ " W, 9" H Back Plate | | 1-100w Med. | | OL |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

CORDILLERA™

Cordillera conveys contemporary chic with tall tubular glass, three-quarter trim rings and dramatic scaling. Solid aluminum construction and a Buckeye Bronze finish is paired with light etched amber glass to complete this bold design.

FINISH Buckeye Bronze

GLASS Light Etched Amber



Cordillera Chandeliers,
pages 104-105



1695 KZ
1695 KZ-GU24





1694 KZ
1694 KZ-GU24







1690 KZ
1690 KZ-GU24



1691 KZ
1691 KZ-GU24



CORDILLERA Buckeye Bronze (KZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|-------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|
| 1690 KZ | 4½" W | 16" | 7½" | 8" | 4½" W, 11" H Back Plate | 1-75w Med. |  GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | KZ |
| 1691 KZ | 7¾" W | 23" | | | 3" Dia. Post Fitter | 1-100w Med. |  1691 KZ-GU24 | KZ |
| 1694 KZ | 4¾" W | 18" | 8½" | 9" | 4½" W, 11" H Back Plate | 1-100w Med. |  1694 KZ-GU24 | KZ |
| 1695 KZ | 4¾" W | 24" | 8½" | 12" | 4½" W, 11" H Back Plate | 1-100w Med. |  1695 KZ-GU24 | KZ |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

THISTLEDOWN™

Thistledown is an updated traditional design with smooth, flowing transitions that blend into an industrial yoke-mount center stem. Solid aluminum construction in a Victorian Bronze finish complements its amber linen glass for a warm elegance.

FINISH Victorian Bronze

GLASS Amber Linen



Thistledown Chandeliers,
pages 130-132



Thistledown path lights are
available in the Hinkley
Landscape Lighting catalog.



1285 VZ



1282 VZ



4171 VZ



1280 VZ



1286 VZ



1284 VZ



1281 VZ

THISTLEDOWN Victorian Bronze (VZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|------------------------|----------------|-------------|-----------------------|
| 1280 VZ | 8½" W | 13¼" | 10" | 7" | 5" W, 9" H Back Plate | | 1-60w Med. | VZ |
| 1281 VZ | 12¾" Dia. | 22½" | | | 3" Dia. Post Fitter | | 1-100w Med. | VZ |
| 1282 VZ | 12¾" Dia. | 20¾" | | | 5¾" Dia. Canopy | 6', 5' | 1-100w Med. | VZ |
| 1284 VZ | 10½" W | 16" | 11½" | 8½" | 5" W, 9" H Back Plate | | 1-75w Med. | VZ |
| 1285 VZ | 12¾" W | 20½" | 14¾" | 11" | 5" W, 12" H Back Plate | | 1-100w Med. | VZ |
| 1286 VZ | 6½" W | 9¾" | 7½" | 5¼" | 5" W, 7" H Back Plate | | 1-60w Med. | VZ |
| 4171 VZ | 15¼" Dia. | 8" | | | | | 3-60w Med. | VZ |

For posts and pier mounts, see pages 613-614. When fitted with DSL-40, this item is Dark Sky compliant, see pages 412-413.

WABASH™

Wabash features solid aluminum construction with clear beveled glass, etched glass corner panels and decorative chevron detailing in a distressed finish.

FINISH Mocha

GLASS Clear Beveled with Etched Glass Corner Panels



1336 MO
1336 MO-GU24



1334 MO
1334 MO-GU24



1332 MO
1332 MO-GU24



1331 MO
1331 MO-GU24



1335 MO
1335 MO-GU24



WABASH Mocha (MO)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | |
|---------|----------------|--------|------|------------------|--------------------------|----------------|-------------|-------------|------------------------|-----------------------|
| | | | | | | | | LED | LED LIGHT ENGINE | AVAILABLE FINISHES |
| 1331 MO | 11" W | 23" | | | 3" Dia. Post Fitter | | 3-40w Cand. | 1331 MO-LED | UNI-100 | MB, MO |
| 1332 MO | 11" W | 17¾" | | | 4½" Dia. Canopy | 6', 5' | 3-40w Cand. | 1332 MO-LED | UNI-100 | MB, MO |
| 1334 MO | 8¼" W | 13¾" | 10" | 4¼" | 6" W, 9" H Back Plate | | 2-40w Cand. | 1334 MO-LED | UNI-60 | MB, MO |
| 1335 MO | 11" W | 18½" | 13¾" | 5¼" | 5½" W, 11¾" H Back Plate | | 3-40w Cand. | 1335 MO-LED | UNI-100 | MB, MO |
| 1336 MO | 6¼" W | 10½" | 7¾" | 3½" | 4½" W, 6¾" H Back Plate | | 1-60w Med. | 1336 MO-LED | UNI-60 | MB, MO |

For posts and pier mounts, see pages 613-614. For LED specifications, see pages 412-413.

Wabash features solid aluminum construction with clear beveled glass, etched glass corner panels and decorative chevron detailing in a distressed finish.

Museum Black FINISH

Clear Beveled with Etched Glass Corner Panels GLASS

WABASH™



1332 MB
1332 MB-GU24



1334 MB
1334 MB-GU24



1336 MB
1336 MB-GU24



1335 MB
1335 MB-GU24



1331 MB
1331 MB-GU24



WABASH Museum Black (MB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | |
|---------|----------------|--------|------|------------------|--------------------------|----------------|-------------|-------------|------------------------|-----------------------|
| | | | | | | | | LED | LED LIGHT ENGINE | AVAILABLE FINISHES |
| 1331 MB | 11" W | 23" | | | 3" Dia. Post Fitter | | 3-40w Cand. | 1331 MB-LED | UNI-100 | MB, MO |
| 1332 MB | 11" W | 17¾" | | | 4½" Dia. Canopy | 6', 5' | 3-40w Cand. | 1332 MB-LED | UNI-100 | MB, MO |
| 1334 MB | 8¼" W | 13¾" | 10" | 4¼" | 6" W, 9" H Back Plate | | 2-40w Cand. | 1334 MB-LED | UNI-60 | MB, MO |
| 1335 MB | 11" W | 18½" | 13¾" | 5¼" | 5½" W, 11¼" H Back Plate | | 3-40w Cand. | 1335 MB-LED | UNI-100 | MB, MO |
| 1336 MB | 6¼" W | 10½" | 7¾" | 3½" | 4½" W, 6¾" H Back Plate | | 1-60w Med. | 1336 MB-LED | UNI-60 | MB, MO |

For posts and pier mounts, see pages 613-614. For LED specifications, see pages 412-413.

TRAFALGAR™

Trafalgar's grand design in sturdy cast aluminum adds historical flair with delicate scroll arch detail, authentic distressed finish and clear seeded glass.

FINISH Mocha

GLASS Clear Seedy



TRAFALGAR Mocha (MO)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOPTO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------|------|-----------------|--------------------------|----------------|-------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1311 MO | 12" W | 27½" | | | 3" Dia. Post Fitter | | 3-40w Cand. | 1311 MO-GU24 | | | MB, MO |
| 1312 MO | 12" W | 24¾" | | | 5" Dia. Canopy | 6', 5' | 3-40w Cand. | 1312 MO-GU24 | | | MB, MO |
| 1314 MO | 8" W | 17½" | 10½" | 7½" | 6" W, 12" H Back Plate | | 1-75w Med. | 1314 MO-GU24 | | | MB, MO |
| 1315 MO | 10" W | 22" | 13½" | 9½" | 7¼" W, 14¼" H Back Plate | | 3-40w Cand. | 1315 MO-GU24 | | | MB, MO |
| 1316 MO | 6" W | 10" | 7½" | 5¼" | 4½" W, 7" H Back Plate | | 1-60w Med. | 1316 MO-GU24 | 1316 MO-LED | UNI-60 | MB, MO |
| 1319 MO | 12" W | 26½" | 16" | 11½" | 7¼" W, 17¼" H Back Plate | | 3-40w Cand. | 1319 MO-GU24 | | | MB, MO |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

Trafalgar's grand design in sturdy cast aluminum adds historical flair with delicate scroll arch detail, authentic distressed finish and clear seedy glass.

Museum Black FINISH
Clear Seedy GLASS

TRAFALGAR™



TRAFALGAR Museum Black (MB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOPTO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------|------|-----------------|--------------------------|----------------|-------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1311 MB | 12" W | 27½" | | | 3" Dia. Post Fitter | | 3-40w Cand. | 1311 MB-GU24 | | | MB, MO |
| 1312 MB | 12" W | 24¾" | | | 5" Dia. Canopy | 6', 5' | 3-40w Cand. | 1312 MB-GU24 | | | MB, MO |
| 1314 MB | 8" W | 17½" | 10½" | 7½" | 6" W, 12" H Back Plate | | 1-75w Med. | 1314 MB-GU24 | | | MB, MO |
| 1315 MB | 10" W | 22" | 13½" | 9½" | 7¼" W, 14¼" H Back Plate | | 3-40w Cand. | 1315 MB-GU24 | | | MB, MO |
| 1316 MB | 6" W | 10" | 7½" | 5¼" | 4½" W, 7" H Back Plate | | 1-60w Med. | 1316 MB-GU24 | 1316 MB-LED | UNI-60 | MB, MO |
| 1319 MB | 12" W | 26½" | 16" | 11½" | 7¼" W, 17¼" H Back Plate | | 3-40w Cand. | 1319 MB-GU24 | | | MB, MO |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

CHESTERFIELD™

Chesterfield's clean lines and seamless transitions contribute a current design element to its traditional form. Its updated scroll arm is made from laser cut aluminum, complemented by candelabra lamping, clear seedy glass and Black powder coat finish.

FINISH Black

GLASS Clear Seedy



1385 BK



CHESTERFIELD Black (BK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-----------------------|
| 1380 BK | 6½" W | 17¼" | 8½" | 11" | 4½" W, 7¼" H Back Plate | | 1-100w Med. | BK |
| 1381 BK | 10½" W | 23¾" | | | 3" Dia. Post Fitter | | 3-60w Cand. | BK |
| 1382 BK | 10½" W | 20½" | | | 6½" Dia. Canopy | 6', 5' | 3-60w Cand. | BK |
| 1384 BK | 8½" W | 20" | 10½" | 11¼" | 4½" W, 7¼" H Back Plate | | 2-60w Cand. | BK |
| 1385 BK | 10½" W | 23½" | 12¾" | 12" | 4½" W, 7¼" H Back Plate | | 3-60w Cand. | BK |

For posts and pier mounts, see pages 613-614.

TRELLIS™

Trellis is a traditional European hanging wall lantern design featuring a solid aluminum construction in a Regency Bronze finish with dense clear seedy glass. The large scroll arm detail, cast loop finial and true rivet detail create a refined elegance.

FINISH Regency Bronze

GLASS Clear Seedy



1435 RB
1435 RB-LED





1432 RB
1432 RB-LED



1438 RB
1438 RB-LED



1437 RB
(pier mount)



1431 RB
1431 RB-LED



TRELLIS Regency Bronze (RB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | AVAILABLE FINISHES |
| 1431 RB | 11" W | 21" | | | 3" Dia. Post Fitter | | 3-60w Cand. | 1431 RB-LED | UNI-100 | RB |
| 1432 RB | 11" W | 23¼" | | | 4½" Square Canopy | 6', 5' | 3-60w Cand. | 1432 RB-LED | UNI-100 | RB |
| 1435 RB | 11" W | 22¼" | 16¼" | 8" | 4½" W, 10" H Back Plate | | 4-60w Cand. | 1435 RB-LED | UNI-100 | RB |
| 1437 RB | 11" W | 19¾" | | | 10¼" Square Base | | 4-60w Cand. | | | RB |
| 1438 RB | 13" W | 26¼" | 19" | 9½" | 5" W, 13" H Back Plate | | 4-60w Cand. | 1438 RB-LED | UNI-100 | RB |

For posts and pier mounts, see pages 613-614. For LED specifications, see pages 412-413.



TRELLIS Regency Bronze (RB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-------------|------------------------|-----------------------|
| | | | | | | | | LED | LED LIGHT ENGINE | AVAILABLE FINISHES |
| 1430 RB | 7" W | 15¼" | 11¼" | 6" | 4½" W, 7" H Back Plate | | 1-100w Med. | 1430 RB-LED | UNI-100 | RB |
| 1434 RB | 9" W | 19¾" | 14¼" | 8" | 4½" W, 10" H Back Plate | | 3-60w Cand. | 1434 RB-LED | UNI-100 | RB |
| 1436 RB | 11" W | 35¾" | 16½" | 18¾" | 4½" W, 13" H Back Plate | | 4-60w Cand. | | | RB |
| 1439 RB | 16" W | 52" | 24" | 27½" | 4¾" W, 20" H Back Plate | | 4-60w Cand. | | | RB |

For LED specifications, see pages 412-413.



Fixtures shown: Trellis 1435 RB, page 567;
Hardy Island path lights 16007 MZ (Hinkley Landscape Lighting Catalog)

BARRINGTON™

Barrington's chic, classic style transforms this design into a modern interpretation of the traditional outdoor lantern, constructed of solid aluminum. The cast finials combine with the clear seedy glass for added authenticity, while the lustrous finish is created in a multi-step, hand-painted process.

FINISH Victorian Bronze **GLASS** Clear Seedy



1754 VZ



1752 VZ



1750 VZ



1751 VZ

BARRINGTON Victorian Bronze (VZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|--------------------------|----------------|-------------|-----------------------|
| 1750 VZ | 7½" W | 20¼" | 10½" | 10¼" | 4½" W, 11½" H Back Plate | | 3-60w Cand. | VZ |
| 1751 VZ | 9" Dia. | 23¼" | | | 3" Dia. Post Fitter | | 4-60w Cand. | VZ |
| 1752 VZ | 9" Dia. | 24¼" | | | 5¾" Dia. Canopy | 6', 5' | 4-60w Cand. | VZ |
| 1754 VZ | 9" W | 22½" | 12½" | 13¾" | 4½" W, 11½" H Back Plate | | 4-60w Cand. | VZ |

For posts and pier mounts, see pages 613-614.

OXFORD™

Oxford's sophisticated silhouette features solid aluminum construction with bead detailing in a Midnight Bronze finish, complemented by clear optic glass for a chic yet classic style statement.

FINISH Midnight Bronze

GLASS Clear Optic



1245 MN



OXFORD Midnight Bronze (MN)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-----------------------|
| 1240 MN | 7" W | 17¼" | 9" | 10" | 4¾" W, 9" H Back Plate | | 1-60w Med. | MN |
| 1241 MN | 12" Dia. | 28¼" | | | 3" Dia. Post Fitter | | 3-40w Cand. | MN |
| 1242 MN | 12" Dia. | 27½" | | | 6¾" Dia. Canopy | 6', 5' | 3-40w Cand. | MN |
| 1243 MN | 16¼" Dia. | 7½" | | | | | 2-60w Med. | MN |
| 1244 MN | 9¾" W | 23½" | 12¼" | 12½" | 4¾" W, 9" H Back Plate | | 3-40w Cand. | MN |
| 1245 MN | 12" W | 28½" | 15" | 16" | 4¾" W, 16" H Back Plate | | 3-40w Cand. | MN |

For posts and pier mounts, see pages 613-614.

KEY WEST™

Key West captures a gracious elegance featuring cast aluminum construction and ornate decorative cast detailing in a Regency Bronze finish, complemented by antique vanilla glass.

FINISH Regency Bronze

GLASS Antique Vanilla



1615 RB
1615 RB-GU24





1614 RB
1614 RB-GU24

1613 RB
1613 RB-GU24

1612 RB
1612 RB-GU24

1616 RB
1616 RB-GU24
1616 RB-LED

1610 RB
1610 RB-GU24

1611 RB
1611 RB-GU24

KEY WEST Regency Bronze (RB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1610 RB | 7" W | 16¼" | 9¼" | 8¾" | 4½" W, 7" H Back Plate | | 1-60w Med. | 1610 RB-GU24 | | | RB |
| 1611 RB | 12" Dia. | 21¼" | | | 3" Dia. Post Fitter | | 1-100w Med. | 1611 RB-GU24 | | | RB |
| 1612 RB | 12" Dia. | 23¾" | | | 5½" Dia. Canopy | 6', 5' | 1-100w Med. | 1612 RB-GU24 | | | RB |
| 1613 RB | 15" Dia. | 8¼" | | | | | 2-60w Med. | 1613 RB-GU24 | | | RB |
| 1614 RB | 9" W | 21" | 12¼" | 12½" | 4½" W, 9" H Back Plate | | 1-75w Med. | 1614 RB-GU24 | | | RB |
| 1615 RB | 12" W | 27" | 14¾" | 13¾" | 4½" W, 9" H Back Plate | | 1-100w Med. | 1615 RB-GU24 | | | RB |
| 1616 RB | 5½" W | 8½" | 6¾" | 3" | 4½" W, 4½" H Back Plate | | 1-60w Med. | 1616 RB-GU24 | 1616 RB-LED | UNI-60 | RB |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

LUCERNE™

Lucerne's grand silhouette features exquisite decorative cast detailing and solid brass construction in a Copper Bronze finish. Clear bent glass is captured in the fixture's gentle arches.

FINISH Copper Bronze

GLASS Clear Bent Panels



2315 CB
2315 CB-LED





LUCERNE Copper Bronze (CB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | AVAILABLE FINISHES |
| 2310 CB | 8½" W | 15" | 10½" | 3½" | 4½" W, 7½" H Back Plate | | 2-40w Cand. | 2310 CB-LED | UNI-60 | CB |
| 2311 CB | 13¼" Dia. | 26½" | | | 3" Dia. Post Fitter | | 4-40w Cand. | | | CB |
| 2312 CB | 13¼" Dia. | 26½" | | | 5" Dia. Canopy | 6', 5 | 4-40w Cand. | 2312 CB-LED | UNI-100 | CB |
| 2313 CB | 12½" Dia. | 7¼" | | | | | 2-60w Cand. | | | CB |
| 2314 CB | 10½" W | 24½" | 13¾" | 11¾" | 5" W, 16" H Back Plate | | 3-40w Cand. | 2314 CB-LED | UNI-100 | CB |
| 2315 CB | 13¼" W | 30" | 17¼" | 13½" | 5" W, 16½" H Back Plate | | 4-40w Cand. | 2315 CB-LED | UNI-100 | CB |
| 2316 CB | 6" W | 11¼" | 7¼" | 3½" | 5" W, 7" H Back Plate | | 1-60w Cand. | 2316 CB-LED | UNI-60 | CB |
| 2317 CB | 10½" Dia. | 22¼" | | | 3" Dia. Post Fitter | | 3-40w Cand. | | | CB |

For posts and pier mounts, see pages 613-614. For LED specifications, see pages 412-413.

AUGUSTA™

Augusta's sophisticated beauty showcases its stylish clear bent, beveled and bound glass. Constructed in solid brass with a Copper Bronze finish, this classic traditional design also offers removable scrolls.

FINISH Copper Bronze

GLASS Bound, Bent & Beveled Clear Panels



2456 CB



2452 CB



2443 CB



2450 CB



2454 CB



2451 CB

AUGUSTA Copper Bronze (CB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------------|------|------------------|-------------------------|----------------|------------|-----------------------|
| 2443 CB | 15¾" Dia. | 9" | | | 12" Dia. Canopy | | 2-60w Med. | CB, MB |
| 2450 CB | 9" W | 15½", 12½"** | 8½" | 7½", 4½"** | 4½" W, 6½" H Back Plate | | 1-60w Med. | CB |
| 2451 CB | 13" Dia. | 23¼" | | | 3" Dia. Post Fitter | | 3-40w Med. | CB |
| 2452 CB | 13" Dia. | 27½" | | | 5" Dia. Canopy | 6', 5' | 3-40w Med. | CB |
| 2454 CB | 11" W | 27", 22½"** | 10½" | 18¼", 13¾"** | 4½" W, 17" H Back Plate | | 3-40w Med. | CB |
| 2456 CB | 16" W | 38¾", 31¾"** | 14½" | 26¼", 19½"** | 5" W, 24" H Back Plate | | 4-40w Med. | CB |

*Measurement without removable scroll. For posts and pier mounts, see pages 613-614.

WINDSOR™

Windsor combines elegant details and decorative cast detailing into its cast aluminum construction. The unique River Rock finish and clear water glass add to its majestic style.

FINISH River Rock

GLASS Clear Water Glass



1929 RK



1892 RK



1895 RK



1894 RK



1890 RK
1890 RK-LED



1898 RK
1898 RK-LED



1899 RK
1899 RK-LED



1891 RK



1921 RK

WINDSOR River Rock (RK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | AVAILABLE FINISHES |
| 1890 RK | 7" W | 12½" | 8¼" | 4¾" | 5¾" W, 8" H Back Plate | | 1-75w Med. | 1890 RK-LED | UNI-60 | BK, RK |
| 1891 RK | 12½" Dia. | 30" | | | 3" Dia. Post Fitter | | 4-40w Cand. | | | BK, RK |
| 1892 RK | 12½" Dia. | 28½" | | | 5½" Dia. Canopy | 6', 5' | 4-40w Cand. | | | BK, RK |
| 1894 RK | 9½" W | 25½" | 12" | 13" | 5¾" W, 12" H Back Plate | | 3-40w Cand. | | | BK, RK |
| 1895 RK | 12½" W | 32" | 15½" | 16½" | 6¼" W, 15" H Back Plate | | 4-40w Cand. | | | BK, RK |
| 1898 RK | 9½" W | 20¾" | 11¾" | 12½" | 5¾" W, 12" H Back Plate | | 3-40w Cand. | 1898 RK-LED | UNI-100 | BK, RK |
| 1899 RK | 12½" W | 25¾" | 15½" | 15¼" | 6¼" W, 15" H Back Plate | | 4-40w Cand. | 1899 RK-LED | UNI-100 | BK, RK |
| 1921 RK | 14½" Dia. | 34¾" | | | 3" Dia. Post Fitter | | 6-40w Cand. | | | BK, RK |
| 1929 RK | 14" W | 42" | 17" | 19½" | 6¼" W, 17" H Back Plate | | 6-40w Cand. | | | BK, RK |

For posts and pier mounts, see pages 613-614. For LED specifications, see pages 412-413.

WINDSOR™

Windsor combines elegant details and decorative cast detailing into its cast aluminum construction. The Black finish and clear water glass add to its majestic style.

FINISH Black

GLASS Clear Water Glass



1929 BK



1892 BK



1895 BK



1894 BK



1890 BK
1890 BK-LED



1898 BK
1898 BK-LED



1899 BK
1899 BK-LED



1891 BK



1921 BK

WINDSOR Black (BK)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | AVAILABLE FINISHES |
| 1890 BK | 7" W | 12½" | 8¼" | 4¾" | 5¾" W, 8" H Back Plate | | 1-75w Med. | 1890 BK-LED | UNI-60 | BK, RK |
| 1891 BK | 12½" Dia. | 30" | | | 3" Dia. Post Fitter | | 4-40w Cand. | | | BK, RK |
| 1892 BK | 12½" Dia. | 28½" | | | 5½" Dia. Canopy | 6', 5' | 4-40w Cand. | | | BK, RK |
| 1894 BK | 9½" W | 25½" | 12" | 13" | 5¾" W, 12" H Back Plate | | 3-40w Cand. | | | BK, RK |
| 1895 BK | 12½" W | 32" | 15½" | 16½" | 6¼" W, 15" H Back Plate | | 4-40w Cand. | | | BK, RK |
| 1898 BK | 9½" W | 20¾" | 11¾" | 12½" | 5¾" W, 12" H Back Plate | | 3-40w Cand. | 1898 BK-LED | UNI-100 | BK, RK |
| 1899 BK | 12½" W | 25¾" | 15½" | 15¼" | 6¼" W, 15" H Back Plate | | 4-40w Cand. | 1899 BK-LED | UNI-100 | BK, RK |
| 1921 BK | 14½" Dia. | 34¾" | | | 3" Dia. Post Fitter | | 6-40w Cand. | | | BK, RK |
| 1929 BK | 14" W | 42" | 17" | 19½" | 6¼" W, 17" H Back Plate | | 6-40w Cand. | | | BK, RK |

For posts and pier mounts, see pages 613-614. For LED specifications, see pages 412-413.

FORUM™

Forum's distinguished silhouette features cast aluminum construction in a French Bronze finish with decorative cast detailing and generous panels of seedy water glass.

FINISH French Bronze

GLASS Seedy Water Glass



1944 FZ



1942 FZ



1940 FZ



1946 FZ
1946 FZ-LED



1941 FZ

FORUM French Bronze (FZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-------------|------------------------|-----------------------|
| | | | | | | | | LED | LED LIGHT ENGINE | AVAILABLE FINISHES |
| 1940 FZ | 7" W | 21" | 9¾" | 9½" | 5" W, 8" H Back Plate | | 1-75w Med. | | | FZ, MB |
| 1941 FZ | 9½" W | 23½" | | | 3" Dia. Post Fitter | | 3-40w Cand. | | | FZ, MB |
| 1942 FZ | 9½" W | 25¾" | | | 5½" Dia. Canopy | 6', 5' | 3-40w Cand. | | | FZ, MB |
| 1944 FZ | 9½" W | 27½" | 12" | 11" | 5" W, 8" H Back Plate | | 3-40w Cand. | | | FZ, MB |
| 1946 FZ | 5½" W | 12¾" | 7½" | 6" | 4¾" W, 6½" H Back Plate | | 1-40w Med. | 1946 FZ-LED | UNI-100 | FZ, MB |

For posts and pier mounts, see pages 613-614. For LED specifications, see pages 412-413.

FORUM™

Forum's distinguished silhouette features cast aluminum construction in a Museum Black finish with decorative cast detailing and generous panels of seedy water glass.

FINISH Museum Black

GLASS Seedy Water Glass



1944 MB



1942 MB



1940 MB



1946 MB
1946 MB-LED



1941 MB

FORUM Museum Black (MB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | |
|---------|----------------|--------|------|------------------|-------------------------|----------------|-------------|-------------|------------------------|-----------------------|
| | | | | | | | | LED | LED LIGHT ENGINE | AVAILABLE FINISHES |
| 1940 MB | 7" W | 21" | 9¾" | 9½" | 5" W, 8" H Back Plate | | 1-75w Med. | | | FZ, MB |
| 1941 MB | 9½" W | 23½" | | | 3" Dia. Post Fitter | | 3-40w Cand. | | | FZ, MB |
| 1942 MB | 9½" W | 25¾" | | | 5½" Dia. Canopy | 6', 5' | 3-40w Cand. | | | FZ, MB |
| 1944 MB | 9½" W | 27½" | 12" | 11" | 5" W, 8" H Back Plate | | 3-40w Cand. | | | FZ, MB |
| 1946 MB | 5½" W | 12¾" | 7½" | 6" | 4¾" W, 6½" H Back Plate | | 1-40w Med. | 1946 MB-LED | UNI-100 | FZ, MB |

For posts and pier mounts, see pages 613-614. For LED specifications, see pages 412-413.

SAN CLEMENTE™

San Clemente's elegant shape takes center stage with clear bent, beveled and bound glass as the central design element. Cast aluminum and brass construction complemented by exquisite cast ornamental detailing completes its captivating appeal.

FINISH Copper Bronze

GLASS Clear Bent, Beveled and Bound Panels



2446 CB



2442 CB



2443 CB



2440 CB



2445 CB



2444 CB



2441 CB



2447 CB

SAN CLEMENTE Copper Bronze (CB)

| ITEM | WIDTH/DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/CHAIN | BULBS | AVAILABLE FINISHES |
|---------|------------|--------|------|---------------|-------------------------|------------|-------------|--------------------|
| 2440 CB | 9½" W | 14½" | 9½" | 5½" | 4½" W, 6½" H Back Plate | | 1-60w Med. | CB, MB |
| 2441 CB | 14" Dia. | 23" | | | 3" Dia. Post Fitter | | 3-40w Cand. | CB, MB |
| 2442 CB | 14" Dia. | 22" | | | 5" Dia. Canopy | 6', 5' | 3-40w Cand. | CB, MB |
| 2443 CB | 15¾" Dia. | 9" | | | | | 2-60w Med. | CB, MB |
| 2444 CB | 12" W | 21" | 12½" | 6½" | 4½" W, 9" H Back Plate | | 3-40w Cand. | CB, MB |
| 2445 CB | 14" W | 21½" | 13" | 6" | 4½" W, 9" H Back Plate | | 3-40w Cand. | CB |
| 2446 CB | 18" W | 28" | 16" | 8¼" | 5" W, 14" H Back Plate | | 4-40w Cand. | CB, MB |
| 2447 CB | 15½" Dia. | 26½" | | | 3" Dia. Post Fitter | | 3-40w Cand. | CB, MB |

For posts and pier mounts, see pages 613-614.

SAN CLEMENTE™

San Clemente's elegant shape takes center stage with clear bent, beveled and bound glass as the central design element. Cast aluminum and brass construction complemented by exquisite cast ornamental detailing completes its captivating appeal.

FINISH Museum Black

GLASS Clear Bent, Beveled and Bound Panels



2446 MB



2442 MB



2444 MB



2443 MB



2440 MB



2441 MB



2447 MB

SAN CLEMENTE Museum Black (MB)

| ITEM | WIDTH/DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|------------|--------|------|------------------|-------------------------|----------------|-------------|-----------------------|
| 2440 MB | 9½" W | 14½" | 9½" | 5½" | 4½" W, 6½" H Back Plate | | 1-60w Med. | CB, MB |
| 2441 MB | 14" Dia. | 23" | | | 3" Dia. Post Fitter | | 3-40w Cand. | CB, MB |
| 2442 MB | 14" Dia. | 22" | | | 5" Dia. Canopy | 6', 5' | 3-40w Cand. | CB, MB |
| 2443 MB | 15¾" Dia. | 9" | | | | | 2-60w Med. | CB, MB |
| 2444 MB | 12" W | 21" | 12½" | 6½" | 4½" W, 9" H Back Plate | | 3-40w Cand. | CB, MB |
| 2446 MB | 18" W | 28" | 16" | 8¼" | 5" W, 14" H Back Plate | | 4-40w Cand. | CB, MB |
| 2447 MB | 15½" Dia. | 26½" | | | 3" Dia. Post Fitter | | 3-40w Cand. | CB, MB |

For posts and pier mounts, see pages 613-614.

MONTICELLO™

Monticello's graceful curves emphasize its clear bent, beveled and bound glass panels. The durable solid brass construction showcases a rich Copper Bronze finish.

FINISH Copper Bronze

GLASS Clear Bent, Beveled and Bound Panels



2336 CB



2332 CB



2443 CB



2330 CB



2335 CB



2334 CB



2331 CB



2337 CB

MONTICELLO Copper Bronze (CB)

| ITEM | WIDTH/DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/CHAIN | BULBS | AVAILABLE FINISHES |
|---------|------------|--------|------|---------------|-------------------------|------------|-------------|--------------------|
| 2330 CB | 9" W | 15¼" | 9¾" | 5" | 5" W, 7" H Back Plate | | 1-60w Med. | CB |
| 2331 CB | 13" Dia. | 21¼" | | | 3" Dia. Post Fitter | | 3-40w Cand. | CB |
| 2332 CB | 13" Dia. | 20¼" | | | 5" Dia. Canopy | 6', 5' | 3-40w Cand. | CB |
| 2334 CB | 11" W | 19¼" | 12½" | 6" | 4½" W, 9¼" H Back Plate | | 3-40w Cand. | CB |
| 2335 CB | 13" W | 20½" | 13¾" | 6¼" | 5" W, 9¼" H Back Plate | | 3-40w Cand. | CB |
| 2336 CB | 16½" W | 26½" | 15¾" | 8" | 4½" W, 16" H Back Plate | | 4-40w Cand. | CB |
| 2337 CB | 16½" Dia. | 27" | | | 3" Dia. Post Fitter | | 4-40w Cand. | CB |
| 2443 CB | 15¾" Dia. | 9" | | | | | 2-60w Cand. | CB, MB |

For posts and pier mounts, see pages 613-614.

CLIFTON BEACH™

Clifton Beach is an aristocratic style that adds a dignified air to a home's façade. The lustrous Antique Copper finish, durable solid brass construction and clear seedy bound glass add to the genteel design.

FINISH Antique Copper

GLASS Clear Seedy Bound



2268 AP



CLIFTON BEACH Antique Copper (AP)

| ITEM | WIDTH/DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/CHAIN | BULBS | AVAILABLE FINISHES |
|---------|------------|--------|------|---------------|--------------------------|------------|-------------|--------------------|
| 2260 AP | 6¾" W | 11" | 6½" | 4½" | 4¾" W, 5½" H Back Plate | | 1-60w Med. | AP |
| 2261 AP | 12½" Dia. | 24" | | | 3" Dia. Post Fitter | | 3-40w Cand. | AP |
| 2262 AP | 10½" Dia. | 19" | | | 5" Dia. Canopy | 6', 5' | 3-40w Cand. | AP |
| 2263 AP | 9½" W | 14¾" | 8¾" | 6" | 4¾" W, 7" H Back Plate | | 1-75w Med. | AP |
| 2265 AP | 9½" W | 17¾" | 9" | 11¼" | 4¾" W, 12¾" H Back Plate | | 2-40w Cand. | AP |
| 2268 AP | 12½" W | 25½" | 11½" | 16½" | 4¾" W, 18" H Back Plate | | 3-40w Cand. | AP |

For posts and pier mounts, see pages 613-614.

CLIFTON PARK™

Clifton Park has an aristocratic style that adds a dignified air to a home's façade. The sleek Copper Bronze finish, durable solid brass construction and clear beveled and bound glass add to the genteel style.

FINISH Copper Bronze

GLASS Glass



2429 CB



2420 CB
2420 CB-LED



2428 CB



2426 CB



2406 CB

CLIFTON PARK Copper Bronze (CB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | BULBS | ECO-OPTIONS | | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|--------------------------|-------------|-------------|------------------------|-----------------------|
| | | | | | | | LED | LED LIGHT ENGINE | |
| 2406 CB | 17½" W | 36" | 16" | 21¼" | 4¾" W, 27¼" H Back Plate | 4-40w Cand. | | | CB |
| 2420 CB | 6¾" W | 10¾" | 6½" | 4½" | 4¾" W, 5½" H Back Plate | 1-60w Med. | 2420 CB-LED | UNI-60 | CB |
| 2426 CB | 10½" W | 21½" | 10" | 14" | 4¾" W, 14¼" H Back Plate | 3-40w Cand. | | | CB |
| 2428 CB | 12½" W | 25½" | 11½" | 15¼" | 4¾" W, 18¼" H Back Plate | 3-40w Cand. | | | CB |
| 2429 CB | 12½" Dia. | 6¾" | | | | 2-60w Med. | | | CB |

For LED specifications, see pages 412-413.



2422 CB



2424 CB
2424 CB-LED



2425 CB



2423 CB
2423 CB-LED



2421 CB



2407 CB

CLIFTON PARK Copper Bronze (CB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | |
|---------|----------------|--------|------|------------------|--------------------------|----------------|-------------|-------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | AVAILABLE FINISHES |
| 2407 CB | 17½" Dia. | 26½" | | | 3" Dia. Post Fitter | | 4-40w Cand. | | | CB |
| 2421 CB | 12½" Dia. | 23¾" | | | 3" Dia. Post Fitter | | 3-40w Cand. | | | CB |
| 2422 CB | 10½" Dia. | 19" | | | 5" Dia. Canopy | 6', 5' | 3-40w Cand. | | | CB |
| 2423 CB | 9¼" W | 14¾" | 8¾" | 6¼" | 4¾" W, 7" H Back Plate | | 1-75w Med. | 2423 CB-LED | UNI-60 | CB |
| 2424 CB | 10½" W | 18½" | 10" | 7" | 4¾" W, 7" H Back Plate | | 3-40w Cand. | 2424 CB-LED | UNI-100 | CB |
| 2425 CB | 9¼" W | 17¾" | 8¾" | 11¼" | 4¾" W, 12¾" H Back Plate | | 2-40w Cand. | | | CB |

For posts and pier mounts, see pages 613-614. For LED specifications, see pages 412-413.

BRYNMAR™

Gorgeous details add drama to Brynmar's classic cast aluminum design. The decorative cast leaf and cross-hatch detailing in a Regency Bronze finish complement the stylish amber linen glass.

FINISH Regency Bronze
GLASS Amber Linen



1935 RB
1935 RB-GU24
1935 RB-LED



BRYN MAR Regency Bronze (RB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | | | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|------------------------|----------------|-------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------|-----------------------|
| | | | | | | | | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | LED Includes integrated high efficiency LED light source. | LED LIGHT ENGINE | |
| 1930 RB | 7" W | 12¼" | 8" | 4" | 4¾" W, 7" H Back Plate | | 1-60w Med. | 1930 RB-GU24 | 1930 RB-LED | UNI-60 | RB |
| 1931 RB | 12" W | 27" | | | 3" Dia. Post Fitter | | 1-100w Med. | 1931 RB-GU24 | 1931 RB-LED | UNI-100 | RB |
| 1932 RB | 12" W | 27¾" | | | 5½" Dia. Canopy | 6', 5' | 1-100w Med. | 1932 RB-GU24 | 1932 RB-LED | UNI-100 | RB |
| 1934 RB | 9½" W | 20¼" | 10½" | 10¾" | 5" W, 14" H Back Plate | | 1-75w Med. | 1934 RB-GU24 | 1934 RB-LED | UNI-60 | RB |
| 1935 RB | 12" W | 27½" | 12¾" | 14" | 5" W, 18" H Back Plate | | 1-100w Med. | 1935 RB-GU24 | 1935 RB-LED | UNI-100 | RB |
| 1936 RB | 5" W | 8¾" | 6" | 3¼" | 4¾" W, 6" H Back Plate | | 1-60w Med. | 1936 RB-GU24 | 1936 RB-LED | UNI-60 | RB |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.

ROWE PARK™

Rowe Park features a classic design in cast aluminum with European flair including a sweeping scroll, paneled glass and fine architectural details.

FINISH Pearl Bronze

GLASS Amber Linen



2135 PZ



2132 PZ



2134 PZ



2130 PZ



2131 PZ

ROWE PARK Pearl Bronze (PZ)

| ITEM | WIDTH/DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|------------|--------|------|------------------|------------------------|----------------|-------------|-----------------------|
| 2130 PZ | 7¼" W | 16½" | 9½" | 10¼" | 4½"W, 7½" H Back Plate | | 1-60w Med. | OZ, PZ |
| 2131 PZ | 11¾" Dia. | 26¼" | | | 3" Dia. Post Fitter | | 1-100w Med. | OZ, PZ |
| 2132 PZ | 11¾" Dia. | 21¾" | | | 5½" Dia. Canopy | 6', 5' | 1-100w Med. | OZ, PZ |
| 2134 PZ | 9½" W | 21¾" | 12¼" | 13¾" | 4½"W, 9" H Back Plate | | 1-100w Med. | OZ, PZ |
| 2135 PZ | 11¾" W | 25¾" | 14¾" | 15¾" | 4½"W, 9" H Back Plate | | 1-100w Med. | OZ, PZ |

For posts and pier mounts, see pages 613-614. When fitted with DSL-40, this item is Dark Sky compliant, see pages 412-413.

ROWE PARK™

Rowe Park features a classic design in cast aluminum with European flair including sweeping scroll details, paneled glass and fine architectural details.

FINISH Oil Rubbed Bronze

GLASS Amber Linen



2135 OZ



2132 OZ



2134 OZ



2130 OZ



2131 OZ

ROWE PARK Oil Rubbed Bronze (OZ)

| ITEM | WIDTH/DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/CHAIN | BULBS | AVAILABLE FINISHES |
|---------|------------|--------|------|---------------|------------------------|------------|-------------|--------------------|
| 2130 OZ | 7¼" W | 16½" | 9½" | 10¼" | 4½"W, 7½" H Back Plate | | 1-60w Med. | OZ, PZ |
| 2131 OZ | 11¾" Dia. | 26¼" | | | 3" Dia. Post Fitter | | 1-100w Med. | OZ, PZ |
| 2132 OZ | 11¾" Dia. | 21¾" | | | 5½" Dia. Canopy | 6', 5' | 1-100w Med. | OZ, PZ |
| 2134 OZ | 9½" W | 21¾" | 12¼" | 13¾" | 4½"W, 9" H Back Plate | | 1-100w Med. | OZ, PZ |
| 2135 OZ | 11¾" W | 25¾" | 14¾" | 15¾" | 4½"W, 9" H Back Plate | | 1-100w Med. | OZ, PZ |

For posts and pier mounts, see pages 613-614. When fitted with DSL-40, this item is Dark Sky compliant, see pages 412-413.

SORRENTO™

Sorrento's cast aluminum construction and flourishing cast details are enhanced by its hand-applied Aged Iron finish with copper highlights. Stunning optic etched amber inner glass is surrounded by panels of clear seedy outer glass, creating a grand statement.

FINISH Aged Iron

GLASS Clear Seedy (outer glass), Optic Etched Amber (inner glass)



1425 AI



1422 AI



1424 AI



1420 AI



1421 AI

SORRENTO Aged Iron (AI)

| ITEM | WIDTH/DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|------------|--------|------|------------------|------------------------|----------------|-------------|-----------------------|
| 1420 AI | 8" W | 17" | 11½" | 10" | 5" W, 9" H Back Plate | | 1-100w Med. | AI |
| 1421 AI | 12¼" Dia. | 28¾" | | | 3" Dia. Post Fitter | | 1-100w Med. | AI |
| 1422 AI | 12¼" Dia. | 24" | | | 5½" Dia. Canopy | 6', 5' | 1-100w Med. | AI |
| 1424 AI | 9¾" W | 20½" | 13½" | 12" | 5" W, 9" H Back Plate | | 1-100w Med. | AI |
| 1425 AI | 12¼" W | 26¾" | 16½" | 16½" | 5" W, 13" H Back Plate | | 1-100w Med. | AI |

For posts and pier mounts, see pages 613-614.

MONTREAL™

Montreal's traditional Old World styling features ornate cast aluminum construction in an Aged Iron finish with stunning amber inside etched optic glass.

FINISH Aged Iron

GLASS Amber Inside Etched Optic




1735 AI
1735 AI-GU24





MONTREAL Aged Iron (AI)

| ITEM | WIDTH/DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/CHAIN | BULBS | ECO-OPTIONS | AVAILABLE FINISHES |
|---------|------------|--------|------|---------------|---------------------|------------|-------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| 1730 AI | 7" W | 20½" | 10½" | 9" | 7" Dia. Back Plate | | 1-100w Med. |  GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | AI |
| 1731 AI | 11" Dia. | 27½" | | | 3" Dia. Post Fitter | | 3-60w Cand. | | AI |
| 1732 AI | 11" Dia. | 29" | | | 7" Dia. Canopy | 6', 5' | 3-60w Cand. | | AI |
| 1734 AI | 8¾" W | 25¼" | 12½" | 10¾" | 7" Dia. Back Plate | | 1-100w Med. | | AI |
| 1735 AI | 11" W | 32" | 16" | 14" | 7" Dia. Back Plate | | 3-60w Cand. | | AI |
| 1736 AI | 7" W | 17¾" | 9" | 5¼" | 7" Dia. Back Plate | | 1-75w Med. | | AI |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

PLANTATION™

A Hinkley classic, the ornate Plantation collection features exceptional pineapple shaped optic glass, durable brass and aluminum construction and elaborate, decorative cast detailing to create a noble statement.

FINISH Pearl Bronze

GLASS Amber Inside Etched Optic



Plantation Chandeliers,
pages 196-203



Plantation Bath,
pages 400-401



Plantation path lights are
available in the Hinkley
Landscape Lighting catalog.



2124 PZ
2124 PZ-GU24





2122 PZ
2122 PZ-GU24



2128 PZ
2128 PZ-GU24



2123 PZ
2123 PZ-GU24



2126 PZ
2126 PZ-GU24



2120 PZ
2120 PZ-GU24



2121 PZ
2121 PZ-GU24

PLANTATION Pearl Bronze (PZ)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOPTO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | ECO-OPTIONS | AVAILABLE FINISHES |
|---------|----------------|--------|------|-----------------|------------------------|----------------|-------------|---------------------------------------------------------------------------------------|-----------------------|
| 2120 PZ | 8" W | 21¼" | 11" | 11½" | 5" W, 16" H Back Plate | | 1-75w Med. | GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps. | PZ |
| 2121 PZ | 10¼" Dia. | 25¼" | | | 3" Dia. Post Fitter | | 1-100w Med. | | PZ |
| 2122 PZ | 12½" Dia. | 28½" | | | 6" Dia. Canopy | 6', 5' | 1-100w Med. | | PZ |
| 2123 PZ | 16" Dia. | 8¾" | | | | | 3-60w Med. | | PZ |
| 2124 PZ | 10¼" W | 28" | 13½" | 14½" | 5" W, 20" H Back Plate | | 1-75w Med. | | PZ |
| 2126 PZ | 6" W | 14" | 7" | 5" | 4¾" W, 8" H Back Plate | | 1-60w Med. | | PZ |
| 2128 PZ | 12" Dia. | 8" | | | | | 2-60w Med. | | PZ |

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps, see pages 412-413.

PLANTATION™

A Hinkley classic, the ornate Plantation collection features exceptional pineapple shaped optic glass, durable brass and aluminum construction and elaborate, decorative cast detailing to create a noble statement.

FINISH Copper Bronze

GLASS Clear Optic



Plantation Chandeliers,
pages 196-203



Plantation Bath,
pages 400-401



Plantation path lights are
available in the Hinkley
Landscape Lighting catalog.



2225 CB



2224 CB



2220 CB



2221 CB



2227 CB

PLANTATION Copper Bronze (CB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|------------------------|----------------|-------------|-----------------------|
| 2220 CB | 8" W | 21¼" | 11" | 11½" | 5" W, 16" H Back Plate | | 1-75w Med. | CB |
| 2221 CB | 10¼" Dia. | 25¼" | | | 3" Dia. Post Fitter | | 3-40w Cand. | CB |
| 2224 CB | 10¼" W | 28" | 13½" | 14½" | 5" W, 20" H Back Plate | | 3-40w Cand. | CB |
| 2225 CB | 12½" W | 34" | 17½" | 17½" | 5" W, 24" H Back Plate | | 4-40w Cand. | CB |
| 2227 CB | 12½" Dia. | 29½" | | | 3" Dia. Post Fitter | | 4-40w Cand. | CB |

For posts and pier mounts, see pages 613-614.

PIER MOUNTS



2226 CB



4102 CB



4881 CB




2222 CB

PLANTATION Copper Bronze (CB)

| ITEM | WIDTH/ DIA. | HEIGHT | EXT. | TOP TO OUTLET | BACK PLATE/CANOPY | WIRE/ CHAIN | BULBS | AVAILABLE FINISHES |
|---------|----------------|--------|------|------------------|------------------------|----------------|-------------|-----------------------|
| 2222 CB | 12½" Dia. | 28½" | | | 6" Dia. Canopy | 6', 5' | 4-40w Cand. | BB, CB, PL, PZ |
| 2226 CB | 6" W | 14" | 7" | 5" | 4¾" W, 8" H Back Plate | | 1-60w Med. | CB |
| 4102 CB | 12" Dia. | 8" | | | | | 2-60w Med. | BB, CB, PL, PZ |
| 4881 CB | 16" Dia. | 8¾" | | | | | 3-60w Med. | BB, CB, PL, PZ |

POSTS



| ITEM | DIAMETER | HEIGHT | FITTER DIAMETER | WALL THICKNESS | CONSTRUCTION | ACCESSORIES INCLUDED/NOTES |
|---------|----------|--------|-----------------|----------------|-------------------------------------------|----------------------------------------|
| 6610 BK | 3" | 10' | 3" | .072" | One-Piece Post, Aluminum | Ground Outlet, Photo Cell |
| 6611 BK | 3" | 10' | 3" | .072" | One-Piece Post, Aluminum | Photo Cell |
| 6638 BK | 3" | 6½' | 3" | .080" | Post, Cast Aluminum | Cast Aluminum Base |
| 6660 BK | 3" | 7' | 3" | .050" | One-Piece Post, Aluminum | |
| 6660 BZ | 3" | 7' | 3" | .050" | One-Piece Post, Aluminum | |
| 6660 OI | 3" | 7' | 3" | .050" | One-Piece Post, Aluminum | |
| 6661 BK | 3" | 7' | 3" | .050" | One-Piece Post with Ladder Rest, Aluminum | |
| 6662 BK | 3" | 7' | 3" | .050" | One-Piece Post, Aluminum | Photo Cell |
| 6663 BK | 3" | 7' | 3" | .050" | One-Piece Post with Ladder Rest, Aluminum | Photo Cell |
| 6667 BK | 3" | 7' | 3" | .050" | One-Piece Post with Ladder Rest, Aluminum | Photo Cell and Ground Outlet |
| 6680 BK | 7¼" | 18¼" | 3" | | Slip Base, Die Cast Aluminum | 2-Piece, Used with Direct Burial Posts |
| 6808 BK | 10½" | 8' | 3" | .125" | Post, Cast Aluminum | Decorative Flange Bolt Cover |
| 6810 BK | 10½" | 10' | 3" | .125" | Post, Cast Aluminum | Decorative Flange Bolt Cover |
| 6812 BK | 10½" | 12' | 3" | .125" | Post, Cast Aluminum | Decorative Flange Bolt Cover |
| 6814 BK | 10½" | 14' | 3" | .125" | Post, Cast Aluminum | Decorative Flange Bolt Cover |

PIER MOUNTS



1301 BK



1304 BK



1305 OB



1307 BG



1307 BK



1307 FZ



1307 HE



1307 MN



1307 MO



1307 MR



1307 PZ



1307 RB



1307 RK



1307 VK



1307 VZ



1308 AP



1308 AS



1308 CB



1308 MT



1308 SN

| ITEM | FINISH | DIAMETER | BASE HEIGHT | FITTER DIAMETER | ITEM | FINISH | DIAMETER | BASE HEIGHT | FITTER DIAMETER |
|----------|-----------------|----------|-------------|-----------------|---------|------------------|----------|-------------|-----------------|
| 1301 BK | Black | 3" | ¼" | 3" | 1307 PZ | Pearl Bronze | 7" | 2" | 3" |
| 1304 BK* | Black | 7" | 2" | 3" | 1307 RB | Regency Bronze | 7" | 2" | 3" |
| 1305 OB | Olde Bronze | 7" | 2" | 3" | 1307 RK | River Rock | 7" | 2" | 3" |
| 1307 BG | Black Granite | 7" | 2" | 3" | 1307 VK | Vintage Black | 7" | 2" | 3" |
| 1307 BK | Black | 7" | 2" | 3" | 1307 VZ | Victorian Bronze | 7" | 2" | 3" |
| 1307 FZ | French Bronze | 7" | 2" | 3" | 1308 AP | Antique Copper | 7" | 2" | 3" |
| 1307 HE | Hematite | 7" | 2" | 3" | 1308 AS | Aged Brass | 7" | 2" | 3" |
| 1307 MN | Midnight Bronze | 7" | 2" | 3" | 1308 CB | Copper Bronze | 7" | 2" | 3" |
| 1307 MO | Mocha | 7" | 2" | 3" | 1308 MT | Metro Bronze | 7" | 2" | 3" |
| 1307 MR | Museum Bronze | 7" | 2" | 3" | 1308 SN | Sienna | 7" | 2" | 3" |

Mounting hardware not included. *Concealed fasteners.

INDEX

1100

| | |
|---------|-----|
| 1120 MR | 481 |
| 1120 VK | 479 |
| 1121 MR | 481 |
| 1121 VK | 479 |
| 1122 MR | 481 |
| 1122 VK | 479 |
| 1124 MR | 481 |
| 1124 VK | 479 |
| 1125 MR | 481 |
| 1125 VK | 479 |
| 1126 MR | 481 |
| 1126 VK | 479 |
| 1129 MR | 480 |
| 1129 VK | 478 |
| 1140 OL | 555 |
| 1141 OL | 555 |
| 1142 OL | 555 |
| 1144 OL | 555 |
| 1145 OL | 554 |
| 1150 RB | 553 |
| 1151 RB | 553 |
| 1152 RB | 553 |
| 1154 RB | 553 |
| 1155 RB | 552 |
| 1180 SN | 517 |
| 1181 SN | 517 |
| 1182 SN | 517 |
| 1184 SN | 517 |
| 1185 SN | 516 |
| 1187 SN | 517 |

1200

| | |
|---------|-----|
| 1200 SN | 505 |
| 1201 SN | 505 |
| 1202 SN | 505 |
| 1204 SN | 505 |
| 1205 SN | 504 |
| 1240 MN | 573 |
| 1241 MN | 573 |
| 1242 MN | 573 |
| 1243 MN | 573 |
| 1244 MN | 573 |
| 1245 MN | 572 |
| 1270 OZ | 547 |
| 1270 VK | 545 |
| 1271 OZ | 547 |
| 1271 VK | 545 |
| 1272 OZ | 547 |
| 1272 VK | 545 |
| 1273 OZ | 547 |
| 1273 VK | 545 |
| 1274 OZ | 547 |
| 1274 VK | 545 |
| 1275 OZ | 546 |
| 1275 VK | 544 |
| 1280 VZ | 559 |
| 1281 VZ | 559 |
| 1282 VZ | 559 |
| 1284 VZ | 559 |
| 1285 VZ | 558 |
| 1286 VZ | 559 |

1300

| | |
|---------|-----|
| 1301 BK | 614 |
|---------|-----|

| | |
|---------|-----|
| 1304 BK | 614 |
| 1305 OB | 614 |
| 1307 BG | 614 |
| 1307 BK | 614 |
| 1307 FZ | 614 |
| 1307 HE | 614 |
| 1307 MN | 614 |
| 1307 MO | 614 |
| 1307 MR | 614 |
| 1307 PZ | 614 |
| 1307 RB | 614 |
| 1307 RK | 614 |
| 1307 VK | 614 |
| 1307 VZ | 614 |
| 1308 AP | 614 |
| 1308 AS | 614 |
| 1308 CB | 614 |
| 1308 MT | 614 |
| 1308 SN | 614 |
| 1311 MB | 563 |
| 1311 MO | 562 |
| 1312 MB | 563 |
| 1312 MO | 562 |
| 1314 MB | 563 |
| 1314 MO | 562 |
| 1315 MB | 563 |
| 1315 MO | 562 |
| 1316 MB | 563 |
| 1316 MO | 562 |
| 1319 MB | 563 |
| 1319 MO | 562 |
| 1320 BK | 455 |
| 1320 HE | 453 |
| 1320 KZ | 457 |
| 1321 BK | 455 |
| 1321 HE | 453 |
| 1321 KZ | 457 |
| 1322 BK | 455 |
| 1322 HE | 453 |
| 1322 KZ | 457 |
| 1324 BK | 455 |
| 1324 HE | 453 |
| 1324 KZ | 457 |
| 1325 BK | 454 |
| 1325 HE | 452 |
| 1325 KZ | 456 |
| 1326 BZ | 455 |
| 1326 HE | 453 |
| 1326 KZ | 457 |
| 1328 BK | 455 |
| 1331 MB | 561 |
| 1331 MO | 560 |
| 1332 MB | 561 |
| 1332 MO | 560 |
| 1334 MB | 561 |
| 1334 MO | 560 |
| 1335 MB | 561 |
| 1335 MO | 560 |
| 1336 MB | 561 |
| 1336 MO | 560 |
| 1350 MB | 543 |
| 1350 OZ | 542 |
| 1351 MB | 543 |
| 1351 OZ | 542 |
| 1352 MB | 543 |

| | |
|---------|-----|
| 1352 OZ | 542 |
| 1354 MB | 543 |
| 1354 OZ | 542 |
| 1356 MB | 543 |
| 1356 OZ | 542 |
| 1380 BK | 565 |
| 1381 BK | 565 |
| 1382 BK | 565 |
| 1384 BK | 565 |
| 1385 BK | 564 |
| 1390 BK | 483 |
| 1390 BZ | 485 |
| 1391 BK | 483 |
| 1391 BZ | 485 |
| 1392 BK | 483 |
| 1392 BZ | 485 |
| 1394 BK | 483 |
| 1394 BZ | 485 |
| 1395 BK | 482 |
| 1395 BZ | 484 |
| 1396 BK | 483 |
| 1396 BZ | 485 |
| 1397 BK | 483 |
| 1397 BZ | 485 |

1400

| | |
|---------|-----|
| 1410 BK | 528 |
| 1412 BK | 529 |
| 1419 BK | 528 |
| 1420 AI | 605 |
| 1421 AI | 605 |
| 1422 AI | 605 |
| 1424 AI | 605 |
| 1425 AI | 604 |
| 1430 RB | 568 |
| 1431 RB | 567 |
| 1432 RB | 567 |
| 1434 RB | 568 |
| 1435 RB | 567 |
| 1436 RB | 568 |
| 1437 RB | 567 |
| 1438 RB | 566 |
| 1439 RB | 568 |
| 1440 BK | 528 |
| 1441 BK | 529 |
| 1445 BK | 529 |
| 1449 BK | 528 |
| 1450 SB | 474 |
| 1452 SB | 474 |
| 1454 SB | 474 |
| 1455 SB | 474 |
| 1470 BK | 528 |
| 1471 BK | 529 |
| 1472 BK | 529 |
| 1480 MB | 525 |
| 1481 MB | 525 |
| 1482 MB | 525 |
| 1484 MB | 525 |
| 1485 MB | 524 |
| 1487 MB | 525 |
| 1490 AM | 537 |
| 1490 BK | 539 |
| 1491 AM | 537 |
| 1491 BK | 539 |
| 1492 AM | 537 |

| | |
|---------|-----|
| 1492 BK | 539 |
| 1494 AM | 537 |
| 1494 BK | 539 |
| 1495 AM | 536 |
| 1495 BK | 538 |
| 1499 AM | 537 |
| 1499 BK | 539 |

1600

| | |
|---------|-----|
| 1600 MB | 527 |
| 1601 MB | 527 |
| 1602 MB | 527 |
| 1604 MB | 527 |
| 1605 MB | 527 |
| 1606 MB | 527 |
| 1609 MB | 526 |
| 1610 RB | 575 |
| 1611 RB | 575 |
| 1612 RB | 575 |
| 1613 RB | 575 |
| 1614 RB | 575 |
| 1615 RB | 574 |
| 1616 RB | 575 |
| 1640 BZ | 423 |
| 1640 SK | 429 |
| 1640 SW | 427 |
| 1640 TT | 425 |
| 1641 BZ | 423 |
| 1641 SK | 429 |
| 1641 SW | 427 |
| 1641 TT | 425 |
| 1644 BZ | 423 |
| 1644 SK | 429 |
| 1644 SW | 427 |
| 1644 TT | 425 |
| 1645 BZ | 423 |
| 1645 SK | 429 |
| 1645 SW | 427 |
| 1645 TT | 425 |
| 1646 BZ | 423 |
| 1646 SK | 429 |
| 1646 SW | 427 |
| 1646 TT | 425 |
| 1647 BZ | 442 |
| 1647 SK | 442 |
| 1647 SW | 442 |
| 1647 TT | 442 |
| 1648 BZ | 423 |
| 1648 SK | 429 |
| 1648 SW | 427 |
| 1648 TT | 425 |
| 1649 BZ | 422 |
| 1649 SK | 428 |
| 1649 SW | 426 |
| 1649 TT | 424 |
| 1650 BZ | 423 |
| 1650 TT | 425 |
| 1655 BZ | 423 |
| 1655 TT | 425 |
| 1660 BZ | 441 |
| 1660 SK | 441 |
| 1660 TT | 441 |
| 1663 BZ | 442 |
| 1663 SK | 442 |
| 1663 TT | 442 |

| | |
|---------|-----|
| 1664 BZ | 441 |
| 1664 SK | 440 |
| 1664 TT | 441 |
| 1666 BZ | 443 |
| 1666 SK | 443 |
| 1666 TT | 443 |
| 1667 BZ | 443 |
| 1667 SK | 443 |
| 1667 TT | 443 |
| 1670 BK | 531 |
| 1671 BK | 531 |
| 1672 BK | 531 |
| 1674 BK | 531 |
| 1675 BK | 530 |
| 1676 BK | 531 |
| 1677 BK | 531 |
| 1683 BK | 531 |
| 1690 KZ | 557 |
| 1691 KZ | 557 |
| 1694 KZ | 557 |
| 1695 KZ | 556 |

1700

| | |
|---------|-----|
| 1700 BK | 533 |
| 1701 BK | 533 |
| 1702 BK | 533 |
| 1704 BK | 533 |
| 1705 BK | 532 |
| 1707 BK | 533 |
| 1712 BK | 533 |
| 1713 BG | 535 |
| 1720 BG | 535 |
| 1721 BG | 535 |
| 1722 BG | 535 |
| 1725 BG | 535 |
| 1726 BG | 534 |
| 1727 BG | 535 |
| 1730 AI | 607 |
| 1731 AI | 607 |
| 1732 AI | 607 |
| 1734 AI | 607 |
| 1735 AI | 606 |
| 1736 AI | 607 |
| 1741 BK | 459 |
| 1741 HE | 458 |
| 1744 BK | 459 |
| 1744 HE | 458 |
| 1745 BK | 459 |
| 1745 HE | 458 |
| 1750 VZ | 571 |
| 1751 VZ | 571 |
| 1752 VZ | 571 |
| 1754 VZ | 570 |
| 1760 BZ | 437 |
| 1760 SK | 437 |
| 1760 TT | 437 |
| 1761 BZ | 438 |
| 1761 SK | 438 |
| 1761 TT | 438 |
| 1763 BZ | 438 |
| 1763 SK | 438 |
| 1763 SW | 438 |
| 1763 TT | 438 |
| 1764 BZ | 437 |
| 1764 SK | 437 |

| | |
|---------|-----|
| 1764 TT | 436 |
| 1766 BZ | 439 |
| 1766 SK | 439 |
| 1766 SW | 439 |
| 1766 TT | 439 |
| 1767 BZ | 439 |
| 1767 SK | 439 |
| 1767 SW | 439 |
| 1767 TT | 439 |
| 1770 SN | 515 |
| 1771 SN | 515 |
| 1772 SN | 515 |
| 1774 SN | 515 |
| 1775 SN | 514 |
| 1790 BK | 551 |
| 1791 BK | 551 |
| 1792 BK | 551 |
| 1794 BK | 550 |
| 1797 BK | 551 |

1800

| | |
|---------|-----|
| 1800 BK | 466 |
| 1800 OP | 467 |
| 1800 OZ | 465 |
| 1801 BK | 466 |
| 1801 OP | 467 |
| 1801 OZ | 465 |
| 1802 BK | 466 |
| 1802 OP | 467 |
| 1802 OZ | 465 |
| 1804 BK | 466 |
| 1804 OP | 467 |
| 1804 OZ | 465 |
| 1805 BK | 466 |
| 1805 OP | 467 |
| 1805 OZ | 464 |
| 1810 BK | 528 |
| 1819 BK | 529 |
| 1830 BZ | 433 |
| 1830 SK | 433 |
| 1830 TT | 433 |
| 1831 BZ | 435 |
| 1831 SK | 435 |
| 1831 TT | 435 |
| 1832 BZ | 434 |
| 1832 TT | 434 |
| 1834 BZ | 432 |
| 1834 SK | 433 |
| 1834 TT | 433 |
| 1836 BZ | 434 |
| 1836 TT | 434 |
| 1840 BK | 521 |
| 1841 BK | 521 |
| 1842 BK | 521 |
| 1844 BK | 521 |
| 1845 BK | 520 |
| 1890 BK | 583 |
| 1890 RK | 580 |
| 1891 BK | 583 |
| 1891 RK | 581 |
| 1892 BK | 583 |
| 1892 RK | 581 |
| 1893 RK | 581 |
| 1894 BK | 583 |
| 1894 RK | 580 |

| | | | | | | | | | | | |
|-------------|-----|-------------|-----|-------------|-----|-------------|-----|-------------|-----|---------|-----|
| 1895 BK | 583 | 2026 TT | 448 | 2202 SZ | 495 | 2354 BZ | 415 | 2600 | | 3130 OZ | 215 |
| 1895 RK | 580 | 2027 BZ | 449 | 2203 SZ | 495 | 2354 SS | 415 | 2630 BK | 489 | 3131 AN | 214 |
| 1896 RK | 580 | 2027 TT | 448 | 2204 SZ | 495 | 2355 BZ | 414 | 2630 OB | 487 | 3131 BC | 214 |
| 1898 BK | 583 | 2030 AM | 492 | 2205 SZ | 494 | 2355 SS | 414 | 2631 BK | 489 | 3131 CM | 214 |
| 1898 RK | 581 | 2030 CL | 493 | 2206 SZ | 495 | 2370 AS | 507 | 2631 OB | 487 | 3131 OZ | 214 |
| 1899 BK | 583 | 2034 AM | 492 | 2207 SZ | 495 | 2371 AS | 507 | 2632 BK | 489 | 3133 AN | 216 |
| 1899 RK | 581 | 2034 CL | 493 | 2220 CB | 611 | 2372 AS | 507 | 2632 OB | 487 | 3133 BC | 216 |
| | | 2040 SN | 519 | 2221 CB | 611 | 2374 AS | 506 | 2633 BK | 489 | 3133 CM | 216 |
| 1900 | | 2041 SN | 519 | 2222 BB | 200 | 2376 AS | 507 | 2633 OB | 487 | 3133 OZ | 216 |
| 1900 MT | 419 | 2042 SN | 519 | 2222 CB | 612 | | | 2634 BK | 489 | 3134 AN | 217 |
| 1900 SS | 417 | 2044 SN | 519 | 2222 PL | 197 | 2400 | | 2634 OB | 487 | 3134 BC | 217 |
| 1901 MT | 419 | 2045 SN | 518 | 2222 PZ | 203 | 2406 CB | 596 | 2635 BK | 489 | 3134 CM | 216 |
| 1901 SS | 417 | 2050 HE | 445 | 2224 CB | 611 | 2407 CB | 597 | 2635 OB | 487 | 3134 OZ | 216 |
| 1902 MT | 419 | 2050 KZ | 445 | 2225 CB | 610 | 2420 CB | 596 | 2636 BK | 489 | 3135 AN | 217 |
| 1902 SS | 417 | 2050 TT | 445 | 2226 CB | 612 | 2421 CB | 597 | 2636 OB | 487 | 3135 BC | 217 |
| 1904 MT | 419 | 2054 HE | 444 | 2227 CB | 611 | 2422 CB | 597 | 2639 BK | 488 | 3135 CM | 217 |
| 1904 SS | 417 | 2054 KZ | 445 | 2230 OZ | 477 | 2423 CB | 597 | 2639 OB | 486 | 3135 OZ | 217 |
| 1905 MT | 419 | 2054 TT | 445 | 2231 OZ | 477 | 2424 CB | 597 | 2650 BK | 513 | 3136 AN | 215 |
| 1905 SS | 417 | 2070 SN | 511 | 2232 OZ | 477 | 2425 CB | 597 | 2651 BK | 513 | 3136 BC | 215 |
| 1908 MT | 419 | 2071 SN | 511 | 2234 OZ | 477 | 2426 CB | 596 | 2652 BK | 513 | 3136 CM | 215 |
| 1908 SS | 417 | 2072 SN | 511 | 2235 OZ | 476 | 2428 CB | 596 | 2654 BK | 513 | 3136 OZ | 215 |
| 1909 MT | 418 | 2074 SN | 511 | 2240 RB | 549 | 2429 CB | 596 | 2655 BK | 512 | 3137 AN | 214 |
| 1909 SS | 416 | 2075 SN | 510 | 2241 RB | 549 | 2440 CB | 589 | | | 3137 BC | 214 |
| 1921 BK | 583 | 2080 SB | 463 | 2242 RB | 549 | 2440 MB | 591 | 2900 | | 3137 CM | 214 |
| 1921 RK | 581 | 2081 SB | 463 | 2243 RB | 549 | 2441 CB | 589 | 2989 SN | 499 | 3137 OZ | 214 |
| 1929 BK | 582 | 2082 SB | 463 | 2244 RB | 548 | 2441 MB | 591 | 2990 SN | 499 | 3138 AN | 222 |
| 1929 RK | 580 | 2084 SB | 462 | 2245 RB | 549 | 2442 CB | 589 | 2991 SN | 499 | 3138 BC | 222 |
| 1930 RB | 599 | | | 2250 BK | 497 | 2442 MB | 591 | 2992 SN | 499 | 3138 CM | 222 |
| 1931 RB | 599 | 2100 | | 2251 BK | 497 | 2443 CB | 589 | 2993 SN | 499 | 3138 OZ | 222 |
| 1932 RB | 599 | 2110 BZ | 421 | 2252 BK | 497 | 2443 MB | 591 | 2994 SN | 499 | 3139 AN | 217 |
| 1934 RB | 599 | 2110 TT | 421 | 2254 BK | 497 | 2444 CB | 589 | 2995 SN | 499 | 3139 BC | 217 |
| 1935 RB | 598 | 2114 BZ | 421 | 2255 BK | 497 | 2444 MB | 591 | 2996 SN | 498 | 3139 CM | 217 |
| 1936 RB | 599 | 2114 TT | 421 | 2258 BK | 496 | 2445 CB | 589 | 2999 SN | 499 | 3139 OZ | 217 |
| 1940 FZ | 585 | 2115 BZ | 420 | 2260 AP | 595 | 2446 CB | 588 | | | 3140 AN | 218 |
| 1940 MB | 587 | 2115 TT | 420 | 2261 AP | 595 | 2446 MB | 590 | 3000 | | 3140 BC | 218 |
| 1941 FZ | 585 | 2120 PZ | 609 | 2262 AP | 595 | 2447 CB | 589 | 3000 OZ | 175 | 3140 CM | 218 |
| 1941 MB | 587 | 2121 PZ | 609 | 2263 AP | 595 | 2447 MB | 591 | 3000 PL | 172 | 3140 OZ | 218 |
| 1942 FZ | 585 | 2122 PZ | 609 | 2265 AP | 595 | 2450 CB | 579 | 3001 OZ | 174 | 3141 AN | 218 |
| 1942 MB | 587 | 2123 PZ | 609 | 2268 AP | 594 | 2451 CB | 579 | 3001 PL | 171 | 3141 BC | 218 |
| 1944 FZ | 584 | 2124 PZ | 608 | 2280 MT | 491 | 2452 CB | 579 | 3002 OZ | 175 | 3141 CM | 218 |
| 1944 MB | 586 | 2126 PZ | 609 | 2281 MT | 491 | 2454 CB | 579 | 3002 PL | 172 | 3141 OZ | 218 |
| 1946 FZ | 585 | 2128 PZ | 609 | 2282 MT | 491 | 2456 CB | 578 | 3003 OZ | 174 | 3143 AN | 219 |
| 1946 MB | 587 | 2130 OZ | 603 | 2284 MT | 491 | | | 3003 PL | 171 | 3143 BC | 219 |
| 1950 HE | 460 | 2130 PZ | 601 | 2285 MT | 491 | 2500 | | 3004 OZ | 174 | 3143 CM | 219 |
| 1950 VZ | 461 | 2131 OZ | 603 | 2289 MT | 490 | 2500 BK | 523 | 3004 PL | 171 | 3143 OZ | 219 |
| 1951 HE | 460 | 2131 PZ | 601 | 2290 SN | 509 | 2501 BK | 523 | 3005 OZ | 175 | 3144 AN | 219 |
| 1951 VZ | 461 | 2132 OZ | 603 | 2291 SN | 509 | 2502 BK | 523 | 3005 PL | 172 | 3144 BC | 219 |
| 1952 HE | 460 | 2132 PZ | 601 | 2292 SN | 509 | 2504 BK | 523 | 3006 OZ | 175 | 3144 CM | 219 |
| 1952 VZ | 461 | 2134 OZ | 603 | 2294 SN | 509 | 2505 BK | 523 | 3006 PL | 172 | 3144 OZ | 219 |
| 1954 HE | 460 | 2134 PZ | 601 | 2295 SN | 509 | 2506 BK | 523 | 3008 OZ | 174 | 3145 AN | 219 |
| 1954 VZ | 461 | 2135 OZ | 602 | 2297 SN | 509 | 2570 AR | 471 | 3008 PL | 171 | 3145 BC | 219 |
| 1956 HE | 460 | 2135 PZ | 600 | 2298 SN | 508 | 2570 SK | 473 | 3009 OZ | 173 | 3145 CM | 219 |
| 1956 VZ | 461 | 2150 KZ | 475 | | | 2570 TT | 469 | 3009 PL | 170 | 3145 OZ | 219 |
| 1980 BK | 541 | 2154 KZ | 475 | 2300 | | 2571 AR | 471 | 3013 BN | 169 | 3146 AN | 218 |
| 1980 OZ | 540 | 2170 SN | 502 | 2300 KZ | 451 | 2571 SK | 473 | 3014 BN | 169 | 3146 BC | 218 |
| 1981 BK | 541 | 2170 VZ | 503 | 2302 KZ | 451 | 2571 TT | 469 | 3015 BN | 168 | 3146 CM | 218 |
| 1981 OZ | 540 | 2171 SN | 502 | 2304 KZ | 451 | 2572 AR | 471 | 3017 BN | 169 | 3146 OZ | 218 |
| 1982 BK | 541 | 2171 VZ | 503 | 2305 KZ | 450 | 2572 SK | 473 | | | 3147 AN | 218 |
| 1982 OZ | 540 | 2172 SN | 502 | 2306 KZ | 451 | 2572 TT | 469 | 3100 | | 3147 BC | 218 |
| 1984 BK | 541 | 2172 VZ | 503 | 2310 CB | 577 | 2573 AR | 471 | 3124 CM | 211 | 3147 CM | 218 |
| 1984 OZ | 540 | 2174 SN | 502 | 2311 CB | 577 | 2573 SK | 473 | 3124 KZ | 212 | 3147 OZ | 218 |
| 1985 BK | 541 | 2174 VZ | 503 | 2312 CB | 577 | 2573 TT | 469 | 3124 PL | 212 | 3148 AN | 222 |
| 1985 OZ | 540 | 2190 BZ | 447 | 2313 CB | 577 | 2574 AR | 471 | 3127 CM | 211 | 3148 BC | 222 |
| 1989 BK | 541 | 2190 TT | 446 | 2314 CB | 577 | 2574 SK | 473 | 3127 KZ | 212 | 3148 CM | 222 |
| 1989 OZ | 540 | 2191 BZ | 447 | 2315 CB | 576 | 2574 TT | 469 | 3127 PL | 212 | 3148 OZ | 222 |
| | | 2191 TT | 446 | 2316 CB | 577 | 2575 AR | 471 | 3128 AN | 216 | 3149 AN | 219 |
| 2000 | | 2192 BZ | 447 | 2317 CB | 577 | 2575 SK | 473 | 3128 BC | 216 | 3149 BC | 219 |
| 2020 BZ | 449 | 2192 TT | 446 | 2330 CB | 593 | 2575 TT | 469 | 3128 CM | 216 | 3149 CM | 219 |
| 2020 TT | 448 | 2194 BZ | 447 | 2331 CB | 593 | 2576 AR | 471 | 3128 OZ | 216 | 3149 OZ | 219 |
| 2021 BZ | 449 | 2194 TT | 446 | 2332 CB | 593 | 2576 SK | 473 | 3129 AN | 216 | 3150 AN | 219 |
| 2021 TT | 448 | 2195 BZ | 447 | 2334 CB | 593 | 2576 TT | 469 | 3129 BC | 216 | 3150 BC | 219 |
| 2024 BZ | 449 | 2195 TT | 446 | 2335 CB | 593 | 2579 AR | 470 | 3129 CM | 217 | 3150 CM | 219 |
| 2024 TT | 448 | | | 2336 CB | 592 | 2579 SK | 472 | 3129 OZ | 217 | 3150 OZ | 219 |
| 2025 BZ | 449 | 2200 | | 2337 CB | 593 | 2579 TT | 468 | 3130 AN | 215 | 3151 AN | 219 |
| 2025 TT | 448 | 2200 SZ | 495 | 2350 BZ | 415 | | | 3130 BC | 215 | 3151 BC | 219 |
| 2026 BZ | 449 | 2201 SZ | 495 | 2350 SS | 415 | | | 3130 CM | 215 | 3151 CM | 219 |

| | | | | | | | | | | | |
|-------------|-----|-------------|-----|-------------|-----|-------------|-----|-------------|-----|-------------|-----|
| 3151 OZ | 219 | 3224 AN | 102 | 3587 VS | 061 | 3876 SK | 066 | 4173 VZ | 131 | 4405 GR | 205 |
| 3161 OZ | 101 | 3224 OB | 102 | 3588 PN | 058 | 3877 BN | 065 | 4174 VZ | 131 | 4406 GR | 205 |
| 3162 OZ | 101 | 3281 SL | 097 | 3588 VS | 060 | 3877 SK | 069 | 4176 VZ | 131 | 4408 GR | 204 |
| 3163 OZ | 100 | 3282 SL | 097 | | | 3878 BN | 064 | 4177 VZ | 131 | 4410 BB | 181 |
| 3164 OZ | 101 | 3284 SL | 097 | 3600 | | 3878 SK | 068 | 4178 VZ | 131 | 4410 OB | 184 |
| 3170 AN | 221 | 3285 SL | 097 | 3610 BB | 181 | | | 4179 VZ | 130 | 4410 PW | 187 |
| 3170 BC | 221 | 3286 SL | 097 | 3610 OB | 185 | 3900 | | | | 4412 BB | 181 |
| 3170 CM | 221 | 3287 SL | 096 | 3610 PW | 188 | 3960 PL | 081 | 4200 | | 4412 OB | 184 |
| 3170 OZ | 221 | | | 3612 BB | 182 | 3961 PL | 081 | 4210 BC | 053 | 4412 PW | 187 |
| 3171 AN | 220 | 3300 | | 3612 OB | 185 | 3963 PL | 081 | 4210 PN | 051 | 4415 BB | 181 |
| 3171 BC | 220 | 3301 AN | 232 | 3612 PW | 188 | 3965 PL | 081 | 4212 BC | 053 | 4415 OB | 185 |
| 3171 CM | 220 | 3301 BR | 232 | 3613 BB | 182 | 3966 PL | 080 | 4212 PN | 051 | 4415 PW | 188 |
| 3171 OZ | 220 | 3301 CM | 233 | 3613 OB | 185 | | | 4213 BC | 053 | 4416 BB | 181 |
| 3172 AN | 221 | 3301 OZ | 233 | 3613 PW | 188 | 4000 | | 4213 PN | 051 | 4416 OB | 184 |
| 3172 BC | 221 | 3302 AN | 232 | 3614 BB | 182 | 4010 OL | 142 | 4216 BC | 053 | 4416 PW | 187 |
| 3172 CM | 221 | | 387 | 3614 OB | 185 | | 394 | 4216 PN | 051 | 4417 BB | 181 |
| 3172 OZ | 221 | 3302 BR | 232 | 3614 PW | 188 | 4011 OL | 143 | 4218 BC | 052 | 4417 OB | 184 |
| 3173 AN | 220 | 3302 CM | 233 | 3616 BB | 182 | 4013 OL | 141 | 4218 PN | 050 | 4417 PW | 187 |
| 3173 BC | 220 | 3302 OZ | 233 | 3616 OB | 185 | 4015 OL | 141 | 4220 BN | 079 | 4419 BB | 180 |
| 3173 CM | 220 | 3304 AN | 232 | 3616 PW | 188 | 4015 OL | 141 | 4224 BN | 079 | 4419 OB | 183 |
| 3173 OZ | 220 | 3304 BR | 232 | 3620 AN | 165 | 4016 OL | 142 | 4225 BN | 079 | 4419 PW | 186 |
| 3174 AN | 220 | 3304 CM | 233 | 3620 BR | 167 | 4017 OL | 143 | 4228 BN | 078 | 4421 OW | 181 |
| 3174 BC | 220 | 3304 OZ | 233 | 3622 AN | 165 | 4018 OL | 141 | 4240 OB | 160 | 4430 KZ | 129 |
| 3174 CM | 220 | 3305 AN | 234 | 3622 BR | 167 | 4019 OL | 141 | 4241 OB | 160 | 4431 KZ | 129 |
| 3174 OZ | 220 | 3305 BR | 235 | 3623 AN | 165 | 4020 AN | 155 | | 391 | 4433 KZ | 129 |
| 3175 AN | 220 | 3305 CM | 235 | 3623 BR | 167 | 4021 AN | 155 | 4242 OB | 160 | 4434 KZ | 129 |
| 3175 BC | 220 | 3305 OZ | 235 | 3625 AN | 165 | 4023 AN | 155 | 4243 OB | 159 | 4436 KZ | 129 |
| 3175 CM | 220 | 3321 BN | 231 | 3625 BR | 167 | 4024 AN | 155 | 4244 OB | 160 | 4437 KZ | 129 |
| 3175 OZ | 220 | 3321 CM | 231 | 3626 AN | 165 | 4025 AN | 155 | 4245 OB | 159 | 4438 KZ | 129 |
| 3176 AN | 221 | 3321 OZ | 230 | 3626 BR | 167 | 4027 AN | 155 | 4246 OB | 159 | 4439 KZ | 128 |
| 3176 BC | 221 | | | 3628 AN | 164 | 4028 AN | 154 | 4247 OB | 159 | 4470 TB | 139 |
| 3176 CM | 221 | 3400 | | 3628 BR | 166 | 4060 VZ | 137 | 4248 OB | 159 | 4473 TB | 139 |
| 3176 OZ | 221 | 3440 PN | 055 | 3641 BN | 226 | 4061 VZ | 137 | 4249 OB | 158 | 4474 TB | 139 |
| 3177 AN | 221 | 3440 VS | 057 | 3641 CM | 227 | 4062 VZ | 137 | 4252 OB | 160 | 4475 TB | 139 |
| 3177 BC | 221 | 3441 PN | 055 | 3641 OZ | 227 | 4063 VZ | 137 | 4254 OB | 161 | 4478 TB | 138 |
| 3177 CM | 221 | 3441 VS | 057 | 3660 BN | 083 | 4064 VZ | 137 | 4258 OB | 161 | | |
| 3177 OZ | 221 | 3444 PN | 055 | 3661 BN | 083 | 4065 VZ | 137 | 4259 OB | 161 | 4500 | |
| 3178 AN | 222 | 3444 VS | 057 | 3662 BN | 083 | 4067 VZ | 137 | | | 4505 VZ | 132 |
| 3178 BC | 222 | 3445 PN | 055 | 3663 BN | 083 | 4068 VZ | 136 | 4300 | | 4508 VZ | 132 |
| 3178 CM | 222 | 3445 VS | 057 | 3664 BN | 083 | 4070 BN | 063 | 4300 OL | 142 | 4512 BN | 049 |
| 3178 OZ | 222 | 3446 PN | 055 | 3665 BN | 083 | 4071 BN | 063 | 4304 OL | 143 | 4512 CM | 212 |
| | | 3446 VS | 057 | 3667 BN | 083 | 4073 BN | 063 | 4308 OL | 142 | 4512 KZ | 212 |
| 3200 | | 3447 PN | 055 | 3668 BN | 082 | 4076 BN | 063 | 4309 OL | 140 | 4512 OB | 157 |
| 3200 AN | 091 | 3447 VS | 057 | | | 4078 BN | 062 | 4311 OL | 143 | 4512 PL | 212 |
| 3200 BR | 094 | 3448 PN | 054 | 3700 | | 4090 RI | 105 | 4312 AN | 079 | 4512 RB | 145 |
| 3201 AN | 091 | 3448 VS | 056 | 3712 FB | 191 | 4094 RI | 105 | 4312 AT | 163 | 4512 SK | 066 |
| 3201 BR | 094 | 3470 PB | 179 | 3713 FB | 191 | 4095 RI | 105 | 4312 BB | 199 | 4540 RB | 145 |
| 3202 AN | 092 | 3470 PW | 177 | 3714 FB | 191 | 4097 RI | 105 | 4312 BC | 215 | 4541 RB | 145 |
| 3202 BR | 095 | 3472 PB | 179 | 3716 FB | 191 | 4099 RI | 104 | 4312 BK | 455 | 4542 RB | 145 |
| 3203 AN | 091 | 3472 PW | 177 | | | | | 4312 BN | 087 | 4543 RB | 145 |
| 3203 BR | 094 | 3473 PB | 179 | 3800 | | 4100 | | 4312 BR | 095 | 4544 RB | 145 |
| 3204 AN | 091 | 3473 PW | 177 | 3800 BN | 099 | 4102 BB | 200 | 4312 CM | 215 | 4545 RB | 145 |
| 3204 BR | 094 | 3474 PB | 179 | 3802 BN | 099 | | 401 | 4312 HE | 453 | 4546 RB | 145 |
| 3205 AN | 091 | 3474 PW | 177 | 3804 BN | 099 | 4102 CB | 612 | 4312 KZ | 107 | 4547 RB | 145 |
| 3205 BR | 094 | 3478 PB | 179 | 3805 BN | 099 | 4102 PL | 197 | 4312 MC | 135 | 4548 RB | 144 |
| 3206 AN | 090 | 3478 PW | 177 | 3806 BN | 098 | | 400 | 4312 OB | 113 | 4561 AT | 163 |
| 3206 BR | 093 | 3479 PB | 178 | 3821 BN | 228 | 4102 PZ | 203 | 4312 OL | 143 | 4563 AT | 163 |
| 3206 BR | 094 | 3479 PW | 176 | 3821 BR | 229 | 4103 BB | 200 | 4312 OZ | 125 | 4564 AT | 163 |
| 3207 AN | 092 | | | 3821 CM | 229 | 4103 PL | 197 | 4312 PL | 197 | 4566 AT | 163 |
| 3207 BR | 095 | 3500 | | 3821 OZ | 229 | 4103 PZ | 203 | 4312 PN | 055 | 4567 AT | 163 |
| 3208 AN | 092 | 3501 OL | 143 | 3870 BN | 065 | 4130 BN | 085 | 4312 PZ | 202 | 4568 AT | 163 |
| 3208 BR | 095 | | 394 | 3870 SK | 069 | 4133 BN | 085 | 4312 RI | 105 | 4569 AT | 162 |
| 3209 AN | 092 | 3502 OL | 142 | 3871 BN | 065 | 4134 BN | 085 | 4312 SK | 069 | 4570 KZ | 107 |
| 3209 BR | 095 | 3503 OL | 141 | | 367 | 4136 BN | 085 | 4312 TB | 127 | 4571 KZ | 107 |
| 3210 AN | 092 | 3504 OL | 142 | 3871 CM | 366 | 4138 BN | 084 | 4312 VK | 089 | 4572 KZ | 107 |
| 3210 BR | 095 | 3506 OL | 142 | 3871 SK | 069 | 4140 BB | 199 | 4312 VS | 057 | 4574 KZ | 107 |
| 3211 AN | 091 | 3508 OL | 141 | | 368 | 4140 PZ | 202 | 4312 VZ | 131 | 4575 KZ | 107 |
| 3211 BR | 094 | 3580 PN | 059 | 3872 BN | 065 | 4151 OB | 157 | 4313 OL | 143 | 4576 KZ | 106 |
| 3214 AN | 092 | 3580 VS | 061 | 3872 SK | 069 | 4161 OB | 157 | 4314 OL | 143 | 4577 KZ | 107 |
| 3214 BR | 095 | 3582 PN | 059 | 3873 BN | 065 | 4162 OB | 157 | 4316 OL | 143 | 4590 RY | 153 |
| 3220 AN | 103 | 3582 VS | 061 | 3873 SK | 069 | 4166 OB | 157 | | | 4591 RY | 153 |
| 3220 OB | 103 | 3585 PN | 059 | 3874 BN | 065 | 4167 OB | 157 | 4400 | | 4594 RY | 153 |
| 3221 AN | 103 | 3585 VS | 061 | 3874 SK | 069 | 4168 OB | 156 | 4400 GR | 205 | 4595 RY | 153 |
| 3221 OB | 103 | 3586 PN | 059 | 3875 BN | 065 | 4170 VZ | 132 | 4401 OW | 205 | 4598 RY | 153 |
| 3222 AN | 103 | 3586 VS | 061 | 3875 SK | 069 | 4171 VZ | 132 | 4403 GR | 205 | 4599 RY | 152 |
| 3222 OB | 103 | 3587 PN | 059 | 3876 BN | 066 | | 559 | 4404 GR | 205 | | |

4600

| | |
|---------|-----|
| 4610 BN | 121 |
| 4611 BN | 121 |
| 4613 BN | 121 |
| 4615 BN | 121 |
| 4616 BN | 121 |
| 4618 BN | 120 |
| 4620 FB | 191 |
| 4622 FB | 191 |
| 4626 FB | 190 |
| 4630 BN | 123 |
| | 383 |
| 4630 OZ | 125 |
| 4630 TB | 127 |
| 4631 BN | 123 |
| | 383 |
| 4631 OZ | 125 |
| 4631 TB | 127 |
| | 369 |
| 4632 BN | 123 |
| 4632 OZ | 125 |
| 4632 TB | 127 |
| 4633 BN | 123 |
| 4633 OZ | 125 |
| 4633 TB | 127 |
| 4636 BN | 123 |
| 4636 OZ | 125 |
| 4636 TB | 127 |
| 4637 BN | 123 |
| 4637 OZ | 125 |
| 4637 TB | 127 |
| 4638 BN | 123 |
| 4638 OZ | 125 |
| 4638 TB | 127 |
| 4639 BN | 122 |
| 4639 OZ | 124 |
| 4639 TB | 126 |
| 4640 BB | 182 |
| 4642 BB | 182 |
| 4650 BN | 110 |
| | 388 |
| 4650 BR | 118 |
| | 389 |
| 4650 OB | 114 |
| | 390 |
| 4651 BN | 111 |
| 4651 BR | 119 |
| 4651 OB | 115 |
| 4652 BN | 111 |
| 4652 BR | 119 |
| 4652 OB | 115 |
| 4653 BN | 109 |
| 4653 BR | 117 |
| 4653 OB | 113 |
| 4655 BN | 109 |
| 4655 BR | 117 |
| 4655 OB | 113 |
| 4656 BN | 109 |
| 4656 BR | 117 |
| 4656 OB | 113 |
| 4657 BN | 109 |
| 4657 BR | 117 |
| 4657 OB | 113 |
| 4659 BN | 108 |
| 4659 BR | 116 |
| 4659 OB | 112 |
| 4660 BN | 111 |
| | 388 |
| 4660 BR | 119 |
| | 389 |
| 4660 OB | 115 |
| | 390 |
| 4661 BN | 110 |
| 4661 BR | 118 |
| 4661 OB | 114 |
| 4662 BN | 110 |

| | |
|---------|-----|
| 4662 BR | 118 |
| 4662 OB | 114 |
| 4663 BN | 110 |
| 4663 BR | 118 |
| 4663 OB | 114 |
| 4664 BN | 111 |
| 4664 BR | 119 |
| 4664 OB | 115 |
| 4665 BN | 111 |
| 4665 BR | 119 |
| 4665 OB | 115 |
| 4666 BN | 110 |
| 4666 BR | 118 |
| 4666 OB | 114 |
| 4667 BN | 109 |
| 4667 BR | 117 |
| 4667 OB | 113 |
| 4669 BN | 225 |
| 4669 BR | 225 |
| 4669 OB | 225 |
| 4670 BN | 110 |
| 4670 BR | 118 |
| 4670 OB | 114 |

4700

| | |
|---------|-----|
| 4700 BN | 087 |
| 4700 VK | 089 |
| 4701 BN | 087 |
| 4701 VK | 089 |
| 4702 BN | 087 |
| 4702 VK | 089 |
| 4703 BN | 087 |
| 4703 VK | 089 |
| 4704 BN | 087 |
| 4704 VK | 089 |
| 4705 BN | 087 |
| 4705 VK | 089 |
| 4707 BN | 087 |
| 4707 VK | 089 |
| 4708 BN | 086 |
| 4708 VK | 088 |
| 4720 MC | 135 |
| | 392 |
| 4721 MC | 135 |
| | 392 |
| 4724 MC | 135 |
| 4725 MC | 135 |
| 4727 MC | 135 |
| 4728 MC | 135 |
| 4729 MC | 134 |
| 4770 SH | 207 |
| 4771 SL | 207 |
| 4772 SL | 207 |
| 4774 SL | 207 |
| 4775 SL | 207 |
| 4776 SL | 207 |
| 4778 SL | 207 |
| 4779 SL | 206 |
| 4790 BN | 147 |
| 4790 EZ | 150 |
| 4791 BN | 148 |
| 4791 EZ | 151 |
| 4792 BN | 147 |
| 4792 EZ | 150 |
| 4793 BN | 148 |
| 4793 EZ | 151 |
| 4794 BN | 148 |
| 4794 EZ | 151 |
| 4795 BN | 148 |
| 4795 EZ | 151 |
| 4796 BN | 147 |
| 4796 EZ | 150 |
| 4797 BN | 148 |
| 4797 EZ | 151 |
| 4798 BN | 147 |
| 4798 EZ | 150 |

| | |
|---------|-----|
| 4799 BN | 146 |
| 4799 EZ | 149 |

4800

| | |
|---------|-----|
| 4801 SU | 209 |
| 4802 SU | 209 |
| 4806 SU | 209 |
| 4807 SU | 209 |
| 4809 SU | 209 |
| 4850 BC | 077 |
| 4850 BN | 075 |
| 4851 BC | 077 |
| 4851 BN | 075 |
| 4852 BC | 077 |
| 4852 BN | 075 |
| 4853 BC | 077 |
| 4853 BN | 075 |
| 4855 BC | 077 |
| 4855 BN | 075 |
| 4856 BC | 076 |
| 4856 BN | 074 |
| 4858 BC | 077 |
| 4858 BN | 075 |
| 4860 BN | 073 |
| 4865 BN | 073 |
| 4868 BN | 072 |
| 4880 BB | 199 |
| 4880 PL | 197 |
| 4880 PZ | 202 |
| 4881 BB | 200 |
| | 401 |
| 4881 CB | 612 |
| 4881 PL | 197 |
| | 400 |
| 4881 PZ | 203 |
| 4885 BB | 200 |
| 4885 PL | 197 |
| 4885 PZ | 203 |
| 4886 BB | 199 |
| 4886 PL | 196 |
| 4886 PZ | 202 |
| 4887 BB | 199 |
| 4887 PZ | 202 |
| 4889 BB | 198 |
| 4889 PZ | 201 |
| 4893 SU | 209 |
| 4899 SU | 208 |

4900

| | |
|---------|-----|
| 4900 BN | 147 |
| 4900 EZ | 150 |
| 4922 BN | 049 |
| 4924 BN | 049 |
| 4926 BN | 049 |
| 4928 BN | 048 |
| 4970 BN | 071 |
| 4971 BN | 071 |
| 4972 BN | 071 |
| 4975 BN | 071 |
| 4976 BN | 071 |
| 4978 BN | 070 |

5000

| | |
|----------|-----|
| 5000 AN | 386 |
| 5002 AN | 386 |
| 5003 AN | 386 |
| 5004 AN | 386 |
| 5010 BN | 381 |
| 5010 CM | 380 |
| 5012 BN | 381 |
| 5012 CM | 380 |
| 5013 BN | 381 |
| 5013 CM | 380 |
| 5014 BN | 381 |
| 5014 CM | 380 |
| 50200 CM | 334 |

| | |
|----------|-----|
| 50202 CM | 334 |
| 50203 CM | 334 |
| 50204 CM | 334 |
| 5020 BN | 345 |
| 5020 CM | 344 |
| 5022 BN | 345 |
| 5022 CM | 344 |
| 5023 BN | 345 |
| 5023 CM | 344 |
| 5024 BN | 345 |
| 5024 CM | 344 |
| 5025 BN | 345 |
| 5025 CM | 344 |
| 5050 CM | 330 |
| 5050 BC | 332 |
| 5050 BN | 331 |
| 5052 BC | 332 |
| 5052 BN | 331 |
| 5052 CM | 330 |
| 5053 BC | 332 |
| 5053 BN | 331 |
| 5053 CM | 330 |
| 5054 BC | 332 |
| 5054 BN | 331 |
| 5054 CM | 330 |

5100

| | |
|----------|-----|
| 5100 AN | 372 |
| 5100 BR | 373 |
| 5102 AN | 372 |
| 5102 BR | 373 |
| 5103 AN | 372 |
| 5103 BR | 373 |
| 5104 AN | 372 |
| 5104 BR | 373 |
| 5105 AN | 372 |
| 5105 BR | 373 |
| 5120 PB | 193 |
| 5120 PW | 195 |
| 5122 BK | 187 |
| 5124 PB | 193 |
| 5124 PW | 195 |
| 5126 PB | 193 |
| 5126 PW | 195 |
| 5127 PB | 192 |
| 5127 PW | 194 |
| 5128 PB | 193 |
| 5128 PW | 195 |
| 5129 PB | 193 |
| 5129 PW | 195 |
| 51350 BN | 370 |
| 51352 BN | 370 |
| 51353 BN | 370 |
| 51354 BN | 370 |
| 51560 BN | 363 |
| 51562 BN | 363 |
| 51563 BN | 363 |
| 51564 BN | 363 |
| 5190 CM | 333 |
| 5191 CM | 333 |
| 5192 CM | 333 |
| 5193 CM | 333 |
| 5194 CM | 333 |

5200

| | |
|---------|-----|
| 5200 BN | 382 |
| 5202 BN | 382 |
| 5203 BN | 382 |
| 5204 BN | 382 |
| 5220 BN | 365 |
| 5222 BN | 365 |
| 5223 BN | 365 |
| 5224 BN | 365 |
| 5232 BN | 359 |
| 5232 CM | 358 |
| 5234 BN | 359 |

| | |
|----------|-----|
| 5234 CM | 358 |
| 5236 BN | 359 |
| 5236 CM | 358 |
| 5250 AN | 339 |
| 5250 CM | 338 |
| 5251 AN | 339 |
| 5251 CM | 338 |
| 5252 AN | 339 |
| 5252 CM | 338 |
| 5253 AN | 339 |
| 5253 CM | 338 |
| 5254 AN | 339 |
| 5254 CM | 338 |
| 5255 AN | 339 |
| 5255 CM | 338 |
| 52700 BN | 340 |
| 52702 BN | 340 |
| 52703 BN | 340 |
| 52704 BN | 340 |

5300

| | |
|----------|-----|
| 5310 BB | 200 |
| | 401 |
| 5310 PL | 197 |
| 5310 PL | 400 |
| 5310 PZ | 203 |
| 5312 BB | 401 |
| 5312 PL | 400 |
| 5313 BB | 401 |
| 5313 PL | 400 |
| 5314 BB | 401 |
| 5314 PL | 400 |
| 5317 BB | 199 |
| 5317 PL | 197 |
| 5317 PZ | 202 |
| 53240 BN | 360 |
| 53241 BN | 360 |
| 53242 BN | 360 |
| 53243 BN | 360 |
| 53244 BN | 360 |
| 5340 BN | 371 |
| 5342 BN | 371 |
| 5343 BN | 371 |
| 5344 BN | 371 |
| 5362 BN | 383 |
| 5363 BN | 383 |
| 5370 BN | 341 |
| 5372 BN | 341 |
| 5373 BN | 341 |
| 5375 BN | 341 |
| 5390 BB | 397 |
| 5390 PL | 396 |
| 5391 BB | 397 |
| 5391 PL | 396 |
| 5392 BB | 397 |
| 5392 PL | 396 |
| 5393 BB | 397 |
| 5394 BB | 397 |
| 5393 PL | 396 |
| 5394 PL | 396 |
| 5394 PL | 396 |

5400

| | |
|----------|-----|
| 5420 CM | 342 |
| 5421 BC | 378 |
| 5421 BN | 331 |
| 5421 BR | 332 |
| 5421 CM | 342 |
| 5422 CM | 342 |
| 5423 CM | 342 |
| 5424 CM | 342 |
| 5450 AT | 163 |
| 54680 BN | 364 |
| 54682 BN | 364 |
| 54683 BN | 364 |
| 54684 BN | 364 |

| | |
|---------|-----|
| 5470 OB | 160 |
| | 391 |
| 5472 OB | 391 |
| 5473 OB | 391 |
| 5474 OB | 391 |

5500

| | |
|----------|-----|
| 5542 OL | 394 |
| 5543 OL | 394 |
| 5544 OL | 394 |
| 5545 OL | 394 |
| 55482 CM | 356 |
| 55483 CM | 356 |
| 55484 CM | 356 |
| 5550 BN | 337 |
| 5550 CM | 336 |
| 5551 BN | 337 |
| 5551 BR | 375 |
| 5551 CM | 336 |
| 5552 BN | 337 |
| 5552 CM | 336 |
| 5553 BN | 337 |
| 5553 CM | 336 |
| 5554 BN | 337 |
| 5554 CM | 336 |
| 5555 BN | 337 |
| 5555 CM | 336 |
| 5556 CM | 336 |
| 5556 CM | 337 |
| 5580 BB | 399 |
| 5580 PL | 398 |
| 5582 BB | 399 |
| 5582 PL | 398 |
| 5583 BB | 399 |
| 5583 PL | 398 |
| 5584 BB | 399 |
| 5584 PL | 398 |
| 5585 BB | 399 |
| 5585 PL | 398 |
| 5590 BN | 065 |
| | 367 |
| 5590 CM | 366 |
| 5590 SK | 069 |
| | 368 |
| 5592 BN | 367 |
| 5592 CM | 366 |
| 5592 SK | 368 |
| 5593 BN | 367 |
| 5593 CM | 366 |
| 5593 SK | 368 |
| 5594 BN | 367 |
| 5594 CM | 366 |
| 5594 SK | 368 |

5600

| | |
|----------|-----|
| 5612 BN | 357 |
| 5613 BN | 357 |
| 5614 BN | 357 |
| 5615 BN | 357 |
| 56320 AN | 387 |
| 56322 AN | 387 |
| 56323 AN | 387 |
| 5650 BN | 361 |
| 5652 BN | 361 |
| 5654 BN | 361 |
| 5670 OB | 157 |
| 5680 VZ | 132 |
| 5690 TB | 369 |
| 5692 TB | 369 |
| 5693 TB | 369 |

5700

| | |
|---------|-----|
| 5700 CM | 343 |
| 5702 CM | 343 |
| 5703 CM | 343 |
| 5704 CM | 343 |

| | | | | | | | | | | | |
|-------------|-----|---------------|-----|---------------|-----|---------------|-----|---------------|-----|---------------|-----|
| 57202 PN | 335 | 5914 BN | 347 | FR3300 | | FR41431PAL | 253 | FR43621PNI | 261 | FR49430RCO | 257 |
| 57203 PN | 335 | 5914 CM | 346 | FR33507BNI | 314 | FR41433PAL | 253 | FR43622PNI | 261 | FR49432RCO | 257 |
| 57204 PN | 335 | 5920 BN | 351 | | 318 | FR41434PAL | 252 | FR43624PNI | 261 | FR49433RCO | 257 |
| 57205 PN | 335 | 5920 BR | 352 | FR33507CLD | 314 | FR41435PAL | 253 | FR43625PNI | 261 | FR49434RCO | 257 |
| 5732 MC | 392 | 5920 CM | 350 | | 318 | FR41436PAL | 253 | FR43626PNI | 261 | FR49435RCO | 257 |
| 5733 MC | 392 | 5922 BN | 351 | FR33507PCM | 314 | FR41437PAL | 253 | FR43628PNI | 260 | FR49437RCO | 257 |
| 5734 MC | 392 | 5922 BR | 352 | | 318 | FR41439PAL | 253 | FR43751SLF | 269 | FR49438RCO | 256 |
| 5740 AN | 384 | 5922 CM | 350 | FR3500 | | FR41610ORB | 291 | FR43752SLF | 269 | FR49450BNI | 247 |
| 5740 BR | 385 | 5923 BN | 351 | FR35002MPL | 309 | FR41611ORB | 291 | FR43754SLF | 269 | FR49454BNI | 247 |
| 5742 AN | 384 | 5923 BR | 352 | FR35003MPL | 308 | FR41612ORB | 291 | FR43758SLF | 269 | FR49458BNI | 247 |
| 5742 BR | 385 | 5923 CM | 350 | FR35004MPL | 309 | FR41613ORB | 291 | FR43759SLF | 268 | | |
| 5743 AN | 384 | 5924 BN | 351 | FR35007MPL | 309 | FR41614ORB | 290 | FR4400 | | | |
| 5743 BR | 385 | 5924 BR | 352 | FR35008MPL | 309 | FR41616ORB | 289 | FR44100FRM | 271 | FR5200 | |
| 5744 AN | 384 | 5924 CM | 350 | FR35009MPL | 309 | FR41617ORB | 290 | FR44102FRM | 271 | FR52202ORB | 393 |
| 5744 BR | 385 | 5925 BN | 351 | FR35012WAL | 308 | FR41621ORB | 291 | FR44103FRM | 272 | FR52204ORB | 393 |
| 5770 BN | 362 | 5925 BR | 352 | FR35013WAL | 309 | FR41622ORB | 291 | FR44104FRM | 272 | FR52206ORB | 393 |
| 5772 BN | 362 | 5925 CM | 350 | FR35014WAL | 309 | FR41624ORB | 290 | FR44105FRM | 271 | | |
| 5773 BN | 362 | 6000 | | FR35017WAL | 309 | FR41941PAL | 246 | FR44106FRM | 272 | FR5500 | |
| 5774 BN | 362 | 6035 VZ | 137 | FR35018WAL | 309 | FR41942PAL | 246 | FR44107FRM | 270 | FR55450PCM | 355 |
| 5780 CM | 348 | 6063 SL | 097 | FR35019WAL | 309 | FR41943PAL | 246 | FR44109FRM | 271 | FR55452PCM | 355 |
| 5781 CM | 348 | 6066 AN | 103 | FR35022CHY | 309 | FR41944PAL | 246 | FR44110FRM | 272 | FR55453PCM | 355 |
| 5782 CM | 348 | 6066 BN | 083 | FR35023CHY | 309 | FR41947PAL | 245 | FR44500BBZ | 285 | FR55454PCM | 355 |
| 5783 CM | 348 | 6066 BR | 235 | FR35024CHY | 308 | FR41948PAL | 244 | FR44501BBZ | 284 | FR5600 | |
| 5784 CM | 348 | 6066 CM | 235 | FR35027CHY | 309 | FR41949PAL | 245 | FR44502BBZ | 285 | FR56560PCM | 353 |
| 5800 | | 6066 OB | 103 | FR35028CHY | 309 | FR41950PAL | 245 | FR44504BBZ | 285 | FR56562PCM | 353 |
| 5820 BH | 395 | 6066 OZ | 101 | FR35029CHY | 309 | FR4200 | | FR44505BBZ | 285 | FR56563PCM | 353 |
| 5822 BH | 395 | 6200 | | FR3600 | | FR42340PCM | 293 | FR44506BBZ | 285 | FR56564PCM | 353 |
| 5823 BH | 395 | 6212 BC | 077 | FR36501ANB | 249 | FR42341PCM | 293 | FR44508BBZ | 284 | FR5900 | |
| 5824 BH | 395 | 6212 PN | 059 | FR36501ANG | 249 | FR42342PCM | 293 | FR44620BCH | 275 | FR59192SLF | 402 |
| 5830 AN | 374 | 6212 VS | 061 | FR36501ANS | 249 | FR42343PCM | 293 | FR44621BCH | 275 | FR59193SLF | 402 |
| 5830 BR | 375 | 6600 | | FR36504ANB | 249 | FR42344PCM | 292 | FR44622BCH | 274 | FR59194SLF | 402 |
| 5832 AN | 374 | 6610 BK | 613 | FR36504ANG | 249 | FR42347PCM | 293 | FR44623BCH | 274 | FR8300 | |
| 5832 BR | 375 | 6611 BK | 613 | FR36504ANS | 248 | FR42400BRC | 288 | FR44624BCH | 275 | FR83661BNI | 318 |
| 5833 AN | 374 | 6638 BK | 613 | FR3700 | | FR42401BRC | 288 | FR44625BCH | 275 | FR83661PCM | 318 |
| 5833 BR | 375 | 6660 BK | 613 | FR37554BLK | 310 | FR42402BRC | 288 | FR44626BCH | 273 | FR83661VBZ | 318 |
| 5834 AN | 374 | 6660 BZ | 613 | FR37554CLD | 311 | FR42404BRC | 287 | FR44627BCH | 274 | FR83664BNI | 318 |
| 5834 BR | 375 | 6660 OI | 613 | FR37554PTR | 311 | FR42405BRC | 287 | FR4500 | | FR83664PCM | 318 |
| 5850 BC | 378 | 6661 BK | 613 | FR37554RBR | 310 | FR42406BRC | 287 | FR45601BNI | 263 | FR83664VBZ | 318 |
| 5850 BN | 377 | 6662 BK | 613 | FR3800 | | FR42407BRC | 288 | FR45602BNI | 263 | FR8400 | |
| 5850 CM | 376 | 6663 BK | 613 | FR38510BNI | 312 | FR42408BRC | 286 | FR45602FBZ | 265 | FR84312BNI | 250 |
| 5852 BC | 378 | 6664 BK | 613 | FR38510CLD | 312 | FR42500BME | 281 | FR45604BNI | 263 | FR84312FBZ | 264 |
| 5852 BN | 377 | 6667 BK | 613 | FR38510PCM | 312 | FR42504BME | 281 | FR45604FBZ | 265 | FR84312ORB | 290 |
| 5852 CM | 376 | 6680 BK | 613 | FR4000 | | FR42508BME | 280 | FR45606BNI | 263 | FR84312PAL | 252 |
| 5853 BC | 378 | 6808 BK | 613 | FR40100BNI | 251 | FR42640SLF | 277 | FR45606FBZ | 265 | FR84512ORB | 290 |
| 5853 BN | 377 | 6810 BK | 613 | FR40102BNI | 251 | FR42642SLF | 277 | FR45607BNI | 263 | FR8600 | |
| 5853 CM | 376 | 6812 BK | 613 | FR40103BNI | 251 | FR42644SLF | 277 | FR45607FBZ | 265 | FR86212BRC | 286 |
| 5854 BC | 378 | 6814 BK | 613 | FR40106BNI | 251 | FR42645SLF | 276 | FR45608BNI | 262 | FR86212PAL | 244 |
| 5854 BN | 377 | 8400 | | FR40108BNI | 250 | FR42720SLF | 283 | FR45608FBZ | 264 | FR86212PNI | 240 |
| 5854 CM | 376 | 8471 SH | 139 | FR402001RN | 303 | FR42721SLF | 283 | FR4600 | | FR8800 | |
| 5855 BC | 378 | COL-35 | 413 | FR402031RN | 303 | FR42722SLF | 283 | FR46200BAM | 305 | FR88005GL | 318 |
| 5855 BN | 377 | DSL-40 | 413 | FR402041RN | 303 | FR42725SLF | 283 | FR46204BAM | 305 | FR88009GL | 318 |
| 5855 CM | 376 | DSL-40 | 413 | FR402051RN | 303 | FR42728SLF | 282 | FR46205BAM | 305 | FR88013GL | 318 |
| 5882 CM | 349 | EB-04A | 413 | FR402061RN | 302 | FR42862VBZ | 295 | FR46206BAM | 304 | FR88021GL | 318 |
| 5884 CM | 349 | FR3000 | | FR40312SLF | 267 | FR42865VBZ | 295 | FR46207BAM | 305 | FR88025GL | 318 |
| 5886 CM | 349 | FR30407BBA | 313 | FR40313SLF | 267 | FR42872VBZ | 301 | FR46208BAM | 305 | FR88033GL | 318 |
| 5892 BN | 388 | FR30407BNI | 313 | FR40315SLF | 267 | FR42873VBZ | 301 | FR4700 | | FR88037GL | 318 |
| 5892 BR | 389 | FR30407PBA | 313 | FR40316SLF | 267 | FR42875VBZ | 301 | FR47200PNI | 241 | FR88101GL | 314 |
| 5892 OB | 390 | FR30407PNI | 313 | FR40318SLF | 266 | FR42876VBZ | 300 | | 355 | FR88105GL | 314 |
| 5893 BN | 388 | FR3100 | | FR40570IRR | 297 | FR4300 | | FR47201PNI | 241 | FR88504GL | 318 |
| 5893 BR | 389 | FR31557BNI | 316 | FR40572IRR | 297 | FR43351PSS | 255 | FR47204PNI | 241 | FR88508GL | 318 |
| 5893 OB | 390 | FR31557PCM | 316 | FR40573IRR | 297 | FR43352PSS | 255 | FR47206PNI | 241 | FR88512GL | 318 |
| 5894 BN | 388 | FR31557VBZ | 316 | FR40574IRR | 297 | FR43354PSS | 255 | FR47208PNI | 241 | FR88516GL | 318 |
| 5894 BR | 389 | FR3200 | | FR40575IRR | 297 | FR43355PSS | 255 | FR47209PNI | 240 | | |
| 5894 OB | 390 | FR32903BKS | 299 | FR40576IRR | 296 | FR43358PSS | 254 | FR4900 | | | |
| 5895 BN | 388 | FR32904BKS | 299 | FR40600BKS | 279 | FR43359PSS | 255 | FR49190SLF | 402 | UNI | |
| 5895 BR | 389 | FR32905BKS | 298 | FR40604BKS | 279 | FR43530PNI | 259 | FR49292PCM | 243 | UNI-100 | 413 |
| 5895 OB | 390 | FR32906BKS | 299 | FR40605BKS | 279 | FR43531PNI | 259 | FR49293PCM | 243 | UNI-60 | 413 |
| 5900 | | FR4100 | | FR41430PAL | 253 | FR43535PNI | 259 | FR49296PCM | 243 | UNI-75 | 413 |
| 5910 BN | 347 | | | | | FR43536PNI | 259 | FR49298PCM | 243 | | |
| 5910 CM | 346 | | | | | FR43538PNI | 258 | FR49299PCM | 242 | | |
| 5912 BN | 347 | | | | | FR43620PNI | 261 | | | | |
| 5912 CM | 346 | | | | | | | | | | |
| 5913 BN | 347 | | | | | | | | | | |
| 5913 CM | 346 | | | | | | | | | | |



THIS IS HINKLEY

At your fingertips | AWARD-WINNING CATALOGS

Check out our full range of products in easy-to-use, full color catalogs complete with sizing guidelines, design ideas and eco-tips.

Information 24/7/365 | DYNAMIC WEBSITE

hinkleylighting.com

Surf all of the details on our lighting collections, including the newest products from Hinkley and Fredrick Ramond, tips from professional designers, and locate a Hinkley showroom in your area.

Be inspired | ENGAGING VIDEOS

youtube.com/hinkleylightinginc

Visit Hinkley on YouTube to watch our product, educational and brand videos.

Get to know us | SOCIAL MEDIA

See what captivates us:

pinterest.com/hinkleylighting

facebook.com/hinkleylighting

houzz.com/hinkleylighting



Make the world a better place | COMMUNITY INVOLVEMENT

The Hinkley Lighting family proudly supports breast cancer initiatives in an effort to help eradicate this horrible disease. By increasing awareness and supporting education and community events, together we can work towards finding a cure. Hinkley also supports a variety of other charitable organizations that strive to make a positive difference in the lives of others. Visit hinkleylighting.com for more information.



Hinkley Lighting stands behind the quality of our lighting fixtures with product warranties that are among the strongest in the industry. For details of warranty coverage on specific products, please refer to hinkleylighting.com or consult a qualified Hinkley retail distributor.

Hinkley Lighting is a proud partner of the American Lighting Association.



Consistent with our corporate strategy, we have printed this catalog using vegetable-based inks, paper made with wind power and FSC certified paper which consists of 10% post-consumer recovered fiber. Our paper selection preserves 334 trees for the future and prevents 30,865 lbs of greenhouse gasses from being emitted into the atmosphere.

Please consider joining our environmental efforts and recycling this catalog by passing it along to your family and friends.

©2013 Hinkley Lighting, Inc. All rights reserved in all copyrightable works. Many Hinkley Lighting fixtures are U.S. Patent Pending.





design • illuminate • enjoy

HINKLEY LIGHTING : CLASSIC, TIMELESS COLLECTIONS FEATURING
A VARIETY OF DESIGNS RANGING FROM TRADITIONAL TO CONTEMPORARY.

HINKLEYLIGHTING.COM




FREDRICK RAMOND

ESTABLISHED 1965

FREDRICK RAMOND : CHIC, FASHIONABLE LIGHTING WITH A FOCUS ON
MODERN ELEGANCE AND LUXURIOUS DETAILS.

FREDRICKRAMOND.COM



2013 | 2014 CATALOG CAT13

33000 PIN OAK PARKWAY | AVON LAKE, OHIO 44012
PHONE (440) 653 5500 | FAX (440) 653 5555
SHOWROOM 3210 | DALLAS TRADE MART | DALLAS, TEXAS 75207

