

Section C: Weatherproof Products





Weatherproof Covers



US Patent:
6,982,381

Easy-Install While-In-Use Covers

WHILE-IN-USE COVERS WITH INTERCHANGEABLE INSERTS

Features:

- Patented Slide-In Device Inserts
- High-Impact Polycarbonate Construction
- Pad Lockable Design
- Instruction Sheet
- Meet NEC Article 406.8 (B) (1) For Receptacles in Damp Locations
- NEMA 3R-Rated




Cat. No.	Description	Std. Pkg.
WIU-1V	1-Gang Vertical, 2-3/4" Deep	20
WIU-2	2-Gang, 2-1/4" Deep	20




WIU-1V



WIU-2



3 in 1



9 in 1



Featuring Orbit's Patented
Slide-In Interchangeable Device Inserts
For Quick and Easy Installations

Certification:

• File E227970



US Patent Pending

Universal While-In-Use Covers

UNIVERSAL DEVICE COVERS

Features:

- Patented Device Inserts
- Clean Installation with No Break-Off Parts
- High-Impact Polycarbonate Construction
- Heavy-Duty Die-Cast Metal (AL) Construction in "M" Versions
- Pad Lockable Design
- Pre-installed Adhesive Gasket
- Extra Large Cord Opening with Rubber Flaps that Minimize Debris and Insect Accumulation
- Instruction Sheet
- Meet NEC Article 406.8 (B) (1) For Receptacles in Damp Locations
- NEMA 3R-Rated

Cat. No.	Description	Color (Cat. No. - Color Code)		Std. Pkg.
		Gray	White	
WIU-1U	1-Gang Vert./Horiz. - 2 3/4" Deep	WIU-1U		8
WIU-1UD	1-Gang Vert./Horiz. - 3 1/2" Deep	WIU-1UD		8
WIUM-1UD	Metal, 1-Gang Vert./Horiz. - 3 1/2" Deep	WIUM-1UD	WIUM-1UD-W	8
WIU-2UD	2-Gang - 3 1/2" Deep	WIU-2UD		6
WIUM-2UD	Metal, 2-Gang - 3 1/2" Deep	WIUM-2UD	WIUM-2UD-W	6




WIU-1U

WIU-1UD

WIUM-1UD (Metal)

7 in 1

Easy-to-Assemble Building-Block Style Adapters Accommodate a Wide Range of Wiring Devices



1-3/8", 1-5/8", 1-11/16", & 2-1/8" Dia.

2-Gang Models Include Two Sets of Adapter Plates (One each of 1-11/16" and 2-1/8" Plus a 2-5/8" Dia. with an Oversized Adapter Plate)



WIU-2UD

WIUM-2UD (Metal)

31 in 1



Weatherproof



Weatherproof Covers



US Patent Pending


Universal Flat Device Covers

UNIVERSAL DEVICE COVERS

Features:

- Patented Device Inserts
- Clean Installation with No Break-Off Parts
- Heavy-Duty Die-Cast Metal with Polycarbonate Inserts
- Pad Lockable Design
- Pre-installed Adhesive Gasket
- Instruction Sheet
- NEMA 3R-Rated

Easy-to-Assemble Building-Block Style Adapters Accommodate a Wide Range of Wiring Devices



1-3/8", 1-5/8", 1-11/16", & 2-1/8" Dia.

2-Gang Model Includes Two Sets of Adapter Plates
3-Gang Model Includes Three Sets of Adapter Plates
(Maximum Receptacle Dia. 1-3/8" in 2 & 3 Gang)



Cat. No.	Description	Color (Cat. No. - Color Code)			Std. Pkg.
		Gray	Bronze	White	
1C-U	1-Gang	1C-U	1C-U-BR	1C-U-W	25
2C-U	2-Gang	2C-U	2C-U-BR	2C-U-W	12
2C-USW	2-Gang, One Lever with 15A SW., One Universal	2C-USW	-	-	1
3C-U	3-Gang	3C-U	-	-	1



1C-U

7 in 1



UL Listed for Horizontal Installation



2C-U

16 in 1



2C-USW

4 in 1



3C-U

64 in 1

Weatherproof

Weatherproof Covers




1-GANG BLANK AND DEVICE COVERS

2-3/4" W x 4-1/2" H

- Die-Cast Zinc (Except 1-BC & 1-BC-G)
- Gasket Included



Cat. No.	Description	Color (Cat. No. - Color Code)			Std. Pkg.
		Gray	Bronze	White	
1-BC	Aluminum Blank (Unpainted)	1-BC			50
1-BC-G	Heavy-Duty Galvanized Steel Blank	1-BC-G	1-BC-BR	1-BC-W	50
1C-TS	Toggle Switch	1C-TS	1C-TS-BR	1C-TS-W	25
1C-DH	Duplex/Combo. Device - Horizontal	1C-DH	1C-DH-BR	1C-DH-W	25
1C-DV	Duplex/Combo. Device - Vertical	1C-DV	1C-DV-BR	1C-DV-W	25
1C-GH	GFCI - Horizontal	1C-GH	1C-GH-BR	1C-GH-W	25
1C-GV	GFCI - Vertical	1C-GV	1C-GV-BR	1C-GV-W	25
1C-SH	S/R or Switch Horizontal - 1.406" Diameter	1C-SH			25
1C-SV	S/R or Switch Vertical - 1.406" Diameter	1C-SV	1C-SV-BR	1C-SV-W	25
1C-PO20	20A Power Outlet - 1.594" Diameter	1C-PO20			25
1C-PO30	30A Power Outlet - 1.750" Diameter	1C-PO30			25
1C-PO40	40-50A Power Outlet - 2.281" Diameter	1C-PO40			25
1C-SW	Lever + 15A Single-Pole Switch	1C-SW	1C-SW-BR	1C-SW-W	25
1C-SW-20	Lever + 20A Single-Pole Switch	1C-SW-20			25
1C-SW-NS	Lever Cover without Switch	1C-SW-NS			25
G-1	Universal 1-Gang Foam Gasket	G-1 (Black only)			50



Certification:

• File E227970



Weatherproof



Weatherproof Covers

PLASTIC 1-GANG DEVICE COVERS

2-3/4" W x 4-1/2" H

- Polycarbonate Composite
- Gasket Included



Cat. No.	Description	Color (Cat. No. - Color Code)		Std. Pkg.
		Gray	White	
1CP-DH	Duplex/Combo. Device - Horizontal	1CP-DH	1CP-DH-W	20
1CP-DV	Duplex/Combo. Device - Vertical	1CP-DV	1CP-DV-W	20
1CP-GV	GFCI - Vertical	1CP-GV	1CP-GV-W	20



1CP-DH



1CP-DV



1CP-GV

1-GANG DEVICE COVERS with Padlock Hasp

2-3/4" W x 4-1/2" H

- Die Cast Zinc
- Gasket Included
- Pad Lockable Design



Cat. No.	Description	Std. Pkg.
1CL-DV*	Duplex/Combo. Device - Horizontal	25
1CL-GV*	GFCI - Vertical	25
1CL-SV*	SR or Switch Vertical - 1.406" Diameter	25

*While Supplies Last - See Page C3 for Universal Cover




1-GANG RAISED COVERS

2-7/8" W x 4-5/8" H


- Die Cast Copper-Free Aluminum
- Gasket Included




Cat. No.	Description	Color (Cat. No. - Color Code)			Std. Pkg.
		Gray	Bronze	White	
RE-1	1 - 1/2" Outlet	RE-1	RE-1-BR	RE-1-W	25
RE-2	2 - 1/2" Outlet	RE-2	RE-2-BR	RE-2-W	25
RE-3	3 - 1/2" Outlet	RE-3	RE-3-BR	RE-3-W	25



RE-1
RE-1-BR
RE-1-W



RE-2
RE-2-W
RE-2-BR



RE-3
RE-3-BR
RE-3-W

Certification:

- File E227970

Weatherproof Covers




2-GANG BLANK AND DEVICE COVERS

4-9/16" W x 4-1/2" H


- Device-Mount
- Die-Cast Zinc (Except 2-BC & 2-BC-G)
- Gasket Included
- Powder Coat Finish




Cat. No.	Description	Color (Cat. No. - Color Code)			Std. Pkg.
		Gray	Bronze	White	
2-BC	Aluminum Blank (Unpainted)	2-BC			25
2-BC-G	Heavy-Duty Galvanized Steel Blank	2-BC-G	2-BC-G-BR	2-BC-G-W	25
2C-2D	Two Duplex	2C-2D	2C-2D-BR	2C-2D-W	12
2C-2G	Two GFCI	2C-2G	2C-2G-BR	2C-2G-W	12
2C-2S	Two Switches or S/R - 1.406" Diameter	2C-2S	2C-2S-BR	2C-2S-WH	12
2C-2SW	Two Levers + Two 15A Single-Pole Switches	2C-2SW	2C-2SW-BR	2C-2SW-W	12
2C-GD	One GFCI, One Duplex	2C-GD			12
2C-SD	One Duplex, One S/R - 1.406" Diameter	2C-GS			12
2C-GS	One GFCI, One Switch or S/R - 1.406" Diameter	2C-GS			12
2C-DH	Oversized One Duplex - Horizontal Device Mount Unit has Knock Outs for Box Mounting	2C-DH			12
2CL-PO60	One 30, 50, 60 Amp 3 & 4 Wire With Built-In Padlock Hasp - 2.468" Diameter	2CL-PO60			12
G-2	Universal 2-Gang Foam Gasket	G-2 (Black Only)			50




2-BC
2-BC-G




2C-2D



2C-2G




2C-2S



2C-2SW
2C-2SW-BR
2C-2SW-WH



2C-GD




2C-SD




2C-GS



2C-DH



2CL-PO60



G-2

3-GANG BLANK AND DEVICE COVERS


6-3/8" W x 4-1/2" H

- Die-Cast Zinc
- Gasket Included
- Gray Powder Coat Finish




Cat. No.	Description	Std. Pkg.
3-BC	Aluminum Blank	1
3C-3D*	Three Duplex	1
3C-3G*	Three GFCI	1
3C-3S*	Three SR or Switches - 1.406" Diameter	1


*While Supplies Last - See Page C3 for Universal Cover



3-BC



3C-3D



3C-3G



3C-3S

Certification:

UL File E227970

Weatherproof Boxes

1-GANG BOXES 2" DEEP

2-3/4" W x 4-1/2" H

Cat. No.	Outlet Holes	Hole Size	Color (Cat. No. - Color Code)			Cu. Inch	Std. Pkg.
			Gray	Bronze	White		
1B50-3	3	1/2"	1B50-3	1B50-3-BR	1B50-3-W	18.3	20
1B50-4	4	1/2"	1B50-4	1B50-4-BR	1B50-4-W	18.3	20
1B50-5	5	1/2"	1B50-5	1B50-5-BR	1B50-5-W	18.3	20
1B50-5X	5	1/2"	1B50-5X			18.3	20
1B75-3	3	3/4"	1B75-3	1B75-3-BR	1B75-3-W	18.3	20
1B75-4	4	3/4"	1B75-4	1B75-4-BR	1B75-4-W	18.3	20
1B75-5	5	3/4"	1B75-5	1B75-5-BR	1B75-5-W	18.3	20
1B75-5X	5	3/4"	1B75-5X			18.3	20
1B100-3	3	1"	1B100-3			18.3	20



1B50-3
1B50-3-BR
1B50-3-W
1B75-3
1B75-3-BR
1B75-3-W
1B100-3



1B50-4
1B50-4-BR
1B50-4-W
1B75-4
1B75-4-BR
1B75-4-W



1B50-5
1B75-5



1B50-5X
1B75-5X

Features:

- Die Cast Copper-Free Aluminum
- Premium Powder Coat Finish
- Two Closure Plugs Included
- Ground Screw Installed
- Lugs Included
- Individually Shrink-wrapped with Barcode
- Retail Shelf Packaging



1-GANG DEEP BOXES 2-5/8" DEEP

2-3/4" W x 4-1/2" H

- Gray Finish


Cat. No.	Outlet Holes	Hole Size	Cu. Inch	Std. Pkg.
1DB50-3	3	1/2"	23.8	12
1DB50-4	4	1/2"	23.8	12
1DB50-5X	5	1/2"	23.8	12
1DB75-3	3	3/4"	23.8	12
1DB75-4	4	3/4"	23.8	12
1DB75-5X	5	3/4"	23.8	12
1DB100-3	3	1"	23.8	12
1DB100-5X	5	1"	23.8	12



1DB50-3
1DB75-3
1DB100-3



1DB50-4
1DB75-4



1DB50-5X
1DB75-5X
1DB100-5X

Certification:

-  File E227970

Weatherproof

Weatherproof Boxes




2-GANG BOXES 2" DEEP

4-9/16" W x 4-1/2" H

Cat. No.	Outlet Holes	Hole Size	Color (Cat. No. - Color Code)			Cu. Inch	Std. Pkg.
			Gray	Bronze	White		
2B50-3	3	1/2"	2B50-3	2B50-3-BR	2B50-3-W	30.5	12
2B50-4	4	1/2"	2B50-4			30.5	12
2B50-5	5	1/2"	2B50-5	2B50-5-BR	2B50-5-W	30.5	12
2B50-5X	5	1/2"	2B50-5X			30.5	12
2B50-6X	6	1/2"	2B50-6X			30.5	12
2B50-7	7	1/2"	2B50-7			30.5	12
2B50-7X	7	1/2"	2B50-7X			30.5	12
2B50-9	9	1/2"	2B50-9			30.5	12
2B75-3	3	3/4"	2B75-3	2B75-3-BR	2B75-3-W	30.5	12
2B75-4	4	3/4"	2B75-4			30.5	12
2B75-5	5	3/4"	2B75-5	2B75-5-BR	2B75-5-W	30.5	12
2B75-5X	5	3/4"	2B75-5X			30.5	12
2B75-6X	6	3/4"	2B75-6X			30.5	12
2B75-7	7	3/4"	2B75-7			30.5	12
2B75-7X	7	3/4"	2B75-7X			30.5	12
2B75-9	9	3/4"	2B75-9			30.5	12
2B100-3	3	1"	2B100-3	2B100-3-BR	2B100-3-W	30.5	12
2B100-4	4	1"	2B100-4			30.5	12
2B100-5X	5	1"	2B100-5X			30.5	12

Features:

- Die Cast Copper-Free Aluminum
- Premium Powder Coat Finish
- Two Closure Plugs Included
- Ground Screw Installed
- Lugs Included
- Individually Shrink-wrapped with Barcode
- Retail Shelf Packaging



2-GANG DEEP BOXES 2-5/8" DEEP

4-9/16" W x 4-1/2" H

- Gray Finish

Cat. No.	Outlet Holes	Hole Size	Cubic Inch	Std. Pkg.
2DB50-5	5	1/2"	40.3	9
2DB75-5	5	3/4"	40.3	9
2DB100-5	5	1"	40.3	9
2DB75-7X	7	3/4"	40.3	9
2DB100-7X	7	1"	40.3	9



Certification:

- File E227970

Weatherproof

Weatherproof Boxes


3-GANG DEEP BOX 2-5/8" DEEP

6-3/8" W x 4-1/2" H


- Gray Finish

Features:

- Die Cast Copper-Free Aluminum
- Premium Powder Coat Finish
- Two Closure Plugs Included
- Ground Screw Installed
- Lugs Included
- Individually Shrink-wrapped with Barcode
- Retail Shelf Packaging



Cat. No.	Outlet Holes	Hole Size	Cubic Inch	Std. Pkg.
3DB50-7	7	1/2"	54.0	1
3DB75-7	7	3/4"	54.0	1
3DB100-7	7	1"	54.0	1



3DB50-7
3DB75-7
3DB100-7

Weatherproof

Certification:

-  File E227970

Weatherproof Boxes




1-GANG EXTENSION RINGS 1" DEEP

2-3/4" W x 4-1/2" H


- Gray Finish




Cat. No.	Outlet Holes	Hole Size	Cu. Inch	Std. Pkg.
EXB50-4	4	1/2"	9.5	12
EXB50-6	6	1/2"	9.5	12
EXB75-4	4	3/4"	9.5	12
EXB75-6	6	3/4"	9.5	12
EXR-1	-	-	10.0	24



EXB50-4
EXB75-4



EXB50-6
EXB75-6



EXR-1

Features:

- Die Cast Copper-Free Aluminum
- Premium Powder Coat Finish
- Two Closure Plugs Included
- Individually Shrink-wrapped with Barcode
- Retail Shelf Packaging


1-GANG FLANGED EXTENSION BOXES 1-1/2" DEEP

3-1/2" W x 5-1/4" H


- Gray Finish



Cat. No.	Outlet Holes	Hole Size	Cu. Inch	Std. Pkg.
EXF50-2	2	1/2"	13.5	10
EXF50-4	4	1/2"	13.5	10
EXF50-6	6	1/2"	13.5	10
EXF75-2	2	3/4"	13.5	10
EXF75-4	4	3/4"	13.5	10
EXF75-6	6	3/4"	13.5	10



EXF50-2
EXF75-2



EXF50-4
EXF75-4



EXF50-6
EXF75-6

2-GANG EXTENSION RINGS 1" DEEP

4-9/16" W x 4-1/2" H

- Gray Finish




Cat. No.	Outlet Holes	Hole Size	Cu. Inch	Std. Pkg.
2EXB50-6	6	1/2"	15.0	9
2EXB75-6	6	3/4"	15.0	9
2EXB50-8	8	1/2"	15.0	9
2EXB75-8	8	3/4"	15.0	9
EXR-2	-	-	16.3	12



2EXB50-6
2EXB75-6



2EXB50-8
2EXB75-8



EXR-2

Certification:

- File E227970

Round Extension Rings & Covers




4" ROUND BOXES & EXTENSION RINGS

1-1/2" Deep


• Die-Cast Aluminum




Cat. No.	Outlet Holes	Hole Size	Color (Cat. No. - Color Code)			Cu. Inch	Std. Pkg.
			Gray	Bronze	White		
RB50-5	5	1/2"	RB50-5	RB50-5-BR	RB50-5-W	15.8	16
RB75-5	5	3/4"	RB75-5			15.8	16
EXR50-4	4	1/2"	EXR50-4			19.0	16
EXR75-4	4	3/4"	EXR75-4			19.0	16
EXR-R	-	-	EXR-R			19.0	50



RB50-5
RB50-5-BR
RB50-5-W
RB75-5



EXR50-4
EXR75-4



EXR-R

4" ROUND COVERS

• Die-Cast Copper-Free Aluminum (Except RBC-4)



Cat. No.	Outlet Holes	Hole Size	Color (Cat. No. - Color Code)				Std. Pkg.
			Gray	Bronze	Black	White	
RBC-4 Galvanized Steel	-	-	RBC-4				25
RC-1	1	1/2"	RC-1	RC-1-BR	RC-1-BK	RC-1-W	25
RC-2	2	1/2"	RC-2	RC-2-BR		RC-2-W	25
RC-3D (Dome)	3	1/2"	RC-3D				25
RC-3	3	1/2"	RC-3	RC-3-BR	RC-3-BK	RC-3-W	25
G-R	Foam Gasket	-			G-R		25



RBC-4



RC-1
RC-1-BK
RC-1-BR
RC-1-W



RC-2
RC-2-BR
RC-2-W



RC-3D

Can be Mounted on a 3" Plaster Ring



RC-3
RC-3-BK
RC-3-BR
RC3-W



G-R

Certification:

• File E227970

Weatherproof



Swimming Pool Junction Boxes



SWIMMING POOL JUNCTION BOXES

Metal/Plastic

For use with installation of underwater pool lights.

For connecting to 120V or low voltage below normal water level of the pool. Complies with the latest NEC & UL Standards. Solid brass wiring platform with grounding post and 3 ground terminals for use with metallic or PVC conduit.

Note:

To achieve watertight installation, reference is made to the 1999 NEC National Electrical Code (NEC) Article 680-20(b)(2) which states "The end of the flexible-cord jacket and the flexible-cord conductor terminations within a fixture shall be covered with, or encapsulated in, a suitable potting compound to prevent the entry of water into the fixture through the cord or its conductors. In addition, the grounding connection within a fixture shall be similarly treated to protect such connection from the deteriorating effect of pool water in the event of water entry into the fixture." Article 680-21 Exception (a), which states, "An approved potting compound is used to fill the box to prevent the entrance of moisture."

Cat. No.	Description	Size & Remarks	Std. Pkg.
SJB-50/100	Two 1/2", One 1" Outlets With 1" to 1/2" Port Adapter Black Lexan Cover with Built-In Gasket Brass Bottom	3.5"W x 5.38"H x 2"D 22.0 Cu. In.	1
SJB-75/100	Two 3/4", One 1" Outlets With 1" to 3/4" Port Adapter Black Lexan Material With Built-In Gasket Brass Bottom	3.5"W x 5.38"H x 2"D 22.0 Cu. In.	1
SJB100-3 (Black) SJB100-3-W (White)	Two 3/4", One 1" Outlets Black or White Lexan Material With Built-In Gasket Brass Terminal Block, Brass Ground Lug	4"Dia. X1.75"D 14.0 Cu. In. (Use with PVC Pipe)	1
SJB100-5 (Black) SJB100-5-W (White)	One 1/2", Two 3/4", Two 1" Outlets Black or White Lexan Material With Built-In Gasket Brass Terminal Block, Brass Ground Lug	5"Dia. X 2"D 23.0 Cu. In. (Use with PVC Pipe)	1
SJB-ROD	4-Ft. Solid PVC Support Rod For Lexan Boxes	1/2" Dia X 4'	2

Weatherproof



SJB-50/100



SJB-75/100



SJB100-3



SJB100-3-W



SJB100-5



SJB100-5-W



SJB-ROD



UNDERWATER JUNCTION BOXES

Solid Brass

Cat. No.	Description
UWJB-6	6-Way Connection
UWJB-8	8-Way Connection
UWJB-10	10-Way Connection



UNDERWATER



UWJB-6



UWJB-8



UWJB-10

Certification:

UL File E227970

Weatherproof Lights

LAMP HOLDERS

Die Cast Aluminum
& Zinc




Cat. No.	Description	Color (Cat. No. - Color Code)				Std. Pkg.
		Gray	Bronze	Black	White	
LH150	120V PAR 38 90W Lampholder	LH150	LH150-BR	LH150-BK	LH150-W	25
LH150-SG	120V PAR 38 90W Lampholder With Premium Silicon Outer Gasket	LH150-SG	LH150-SG-BR	LH150-SG-BK	LH150-SG-W	25
LH90	120V PAR 38 90W Premium Lampholder	LH90-GY	LH90-BR	LH90-BK	LH90-W	25
HL2	120V PAR 38 150W Hooded Lampholder	HL2-GY	HL2-BR	HL2-BK	HL2-W	25
QR100	Commercial Die-Cast Metal Quartz Halogen Lamp Holder 120V Input, 100 Watt T4 Bi-Pin Included	QR100-GY	QR100-BR	QR100-BK	QR100-W	25




Includes Neoprene Outer Gasket

LH150



Includes Premium Silicon Gasket


LH150-SG




LH90



QR100



HL2



See Lighting Sections for More Photos of These and Our Other Offerings of PAR Lamp Holders and Accessories in Different Models, Sizes, and Materials!

LAMP HOLDER ACCESSORIES

Cat. No.	Description	Colors Available	Std. Pkg.
BASE	Surface-Mount Bracket 1/2" Female, Cast Aluminum	BK, BR, GN, VG, WH	10
BASE-R	Round Surface-Mount Bracket 1/2" Female, Cast Aluminum	BK, BR, GN, VG, WH	10
BASE-SB	Round Surface-Mount Bracket 1/2" Female, Solid Brass	Antique Brass, Ant. Brz, Acid Grn	10
TB-LV	Tree-Hugger Canopy, Low-Voltage	BK, BR, GN, VG, WH	1
TB50-3	Tree-Hugger Box and Canopy, 120V, Cast Aluminum	GN	1



BASE



BASE-R



BASE-SB



TB-LV



TB50-3

See Page G63 for Tree Hugger Rubber Straps for TB-LV & TB50-3

Certification:





WEATHERPROOF CLOSURE PLUGS

• UMI Premium Closure Plugs are made of Heavy Zinc Die Cast in 1/2" and 3/4" sizes, and Aluminum Die Cast in 1".



Cat. No.	Description	Color	Std. Pkg.	Master Ctn.
Poly Bagged with Barcode				
PL-50	1/2" Closure Plug, 5 Per Bag, 100 Bags of 5	Gray	500	-
PL-50-BR	1/2" Closure Plug, 5 Per Bag, 100 Bags of 5	Bronze	500	-
PL-50-W	1/2" Closure Plug, 5 Per Bag, 100 Bags of 5	White	500	-
PL-75	3/4" Closure Plug, 5 Per Bag, 100 Bags of 5	Gray	500	-
PL-75-BR	3/4" Closure Plug, 5 Per Bag, 100 Bags of 5	Bronze	500	-
PL-75-WH	3/4" Closure Plug, 5 Per Bag, 100 Bags of 5	White	200	-
PL-100	1" Closure Plug, 2 Per Bag, 100 Bags of 2	Gray	200	-
Bulk, Loose in Box				
PL-50-BULK	1/2" Closure Plug	Natural	100	2000
PL-75-BULK	3/4" Closure Plug	Natural	100	2000
PL-100-BULK	1" Closure Plug	Natural	50	1000



PL-50
PL-50-BR
PL-50-W
PL-50-BULK



PL-75
PL-75-BR
PL-75-BULK



PL-100
PL-100-BULK

WEATHERPROOF ACCESSORIES



Cat. No.	Description	Color	Std. Pkg.
LUG	Mounting Lugs, Each Unit is a Poly Bag Containing 2 Lugs and 2 Screws	Natural	100
SW-SP	1/2" Brass Spacer for Mounting a Toggle Switch in a Lever Switch Cover	Natural	100
G	Inner Fiber Gasket For LH150 Weatherproof Lamp Holder	-	250
SG	Premium Silicon Outer Sealing Gasket for LH150 Weatherproof Lamp Holder	-	25
WG-38	PAR38 Wire Guard for Weatherproof Lamp Holders, Zinc-Plated Steel	-	5
YAD-50	1/2" Die-Cast Aluminum "Y" Adapter, One Male to Two Female Hubs	Gray	25



LUG



SW-SP



G



SG



WG-38



YAD-50

Certification:

• File E227970

Weatherproof



Photocells

PHOTOELECTRIC CONTROLS


- 1.5VA Power Consumption
- 10-20 Lx On Level
- 30-60 Lx Off Level
- 5-Yr Warranty

Cat. No.	Description	Rating		Std. Pkg.
		Tungsten	Ballast	
PC-1	120V 50/60Hz, Standard Contractor Grade	2000 W	1900VA	12
PC-1-277	208/277V 50/60Hz, Standard Contractor Grade	2000 W	1900VA	12
PC-1S	120V 50/60Hz, Swivel-Type	1200 W	1000VA	12
PC-1SH	120V 50/60Hz, High-Wattage Swivel-Type	2000 W	1900VA	12
PC-1AL	120V 50/60Hz, Std Contractor Grade, Cast Alum.	2000 W	2000VA	12
PC-1F	120V 50/60Hz, Wire-In Flush Model	500 W	850VA	12
PC-1F-277	208/277V 50/60Hz, Wire-In Flush Model	500 W	850VA	12
PC-1P	120V 50/60Hz, With Weatherproof Plate & Gasket	500 W	850VA	12
PC-1T	110~277V 50/60Hz, Twist Lock	1800 W	1000VA	12

Weatherproof



PC-1
PC-1-277



PC-1S



PC-1SH



PC-1AL



PC-1F
PC-1F-277



PC-1P



PC-1T



Conduit Bodies Quick Reference

For More Information See Fittings Section Starting on Page D20

Weatherproof



LB-50A
LB-75A
LB-100A
LB-125A
LB-150A
LB-200A



LL-50A
LL-75A
LL-100A
LL-125A
LL-150A
LL-200A



LR-50A
LR-75A
LR-100A
LR-125A
LR-150A
LR-200A



C-50A
C-75A
C-100A
C-125A
C-150A
C-200A



T-50A
T-75A
T-100A
T-125A
T-150A
T-200A



SLB-50
SLB-75
SLB-100
SLB-125
SLB-150
SLB-200



LB-50
LB-75
LB-100
LB-125
LB-150
LB-200
LB-250
LB-300
LB-350
LB-400



LL-50
LL-75
LL-100
LL-125
LL-150
LL-200
LL-250
LL-300
LL-400



LR-50
LR-75
LR-100
LR-125
LR-150
LR-200
LR-250
LR-300
LR-400



C-50
C-75
C-100
C-125
C-150
C-200
C-250
C-300
C-400



T-50
T-75
T-100
T-125
T-150
T-200
T-250
T-300
T-400



CG-50
CG-75
CG-100
CG-125/150
CG-200
CG-250/300
CG-350-400



Malleable Iron

MLB-50
MLB-75
MLB-100
MLB-125
MLB-150
MLB-200
MLB-250
MLB-300
MLB-400



Malleable Iron

MLL-50
MLL-75
MLL-100
MLL-125
MLL-150
MLL-200



Malleable Iron

MLR-50
MLR-75
MLR-100
MLR-125
MLR-150
MLR-200



Malleable Iron

MC-50
MC-75
MC-100
MC-125
MC-150
MC-200



Malleable Iron

MT-50
MT-75
MT-100
MT-125
MT-150
MT-200



SC-50
SC-75
SC-100
SC-125/150
SC-200
SC-250/300
SC-350/400



G-50
G-75
G-100
G-125/150
G-200
G-250/300
G-350-400



Set-Screw EMT

SSLB-50
SSLB-75
SSLB-100
SSLB-125
SSLB-150
SSLB-200



Set-Screw EMT

SSLR-50
SSLR-75
SSLR-100
SSLR-125
SSLR-150
SSLR-200



Set-Screw EMT

SLL-50
SLL-75
SLL-100
SLL-125
SLL-150
SLL-200



Set-Screw EMT

SSC-50
SSC-75
SSC-100
SSC-125
SSC-150
SSC-200



Set-Screw EMT

SST-50
SST-75
SST-100
SST-125
SST-150
SST-200