

Caséta Wireless

Discover the power of smart lighting




Lamp dimmer




Dimmer



Remote



Smart Bridge



Lutron App

NEW! Sonos
endorsed integration



Welcome to Caséta Wireless

Why choose Caséta Wireless?

Save time and hassle on the job, while giving your customers the power of smart lighting.

An easier 3-way

- No-neutral-required dimmer
- Mount remote on any surface — without cutting holes
- No wiring necessary for remote

A smarter timer*

- Set timer once and never have to reset it again
- Timer schedules automatically adjust when seasons change
- No reprogramming for daylight savings or power outages

*Not only does the Smart Bridge provide a smarter timer, it also offers app control, and so much more. See pages 8–9 for details.



How to do it:

Step 1

Install Caséta Wireless dimmer



Step 2

Mount Pico remote



How to do it:

Step 1

Install Caséta Wireless dimmers




Step 2

Plug Smart Bridge into Wi-Fi router




Step 3

Download FREE Lutron App and program timed events



Product information



Controls wall and ceiling lights

Dimmer


- Doesn't require a neutral wire — ideal for retrofit or new construction
- No polarity for line or load wiring — mistake-proof wiring
- Works with compatible dimmable LEDs (up to 150W), and incandescent and halogen bulbs (up to 600W)
- Use Pico remotes for additional dimmers in multi-location dimming applications

Dimmer PRO

- Works with approved dimmable LEDs (up to 250W), and incandescent and halogen bulbs (up to 1000W)
- Also works with MLV lighting (up to 1000VA)
- Compatible with Lutron LTE LED drivers, PHPM, and GRX-TVI interfaces
- Neutral wire optional (required for MLV and drivers/interfaces)
- Use Pico remotes or existing toggle switches in multi-location applications

Caséta Wireless works with energy-efficient, dimmable light bulbs

- UL Listed to dim over 500 different LED light bulbs. The list of compatible bulbs is available at **CasetaWireless.com**.
- Patent-pending technology ensures superior performance with dimmable LEDs, as well as halogen and incandescent bulbs. You can even use different light bulb types with the same dimmer.
- Questions about LED control? The Lutron LED Center of Excellence is the industry resource for LED control: 1.877.DIM.LED8 or LED8@lutron.com.




Controls ELV,
LED, and more.

Dimmer ELV+ **NEW**

- Works with all load types
- Favorite button for preset level on dimmer (matches Pico)
- 500W ELV/INC/HAL
- 400W MLV
- 250W LED
- Neutral wire required
- 10W minimum load
- Use Pico remotes for additional dimmers in multi-location dimming applications

Product information



Controls wall and ceiling lights,
as well as general purpose fans

Neutral switch

- Neutral wire required — provides higher capacity and 10W minimum load or one LED bulb
- Use Pico remotes or existing toggle switches in multi-location switching applications

Switch PRO

- Dual voltage — works in 120V and 277V applications
- Doesn't require a neutral wire
- Minimum load cap included (for switching LED, CFL, and ELV loads)
- Use Pico remotes or existing toggle switches in multi-location switching applications




Lamp dimmer

- Features two receptacles for simultaneous control of two lamps
- Simply plugs into a standard wall receptacle
- Works with dimmable LEDs (up to 100W)
- Also works with halogen and incandescent bulbs (up to 300W)

Product information

Use Pico mounted to a tabletop pedestal, clipped to a car visor, or mounted to a wall.



Tabletop pedestal



Car visor clip



Wall-mounting kit

Pico remote control

- Provides convenient remote control
- Add a light switch without having to wire anything
- Battery powered — features a 10-year battery life
- Works with Caséta Wireless dimmers, switches, and wireless shades

4-button Pico remote control PRO

Choose from three options

- 3-scene control — create three different scenes, as well as turn all lights off
- 2-group switch control — control two groups of lights independently from one another
- Dimming control — same functionality (full on/off and raise/lower) as standard Pico, but in a 4-button aesthetic

Note: light/shade and shade-only 4-button remotes also available.

Visit [lutron.com/pico](https://www.lutron.com/pico) for information on model numbers and engraving options.



Sonos endorsed integration and works with other select audio control systems.

Pico remote control for audio **NEW**

- Controls any model Sonos speaker(s) from anywhere around your home
- Play/pause, skip tracks, raise/lower volume, and select your favorite playlist or station
- Smart Bridge or Smart Bridge PRO required
- 10-year battery life

Product information



Apple® HomeKit technology provides an easy way to control your lights and shades via Siri®, from your iPhone®, iPad®, or iPod touch®.




Apple, Siri, iPhone, iPad, and iPod touch are trademarks of Apple Inc., registered in the U.S. and other countries.

Smart Bridge

- Enables control of lights, shades, and temperature using the Lutron App
- Compatible with Caséta Wireless dimmers and switches, Lutron-Honeywell Wireless Thermostat, Nest Learning Thermostat, and select Honeywell® Wi-Fi Thermostats
- Easy to install; just plugs into your Wi-Fi router
- Uses Clear Connect wireless technology — no callbacks

Smart Bridge PRO

- Also compatible with Lutron Triathlon battery-powered shades and select styles of Sivoia QS Wireless shades
- Adds integration with third-party A/V remote controls and security systems



The App Store is a service mark of Apple Inc.
Apple Watch is a trademark of Apple Inc.
Google Play is a trademark of Google Inc.

Lutron App

- Control individual lights, shades, and thermostats — even when you're away from home
- Add and schedule scenes to adjust lights and shades automatically
- Receive notifications on your smart device if you've left lights on when you leave home
- Tell Siri to turn lights off and close your shades just before bed, or dim the lights for movie time
- Use the geofencing feature to automatically turn lights on as you arrive home/turn them off as you leave
- Create a lived-in look with the "Smart Away" feature, which allows you to pick several lights that will randomly turn on/off in the evenings when you're away.

Expand your system

Caséta Wireless expands beyond lighting control. It works with other connected home solutions, such as shades, thermostats, ceiling fans, and even other manufacturer's apps.

Remote controlled shades

Eliminate glare, create privacy, and help keep a room cool, all with one touch.



Roller



Honeycomb

Lutron motorized shades

- Battery-powered; batteries last 3–5 years
- Wireless, easy to install
- Cordless design
- Available in roller or insulating honeycomb styles
- Triathlon shades and select styles of Sivoia QS Wireless shades compatible with Smart Bridge PRO only



View the full list of integration partners at CasetaWireless.com.

Wireless thermostats

Control the comfort of your home from anywhere using the Lutron app and a wide range of compatible thermostats.



(available from Lutron)

Lutron-Honeywell Wireless Thermostat

- Remotely control the temperature in your home from the Lutron App
- 7-day programmable schedule
- Large touchscreen display with backlight
- Precise comfort control of temperature and humidity
- The Lutron App is also compatible with the following:

Honeywell



HomeKit-enabled ceiling fans **NEW**

Conveniently adjust ceiling fans from the Lutron App or by using Siri®. Turn them on and off, and change speeds. And if the fan has a light attached to it, you can even adjust that, too — right from your phone.









Hunter Symphony and Signal ceiling fans

- 54" ceiling fans with either plastic (Symphony) or wooden (Signal) blades
- Both fans include an integrated light kit
- Whisperwind® motor delivers quiet, ultra-powerful air movement
- For additional product information visit hunterfan.com



Expand your system

Additional smart home technology

	<p>Apple® HomeKit™ The Smart Bridge contains Apple HomeKit technology, so you can use Siri® to control your lights and shades.</p>
	<p>Nest Protect smoke + CO alarm When smoke or CO is detected your lights will turn on and your shades will open automatically to help you find your way</p>
	<p>IFTTT (If This Then That) Create IFTTT recipes, such as lowering your shades if it's sunny, or turning off lights if the Nest thermostat is set to "Away" mode</p>
	<p>Logitech Harmony Dim lights, lower shades, and start a movie with one button press on Logitech Harmony hub-based remote controls or from the Harmony app.</p>
<p>works with XFINITY Home</p>	<p>XFINITY Home Control your lights from anywhere using the XFINITY Home app.</p>
	<p>Amazon Alexa Create just the right light using Alexa voice control. Ask Alexa to turn lights on, off, or dim them to your favorite level.</p>
	<p>Sonos Control your Sonos Home Sound System from a Pico remote control for audio or from scenes in the Lutron App.</p>

Pro-level integration*

Security

Automatically turn off lights and close shades when arming the security system before leaving for the day. Turn lights on and open shades when disarming the system when arriving home or in the event of an alarm.









A/V

Combine all connected home solutions into one app.

*Smart Bridge PRO required for pro-level integration

Ordering information

Product	Name	Model Number	Specifications/Descriptions	Voltage	List Price
Dimmers and Switches					
	Dimmer	PD-6WCL-XX*	Single pole/multi-location** 150W dimmable LED 600W INC/HAL 434 MHz	120V~ No polarity for line or load wiring	\$72.00
	Dimmer PRO	PD-10NXD-XX*	Single pole/multi-location** 250W dimmable LED 1000W INC/HAL 1000VA MLV 434 MHz	120V~ Neutral optional	\$98.00
	Dimmer ELV+	PD-5NE-XX*	Single pole/multi-location** 500W ELV/INC/HAL 400W MLV 250W dimmable LED 434 MHz	120V~ Neutral required	\$135.00
	Neutral Switch	PD-6ANS-XX*	Single pole/multi-location** 720W INC/HAL/ELV† 720VA MLV 6A LED/CFL† 3.6A general purpose fan 434 MHz	120V~	\$89.00
	Switch PRO	PD-5WS-DV-XX*	Single pole/multi-location** 600W INC/HAL/ELV† 600VA MLV 5A LED/CFL† 3A general purpose fan 434 MHz	120/277V~ No neutral	\$89.00
	Lamp Dimmer	PD-3PCL-WH	Use with one or two lamps 100W dimmable LED 300W INC/HAL 434 MHz	120V~ Plugs into a standard receptacle	\$72.00

* XX denotes gloss color suffix (at right).
Dimmers and switches not available
in White/Gray (WG).



White (WH)

Ivory (IV)



Light Almond (LA)

Black (BL)







White/Gray (WG)

** For multi-location applications, replace additional switches with Pico remote controls using wallplate brackets.


† Switching ELV, LED, CFL requires minimum load cap LUT-MLC (included)

Ordering information

Product	Name	Model Number	Specifications/Descriptions	Voltage	List Price
Remote Controls					
	Pico Remote Control	PJ2-3BRL-WH-L01R (White)	3-button with raise/lower and light icon engraving 434 MHz	3V \equiv 10mA*	\$21.00
		PJ2-3BRL-LA-L01R (Light Almond)	Additional styles of Pico available. Please visit lutron.com/pico to view the full selection		
	2-Button Pico Remote Control	PJ2-2B-GWH-L01 (White)	2-button with light icon engraving 434 MHz	3V \equiv 10mA*	\$25.00
	4-Button Pico Remote Control PRO	PJ2-4B-XX-L01P [†]	Dimming control 4-button with raise/lower and light icon engraving 434 MHz	3V \equiv 10mA*	\$25.00
		PJ2-4B-XX-L21P [†]	2-group switch control 4-button with dual group light icon engraving 434 MHz	3V \equiv 10mA*	\$39.00
		PJ2-4B-XX-L31P [†]	3-scene control 4-button with light icon scene engraving 434 MHz	3V \equiv 10mA*	\$39.00
	Pico Remote Control for Audio	PJ2-3BRL-GWH-A02 (White)	3-button with raise/lower and audio icon engraving 434 MHz	3V \equiv 10mA*	\$49.00
		PJ2-3BRL-GBL-A02 (Black)			




* Uses single CR 2032 battery (included)

[†] XX denotes gloss color suffix (at right). 4-button Pico remotes not available in White/Gray (WG).





Product	Name	Model Number	Specifications/Descriptions	Voltage	List Price
---------	------	--------------	-----------------------------	---------	------------


Remote Control Accessories

	Wallplate Bracket	PICO-WBX-ADAPT	Wallplate bracket allows for easy installation of a Pico remote control over an existing wallbox or directly on any wall surface		\$8.00
	Car Visor Clip	PICO-CAR-CLIP	Provides an easy way to attach a Pico remote control to your car's sun visor		\$9.00
	Tabletop Pedestals	L-PED1-WH	Single pedestal – White		\$15.00
		L-PED1-BL	Single pedestal – Black		\$25.00
		L-PED2-WH	Double pedestal – White		\$30.00
		L-PED2-BL	Double pedestal – Black		\$40.00
		L-PED3-WH	Triple pedestal – White		\$100.00
		L-PED3-BL	Triple pedestal – Black		\$100.00


Smart Bridge and Smart Bridge PRO

	Smart Bridge with HomeKit technology	L-BDG2-WH	Smart Bridge allows control via the Lutron App or via Siri®	120V~ 5V== 300mA (power supply included)	\$110.00
	Smart Bridge PRO with HomeKit technology	L-BDGPRO2-WH	Smart Bridge PRO allows third-party integration and control via the Lutron App or via Siri	120V~ 5V== 300mA (power supply included)	\$150.00








Thermostat



	Lutron-Honeywell Wireless Thermostat	L-HWLV2-WIFI	Up to 3 heat/2 cool heat pump or up to 2 heat/2 cool conventional Requires common wire connection	24V~	\$331.00
---	--------------------------------------	--------------	--	------	----------

Motorized Shades

	Please visit lutron.com/triathlon				
---	---	--	--	--	--

Ordering information

Product	Name	Model Number	Specifications/Descriptions	List Price
Kits				
	1 Dimmer 1 Pico Remote 1 Wallplate	P-PKG1W-WH (White only)	(1) PD-6WCL-WH (1) PJ2-3BRL-WH-L01R (1) CW-1-WH (Claro wallplate)	\$80.00
	1 Lamp Dimmer 1 Pico Remote	P-PKG1P-WH (White only)	(1) PD-3PCL-WH (1) PJ2-3BRL-WH-L01R	\$80.00
	1 Pico Remote 1 Wallplate Bracket 1 Wallplate	PJ2-WALL-WH-L01 (White only)	(1) PJ2-3BRL-WH-L01R (1) PICO-WBX-ADAPT (1) CW-1-WH (Claro wallplate)	\$32.00
	1 Smart Bridge 1 Dimmer 1 Pico Remote 1 Wallplate	P-BDG-PKG1W (White only)	(1) L-BDG2-WH (1) PD-6WCL-WH (1) PJ2-3BRL-WH-L01R (1) CW-1-WH (Claro wallplate)	\$140.00
	1 Smart Bridge 1 Lamp Dimmer 1 Pico Remote	P-BDG-PKG1P (White only)	(1) L-BDG2-WH (1) PD-3PCL-WH (1) PJ2-3BRL-WH-L01R	\$140.00
	1 Smart Bridge 2 Dimmers 2 Pico Remotes 2 Pedestals 2 Wallplates	P-BDG-PKG2W (White only)	(1) L-BDG2-WH (2) PD-6WCL-WH (2) PJ2-3BRL-WH-L01R (2) L-PED1-WH (2) CW-1-WH (Claro wallplate)	\$255.00
	1 Smart Bridge 2 Lamp Dimmers 2 Pico Remotes 2 Pedestals	P-BDG-PKG2P (White only)	(1) L-BDG2-WH (2) PD-3PCL-WH (2) PJ2-3BRL-WH-L01R (2) L-PED1-WH	\$255.00

Product	Name	Model Number	Specifications/Descriptions	List Price
PRO Kits				
	1 Smart Bridge PRO 1 Dimmer 1 Pico Remote 1 Wallplate	P-BDGPRO-PKG1W (White only)	(1) L-BDGPRO2-WH (1) PD-6WCL-WH (1) PJ2-3BRL-WH-L01R (1) CW-1-WH (Claro wallplate)	\$200.00
	1 Smart Bridge PRO 3 Pico Remotes for Audio 2 Pedestals 1 Wallplate Bracket 1 Wallplate	P-BDGPRO-PKG3AW (White only)	(1) L-BDGPRO2-WH (3) PJ2-3BRL-GWH-A02 (2) L-PED1-WH (1) PICO-WBX-ADAPT (1) CW-1-WH (Claro wallplate)	\$340.00

☼, Caséta, Claro, Clear Connect, Lutron, Pico, Sivoia, and Triathlon are trademarks of Lutron Electronics Co., Inc., registered in the U.S. and other countries.

CasetaWireless.com

Lutron Electronics Co., Inc., 7200 Suter Road, Coopersburg, PA 18036-1299

Customer Assistance

Online: lutron.com/help | Email: support@lutron.com | Phone: 1.844.LUTRON1 (588.7661) — includes 24/7 technical support

© 11/2016 Lutron Electronics Co., Inc. | P/N 367-2499 REV L

