





LSER - Serrano® LED Architectural Luminaire



QS 10 10-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 100

| | | | | | | | | | |
|---|---|------------------------------------|------------------|---|--|---|----------|---|--|
| LSER | - | | G | - | | - | U | - | |
| MODEL | COLOR TEMP | CEILING TYPE | SHIELDING | OPTIONS | | | | | |
| LSER Serrano® LED Architectural Luminaire | 35 3500K 40 4000K | G Grid ¹ | C Contour | C388 3-Wire Flex C488 4-Wire Flex C588 5-Wire Flex ELL14 Emergency Battery Pack, 1400 Lumen ² | | | | | |
| SIZE | LUMEN OUTPUT | DRIVER | | VOLTAGE | | | | | |
| 22 2' x 2' 24 2' x 4' | LW Low Watt ML Medium Lumen HL High Lumen VL Very High Lumen | E Fixed Output ED 0-10V Dimming | | U 120V-277V | | | | | |



¹ For drywall, order G with Flange Kit Accessory.
² For compatibility with Dual-Lite LiteGear™ inverters in lieu of installed Battery Pack, contact Hubbell Lighting Representative.




LTRE - Transition® Enclosed LED High Efficiency Architectural Lensed



QS 10 10-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 100

| | | | | | | | | | |
|--|--|------------------------------------|----------------------------|---|------------|---|----------|---|--|
| LTRE | - | | G | - | RFA | - | U | - | |
| MODEL | COLOR TEMP | CEILING TYPE | SHIELDING | OPTIONS | | | | | |
| LTRE Transition® Enclosed LED High Efficiency Architectural Lensed | 35 3500K 40 4000K | G Grid Lay-in ¹ | RFA Ribbed Frosted Acrylic | C388 3-Wire Flex C488 4-Wire Flex C588 5-Wire Flex ELL14 Emergency Battery Pack, 1400 Lumen ² | | | | | |
| SIZE | LUMEN OUTPUT | DRIVER | | VOLTAGE | | | | | |
| 22 2' x 2' 24 2' x 4' | LW Low Watt (2x4 only) ML Medium Lumen HL High Lumen (2x2 only) VL Very High Lumen (2x2 only) | E Fixed Output ED 0-10V Dimming | | U 120V-277V | | | | | |

¹ For drywall, order G with Flange Kit Accessory.
² For compatibility with Dual-Lite LiteGear™ inverters in lieu of installed Battery Pack, contact Hubbell Lighting Representative.



LJT - LED Lensed Troffer



Regional Distribution Center Stock List



| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-------------|-----------------------|--------------|--|-------|-------|-------|-------|----------|-------------|-------|
| 93048975 | LJT22-35HLG-FSA12-EDU | 078531121228 | LED 2X2 Lensed Troffer, 3500K, 3800 Lumens, 0-10V Dimming Driver | • | • | • | • | 20.0 | 36 | |
| 93053880 | LJT22-40HLG-FSA12-EDU | 078531123185 | LED 2X2 Lensed Troffer, 4000K, 3800 Lumens, 0-10V Dimming Driver | | • | | • | 20.0 | 36 | |
| 93048976 | LJT24-35MLG-FSA12-EDU | 078531121235 | LED 2X4 Lensed Troffer, 3500K, 4800 Lumens, 0-10V Dimming Driver | • | • | • | • | 20.0 | 26 | |
| 93053881 | LJT24-40MLG-FSA12-EDU | 078531123192 | LED 2X4 Lensed Troffer, 4000K, 4800 Lumens, 0-10V Dimming Driver | | • | | • | 20.0 | 26 | |



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

| | | | | | | | | | | |
|--|---|--|---|---|---|---|-------------------------------------|---|-------------------------------|--|
| LJT | - | | G | - | FS | - | | U | - | |
| MODEL LJT LED Lensed Troffer | COLOR TEMP 35 3500K 40 4000K | CEILING TYPE G Grid ¹ | SHIELDING A12 Pattern 12 Acrylic Lens A12125 Pattern 12 Acrylic Lens, 0.125" Nominal | OPTIONS C388 3-Wire Flex C488 4-Wire Flex C588 5-Wire Flex ELL14 Emergency Battery Pack Installed, 1400 Lumen ² | SIZE 22 2' x 2' 24 2' x 4' | LUMEN OUTPUT LW Low Watt (2x4 only) ML Medium Lumen HL High Lumen VL Very High Lumen XL Extra High Lumen (2x4 only) | DOOR FS White Flush Steel | DRIVER E Fixed Output ED 0-10V Dimming | VOLTAGE U 120V-277V | |

¹ For hard ceilings use flange kit accessory.
² For compatibility with Dual-Lite LiteGear™ inverters in lieu of EL Battery Pack, contact Hubbell Lighting Representative.




LAW - LED Wraparound



Regional Distribution Center Stock List



| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-------------|----------------|--------------|---|-------|-------|-------|-------|----------|-------------|-------|
| 93058502 | LAW2-35LW-EDU | 078531124229 | LED 2' Wrap, 3500K, 2250 Lumens, 0-10V Dimming Driver | | • | | | 8.0 | 110 | |
| 93058503 | LAW2-40LW-EDU | 078531124236 | LED 2' Wrap, 4000K, 2250 Lumens, 0-10V Dimming Driver | | • | | • | 8.0 | 110 | |
| 93056100 | LAW4-40ML-EDU | 078531123840 | LED 4' Wrap, 4000K, 4500 Lumens, 0-10V Dimming Driver | | • | | • | 14.0 | 55 | |
| 93055614 | LAW4-35ML-EDU | 078531123635 | LED 4' Wrap, 3500K, 4500 Lumens, 0-10V Dimming Driver | | • | | | 14.0 | 55 | |



LLHV - LED Lensed Troffers



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-------------|-------------------|--------------|-----------------------------|-------|-------|-------|-------|----------|-------------|-------|
| 93052470 | LLHV4-40M-WST-EDU | 078531024000 | LED 4', 120-277V, 2 Drivers | | ● | ● | | 20.0 | 30 | |
| 93052471 | LLHV4-40H-WST-EDU | 078531024017 | LED 4', 120-277V, 3 Drivers | | ● | ● | | 20.0 | 24 | |



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

| | | | | | | | | | | | |
|---|---|---|--|---|--|---|---|---|-------------------------------|---|---|
| LLHV | 4 | - | | - | | ST | - | | U | - | |
| MODEL LLHV VersaBay® LED High Bay | COLOR TEMP 35 3500K 40 4000K | | REFLECTOR N Narrow Distribution W Wide Distribution | | | UPLIGHT ST Solid Top (no uplight) | | DRIVER E Fixed Output ED 0-10V Dimming | VOLTAGE U 120V-277V | | OPTIONS C6TL15_ 6' Cord and Twist-Lock™ Plug 15A (Add Voltage: 1=120, 2=277) C6TL20_ 6' Cord and Twist-Lock™ Plug 20A (Add Voltage: 1=120, 2=277) C6P151 6' Cord and Straight Blade Plug 15A, 120V ELL14 Emergency Battery Pack Installed, 1400 Lumen ¹ |
| SIZE 4 4' | LUMEN OUTPUT M Medium Lumen H High Lumen | | | | | | | | | | |

¹ ELL14 reduces max ambient temperature to 40°C. If combined with lens max is 30°C.



LCS - LED Striplight



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-------------|----------------|--------------|---|-------|-------|-------|-------|----------|-------------|-------|
| 93052240 | LCS4-35ML-EDU | 078531122294 | LED 4' Striplight, 3500K, 5000 Lumens, 0-10V Dimming Driver | | ● | | | 9.0 | 66 | |
| 93056105 | LCS4-40ML-EDU | 078531123888 | LED 4' Striplight, 4000K, 5000 Lumens, 0-10V Dimming Driver | | ● | | ● | 9.0 | 66 | |



LXEM - LED Enclosed & Gasketed Luminaire

35 SCHEDULED
STOCK
SHIPMENTS

Regional Distribution Center Stock List



| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-------------|-------------------|--------------|--|----------|----------|----------|----------|-------------|----------------|-------|
| 93055613 | LXEM4-35ML-RFA-EU | 078531123666 | LED 4' Vapor Tight, 3500K, 4900 Lumens | | ● | | | 14.0 | 30 | |



SER - Serrano® Recessed Architectural Luminaire

QS₁₀

10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

| | | | | | | | | | | |
|---|--|-------------------------------|--|--|--|---|--|-------------------------------|---|---|
| SER | - | - | G | - | C | - | - | - | - | - |
| MODEL SER Serrano® Recessed Architectural Luminaire | NO. OF LAMPS 1 One 2 Two 3 Three | CEILING TYPE G Grid | BALLAST E Electronic T8, 0.88 Ballast Factor, Instant Start EP Electronic T5, T5HO, 1.0 Ballast Factor or T8, 0.88 Ballast Factor, Programmed Start ETT Electronic Twin Tube, Instant Start EPTT Electronic Twin Tube, Programmed Start 3E 3-Lamp Electronic T8, Instant Start 3EP 3-Lamp Electronic T8, Programmed Start | VOLTAGE U 120V-277V 347 347V (T5 and T8 only) | OPTIONS EL Emergency Battery Pack, T8 EL5 Emergency Battery Pack, T5 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 C388 3-Wire Flex C488 4-Wire Flex | SIZE 14 1' x 4' 22 2' x 2' 24 2' x 4' | LAMP TYPE 17 2', T8: 17 Watt 24 2', T5HO: 24 Watt 28 4', T5: 28 Watt 32 4', T8 ¹ 40TT Twin Tube Compact, 2G11 Base: 40 Watt | SHIELDING C Contour | REFLECTOR P Performance F Full | LAMPS F830 30K 78+CRI T8 Lamps Installed F835 35K 78+CRI T8 Lamps Installed F841 41K 78+CRI T8 Lamps Installed F0830 30K 82CRI 32W T8 Lamps Installed F0835 35K 82CRI 32W T8 Lamps Installed F0841 41K 82CRI 32W T8 Lamps Installed F5830 30K 85CRI T5 or T5HO Lamps Installed F5835 35K 85CRI T5 or T5HO Lamps Installed F5841 41K 85CRI T5 or T5HO Lamps Installed FTT830 30K 82CRI 40W TT Lamps Installed FTT835 35K 82CRI 40W TT Lamps Installed FTT841 41K 82CRI 40W TT Lamps Installed |

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



EPC - Full Distribution Luminaire



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-------------|-------------------------|--------------|--|-------|-------|-------|-------|----------|-------------|-------|
| EPC000007 | EPC22-224G-SH-EPU-F5835 | 078531015848 | 2x2 24W T5HO 2-Lamp With 1.0 BF Ballast 24W T5HO Lamp, and Shield Lens | | | • | | 25.0 | 44 | |
| EPC000031 | EPC24-228G-SH-EPU-F5835 | 078531121266 | 2x4 28W T5 2-Lamp With 1.00 BF Ballast 28W T5 Lamp, and Shield Lens | • | • | • | • | 25.0 | 22 | |
| EPC000032 | EPC24-232G-SH-EU-F0835 | 078531121273 | 2x4 32W T8 2-Lamp With 0.88 BF Ballast 80 CRI 32W T8 Lamp, and Shield Lens | | • | | • | 25.0 | 22 | |



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

| | | | | | | | | | |
|--|--|---|---------------------------------------|---|---|--|--|--|--|
| EPC | 24 | - 2 | | G | - SH | | | | |
| MODEL EPC e.poc® Full Distribution Luminaire | NO. OF LAMPS 2 Two | CEILING TYPE G Grid | SHIELDING SH Shield Profile | VOLTAGE U 120V-277V 347 347V (E and EP only) | OPTIONS C388 3-Wire Flex EL Emergency Battery Pack, T8 EL5 Emergency Battery Pack, T5 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 | | | | |
| SIZE 24 2' x 4' | LAMP TYPE 28 4', T5: 28 Watt 32 4', T8 ¹ | BALLAST E Electronic T8, 0.88 Ballast Factor, Instant Start E104 Electronic T8, 1.04 Ballast Factor, Instant Start (2-lamp only) EP Electronic T5, T5HO, 1.0 Ballast Factor or T8, 0.88 Ballast Factor, Programmed Start EP95 Electronic T5, 0.95 Ballast Factor, Programmed Start | | | LAMPS INSTALLED (REQUIRED) F830 30K 78+CRI 32W T8 Lamps Installed F835 35K 78+CRI 32W T8 Lamps Installed F841 41K 78+CRI 32W T8 Lamps Installed FO830 30K 82CRI 32W T8 Lamps Installed FO835 35K 82CRI 32W T8 Lamps Installed FO841 41K 82CRI 32W T8 Lamps Installed F5830 30K 85CRI T5 or T5HO Lamps Installed F5835 35K 85CRI T5 or T5HO Lamps Installed F5841 41K 85CRI T5 or T5HO Lamps Installed | | | | |

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



STE - Stratus Recessed Direct/Indirect



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-------------|------------------------------|--------------|--|-------|-------|-------|-------|----------|-------------|-------|
| 93029796 | STE22-217G-MPO-EU | 078531017415 | 2 x 2, 2-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Ballast | • | • | • | • | 12.0 | 24 | |
| 93029798 | STE22-240TTG-MPO-EPTTU-C388 | 078531017477 | 2 x 2, 2-L, Metal Perf. Basket w/Overlay, 120-277V Twin Tube, Elec Prog Start Ballast, 3 Wire Flex | | • | | | 12.0 | 24 | |
| 93029800 | STE22-240TTG-MPO-ETTU | 078531017408 | 2 x 2, 2-L, Metal Perf. Basket w/Overlay, 120-277V Twin Tube, Elec Ballast | • | • | • | | 12.0 | 24 | |
| 93029801 | STE22-317G-MPO-EU | 078531017439 | 2 x 2, 3-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Ballast | | • | • | | 12.0 | 24 | |
| 93029804 | STE24-232G-MPO-EU | 078531017385 | 2 x 4, 2-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Ballast | • | • | • | • | 20.0 | 14 | |
| 93030408 | STE24-232G-MPO-EPU | 078531017446 | 2 x 4, 2-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Prog Start Ballast | • | • | • | • | 20.0 | 14 | |
| 93029803 | STE24-332G-MPO-3EU | 078531017378 | 2 x 4, 3-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Ballast | • | • | • | • | 20.0 | 14 | |
| 93030410 | STE24-332G-MPO-3EPU | 078531017460 | 2 x 4, 3-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Prog Start Ballast | • | • | • | | 20.0 | 14 | |
| 93029802 | STE24-332G-MPO-EU | 078531017392 | 2 x 4, 3-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec (2 Ballasts) | • | • | • | • | 20.0 | 14 | |
| 93043912 | STE24-332G-MPO-EU-FO841 | 078531023409 | 2x4, 3-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Ballast (2 Ballasts), T8 Lamps installed | | • | | | 20.0 | 14 | |
| 93030962 | Kit - STE/TRA 2x4 Dust Guard | 078531017507 | Dust Guard Kit, 4ft fixtures | | | • | | 1.0 | N/A | |



5-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

| STE | | | G | MPO | | U | | |
|-------------------------------|-------------------------------|---------------|--|---|--------------------------|--|--------------------------|--|
| MODEL | NO. OF LAMPS IN CROSS SECTION | CEILING TYPE | BALLAST | OPTIONS | SIZE | LAMP TYPE | SHIELDING | VOLTAGE |
| STE Stratus Recessed Indirect | 2 Two 3 Three | G Grid Lay-in | E Electronic T8, Instant Start EP Electronic T5, T5HO, or T8, Programmed Start ETT Electronic Twin Tube, Instant Start 3E 3-Lamp Electronic T8, Instant Start 3EP 3-Lamp Electronic T8 or T5, Programmed Start | EL Emergency Battery Pack, T8 EL5 Emergency Battery Pack, T5 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 F830 30K 78+CRI 17 or 32W T8 Lamps Installed F835 35K 78+CRI 17 or 32W T8 Lamps Installed F841 41K 78+CRI 17 or 32W T8 Lamps Installed FO830 30K 82CRI 17 or 32W T8Lamps Installed FO835 35K 82CRI 17 or 32W T8Lamps Installed FO841 41K 82CRI 17 or 32W T8Lamps Installed F5830 30K 85CRI T5 or T5HOLamps Installed F5835 35K 85CRI T5 or T5HOLamps Installed F5841 41K 85CRI T5 or T5HOLamps Installed FTT830 30K 82CRI 40W TT Lamps Installed FTT835 35K 82CRI 40W TT Lamps Installed FTT841 41K 82CRI 40W TT Lamps Installed C388 3-Wire Flex C488 4-Wire Flex | 22 2' x 2' 24 2' x 4' | 17 2'; T8: 17 Watt 24 2'; T5HO: 24 Watt 28 4'; T5: 28 Watt 32 4'; T8 ¹ 40TT Twin Tube Compact, 2G11 Base: 40 Watt (2-Lamp only) | MPO Metal Perf w/Overlay | U 120V-277V 347 347V (T5 and T8 only) |

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



TRA - Transition® High Efficiency Architectural Lensed

QS7 10-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 100

| TRA | | | | G | CLO | | | | |
|--------------|--|--------------------------------------|--|---------------------|--|----------------|---|----------------|---|
| MODEL | TRA Transition® High Efficiency Architectural Lensed | NO. OF LAMPS IN CROSS SECTION | 2 Two 3 Three | CEILING TYPE | G Grid Lay-in | BALLAST | E Electronic T8, Instant Start EP Electronic T5, T5HO, or T8, Programmed Start ETT Electronic Twin Tube, Instant Start EPTT Electronic Twin Tube, Programmed Start 3E 3-Lamp Electronic T8, Instant Start 3EP 3-Lamp Electronic T8 or T5, Programmed Start E104 Electronic T8, 1.04 Ballast Factor, Instant Start | OPTIONS | EL Emergency Battery Pack, T8 EL5 Emergency Battery Pack, T5 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 F830 30K 78+CRI 17 or 32W T8 Lamps Installed F835 35K 78+CRI 17 or 32W T8 Lamps Installed F841 41K 78+CRI 17 or 32W T8 Lamps Installed F0830 30K 82CRI 17 or 32W T8 Lamps Installed F0835 35K 82CRI 17 or 32W T8 Lamps Installed F0841 41K 82CRI 17 or 32W T8 Lamps Installed F5830 30K 85CRI T5 or T5HO Lamps Installed F5835 35K 85CRI T5 or T5HO Lamps Installed F5841 41K 85CRI T5 or T5HO Lamps Installed FTT830 30K 82CRI 40W TT Lamps Installed FTT835 35K 82CRI 40W TT Lamps Installed FTT841 41K 82CRI 40W TT Lamps Installed C388 3-Wire Flex C488 4-Wire Flex |
| SIZE | 22 2' x 2' 24 2' x 4' | LAMP TYPE | 17 2', T8: 17 Watt 24 2', T5HO: 24 Watt 28 4', T5: 28 Watt 32 4', T8 ¹ 40TT Twin Tube Compact, 2G11 Base: 40 Watt (2-Lamp only) | SHIELDING | CLO Clear Linear Prism Acrylic with Overlay | VOLTAGE | U 120V-277V 347 347V (T5 and T8 only) | | |


¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



ZPT - Zero Plenum Troffer

QS7 10-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 100

| ZPT | | 2 | | G | | | EP | U | |
|---|--------------------------|---------------------|--|---------------------|---|------------------|---|----------------|---|
| MODEL | ZPT Zero Plenum® Troffer | NO. OF LAMPS | 2 Two | CEILING TYPE | G Grid Lay-in | REFLECTOR | O Open (N/A with PRF) R Ribbed Curve S Smooth Curve | VOLTAGE | U 120V-277V 347 347V (T5 only) |
| SIZE | 22 2' x 2' 24 2' x 4' | LAMP TYPE | 14 2', T5: 14 Watt 24 2', T5HO: 24 Watt 28 4', T5: 28 Watt 54 4', T5HO: 54 or 51 Watt | SHIELDING | LSR Linear Prismatic Lens with Surface Relief Diffuser PRF Metal Perf w/ Overlay | BALLAST | EP Electronic T5, 1.00 Ballast Factor (28W or 54W) | OPTIONS | C38890 3-Wire Flex, 90° Connector EL5 Emergency Battery Pack (N/A 2 x 2) F5835 35K 85CRI T5 or T5HO Lamps Installed F5841 41K 85CRI T5 or T5HO Lamps Installed |
| ACCESSORIES (ORDER SEPARATELY) | | | | | | | | | |
| ZPTSMK22 ZPT Surface Mounting Kit (2' x 2') | | | | | | | | | |
| ZPTSMK24 ZPT Surface Mounting Kit (2' x 4') | | | | | | | | | |



P4D - High Performance Parabolic

3 SCHEDULED
STOCK
SHIPMENTS

Regional Distribution Center Stock List


| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pal- let | Price |
|-----------------|-------------------------------------|--------------|---|----------|----------|----------|----------|-------------|---------------------|-------|
| P4D00162 | P4D22-232U6G-MA33-AV-EU | 078531006501 | 2 x 2, 2-L, 9 Cell MA Lvr, 120-277V T8 Elec Ballast, Air w/Vanes | | | ● | | 32.0 | 28 | |
| P4D00120 | P4D22-232U6G-MA33-S-EU | 078531043445 | 2 x 2, 2-L, 9 Cell MA Lvr, 120-277V T8 Elec Ballast, Static | ● | ● | ● | ● | 32.0 | 28 | |
| P4D00156 | P4D24-232G-MA26-S-EU | 078531043704 | 2 x 4, 2-L, 12 Cell MA Lvr, 120-277V T8 Elec Ballast, Static | ● | ● | ● | ● | 32.0 | 16 | |
| P4D00157 | P4D24-332G-MA36-AV-3EU | 078531043711 | 2 x 4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Air w/Vanes | | | ● | | 33.0 | 16 | |
| P4D00146 | P4D24-332G-MA36-S-3EU | 078531043483 | 2 x 4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Static | ● | ● | ● | ● | 33.0 | 16 | |
| 93043905 | P4D24-332G-MA36-S-3EPU | 078531023331 | 2x4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Prog Start Ballast, Static | | ● | | | 33.0 | 16 | |
| P4D00138 | P4D24-332G-MA36-S-EU | 078531043414 | 2 x 4, 3-L, 18 Cell MA Lvr, 120-277V T8 Elec (2 Ballasts), Static | ● | ● | ● | ● | 35.0 | 16 | |
| 93057986 | P4D24-332G-MA36-S-3EU- F835 | 078531124120 | 2 x 4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Static, T8 Lamps Installed | | ● | ● | ● | 34.0 | 16 | |
| 93057987 | P4D24-332G-MA36-S-3EU- F835-C388 | 078531124137 | 2 x 4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Stat, T8 Lamps Installed, 3 Wire Flex | ● | ● | | ● | 34.0 | 16 | |
| 93057988 | P4D24-332G-MA36-S-3EU- F841 | 078531124144 | 2x4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Static, T8 Lamps Installed | | ● | | | 34.0 | 16 | |
| P4D00147 | P4D24-432G-MA48-S-4EU | 078531043490 | 2 x 4, 4-L, 32 Cell, 120-277V 4-L T8 Elec Ballast, Static | | ● | ● | ● | 34.0 | 16 | |
| P4D019047.16PK1 | LVR P4D24 3X6 MA HK BAG | 078531044985 | Louver for 2 x 4, 18 cell, MA | | ● | ● | | 10.0 | N/A | |

QS75 5-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

| | | | | | | | | | | | | | | |
|--|---|--|--|---|---|---|--|---|----------|---|--|----------|---|--|
| P4D | - | | G | - | MA | - | | - | S | - | | U | - | |
| MODEL P4D High Performance Parabolic | NO. OF LAMPS 2 Two 3 Three | CEILING TYPE G Grid | CELLS WIDE BY CELLS LONG 33 3 x 3 (2' x 2' only) 36 3 x 6 (2' x 4' 3-Lamp only) | | BALLAST E 2-Lamp Electronic T8, Instant Start 3E 3-Lamp Electronic T8, Instant Start EP T8, Programmed Start 3EP 3-Lamp T8, Programmed Start | VOLTAGE U 120V-277V 347 347V | OPTIONS F835 35K 78+CRI Full Wattage T8 Lamps Installed F841 41K 78+CRI Full Wattage T8 Lamps Installed F0835 35K 82CRI Full Wattage T8 Lamps Installed F0841 41K 82CRI Full Wattage T8 Lamps Installed C388 3-Wire Flex C488 4-Wire Flex EL Emergency Battery Pack EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 | | | | | | | |
| SIZE 22 2' x 2' 24 2' x 4' | LAMP TYPE 17 2', T8: 17 Watt 32 4', T8 ¹ 32U6 U-Bent, 6" Leg Spacing T8: 32 Watt (2-Lamp only) | LOUVER FINISH MA Matte Anodized Low Iridescent Semi-Specular Aluminum (Std.) | AIR HANDLING S Static | | | | | | | | | | | |

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



ST8 - Shallow Specification Lensed Troffers



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-----------------|--------------------------|--------------|--|-------|-------|-------|-------|----------|-------------|-------|
| HS241519F000000 | ST824-232G-FSA12125-EU | 078531006853 | 2 x 4, 2-L, 120-277V T8 Elec Ballast, .125" Lens | ● | ● | ● | ● | 22.0 | 24 | |
| HS341519G000000 | ST824-332G-FSA12125-3EU | 078531006884 | 2 x 4, 3-L, 120-277V 3-L T8 Elec Ballast, .125" Lens | | ● | ● | ● | 22.0 | 24 | |
| 93043895 | ST824-332G-FSA12125-3EPU | 078531023416 | 2x4, 3-L, 120-277V 3-L T8 Elec Prog Start Ballast, .125" Lens | | ● | | | 22.0 | 24 | |
| HS341519F000000 | ST824-332G-FSA12125-EU | 078531006877 | 2 x 4, 3-L, 120-277V T8 Elec (2 Ballasts), .125" Lens | | ● | | ● | 25.0 | 24 | |
| 93043896 | ST824-332G-FSA12125-EPU | 078531023423 | 2x4, 3-L, 120-277V T8 Elec Prog Start (2) Ballasts, .125" Lens | | ● | | | 22.0 | 24 | |




5-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 200

| | | | | | | | | | | | | |
|--|--|---------------------|-----------------------------|---|---|-----------|--|---------------------------------------|--|----------|---|--|
| ST8 | - | | | G | - | FS | - | | | U | - | |
| MODEL | NO. OF LAMPS | CEILING TYPE | | | SHIELDING | | | VOLTAGE | | | | |
| ST8 Low Profile Specification Troffer | 2 Two 3 Three (N/A 1 x 4) 4 Four (N/A 1 x 4 or 2 x 2) | G Grid | | | A12 Pattern 12 Acrylic Lens A12125 Pattern 12 Acrylic Lens, 0.125" Nominal | | | U 120V-277V 347 347V | | | | |
| SIZE | LAMP TYPE | | DOOR | BALLAST | | | OPTIONS | | | | | |
| 14 1' x 4' | 17 2', T8: 17 Watt | | FS White Flush Steel | E Electronic T8, Instant Start | | | F835 35K 78+CRI Full Wattage T8 Lamps Installed | | | | | |
| 22 2' x 2' | 32 4', T8 ¹ | | | 3E 3-Lamp Electronic T8, Instant Start | | | F841 41K 78+CRI Full Wattage T8 Lamps Installed | | | | | |
| 24 2' x 4' | 32U6 U-Bent, 6" Leg Spacing T8: 32 Watt (2-lamp only) | | | 4E 4-Lamp Electronic T8, Instant Start | | | F835 35K 82CRI Full Wattage T8 Lamps Installed | | | | | |
| | | | | EP Electronic T8, Programmed Start | | | F0841 41K 82CRI Full Wattage T8 Lamps Installed | | | | | |
| | | | | 3EP 3-Lamp Electronic T8, Programmed Start | | | EL Emergency Battery Pack ² | | | | | |
| | | | | 4EP 4-Lamp Electronic T8, Programmed Start | | | EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 | | | | | |
| | | | | | | | C388 3-Wire Flex | | | | | |
| | | | | | | | C488 4-Wire Flex | | | | | |

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.

² 2 x 2 with 2 ballasts and EL N/A as Quick Ship.



JT8- Lensed Troffers



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-----------------|--------------------------------|--------------|---|----------|----------|----------|----------|-------------|----------------|-------|
| JT243119FTP0000 | JT822-232U6G-FSA12-EU | 078531005603 | 2 x 2, 2-L, 120-277V T8 Elec Ballast | ● | ● | ● | ● | 16.0 | 36 | |
| JT241519F000000 | JT824-232G-FSA12125-EU | 078531006914 | 2 x 4, 2-L, 120-277V T8 Elec Ballast, .125" Lens | ● | ● | ● | ● | 20.0 | 26 | |
| JT24111BL000000 | JT824-232G-FSA12-ELWU | 078531011765 | 2x4, 2-L, 120-277V T8 Elec Low Wattage Ballast | | | ● | | 20.0 | 26 | |
| JT241119F000000 | JT824-232G-FSA12-EU | 078531005610 | 2 x 4, 2-L, 120-277V T8 Elec Ballast | ● | ● | ● | ● | 20.0 | 26 | |
| 93057975 | JT824-232G-FSA12-EU-F835-C388 | 078531124014 | 2 x 4, 2-L, 120-277V T8 Elec Ballast, 3 Wire Flex, T8 Lamps Installed | ● | | | ● | 24.0 | 26 | |
| JT341519G000000 | JT824-332G-FSA12125-3EU | 078531006815 | 2 x 4, 3-L, 120-277V 3-L T8 Elec Ballast, .125" Lens | | ● | ● | ● | 20.0 | 26 | |
| JT34111BM000000 | JT824-332G-FSA12-3ELWU | 078531010867 | 2x4, 3-L, 120-277V 3-L T8 Elec Low Wattage Ballast | | | ● | | 20.0 | 26 | |
| 93043898 | JT824-332G-FSA12-3EPU | 078531023447 | 2x4, 3-L, 120-277V 3-L T8 Elec Prog Start Ballast | | ● | | | 20.0 | 26 | |
| JT341119G000000 | JT824-332G-FSA12-3EU | 078531005627 | 2 x 4, 3-L, 120-277V 3-L T8 Elec Ball. | ● | ● | ● | ● | 20.0 | 26 | |
| 93057976 | JT824-332G-FSA12-3EU-F835 | 078531124021 | 2 x 4, 3-L, 120-277V 3-L T8 Elec Ballast, T8 Lamps Installed | | ● | | ● | 23.0 | 26 | |
| 93057977 | JT824-332G-FSA12-3EU-F835-C388 | 078531124038 | 2 x 4, 3-L, 120-277V 3-L T8 Elec Ballast, T8 Lamps Installed, 3 Wire Flex | ● | ● | | ● | 24.0 | 26 | |
| 93057978 | JT824-332G-FSA12-3EU-F841 | 078531124045 | 2 x 4, 3-L, 120-277V 3-L T8 Elec Ball., T8 Lamps Installed | | ● | | ● | 23.0 | 26 | |
| JT341119F000000 | JT824-332G-FSA12-EU | 078531005634 | 2 x 4, 3-L, 120-277V T8 Elec (2 Ballasts) | ● | ● | ● | ● | 24.0 | 26 | |
| 93046045 | JT824-332SM-FSA12-3EU | 078531121105 | 2 x 4 Surface Mount, 3-L 120-277V T8 Elec Ballast | | ● | | | 24.0 | 9 | |
| JT441119H000000 | JT824-432G-FSA12-4EU | 078531005641 | 2 x 4, 4-L, 120-277V 4-L T8 Elec Ballast | ● | ● | ● | ● | 18.0 | 26 | |
| 93057980 | JT824-432G-FSA12-4EU-F835 | 078531124069 | 2 x 4, 4-L, 120-277V 4-L T8 Elec Ballast, T8 Lamps Installed | | ● | ● | ● | 23.0 | 26 | |
| 93057981 | JT824-432G-FSA12-4EU-F835-C388 | 078531124076 | 2 x 4, 4-L, 120-277V 4-L T8 Elec Ballast, T8 Lamps Installed, 3 Wire Flex | ● | ● | | ● | 24.0 | 26 | |
| 93057982 | JT824-432G-FSA12-4EU-F841 | 078531124083 | 2 x 4, 4-L, 120-277V 4-L T8 Elec Ballast, T8 41K Lamps Installed | | ● | | ● | 23.0 | 26 | |
| 93057983 | JT824-432G-FSA12-4EU-F841-C388 | 078531124090 | 2 x 4, 4-L, 120-277V 4-L T8 Elec Ballast, T8 41K Lamps Installed, 3 Wire Flex | | ● | ● | ● | 24.0 | 26 | |
| JT441119F000000 | JT824-432G-FSA12-EU | 078531005658 | 2 x 4, 4-L, 120-277V T8 Elec (2 Ballasts) | ● | ● | ● | ● | 24.0 | 26 | |
| 93046044 | JT824-432SM-FSA12-4EU | 078531121099 | 2 x 4 Surface Mount, 4-L 120-277V T8 Elec Ballast | | ● | | | 24.0 | 9 | |
| JT2499000800000 | DR&SHLD JT824 FS A12 | 078531012632 | 2 x 4 Replacement Door Assembly with Lens | | | ● | | 5.0 | N/A | |
| 003334.00 | A12.095 22.500-22.500 | 078531004781 | 2 x 2 Replacement Lens | | ● | ● | | 1.0 | N/A | |
| 003335.00 | A12.095 22.500-46.562 | 078531004774 | 2 x 4 Replacement Lens | | ● | ● | | 2.0 | N/A | |
| 003312.00 | A12.125 | 078531022891 | 2 x 4 Replacement Lens | | ● | ● | | 2.5 | N/A | |



JT8 - Lensed Troffers

QS75 5-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 200

| JT8 | | | | G | FS | | | U | |
|---------------------------------|---|----------------------|--|--|---|-------------------------|--|---|--|
| MODEL | NO. OF LAMPS | CEILING TYPE | | | SHIELDING | VOLTAGE | | OPTIONS | |
| JT8 Dedicated T8 Lensed Troffer | 2 Two 3 Three 4 Four (2 x 4 only) | G Grid | | | A12 Pattern 12 Acrylic Lens A12125 Pattern 12 Acrylic Lens, 0.125" Nominal | U 120V-277V 347 347V | | F835 35K 78+CRI Full Wattage T8 Lamps Installed F841 41K 78+CRI Full Wattage T8 Lamps Installed FO835 35K 82CRI Full Wattage T8 Lamps Installed FO841 41K 82CRI Full Wattage T8 Lamps Installed EL Emergency Battery Pack ² EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 C388 3-Wire Flex C488 4-Wire Flex | |
| SIZE | LAMP TYPE | DOOR | | BALLAST | | | | | |
| 22 2' x 2' 24 2' x 4' | 17 2', T8: 17 Watt 32 4', T8 ¹ 32U6 U-Bent, 6" Leg Spacing T8: 32 Watt (2 lamps) | FS White Flush Steel | | E Electronic T8, Instant Start 3E 3-Lamp Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start EP Electronic T8, Programmed Start 3EP 3-Lamp Electronic T8, Programmed Start 4EP 4-Lamp Electronic T8, Programmed Start | | | | | |

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.
² 2 x 2 with 2 ballasts and EL N/A as Quick Ship.



4PS - Specification Grade Lensed Troffers

3S SCHEDULED
STOCK
SHIPMENTS

Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-----------------|-------------------------|--------------|---|----------|----------|----------|----------|-------------|----------------|-------|
| HW241519F000000 | 4PS24-232G-FSA12125-EU | 078531009106 | 2 x 4, 2-L, 120-277V T8 Elec Ballast, .125" Lens | • | • | • | • | 22.0 | 18 | |
| HW341519G000000 | 4PS24-332G-FSA12125-3EU | 078531009113 | 2 x 4, 3-L, 120-277V 3-L T8 Elec Ballast, .125" Lens | | • | | | 23.0 | 18 | |
| HW341519F000000 | 4PS24-332G-FSA12125-EU | 078531009120 | 2 x 4, 3-L, 120-277V T8 Elec (2 Ballasts), .125" Lens | | • | | | 25.0 | 18 | |


QS
10

10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

| | | | | | | | | | | | |
|--|--|-------------------------------|---|---|---|--|--|---|--|---|--|
| 4PS | - | | | G | - | | | | U | - | |
| MODEL 4PS Specification Grade Static Troffer | NO. OF LAMPS 2 Two 3 Three 4 Four (2 x 4 only) | CEILING TYPE G Grid | SHIELDING A12 Pattern 12 Acrylic Lens A12125 Pattern 12 Acrylic Lens, 0.125" Nominal | VOLTAGE U 120V-277V 347 347V (T8 only) | SIZE 22 2' x 2' 24 2' x 4' | LAMP TYPE 32 4', T8 ¹ 32U6 U-Bent, 6" Leg Spacing T8: 32 Watt (2 lamps) 40TT Twin Tube Compact, 2G11 Base: 40 Watt (2 or 3 lamps) | DOOR FS White Flush Steel RA White Regressed Aluminum | BALLAST E Electronic T8, Instant Start 3E 3-Lamp Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start EP Electronic T8, Programmed Start 3EP 3-Lamp Electronic T8, Programmed Start 4EP 4-Lamp Electronic T8, Programmed Start ETT Electronic Twin Tube, Instant Start | OPTIONS F835 35K 78+CRI Full Wattage T8 Lamps Installed F841 41K 78+CRI Full Wattage T8 Lamps Installed FO835 35K 82CRI Full Wattage T8 Lamps Installed FO841 41K 82CRI Full Wattage T8 Lamps Installed EL Emergency Battery Pack, T8 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 C388 3-Wire Flex C488 4-Wire Flex | | |

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.




BIL - Integrated Sensor for Stairwell Applications



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-------------|----------------|--------------|-------------------------------|----------|----------|----------|----------|-------------|----------------|-------|
| BIL000002 | BIL4-232-EPU | 078531016807 | 4', 2-L, 32W T8, Elec Ballast | | ● | ● | | 9.0 | N/A | |



SA - Wall Brackets



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-----------------|----------------|--------------|------------------------------------|----------|----------|----------|----------|-------------|----------------|-------|
| 34241019F000000 | SA4-232-EU | 078531006792 | 2-4' T8, 4', 120-277V Elec Ballast | ● | ● | ● | ● | 13.0 | 24 | |



UC - Undercabinet



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-------------|----------------|--------------|-------------------------------|----------|----------|----------|----------|-------------|----------------|-------|
| 93047671 | UC24-117-EU | 078531023690 | 2', 1-L, 17W T8, Elec Ballast | | ● | ● | ● | 6.0 | 224 | |
| 93047672 | UC36-125-EU | 078531023706 | 3', 1-L, 25W T8, Elec Ballast | ● | ● | ● | ● | 6.0 | 140 | |
| 93047673 | UC48-132-EU | 078531023713 | 4', 1-L, 32W T8, Elec Ballast | ● | ● | ● | ● | 8.0 | 112 | |



W - Wall Mount Light



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-----------------|----------------|--------------|---|----------|----------|----------|----------|-------------|----------------|-------|
| 24222019F000000 | W2-217-EU | 078531010294 | 2-2' T8, 2', 120-277V T8 Elec Ballast Less Switch, Less Convenience Outlet | ● | ● | ● | ● | 6.0 | N/A | |
| 24241019F000000 | W4-232-EU | 078531007287 | 2-4' T8, 4', 120-277V T8 Elec Ballast Less Switch, Less Convenience Outlet | ● | ● | ● | ● | 13.0 | N/A | |



WAL - Wall Mount



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-----------------|----------------|--------------|---------------------------------------|----------|----------|----------|----------|-------------|----------------|-------|
| DS241019F000000 | WAL4-232-EU | 078531006068 | 2-4' T8, 4', 120-277V T8 Elec Ballast | ● | ● | ● | ● | 16.0 | 55 | |




AD - Corridor Wraparounds



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-----------------|----------------|--------------|--------------------------------------|----------|----------|----------|----------|-------------|----------------|-------|
| 22141019F000000 | AD4-132-EU | 078531006327 | 1-4'T8, 4', 120-277V T8 Elec Ballast | | | ● | | 10.0 | 56 | |
| 22241019F000000 | AD4-232-EU | 078531006334 | 2-4'T8, 4', 120-277V T8 Elec Ballast | ● | | ● | | 10.0 | 56 | |



WC - Specification Grade Wraparounds



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-----------------|------------------|--------------|--|----------|----------|----------|----------|-------------|----------------|-------|
| CD241019F000000 | WC4-232-EU | 078531006075 | 2-4'T8, 4', 120-277V T8 Elec Ballast | ● | ● | ● | ● | 13.0 | 48 | |
| CD441019H000000 | WC8-232-4EU | 078531006822 | 4-4'T8, 8', 120-277V 4-L T8 Elec Ballast | | ● | | | 26.0 | 36 | |
| CF341019G000000 | WCW4-332-3EU | 078531006341 | 3-4'T8, 4', 120-277V 3-L T8 Elec Ballast | ● | | ● | | 14.0 | 33 | |
| CF441019H000000 | WCW4-432-4EU | 078531006082 | 4-4'T8, 4', 120-277V 4-L T8 Elec Ballast | ● | ● | ● | | 16.0 | 28 | |
| CD8013802000000 | SHLD ASY WC 4FT | 078531000998 | WC Replacement Lens - 4' | | ● | ● | | 3.1 | 54 | |
| CF8013803000000 | SHLD ASY WCW 4FT | 078531001001 | WCW Replacement Lens | | ● | ● | | 10.0 | 80 | |



AW- Wraparounds

3S SCHEDULED
STOCK
SHIPMENTS

Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-----------------|----------------|--------------|---|----------|----------|----------|----------|-------------|----------------|-------|
| CY222019F000000 | AWN2-217-EU | 078531009984 | 2-2'T8, 2', 120-277V T8 Elec Ballast | | ● | ● | ● | 8.0 | 110 | |
| CY241019F000000 | AWN4-232-EU | 078531004859 | 2-4'T8, 4', 120-277V T8 Elec Ballast | ● | ● | ● | ● | 14.0 | 55 | |
| 93043931 | AWN4-232-EPU | 078531023508 | 2-4'T8, 4', 120-277V T8 Elec Prog Start Ballast | ● | ● | | | 14.0 | 55 | |
| CY24101BL000000 | AWN4-232-ELWU | 078531011857 | 2-4' T8, 4', 120-277V T8 Elec Low Wattage Ballast | ● | | ● | | 14.0 | 55 | |
| CY441019H000000 | AWN8-232-4EU | 078531005979 | 4-4'T8, 8', 120-277V 4-L T8 Elec Ballast | ● | ● | ● | | 26.0 | 30 | |
| 93015558 | AWN8-232-4ELWU | 078531012441 | 4-4' T8, 8', 120-277V 4-L T8 Elec Low Wattage Ballast | | | ● | | 26.0 | 30 | |
| CL341019G000000 | AWW4-332-3EU | 078531004866 | 3-4'T8, 4', 120-277V 3-L T8 Elec Ballast | ● | ● | ● | ● | 14.0 | 33 | |
| CL441019H000000 | AWW4-432-4EU | 078531004873 | 4-4'T8, 4', 120-277V 4-L T8 Elec Ballast | ● | ● | ● | ● | 14.0 | 33 | |
| CY8092746000000 | SHLD AWN 4FT | 078531001148 | AWN Replacement Lens | | ● | ● | | 10.0 | 100 | |
| CL8092721000000 | SHLD AWW 4FT | 078531001155 | AWW Replacement Lens | | ● | ● | | 5.0 | 66 | |

QS 10 10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

| | | | | | | |
|--|--------------------------------------|--|---|--|--------------------|--|
| | | | 32 | | U | EL |
| MODEL | SIZE | | LAMP TYPE | | VOLTAGE | OPTIONS |
| AWN 8 ⁵ / ₁₆ " Wide | 4 4' | | 32 4', T8 ¹ | | U 120V-277V | EL Emergency Battery Pack |
| AWW 14 ⁵ / ₈ " Wide | 8 8' (AWN only) | | | | 347 347V | EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 |
| | NO. OF LAMPS IN CROSS SECTION | | BALLAST | | | |
| | 2 Two | | E Electronic Instant Start | | | |
| | 3 Three (AWW only) | | 3E 3-Lamp Electronic T8, Instant Start | | | |
| | 4 Four (AWW only) | | 4E 4-Lamp Electronic T8, Instant Start | | | |
| | | | EP Electronic T8, Programmed Start | | | |
| | | | 3EP 3-Lamp Electronic T8, Programmed Start | | | |
| | | | 4EP 4-Lamp Electronic T8, Programmed Start | | | |

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



CSR - Industrials

3 SCHEDULED
STOCK
SHIPMENTS

Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-----------------|------------------|--------------|--|----------|----------|----------|----------|-------------|----------------|-------|
| 56241719F910000 | CSR4-232-ST-EU | 078531004934 | 2-4' T8, 4', 120-277V T8 Elec Ballast, Solid Reflector | • | • | • | • | 11.0 | 48 | |
| 5624171BL910000 | CSR4-232-ST-ELWU | 078531011918 | 2-4' T8, 4', 120-277V T8 Elec Low Wattage Ballast, Solid Reflector | | | • | | 11.0 | 48 | |
| 55441719H910000 | CSR8-232-ST-4EU | 078531004941 | 2-4' T8, 8', 120-277V 4-L T8 Elec Ballast, Solid Reflector | • | • | • | • | 20.0 | 27 | |
| 56275719F910000 | CSR8-296T8-ST-EU | 078531005986 | 2-8' T8, 8', 120-277V T8 Elec Ballast, Solid Reflector | | • | • | | 26.0 | 27 | |
| 562092935000000 | CSRWG4 | 078531740139 | 4' Wire Guard for CSR series | • | • | • | • | 2.5 | N/A | |
| 985084348700000 | CSZT | 078531740146 | Zip T-Hanger - 1/2" spacer | | • | • | • | 0.2 | N/A | |



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

| | | | | | | | | | |
|--------------------------------|---|---|---|--|-----------------------------|--|--|---|-----------|
| CSR | - | | - | | - | | U | - | EL |
| MODEL CSR Industrial | NO. OF LAMPS 2 Two 3 Three (T8 only) | REFLECTOR TYPE ST Solid Top Reflector U Apertured Reflector for 5% Uplight (Solid Reflector not recommended with HO units) | VOLTAGE U 120V-277V 347 347V (T8 only) | OPTIONS EL Emergency Battery Pack (T8 only) EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 | SIZE 4 4' 8 8' | LAMP TYPE 32 4', T8 ¹ 96HO 8', T12: 110 or 95 Watt | BALLAST E Electronic, Instant Start 3E 3-Lamp Electronic T8 (32W), Instant Start 4E 4-Lamp Electronic T8 (32W), Instant Start EP Electronic, Programmed Start, T8 3EP 3-Lamp Electronic T8, Programmed Start 4EP 4-Lamp Electronic T8, Programmed Start | | |

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



LHA- Industrial Fluorescent High Bay



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-------------|----------------------------|--------------|--|-------|-------|-------|-------|----------|-------------|-------|
| LHA000016 | LHA4-454-NST-4EPU | 078531022464 | 4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, Narrow Distribution, Solid Reflector | | ● | ● | | 22.0 | 30 | |
| LHA000017 | LHA4-454-NU-4EPU | 78531022112 | 4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, Narrow Distribution, Uplight Reflector | ● | ● | ● | ● | 22.0 | 30 | |
| LHA000019 | LHA4-454-NU-4EPU-F554841 | 78531022129 | 4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, 54 Watt Lamps Installed, Narrow Distribution, Uplight Reflector | ● | ● | | ● | 23.0 | 30 | |
| LHA000024 | LHA4-632-NST-3EHLU | 078531022471 | 6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast, Narrow Distribution, Uplight Reflector | | ● | | | 24.0 | 24 | |
| LHA000025 | LHA4-632-NU-3EHLU | 78531022136 | 6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast Narrow Distribution, Uplight Reflector | ● | ● | ● | ● | 24.0 | 24 | |
| LHA000027 | LHA4-632-NU-3EHLU-FO841 | 078531022143 | 6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast 82 CRI T8 Lamps Installed, Narrow Distribution, Uplight Reflector | | ● | | | 25.0 | 24 | |
| LHA000040 | LHA4-654-NST-24EPU | 078531022488 | 6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast Narrow Distribution, Solid Reflector | ● | ● | ● | ● | 26.0 | 24 | |
| 93043290 | LHA4-654-NST-24EPU-F554841 | 078531023256 | 6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast, 54W-T5 Lamps Installed Narrow Distribution, Solid Reflector | | | ● | | 26.0 | 24 | |
| LHA000041 | LHA4-654-NU-24EPU | 078531022150 | 6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast, Narrow Distribution, Uplight Reflector | ● | ● | ● | ● | 26.0 | 24 | |
| LHA000043 | LHA4-654-NU-24EPU-F554841 | 078531022167 | 6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast, 54 Watt Lamps Installed, Narrow Distribution, Uplight Reflector | ● | ● | ● | ● | 26.0 | 24 | |



5-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

LHA **4** - [] - [] - [] - [] - [] - **U** [] - []

| | | | | | |
|---|--|--|---|---|---|
| SIZE 4 4' | NO. OF LAMPS 4 Four 6 Six | REFLECTOR N Narrow Distribution W Wide Distribution | UPLIGHT ST Solid Top U Uplight | VOLTAGE U 120V-277V 347 347V | OPTIONS EL141 Emergency Battery Pack, T8, 1400 Lumens EL5H Emergency Battery Pack, T5, 1250 Lumens F3C5 3-Conductor Cord F4C5 4-Conductor Cord F3C10 3-Conductor Cord, 10' F4C10 4-Conductor Cord, 10' |
| MODEL LHA Industrial Fluorescent High Bay | LAMP TYPE 32 4', T8 ¹ 54 4', T5HO: 54 or 51 Watt | BALLAST LHA4-454 4EP (1) 4-Lamp Electronic T5HO, Programmed Start LHA4-654 24EP (1) 2-Lamp and (1) 4-Lamp Electronic T5HO, Programmed Start LHA4-432 4EHL (1) 4-Lamp Electronic T8, High Light Output, Instant Start (N/A 480V) LHA4-632 3EHL (2) 3-Lamp Electronic T8, High Light Output, Instant Start 3EPHL (2) 3-Lamp Electronic T8, High Light Output, Programmed Start | | | LAMPS INSTALLED T8 F841 4100K 78+CRI 32W T8 F850 5000K 78+CRI 32W T8 T5HO F554841 54 Watt, 85 CRI, 4100K F554850 54 Watt, 85 CRI, 5000K |

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



LHV - Linear High Bays

3 SCHEDULED
STOCK
SHIPMENTS

Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-------------|----------------------------|--------------|--|----------|----------|----------|----------|-------------|----------------|-------|
| 93014378 | LHV4-432-M4R-ST-4EHLU | 078531019372 | 4-4' T8, 4', 120-277V 4-L T8 HL Elec Ballast | | ● | | | 22.0 | 30 | |
| 93038457 | LHV4-432-M4RU-4EHLU-FO850 | 078531022914 | 4-4' T8, 4', 120-277V 4-L T8 HL Elec Ballast 80 CRI T8 Lamps Installed | | ● | | | 24.0 | 30 | |
| LHV000004 | LHV4-454-GWU-4EPU-F5841 | 078531011086 | 4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, White Reflector T5 Lamps Installed | | ● | | | 23.0 | 30 | |
| 93014379 | LHV4-454-M4RST-4EPU | 078531011703 | 4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, Solid Top Reflectors | | | ● | | 22.0 | 30 | |
| LHV000003 | LHV4-454-M4RU-4EPU | 078531011024 | 4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, Uplight Reflector | ● | ● | ● | ● | 22.0 | 30 | |
| LHV000002 | LHV4-454-M4RU-4EPU-F5841 | 078531011079 | 4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, T5 Lamps Installed | | ● | ● | ● | 23.0 | 30 | |
| 93057984 | LHV4-632-GWU-3EHLU-F841 | 078531124106 | 6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast T8 Lamps Installed, White Reflector | | ● | | | 23.0 | 24 | |
| LHV000009 | LHV4-632-M4RU-3EHLU | 078531011048 | 6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast, | ● | ● | ● | ● | 24.0 | 24 | |
| 93057985 | LHV4-632-M4RU-3EHLU-F841 | 078531124113 | 6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast 70CRI T8 Lamps Installed | | ● | | ● | 25.0 | 24 | |
| LHV000029 | LHV4-632-M4RU-3EHLU-FO850 | 078531016845 | 6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast 80 CRI T8 Lamps Installed | | ● | | | 25.0 | 24 | |
| LHV000007 | LHV4-654-GWU-24EPU-F5841 | 078531011109 | 6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast T5 Lamps Installed, White Reflector | | ● | | ● | 25.0 | 24 | |
| 93020453 | LHV4-654-M4RST-24EPU-F5841 | 078531016296 | 6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast, T5 Lamps Installed Solid Top Reflector | | | | ● | 26.0 | 24 | |
| LHV000006 | LHV4-654-M4RU-24EPU | 078531011031 | 6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast | ● | ● | ● | ● | 26.0 | 24 | |
| LHV000005 | LHV4-654-M4RU-24EPU-F5841 | 078531011093 | 6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast, T5 Lamps Installed | | ● | ● | ● | 26.0 | 24 | |
| LHVOS1360 | LHVOS1360 | 078531023584 | Occupancy/Daylight Sensor, with a 360° lens, 120/277/347V, One Relay | ● | ● | ● | ● | 25.0 | N/A | |
| LHVQM10 | LHVQM10 | 078531012526 | Aircraft Cable Hangers, 10' (pair) | ● | ● | ● | ● | 0.6 | N/A | |
| LHVQM20 | LHVQM20 | 078531012991 | Aircraft Cable Hangers, 20' (pair) | | ● | | ● | 1.2 | N/A | |
| LHVQM5 | LHVQM5 | 078531012670 | Aircraft Cable Hangers, 5' (pair) | ● | ● | ● | ● | 0.5 | N/A | |
| LHVSP | LHVSP | 078531011338 | Side Panels (pair) | | ● | | | 5.0 | N/A | |
| LHVSPM5 | LHVSPM5 | 078531012656 | Single Point Mounting Kit, Includes Aircraft Cable, 5' (pair) | | ● | ● | | 5.0 | N/A | |
| LHVTH | LHVTH | 078531012649 | Tong Hanger (pair) | ● | ● | ● | ● | 0.6 | N/A | |
| LHVWG4-4 | LHVWG4-4 | 078531012625 | Cage Wireguard, 4-L, White | ● | ● | ● | ● | 5.0 | N/A | |
| LHVWG4-6 | LHVWG4-6 | 078531012618 | Cage Wireguard, 6-L, White | ● | ● | ● | ● | 5.0 | N/A | |
| C6P15-120 | C6P15-120 | 078531016111 | Cord and Plug Kit (white), 6 ft Straight Blade Nema 5-15P, 15 amp, 120V | | ● | | | 0.8 | N/A | |
| C6TL15-120 | C6TL15-120 | 078531016098 | Cord and Plug Kit (white), 6 ft Twist Lock Nema L5-15P, 15 amp, 120V | | ● | | | 0.8 | N/A | |
| C6TL15-277 | C6TL15-277 | 078531016104 | Cord and Plug Kit (white), 6 ft Twist Lock Nema L7-15P, 15 amp, 277V | | ● | | | 0.8 | N/A | |



LHV - Linear High Bays



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|---------------------------------------|----------------|--------------|--|-------|-------|-------|-------|----------|-------------|-------|
| VersaBay Shielding Accessories | | | | | | | | | | |
| LHVS4-CA | LHVS4-CA | | LHV 4 lamp Shielding kit, includes frame and clear acrylic lens | | ● | | | | N/A | |
| LHV4SPJ | LHV4SPJ | 078531016142 | Side Panels and End Jaw (pair) for 4 lamp | | ● | | | 2.5 | N/A | |
| LHV4CA | LHV4CA | 078531016203 | Clear Acrylic Lens for 4 lamp | | ● | | | 2.5 | N/A | |
| LHVS4-WG | LHVS4-WG | | LHV 4 lamp Shielding kit, includes frame and flat wire guard | | ● | | | | N/A | |
| LHV4SPJ | LHV4SPJ | 078531016142 | Side Panels and End Jaw (pair) for 4 lamp | | ● | | | 2.5 | N/A | |
| LHV4FWG | LHV4FWG | 078531016173 | Flat Wire Guard for 4 lamp | | ● | | | 2.5 | N/A | |
| LHVS4-CAWG | LHVS4-CAWG | | 4 lamp Shielding kit, includes frame, clear acrylic lens and flat wire guard | | ● | | | | | |
| LHV4SPJ | LHV4SPJ | 078531016142 | Side Panels and End Jaw (pair) for 4 lamp | | ● | | | 2.5 | | |
| LHV4FWG | LHV4FWG | 078531016173 | Flat Wire Guard for 4 lamp | | ● | | | 2.5 | N/A | |
| LHVS6-CA | LHVS6-CA | | LHV 6 lamp Shielding kit, includes frame and clear acrylic lens | | ● | | | | | |
| LHV6SPJ | LHV6SPJ | 078531016159 | Side Panels and End Jaw (pair) for 6 lamp | | ● | | | 2.5 | N/A | |
| LHV6CA | LHV6CA | 078531016210 | Clear Acrylic Lens for 6 lamp | | ● | | | 2.5 | N/A | |
| LHVS6-WG | LHVS6-WG | | LHV 6 lamp Shielding kit, includes frame and flat wire guard | | ● | | | | | |
| LHV6SPJ | LHV6SPJ | 078531016159 | Side Panels and End Jaw (pair) for 6 lamp | | ● | | | 2.5 | N/A | |
| LHV6FWG | LHV6FWG | 078531016180 | Flat Wire Guard for 6 lamp | | ● | | | 2.5 | N/A | |
| LHVS6-CAWG | LHVS6-CAWG | | 6 lamp Shielding kit, includes frame, clear acrylic lens and flat wire guard | | ● | | | | N/A | |
| LHV6SPJ | LHV6SPJ | 078531016159 | Side Panels and End Jaw (pair) for 6 lamp | | ● | | | 2.5 | | |
| LHV6CA | LHV6CA | 078531016210 | Clear Acrylic Lens for 6 lamp | | ● | | | 2.5 | N/A | |
| LHV6FWG | LHV6FWG | 078531016180 | Flat Wire Guard for 6 lamp | | ● | | | 2.5 | N/A | |



LHV - Linear High Bays



5-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

| LHV | | 4 | | | | | | | | | |
|------------------------------------|--|--|--|--|--|---|--|--|--|---|--|
| SIZE | | NO. OF LAMPS | | REFLECTOR | | UPLIGHT | | VOLTAGE | | OPTIONS | |
| 4 4' | | 4 Four 6 Six | | M4R 95% Reflective Specular Aluminum (Narrow Beam) GW Gloss White (Wide Beam) | | ST Solid Top U Uplight | | U 120V-277V 347 347V 480 480V ² | | EL141 Emergency Battery Pack, T8, 1400 Lumens (120-277V) EL5H Emergency Battery Pack, T5, 1250 Lumens (120-277V) F3C5 3-Conductor Cord F4C5 4-Conductor Cord F3C10 3-Conductor Cord, 10' F4C10 4-Conductor Cord, 10' | |
| MODEL | | LAMP TYPE | | BALLAST | | | | LAMPS INSTALLED | | | |
| LHV VersaBay® Fluorescent High Bay | | 32 4'; T8 ¹ 54 4'; T5HO: 54 or 51 Watt | | LHV4-454 4EP (1) 4-Lamp Electronic T5HO, Programmed Start LHV4-654 24EP (1) 2-Lamp and (1) 4-Lamp Electronic T5HO, Programmed Start LHV4-432 4EHL (1) 4-Lamp Electronic T8, High Light Output, Instant Start (N/A 480V) LHV4-632 3EHL (2) 3-Lamp Electronic T8, High Light Output, Instant Start 3EPHL (2) 3-Lamp Electronic T8, High Light Output, Programmed Start ³ | | | | T8 F0841 4100K 82CRI 32W T8 F0850 5000K 82CRI 32W T8 T5HO F5841 4100K 85CRI F5850 5000K 85CRI | | | |

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.
² 480V option on T5HO units only.
³ N/A in 347V.



KL - Specification Grade Industrials


3S SCHEDULED STOCK SHIPMENTS Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-----------------|----------------|--------------|--|-------|-------|-------|-------|----------|-------------|-------|
| 72241819F910000 | KL4-232-U-EU | 078531006471 | 2-4' T8, 4', 120-277V T8 Elec Ballast, Apertured Reflector | • | • | • | • | 15.0 | 21 | |
| 820268450000000 | KLWG4 | 078531007478 | 4' Wire Guard for KL series | • | • | • | • | 3.2 | N/A | |
| 984084190000000 | KHC | 078531000875 | Two 24" chain assemblies for K and KL | • | • | • | • | 0.3 | N/A | |

QS 10 10-Day Quick Ship Ordering Guide Order Limit Per Fixture Selection: 50

| | | | | | | |
|---|--|--|---|--|----------|--|
| KL | | | | | U | |
| MODEL KL Premium Industrial | NO. OF LAMPS 2 Two 3 Three | REFLECTOR TYPE U Apertured Uplight Reflector ST Solid Top | VOLTAGE U 120V-277V 347 347V (T8 only) | OPTIONS EL Emergency Battery Pack EL5 Emergency Battery Pack, T5 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 | | |
| SIZE 4 4' 8 8' | LAMP TYPE 32 4', T8 ¹ 54 4', T5HO: 54 or 51 Watt 96T8 8', T8: 59 Watt (2-Lamp only) 96T8HO 8', T8: 86 Watt (2-Lamp only) | BALLAST E Electronic, Instant Start 3E 3-Lamp Electronic T8 (32W), Instant Start 4E 4-Lamp Electronic T8 (32W), Instant Start EP Electronic, Programmed Start, T5HO or T8 3EP 3-Lamp Electronic T5HO or T8, Programmed Start 4EP 4-Lamp Electronic T5HO or T8, Programmed Start | | | | |
| ACCESSORIES (ORDER SEPARATELY) KLEC Full Depth Endcap (pair) KZT Zip-Tee Hanger KLRU4 4' 5% Uplight Reflector Only KTH Slide Clamp Tong Hanger | | | | | | |
| Instant Start ballasts available for 32 and 96T8. Programmed Start ballasts available for all except 96T8. | | | | | | |

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



K - Heavy Duty Striplights

3S SCHEDULED STOCK SHIPMENTS Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-----------------|----------------|--------------|---|-------|-------|-------|-------|----------|-------------|-------|
| 80241009F910000 | K4-232-EU | 078531007034 | 2-4' T8, 4', 120-277V T8 Elec Ballast | | • | | • | 16.0 | 72 | |
| 93025871 | K8-296HO-EPU | 078531016913 | 2-8' T12HO, 8', 120-277V Ballast | • | • | • | • | 19.0 | 36 | |
| 93032673 | K8-296T8HO-EPU | 078531017699 | 2-8' T8HO, 8', 120-277V Elec.Prog Start Ballast | | • | | | 19.0 | 36 | |
| 984084190000000 | KHC | 078531000875 | Two 24" chain assemblies for K and KL | • | • | • | • | 0.3 | N/A | |



SS - Staggered Strips



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-------------|----------------|--------------|---------------------------------------|----------|----------|----------|----------|-------------|----------------|-------|
| FS000039 | SS4-132-EU | 078531044602 | 1-4' T8, 4', 120-277V T8 Elec Ballast | | | | ● | 9.0 | 72 | |
| FS000040 | SS4-232-EU | 078531044619 | 2-4' T8, 4', 120-277V T8 Elec Ballast | | | | ● | 9.0 | 72 | |



CS - Striplights



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-----------------|----------------|--------------|---|----------|----------|----------|----------|-------------|----------------|-------|
| 04122009F910000 | CS2-117-EU | 078531008079 | 1-2' T8, 2', 120-277V T8 Elec Ballast | | | ● | | 4.0 | 176 | |
| 04222009F910000 | CS2-217-EU | 078531004996 | 2-2' T8, 2', 120-277V T8 Elec Ballast | | ● | ● | ● | 4.0 | 176 | |
| 041220007910000 | CS2-220-L120 | 078531023164 | 2-2' T12, 2', 120V T12 LPF Ballast | | | ● | | 4.0 | 176 | |
| 04231009F910000 | CS3-225-EU | 078531005009 | 2-3' T8, 3', 120-277V T8 Elec Ballast | ● | ● | ● | ● | 7.0 | 88 | |
| 04141009F910000 | CS4-132-EU | 078531006280 | 1-4' T8, 4', 120-277V T8 Elec Ballast | ● | ● | ● | ● | 9.0 | 77 | |
| 04241009F910000 | CS4-232-EU | 078531005016 | 2-4' T8, 4', 120-277V T8 Elec Ballast | ● | ● | ● | ● | 9.0 | 77 | |
| 93022153 | CS4-232-EPU | 078531016609 | 2-4' T8, 4', 120-277V T8 Elec Prog Start Ballast | ● | ● | | | 9.0 | 77 | |
| 93038454 | CS4-254-EPU | 078531022969 | 2-4' T5, 4', 120-277V T5 Elec Ballast | | ● | ● | | 9.0 | 77 | |
| 0424100BL910000 | CS4-232-ELWU | 078531012458 | 2-4' T8, 4', 120-277V T8 Elec Low Wattage Ballast | | | ● | | 9.0 | 77 | |
| 03241009F910000 | CS8-132-EU | 078531009151 | 2-8' T8, 8', 120-277V T8 Elec Ballast | | ● | ● | | 17.0 | 77 | |
| 03441009H910000 | CS8-232-4EU | 078531005023 | 4-8' T8, 8', 120-277V 4-L T8 Elec Ballast | ● | ● | ● | ● | 17.0 | 77 | |
| 0344100BN910000 | CS8-232-4ELWU | 078531011949 | 4-8' T8, 8', 120-277V 4-L T8 Elec Low Wattage Ballast | | | ● | | 17.0 | 77 | |
| 04275009F910000 | CS8-296T8-EU | 078531005795 | 2-8' T8, 8', 120-277V T8 Elec Ballast | ● | ● | ● | ● | 17.0 | 77 | |
| 0427500AS910000 | CS8-296-EU120 | 078531008543 | 2-8' T12, 8', 120V Magnetic DOE Compliant Ballast | | ● | | | 17.0 | 77 | |
| 93038455 | CS8-254-4EPU | 078531022976 | 4-8' T5, 8', 120-277V 4-L T5 Elec Ballast | | ● | | | 17.0 | 77 | |
| 984084158000000 | CSHC | 078531000868 | Two 14" chain assemblies for CS and CSR | ● | ● | ● | ● | 0.2 | N/A | |
| 745013602000000 | CSR4 | 078531001575 | 4' symmetric reflector, white, solid top | ● | ● | ● | ● | 2.0 | N/A | |
| 745013603000000 | CSRU4 | 078531001582 | 4' symmetric reflector, white, uplight | | ● | | | 2.0 | N/A | |
| 982092925000000 | CSWG4 | 078531000882 | 4' Wire Guard for CS series | ● | ● | ● | ● | 1.0 | N/A | |
| 985084348700000 | CSZT | 078531740146 | Zip T-Hanger - 1/2" spacer | | ● | ● | ● | 0.2 | N/A | |



CS - Striplights

QS 10 10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

| CS | | | | | U | EL |
|-----------------------------------|----------------------|-------------------------------|--|--|-------------------------|--|
| MODEL | SIZE | NO. OF LAMPS IN CROSS SECTION | LAMP TYPE | BALLAST | VOLTAGE | OPTIONS |
| CS Straight-Sided Utility Channel | 2 2' 4 4' 8 8' | 1 One 2 Two | 17 2', T8: 17 Watt 32 4', T8 ¹ | E Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start EP Electronic T8, Programmed Start 4EP 4-Lamp Electronic T8, Programmed Start | U 120V-277V 347 347V | EL Emergency Battery Pack EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 |
| | | | | | | ACCESSORIES (ORDER SEPARATELY) |
| | | | | | | CSRA4 4' Asymmetric Reflector |
| | | | | | | CSRU4 4' Symmetric Reflector 5% Uplight |


¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



CH-1-L Striplights

3S SCHEDULED STOCK SHIPMENTS Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-----------------|----------------|--------------|--|-------|-------|-------|-------|----------|-------------|-------|
| 841120007000000 | CH1.5-115-L120 | 078531840228 | 1-1.5' T12, 1.5', 120V T12 LPF Ballast | | | ● | | 3.0 | 156 | |
| 84122009F910000 | CH2-117-EU | 078531005047 | 1-2' T8, 2', 120-277V T8 Elec Ballast | | ● | ● | ● | 3.0 | 156 | |
| 841220007000000 | CH2-120-L120 | 078531840235 | 1-2' T12, 2', 120V T12 LPF Ballast | | ● | ● | ● | 3.0 | 156 | |
| 84131009F910000 | CH3-125-EU | 078531005054 | 1-3' T8, 3', 120-277V T8 Elec Ballast | | | ● | | 7.0 | 156 | |
| 84141009F910000 | CH4-132-EU | 078531005061 | 1-4' T8, 4', 120-277V T8 Elec Ballast | ● | ● | ● | ● | 7.0 | 156 | |
| 841410003910000 | CH4-140-L120 | 078531840259 | 1-4' T12, 4', 120V T12 LPF Ballast | | | ● | | 5.0 | 156 | |
| 83241009F910000 | CH8-132-EU | 078531005078 | 2-4' T8, 8', 120-277V T8 Elec Ballast | | | ● | | 17.0 | 96 | |
| 845034020000000 | CHRA4 | 078531011970 | 4' Asymmetric Reflector (1-lmp only) | | | ● | | 1.9 | N/A | |
| 980929240000000 | CHWG4 | 078531002954 | Wire Guard, 4' for CH Strip | ● | ● | ● | | 10.0 | N/A | |



XEW - Enclosed/Gasketed High Bay



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-------------|---------------------|--------------|---|-------|-------|-------|-------|----------|-------------|-------|
| XEW00021 | XEW4-454-CA-W-4EPU | 078531123598 | 4-4' T5, 4', 120-277V 4-L T5 Elec Program Start Ballast, Wide, Clear Acrylic Lens | | ● | | | 25.0 | 21 | |
| XEW00019 | XEW4-454-CA-N-4EPU | 078531123581 | 4-4' T5, 4', 120-277V 4-L T5 Elec Program Start Ballast, Narrow, Clear Acrylic Lens | | ● | | | 25.0 | 21 | |
| XEW00022 | XEW4-654-CA-W-24EPU | 078531123604 | 6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Program Start Ballast, Wide, Clear Acrylic Lens | | ● | | | 25.0 | 21 | |
| XEW00023 | XEW4-632-CA-W-3EHLU | 078531123611 | 6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast, Wide, Clear Acrylic Lens | | ● | | | 25.0 | 21 | |
| XEWFSBSS | XEWFSBSS | 078531123659 | Flexible Surface Mount Bracket, Pair | | ● | | | 2.0 | | |



XEM - Low Profile Enclosed/Gasketed Industrials



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-------------|---------------------|--------------|--|-------|-------|-------|-------|----------|-------------|-------|
| 93049168 | XEM4-232-RA-EU | 078531023720 | Vapor Tight 2-4'T8, 4', 120-277V T8 Elec Ballast, Fiberglass Housing | ● | ● | ● | ● | 14.0 | 55 | |
| 93049169 | XEM8-232-RA-4EU | 078531023737 | Vapor Tight 4-4'T8, 8', 120-277V 4-L T8 Elec Ballast, Fiberglass Housing | ● | ● | ● | ● | 29.0 | 45 | |
| 93049170 | XEM8-296T8HO-RA-EPU | 078531023744 | Vapor Tight 2-8'T8HO, 8', 120-277V 4-L T8 Elec Program Start Ballast, Fiberglass Housing | | ● | ● | | 29.0 | 45 | |



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 50

| | | | | | | | |
|---|--------------|--------------------------------------|--|--|-----------------------------------|---|--|
| XEM | | 2 | | | | U | |
| MODEL | SIZE | NO. OF LAMPS IN CROSS SECTION | LAMP TYPE | BALLAST | VOLTAGE | OPTIONS | |
| XEM Low Profile Enclosed and Gasketed Fiberglass Industrial | 4 4' 8 8' | 2 Two | 32 4; T8 ¹ 48T8HO 4; T8HO: 44 Watt 96T8 8; T8: 59 Watt 96T8HO 8; T8HO: 86 Watt | E Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start EP Electronic, Programmed Start 4EP 4-Lamp Electronic, Programmed Start | U 120V-277V 347 347V (T8 only) | TP Tamper Proof Screws SSL Stainless Steel Latches | |
| | | | LENS TYPE | BALLAST FACTOR | | | |
| | | | RA Ribbed Acrylic (Standard) | Blank 0.88BF (Standard) | | | |

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.

Accessories



Regional Distribution Center Stock List

| Part Number | Catalog Number | UPC Code | Description | CA 03 | IL 06 | PA 10 | SC 07 | Wt. each | # on Pallet | Price |
|-----------------|----------------|--------------|---|----------|----------|----------|----------|-------------|----------------|-------|
| FK14 | FK14 | 078531000745 | 1 × 4 Flange Kit | • | • | • | • | 5.0 | N/A | |
| FK22 | FK22 | 078531000752 | 2 × 2 Flange Kit | • | • | • | • | 5.0 | N/A | |
| FK24 | FK24 | 078531038991 | 2 × 4 Flange Kit | • | • | • | • | 5.0 | N/A | |
| GLH5 | GLH5 | 078531012700 | 5' Adjustable Cable Kit | • | • | • | • | 0.3 | N/A | |
| GLH10 | GLH10 | 078531013127 | 10' Adjustable Cable Kit | • | • | | • | 0.4 | N/A | |
| 980000011000000 | S18 | 078531000790 | 18" Stem and Canopy | • | • | • | • | 8.0 | N/A | |
| 980000010000000 | SS18 | 078531003456 | 18" Stem only | • | • | • | • | 5.0 | N/A | |
| TBC10K | TBC | 078531017606 | Tall Ballast Cover, For Field Installed Battery Packs | | | • | | 8.0 | N/A | |