

Product Specifications

Project _____

Location _____

Type _____

10042

Manufactured by Kichler® Lighting



DESCRIPTION

Task Work Direct Wire Fluorescent -

Compact undercabinet lighting that employs energy efficient fluorescent lamping.

SPECIFICATIONS

MATERIALS:

Housing: Steel

Lens: PVC

FINISHES: Powder Coated White

DIMENSIONS:

Length: 21.50"

Width: 3.5"

Height: 1.00"

LIGHT SOURCE:

- 1 – 13W T5 Fluorescent
- 2700K Color Temperature
- 85 Color Rendering Index (CRI)
- 7500 hour expected life span

ELECTRICAL DATA:

Input Voltage: 120V AC

Power Consumed: 13 watts

Efficacy: 61.5 lumens/watt

FEATURES

- C-UL Listed for Cabinet Use – UL Standard No. 2108
- Compact Size
- T5 Fluorescent Lamp (Included)
- On/Off Switch
- Keyhole Mounting
- Built-in Transformer
- Snap-in Etched, Ribbed Diffuser
- Hinged Assembly
- Multiple KO's for Installation Ease
- Side KO's for Optional End-to-End Assembly
- Intended for Connection to Power Through NM/BX Cable Connector (Included)
- Cord and Plug Accessory Available

PHOTOMETRIC DATA

Countertop Foot-Candle Measurements Available Upon Request.

FOOT-CANDLE MEASUREMENT ON WORK SURFACE

A	LIGHT OUTPUT FC (COUNTER FRONT)	22
B	LIGHT OUTPUT FC (COUNTER MIDDLE)	43.4
C	LIGHT OUTPUT FC (COUNTER BACK)	63.7
D	LIGHT OUTPUT FC (COUNTER WALL)	20.3

