



Measurements:

<u>Height</u>	<u>Width</u>		
23.50"	26.00"		
<u>Hanging Weight</u>	<u>Canopy Width</u>	<u>Canopy Height</u>	<u>Canopy Length</u>
13.45 lb	5.00"	1.00"	5.00"

Lamping:

Incandescent MB Incandescent 5,750 Rated Lumens
 5.00 100W MB Incandescent Color Temperature
 500 total watt 2,500 Rated Life
 Dimmable : Standard

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
18.89 lb	24.02"	10.63"	25.20"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209058385	Yes	

Finish:

Oil Rubbed Bronze OI

Glass:

Frosted FT

Material:

Steel

Certification:

Dry Location
 Location

Additional:

MB Incandescent (Not Included)