



**Measurements:**

|                       |                     |                      |                      |
|-----------------------|---------------------|----------------------|----------------------|
| <u>Height</u>         | <u>Width</u>        |                      |                      |
| 30.00"                | 30.00"              |                      |                      |
| <u>Hanging Weight</u> | <u>Canopy Width</u> | <u>Canopy Height</u> | <u>Canopy Length</u> |
| 19.80 lb              | 5.00"               | 1.00"                | 5.00"                |

**Lamping:**

Incandescent MB Incandescent 0 Rated Lumens  
 9.00 60W MB Incandescent Color Temperature  
 540 total watt  
 Dimmable : Standard Dimmer

**Shipping:**

|                        |                     |                      |                      |
|------------------------|---------------------|----------------------|----------------------|
| <u>Carton Weight</u>   | <u>Carton Width</u> | <u>Carton Height</u> | <u>Carton Length</u> |
| 26.00 lb               | 26.00"              | 16.50"               | 29.00"               |
| <u>Master Pack Qty</u> | <u>UPC</u>          | <u>UPS</u>           |                      |
| 1.0000                 | 783209108400        | Yes                  |                      |

**Finish:**

Satin Nickel SN

**Glass:**

Frosted FT

**Material:**

Steel

**Certification:**

Dry Location

**Additional:**

MB Incandescent (Not Included)