



*Hoffman*

## HOL-SEALERS Hole Seals

Catalog Number: AS125  
US List Price (USD): \$14.21

### Bulletin Number:

- A80HS

### Material:

- Steel



### Model Code:

- 59740

### Ship Wt. Std. Pkg. (lbs):

- 1.4

### Interchangeable:

- False

### Finish Color:

- ANSI 61 gray

### Industry Standards:

**Steel Hole Seals** UL 508A Component Recognized; Type 3R, 4, 12, 13; File No. E61997 CSA File No. 42186; Type 3R, 4, 12, 13 NEMA/EEMAC Type 3R, 4, 12, 13 IEC 60529, IP66 **Stainless Steel Hole Seals** UL 508A Component Recognized; Type 3R, 4, 4X, 12, 13; File No. E61997 CSA File No. 42186; Type 3R, 4, 4X, 12, 13 NEMA/EEMAC Type 3R, 4, 4X, 12, 13 IEC 60529, IP66

## Description

### Applications:

Seal extra pushbutton holes, conduit openings and knockout openings against dust, dirt, oil and water with Hoffman HOLSEALERS™. Seals will cover any size or shape of hole from .19-in. diameter to maximum diameter shown in table. Can be used on enclosure walls up to .31-in. (8-mm) thick.

### Features:

- Available in multiple colors and sizes
- Oil-resistant gasket provided

### Specifications:

- Steel Models:
  - 16 gauge galvanized steel backplate
  - Plated stud (10-32x5/8) and wing nut
- Stainless Steel Models:
  - 16 gauge stainless steel backplate
  - Seal, backplate, stud (10-24x5/8) and wing nut are 300 series stainless steel

### Finish:

- Steel seals have polyester powder paint finish over galvanized front surface.
- Stainless steel seals have polished front surface.

## Technical Data

---

### HOL-SEALERS Hole Seals

<b>Catalog Number</b>	<a href="#">AS125</a>
<b>For</b>	1 1/4-in. conduit holes
<b>Maximum Hole Diameter in.</b>	1.69
<b>Hol-Sealer Diameter in.</b>	2.19

## Certifications

---



EU Certification

## Documents

---



2D DXF CAD



3D STEP CAD



Spec Sheet

No accessories available.