



Item #: F802-ORB	UPC Code: 706411040207
Product Family Name: Vintage Gyro™	Finish: Oil Rubbed Bronze
Category: Interior Fan	Category Type: Ceiling Fan
Certification E75795	
Patents U.S. Patent(s): 6,832,902; 7,183,680; 7,229,255	
Notes:	

Image File Name:
F802-ORB_0.jpg



MEASUREMENTS

Blade Finish:	Reversible Blades:		
	No		
Blade Material:	Slope:		
ABSplastic, 14" tip to tip	Yes		
Blade Sweep:	No. of Blades:	Blade Pitch:	Hanging Weight:
42	6	20 degrees	34.08
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:
3.5	.75	6	.75
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:
14.25	15.50	80	82X25MM

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	720		980		1350
Amps:	0.70		0.80		0.84
Watts:	48.000		67.000		102.000
CFM:	2900.00		3400.00		5050.00
CFM/Watts	60.42		50.75		49.51



FAN CONTROLS

Pull Chain Control: No	Works with Remote Control: Yes	Works with Wall Control: Yes
	Included Remote Control:	Included Wall Control: WCS212
	Compatible Remote Control[s]: RCS212	Compatible Wall Control[s]:

LAMPING

No. of Bulbs: 1	Light Type: T4(E11) Mini Cand Halogen Frosted			
Max Bulb Wattage: 100	Socket: E11 Mini Cand			
Light Kit: Yes	Dimmable: Yes	Ballast:	Rated Life Hours:	Uplight
Lamp Included: Yes	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

GLASS

Description:	Material: Glass
Part No.: GF802-1	Quantity: 1
Width:	Height:
	Length:



SHIPPING

Carton Width: 18.000	Carton Height: 14.000	Carton Length: 44.380
Carton Weight: 42.240	Carton Cubit Feet: 6.472	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		Master Pack: 1



Title 17

Yes



UL Listed

Yes